Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360681

Luminaire Tested: **GSS-SB5C-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360681
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5C-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 252W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	37781.3 lumens
Efficiency:	N/A
Efficacy:	149.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B5 - U0 - G5


Input Watts (W):	252
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	7.9%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 18.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	18890.7	0.0	18890.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	18890.7	0.0	18890.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	37781.3	0.0	37781.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	720.5	1.9
10°-20°	2196.0	5.8
20°-30°	3670.4	9.7
30°-40°	5061.7	13.4
40°-50°	6205.0	16.4
50°-60°	7271.4	19.2
60°-70°	8074.8	21.4
70°-80°	4391.1	11.6
80°-90°	190.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	37781.3	100.0
0°-180°	37781.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3293.5	8.7			
FM	(30°-60°)	9269.1	24.5			
FH	(60°-80°)	6233.0	16.5			G3/7500
FVH	(80°-90°)	95.1	0.3			G1/100
BL	(0°-30°)	3293.5	8.7	B4/5000		
BM	(30°-60°)	9269.1	24.5	B5		
BH	(60°-80°)	6233.0	16.5	B5		G5
BVH	(80°-90°)	95.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9	7443.9
2.5°	7452.1	7452.1	7427.3	7460.4	7443.9	7452.1	7460.4	7452.1	7443.9	7452.1	7460.4
5°	7493.5	7476.9	7493.5	7510.0	7485.2	7501.7	7493.5	7452.1	7476.9	7476.9	7476.9
7.5°	7567.9	7584.5	7567.9	7609.3	7584.5	7634.1	7584.5	7551.4	7543.1	7534.8	7534.8
10°	7601.0	7601.0	7592.7	7667.2	7683.7	7733.3	7700.3	7650.6	7625.8	7592.7	7559.6
12.5°	7510.0	7526.6	7567.9	7708.5	7774.7	7873.9	7849.1	7749.9	7675.4	7650.6	7601.0
15°	7410.8	7427.3	7510.0	7683.7	7840.9	7989.7	7981.5	7857.4	7766.4	7700.3	7625.8
17.5°	7253.6	7278.4	7394.2	7658.9	7940.1	8105.5	8155.2	8031.1	7931.8	7824.3	7725.1
20°	6989.0	6989.0	7195.7	7534.8	7923.6	8295.8	8428.1	8328.8	8213.1	8039.4	7907.0
22.5°	6691.2	6707.7	6914.5	7361.1	7915.3	8461.2	8717.6	8610.1	8494.3	8304.0	8105.5
25°	6393.4	6393.4	6625.0	7129.6	7807.8	8577.0	9056.7	8998.8	8767.2	8593.5	8337.1
27.5°	6120.5	6120.5	6368.6	6898.0	7625.8	8610.1	9395.8	9395.8	9139.4	8883.0	8601.8
30°	5797.9	5880.6	6161.9	6716.0	7460.4	8552.2	9643.9	9801.1	9569.5	9238.6	8825.1
32.5°	5525.0	5582.9	5872.4	6459.6	7220.5	8486.0	9925.1	10313.9	10074.0	9619.1	9155.9
35°	5202.4	5194.2	5525.0	6104.0	6881.4	8337.1	10148.5	10925.9	10694.3	10206.3	9577.8
37.5°	4780.6	4780.6	5119.7	5682.1	6558.9	8080.7	10330.4	11604.1	11430.4	10876.3	10206.3
40°	4325.7	4375.3	4673.1	5243.8	6170.1	7774.7	10330.4	12158.3	12249.3	11678.6	10983.8
42.5°	3994.9	4011.4	4284.4	4822.0	5740.0	7377.7	10198.1	12638.0	12910.9	12431.2	11529.7
45°	3647.5	3688.8	3920.4	4416.7	5293.4	6906.2	9966.5	13175.6	13614.0	13283.1	12100.4
47.5°	3225.7	3267.0	3531.7	4036.2	4871.6	6393.4	9577.8	13738.0	14656.1	14416.3	13117.7
50°	2737.7	2770.8	3018.9	3556.5	4400.1	5806.2	9089.8	14159.9	15698.3	15938.1	14656.1
52.5°	2142.2	2167.0	2431.7	2952.7	3837.7	5243.8	8403.3	14416.3	16748.7	17592.3	16715.6
55°	1538.4	1579.8	1811.3	2241.4	3093.3	4491.1	7584.5	14548.6	17898.3	19552.5	19271.3
57.5°	1108.3	1124.8	1282.0	1612.8	2299.3	3606.1	6534.0	14325.3	18932.2	21893.2	22480.4
60°	918.1	918.1	942.9	1100.0	1571.5	2547.5	5276.9	13498.2	19817.2	24258.7	26070.0
62.5°	843.6	843.6	860.2	885.0	1033.9	1654.2	3771.6	11819.2	19916.4	26533.2	30007.0
65°	769.2	769.2	785.7	802.3	835.4	1075.2	2274.5	8651.4	17972.8	26558.0	32124.4
67.5°	703.0	703.0	711.3	719.6	736.1	785.7	1248.9	5243.8	14383.2	25855.0	32934.9
70°	636.9	636.9	636.9	628.6	653.4	661.7	827.1	2663.2	9619.1	23348.9	32546.2
72.5°	*562.4*	*562.4*	*554.2*	*537.6*	*545.9*	*545.9*	*612.1*	*1306.8*	*4995.7*	*18560.0*	*29386.7*
75°	479.7	488.0	454.9	438.4	430.1	438.4	488.0	744.4	2233.2	11256.8	21959.4
77.5°	405.3	421.8	372.2	339.1	330.8	330.8	380.5	463.2	959.4	4085.8	9842.4
80°	306.0	314.3	272.9	239.9	239.9	231.6	281.2	339.1	454.9	1215.8	2208.3
82.5°	173.7	173.7	157.1	140.6	132.3	140.6	190.2	231.6	281.2	430.1	603.8
85°	41.4	41.4	49.6	57.9	57.9	74.4	107.5	124.1	148.9	173.7	231.6
87.5°	8.3	8.3	8.3	16.5	24.8	24.8	41.4	57.9	74.4	91.0	99.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360681
CATALOG NUMBER: GSS-SB5C-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	7443.9	7443.9	*7443.9*
2.5°	7460.4	7468.7	*7460.4*
5°	7510.0	7493.5	*7468.7*
7.5°	7518.3	7526.6	*7534.8*
10°	7551.4	7584.5	*7534.8*
12.5°	7584.5	7559.6	*7543.1*
15°	7609.3	7601.0	*7551.4*
17.5°	7700.3	7667.2	*7658.9*
20°	7840.9	7832.6	*7807.8*
22.5°	8006.3	7989.7	*7981.5*
25°	8246.1	8188.2	*8155.2*
27.5°	8444.6	8395.0	*8378.5*
30°	8643.1	8543.9	*8543.9*
32.5°	8816.8	8792.0	*8775.5*
35°	9230.4	9106.3	*9122.9*
37.5°	9734.9	9610.8	*9503.3*
40°	10446.2	10280.8	*10214.6*
42.5°	10901.1	10735.7	*10752.2*
45°	11157.5	10868.0	*10793.6*
47.5°	11852.3	11488.3	*11389.1*
50°	12977.1	12530.5	*12406.4*
52.5°	14796.7	14077.2	*13911.7*
55°	17079.5	16194.5	*16029.1*
57.5°	20205.9	19031.5	*18675.8*
60°	24010.6	22554.9	*22017.3*
62.5°	28584.4	26789.6	*26276.8*
65°	32025.1	30528.1	*29734.1*
67.5°	34779.3	33547.0	*33166.5*
70°	36417.0	36474.9	*36574.1*
72.5°	*34522.9*	*36111.0*	*36871.9*
75°	25300.8	26533.2	*27715.9*
77.5°	9776.3	8816.8	*8535.6*
80°	1579.8	1480.5	*1530.1*
82.5°	711.3	752.7	*794.0*
85°	463.2	537.6	*570.7*
87.5°	107.5	107.5	*107.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)