Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360300

Luminaire Tested: **GSS-SB6B-740-U-T3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360300
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-740-U-T3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 4000K FIXTURE w/ TYPE III DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	25272.8 lumens
Efficiency:	N/A
Efficacy:	115.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.5 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3021.8	0.0	3021.8
	% Fixture	12.0	0.0	12.0
Street Side	Lumens	22251.0	0.0	22251.0
	% Fixture	88.0	0.0	88.0
Total	Lumens	25272.8	0.0	25272.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.7	1.3
10°-20°	842.5	3.3
20°-30°	1501.8	5.9
30°-40°	2687.9	10.6
40°-50°	4234.0	16.8
50°-60°	6158.2	24.4
60°-70°	6700.3	26.5
70°-80°	2706.7	10.7
80°-90°	113.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25272.8	100.0
0°-180°	25272.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1782.1	7.1			
FM	(30°-60°)	11408.8	45.1			
FH	(60°-80°)	8967.8	35.5			G4/12000
FVH	(80°-90°)	92.3	0.4			G1/100
BL	(0°-30°)	889.9	3.5	B2/1000		
BM	(30°-60°)	1671.3	6.6	B2/2500		
BH	(60°-80°)	439.3	1.7	B1/500		G1/500
BVH	(80°-90°)	21.4	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	51°	55°	65°	75°	85°
0°	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	*3588.7*	3588.7	3588.7	3588.7	3588.7
2.5°	3619.0	3611.4	3619.0	3588.7	3603.8	3611.4	*3626.6*	3603.8	3596.3	3603.8	3596.3
5°	3603.8	3596.3	3603.8	3611.4	3626.6	3649.3	*3641.7*	3641.7	3656.8	3626.6	3626.6
7.5°	3475.1	3467.6	3513.0	3528.1	3588.7	3641.7	*3702.3*	3679.5	3709.8	3702.3	3679.5
10°	3316.1	3293.4	3338.9	3422.1	3513.0	3649.3	*3709.8*	3725.0	3793.1	3823.4	3808.3
12.5°	3225.3	3202.6	3263.1	3323.7	3467.6	3634.1	*3740.1*	3778.0	3853.7	3914.3	3929.4
15°	3157.1	3179.9	3240.4	3354.0	3490.3	3664.4	*3755.3*	3831.0	3990.0	4050.5	4050.5
17.5°	3202.6	3195.0	3248.0	3361.6	3528.1	3702.3	*3838.5*	3914.3	4103.5	4186.8	4179.2
20°	3649.3	3603.8	3596.3	3535.7	3588.7	3793.1	*3959.7*	4035.4	4217.1	4330.7	4323.1
22.5°	4224.7	4270.1	4149.0	4012.7	3846.1	3914.3	*4088.4*	4194.4	4376.1	4497.2	4451.8
25°	5004.5	4981.8	4898.5	4625.9	4323.1	4179.2	*4270.1*	4376.1	4603.2	4701.6	4625.9
27.5°	5829.7	5731.3	5625.3	5246.8	4845.5	4580.5	*4595.7*	4663.8	4928.8	4989.3	4815.2
30°	6715.6	6730.7	6556.6	6041.7	5489.0	5087.8	*5057.5*	5087.8	5299.8	5292.2	5049.9
32.5°	7730.1	7692.2	7525.7	6973.0	6359.7	5701.0	*5625.3*	5572.3	5663.2	5579.9	5299.8
35°	8441.8	8479.6	8297.9	7934.5	7321.2	6503.6	*6321.9*	6193.2	6102.3	6011.4	5708.6
37.5°	9077.7	9032.3	8926.3	8721.9	8123.8	7374.2	*7026.0*	6912.4	6715.6	6465.7	6185.6
40°	9221.6	9198.9	9145.9	9153.4	8767.3	8184.3	*7934.5*	7730.1	7389.4	7185.0	6821.6
42.5°	9198.9	9274.6	9289.7	9350.3	9130.7	8986.9	*8729.5*	8532.6	8214.6	7964.8	7586.2
45°	9320.0	9448.7	9554.7	9607.7	9463.9	9448.7	*9479.0*	9388.2	9168.6	8911.2	8479.6
47.5°	9562.3	9781.8	9948.4	10062.0	10031.7	10281.5	*10122.5*	10099.8	10190.7	9940.8	9509.3
50°	10016.6	10077.1	10470.8	10637.4	10917.5	11280.9	*10970.5*	11046.2	11227.9	11250.6	10455.7
52.5°	10357.3	10410.2	10803.9	11296.1	11916.9	12318.2	*12038.0*	12030.5	12356.0	12446.9	11371.8
55°	10448.1	10569.2	11076.5	11932.0	13098.0	13506.8	*13310.0*	13241.8	13673.4	13832.4	12181.9
57.5°	10319.4	10364.8	11091.6	12325.7	13953.5	14839.3	*14899.9*	14687.9	15081.6	15119.5	12780.0
60°	8926.3	9123.2	10395.1	12575.6	14680.3	16285.4	*16603.4*	16482.3	16512.5	16444.4	13226.7
62.5°	6170.4	6208.3	8078.4	12310.6	15278.5	17746.6	*18276.6*	18185.8	17928.3	17284.8	12999.6
65°	2937.6	3142.0	4338.2	10417.8	15361.7	18859.6	*19889.3*	19949.8	18753.6	17292.4	12121.3
67.5°	*2021.5*	*2029.1*	*2309.2*	*7351.5*	*13029.8*	*19177.6*	*20752.4*	*20472.2*	*18677.9*	*17133.4*	*11046.2*
70°	1279.5	1188.7	1332.5	4194.4	8805.2	15058.9	*18511.3*	19495.6	18359.9	16096.1	9335.2
72.5°	507.3	545.1	628.4	1377.9	4315.5	8578.0	*12091.0*	14839.3	16558.0	13923.2	7291.0
75°	227.1	242.3	318.0	575.4	1113.0	3497.8	*4678.9*	6556.6	13249.4	10993.2	5163.5
77.5°	151.4	159.0	204.4	333.1	507.3	976.7	*1711.1*	2006.3	7942.1	6011.4	2422.7
80°	90.9	98.4	136.3	204.4	280.1	348.3	*522.4*	605.7	2097.2	1991.2	666.3
82.5°	60.6	53.0	90.9	113.6	166.6	143.9	*166.6*	196.8	575.4	507.3	181.7
85°	22.7	22.7	37.9	45.4	60.6	75.7	*68.1*	83.3	136.3	136.3	83.3
87.5°	0.0	0.0	7.6	7.6	22.7	30.3	*37.9*	37.9	53.0	53.0	45.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360300
CATALOG NUMBER: GSS-SB6B-740-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7	3588.7
2.5°	3603.8	3581.1	3588.7	3573.6	3581.1	3566.0	3535.7	3566.0	3543.3	3543.3	3566.0
5°	3626.6	3619.0	3596.3	3558.4	3535.7	3482.7	3399.4	3361.6	3323.7	3301.0	3316.1
7.5°	3702.3	3672.0	3634.1	3543.3	3422.1	3263.1	3096.6	2907.3	2763.4	2748.3	2695.3
10°	3800.7	3770.4	3687.1	3482.7	3232.9	2778.6	2415.2	2165.3	2013.9	1915.5	1877.6
12.5°	3929.4	3891.5	3740.1	3391.8	2778.6	2142.6	1711.1	1529.4	1476.4	1453.6	1446.1
15°	4050.5	4005.1	3740.1	3096.6	2248.6	1612.6	1393.1	1347.7	1340.1	1347.7	1340.1
17.5°	4164.1	4103.5	3702.3	2695.3	1726.2	1362.8	1309.8	1287.1	1279.5	1271.9	1271.9
20°	4300.4	4202.0	3596.3	2256.2	1423.4	1294.7	1271.9	1241.7	1241.7	1211.4	1218.9
22.5°	4429.1	4292.8	3391.8	1817.1	1309.8	1256.8	1234.1	1203.8	1188.7	1165.9	1165.9
25°	4557.8	4383.7	3149.6	1506.6	1241.7	1218.9	1196.2	1165.9	1128.1	1097.8	1097.8
27.5°	4747.1	4504.8	2861.9	1377.9	1203.8	1165.9	1143.2	1105.4	1060.0	1022.1	1022.1
30°	4959.1	4671.4	2627.2	1355.2	1188.7	1097.8	1060.0	999.4	969.1	938.8	938.8
32.5°	5216.5	4898.5	2453.0	1393.1	1150.8	1007.0	946.4	885.8	863.1	863.1	863.1
35°	5595.0	5231.6	2263.8	1400.7	1105.4	916.1	817.7	757.1	757.1	787.4	787.4
37.5°	6102.3	5595.0	2165.3	1385.5	1067.5	825.2	711.7	666.3	658.7	689.0	689.0
40°	6685.3	5996.3	2203.2	1332.5	1014.5	734.4	628.4	590.5	583.0	590.5	598.1
42.5°	7321.2	6427.9	2294.0	1256.8	923.7	658.7	567.8	545.1	537.5	537.5	537.5
45°	7995.1	6723.1	2384.9	1181.1	832.8	598.1	530.0	514.8	507.3	507.3	507.3
47.5°	8638.6	6957.8	2324.3	1113.0	757.1	560.3	499.7	499.7	492.1	492.1	492.1
50°	9191.3	6935.1	2066.9	1044.8	673.8	530.0	484.5	477.0	477.0	469.4	469.4
52.5°	9501.7	6473.3	1665.6	969.1	598.1	499.7	469.4	461.8	454.3	446.7	446.7
55°	9622.9	5860.0	1294.7	855.5	545.1	477.0	454.3	446.7	431.6	424.0	416.4
57.5°	9410.9	4959.1	999.4	681.4	499.7	446.7	431.6	424.0	408.8	386.1	378.6
60°	8979.3	3974.8	749.5	522.4	446.7	408.8	408.8	401.3	371.0	333.1	325.6
62.5°	8222.2	2854.3	567.8	424.0	386.1	371.0	386.1	371.0	325.6	272.6	265.0
65°	7154.7	1764.1	439.1	363.4	340.7	325.6	348.3	333.1	280.1	219.6	204.4
67.5°	*5981.2*	*901.0*	*340.7*	*310.4*	*287.7*	*272.6*	*295.3*	*295.3*	*242.3*	*181.7*	*174.1*
70°	4618.4	499.7	272.6	257.4	234.7	212.0	249.8	257.4	212.0	159.0	151.4
72.5°	3429.7	318.0	219.6	212.0	181.7	151.4	204.4	219.6	181.7	121.1	113.6
75°	2241.0	249.8	166.6	166.6	128.7	121.1	174.1	189.3	159.0	90.9	90.9
77.5°	1075.1	189.3	128.7	113.6	90.9	90.9	151.4	159.0	113.6	68.1	68.1
80°	355.8	128.7	90.9	75.7	60.6	60.6	121.1	90.9	60.6	53.0	53.0
82.5°	121.1	83.3	60.6	53.0	45.4	37.9	37.9	45.4	45.4	37.9	37.9
85°	60.6	53.0	45.4	37.9	30.3	30.3	30.3	30.3	37.9	37.9	37.9
87.5°	37.9	37.9	30.3	22.7	22.7	22.7	22.7	22.7	30.3	15.1	15.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)