Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363373

Luminaire Tested: **GSS-SB6C-740-U-SL3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363373
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-740-U-SL3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 4000K FIXTURE w/ TYPE III SPILL CONTROL DISTRIBUTION OPTIC
Light Source:	(156) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	42804.8 lumens
Efficiency:	N/A
Efficacy:	142.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B3 - U0 - G5


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 22.7 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8355.4	0.0	8355.4
	% Fixture	19.5	0.0	19.5
Street Side	Lumens	34449.4	0.0	34449.4
	% Fixture	80.5	0.0	80.5
Total	Lumens	42804.8	0.0	42804.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.4	2.0
10°-20°	2049.9	4.8
20°-30°	3064.8	7.2
30°-40°	4369.0	10.2
40°-50°	6282.2	14.7
50°-60°	8411.5	19.7
60°-70°	9877.4	23.1
70°-80°	7045.1	16.5
80°-90°	869.5	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	42804.8	100.0
0°-180°	42804.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3579.0	8.4			
FM	(30°-60°)	15254.6	35.6			
FH	(60°-80°)	14893.2	34.8			G5
FVH	(80°-90°)	722.6	1.7			G4/750
BL	(0°-30°)	2371.2	5.5	B3/2500		
BM	(30°-60°)	3808.0	8.9	B3/5000		
BH	(60°-80°)	2029.3	4.7	B3/2500		G3/2500
BVH	(80°-90°)	146.9	0.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2
2.5°	9366.9	9377.5	9334.9	9303.0	9303.0	9249.7	9249.7	9249.7	9196.4	9185.7	9111.1
5°	9473.5	9462.8	9441.5	9452.1	9462.8	9441.5	9452.1	9420.2	9345.6	9324.3	9207.0
7.5°	9175.1	9175.1	9228.4	9334.9	9484.1	9558.7	9601.3	9580.0	9548.0	9484.1	9313.6
10°	8098.8	8173.4	8333.2	8684.9	9121.8	9484.1	9718.5	9707.9	9718.5	9633.3	9441.5
12.5°	7150.4	7182.3	7331.5	7640.6	8269.3	9047.2	9697.2	9825.1	9857.1	9803.8	9569.4
15°	6638.9	6628.2	6745.4	6990.5	7470.1	8322.6	9462.8	9814.5	10006.3	9995.6	9750.5
17.5°	6415.1	6425.8	6489.7	6649.5	7001.2	7704.5	9047.2	9686.6	10080.9	10208.7	9921.0
20°	6521.7	6489.7	6521.7	6553.6	6745.4	7299.6	8599.6	9462.8	10144.8	10411.2	10112.8
22.5°	6745.4	6713.5	6702.8	6681.5	6724.1	7065.1	8194.7	9185.7	10198.1	10677.6	10336.6
25°	7139.7	7107.8	7011.8	6894.6	6841.3	6990.5	7928.3	8951.3	10251.4	11050.6	10624.3
27.5°	7704.5	7661.9	7523.3	7246.3	7075.8	7097.1	7843.0	8823.4	10347.3	11412.9	10901.4
30°	8546.4	8525.0	8216.0	7768.4	7416.8	7288.9	7885.7	8791.4	10453.8	11828.5	11178.5
32.5°	9303.0	9281.6	9047.2	8546.4	7960.3	7597.9	7992.2	8834.1	10592.4	12361.3	11583.4
35°	9921.0	9878.4	9686.6	9303.0	8706.2	8066.8	8226.7	8983.3	10890.7	13064.6	12073.6
37.5°	10549.7	10517.8	10251.4	9846.4	9473.5	8716.9	8620.9	9324.3	11295.7	14023.7	12787.6
40°	11306.3	11263.7	10944.0	10464.5	10134.1	9601.3	9185.7	9867.7	11913.7	15121.3	13597.4
42.5°	12031.0	11988.3	11615.4	11199.8	10784.2	10453.8	9985.0	10592.4	12681.0	16517.3	14556.5
45°	12872.8	12872.8	12350.7	11892.4	11455.5	11050.6	10741.6	11423.6	13576.1	18094.4	15622.1
47.5°	13661.4	13586.8	13075.3	12574.4	12148.2	11380.9	11466.2	12297.4	14577.8	19692.8	16773.0
50°	13917.1	13895.8	13554.8	13107.3	12744.9	11785.9	12212.1	13341.7	15707.4	21216.7	17860.0
52.5°	14215.5	14119.6	13629.4	13565.5	13149.9	12297.4	13128.6	14418.0	16741.1	22602.0	18733.8
55°	14588.5	14481.9	13810.6	13682.7	13458.9	12872.8	14172.9	15526.2	17721.4	23678.3	19554.3
57.5°	15270.5	15142.6	14194.2	13917.1	13736.0	13597.4	15355.7	16751.7	18712.5	24520.2	20257.6
60°	15664.8	15558.2	14748.3	14545.9	14279.4	14599.1	16623.8	17881.3	19650.2	25170.2	20801.1
62.5°	15462.3	15387.7	14822.9	15206.5	15419.7	15920.5	18073.1	19053.5	20396.2	25660.4	20822.4
65°	14418.0	14268.8	13885.2	15046.7	16730.4	18147.7	19916.6	20428.1	20886.4	24339.0	19565.0
67.5°	11913.7	11764.6	11988.3	13181.8	15984.5	21579.0	22452.8	20982.3	20001.9	23134.8	19383.8
70°	5413.4	5168.3	6521.7	9324.3	13224.5	20833.1	25980.1	23284.0	20897.0	23028.3	19021.5
72.5°	2653.4	2760.0	3186.2	4187.9	8088.1	15995.1	28644.1	28793.3	23934.1	23305.3	19277.3
74°	2078.0	2109.9	2461.6	2877.2	4518.3	13352.3	27216.2	30061.4	26523.5	23966.0	18883.0
75°	1790.3	1832.9	2184.5	2397.7	2909.2	11242.4	25404.6	29677.8	27706.4	23838.1	18009.2
77.5°	1310.7	1300.1	1555.8	1907.5	1364.0	5008.5	20577.3	22996.3	23625.0	19415.8	12009.7
80°	809.9	841.8	1076.3	1332.0	905.8	1907.5	12094.9	12563.8	11178.5	11242.4	5829.0
82.5°	490.2	511.5	575.4	692.7	500.8	671.3	5477.3	6830.7	5658.5	3676.4	980.4
85°	149.2	159.8	191.8	245.1	181.2	245.1	1843.5	1662.4	1182.8	490.2	287.7
87.5°	10.7	10.7	21.3	21.3	32.0	53.3	74.6	85.3	95.9	106.6	106.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363373
CATALOG NUMBER: GSS-SB6C-740-U-SL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2	9079.2
2.5°	9111.1	9079.2	9036.5	8962.0	8908.7	8855.4	8791.4	8695.5	8663.6	8674.2	8695.5
5°	9185.7	9100.5	8972.6	8802.1	8674.2	8567.7	8397.2	8258.6	8173.4	8173.4	8130.8
7.5°	9260.3	9143.1	8940.6	8652.9	8429.1	8130.8	7811.1	7491.4	7267.6	7171.7	7086.4
10°	9388.2	9207.0	8876.7	8493.1	8013.5	7416.8	6766.8	6106.1	5690.5	5477.3	5466.7
12.5°	9473.5	9292.3	8844.7	8226.7	7320.9	6191.3	5200.3	4656.8	4486.3	4411.7	4390.4
15°	9612.0	9366.9	8770.1	7736.5	6255.2	4901.9	4358.4	4198.6	4187.9	4198.6	4209.2
17.5°	9729.2	9430.8	8578.3	6958.6	5019.1	4262.5	4124.0	4113.3	4187.9	4219.9	4251.9
20°	9857.1	9484.1	8237.3	5871.6	4326.5	4070.7	4049.4	4113.3	4219.9	4305.1	4315.8
22.5°	10038.2	9526.7	7640.6	4795.3	3996.1	3964.1	4017.4	4081.4	4145.3	4219.9	4241.2
25°	10230.1	9526.7	6820.0	4060.1	3825.6	3910.9	3964.1	3910.9	3889.6	3953.5	3953.5
27.5°	10379.2	9452.1	5658.5	3665.8	3708.4	3846.9	3815.0	3697.7	3676.4	3719.0	3708.4
30°	10485.8	9175.1	4486.3	3452.6	3591.2	3708.4	3623.1	3559.2	3516.6	3527.2	3537.9
32.5°	10645.6	8748.8	3676.4	3303.5	3495.3	3484.6	3474.0	3410.0	3356.7	3367.4	3378.0
35°	10837.5	8045.5	3218.2	3196.9	3410.0	3324.8	3335.4	3260.8	3196.9	3196.9	3207.5
37.5°	11082.6	7203.7	3026.4	3154.3	3271.5	3260.8	3228.9	3133.0	3037.0	3015.7	3015.7
40°	11349.0	6170.0	2930.5	3133.0	3207.5	3239.5	3175.6	3058.4	2802.6	2642.8	2632.1
42.5°	11519.5	5317.5	2898.5	3101.0	3196.9	3228.9	3143.6	2781.3	2536.2	2429.6	2419.0
45°	11764.6	4848.6	2898.5	3015.7	3154.3	3186.2	2887.9	2642.8	2504.2	2450.9	2461.6
47.5°	12009.7	4848.6	2898.5	2951.8	3037.0	3079.7	2685.4	2578.8	2450.9	2450.9	2493.6
50°	12350.7	5115.0	2877.2	2855.9	2887.9	2728.0	2557.5	2472.3	2301.8	2237.8	2248.5
52.5°	12862.2	5520.0	2792.0	2717.4	2728.0	2525.5	2472.3	2344.4	2173.9	2046.0	2014.0
55°	13416.3	5956.9	2621.5	2557.5	2546.9	2397.7	2376.4	2237.8	2078.0	1907.5	1875.5
57.5°	14023.7	6308.5	2408.3	2397.7	2365.7	2269.8	2301.8	2205.9	1982.1	1758.3	1726.3
60°	14599.1	6702.8	2205.9	2227.2	2173.9	2152.6	2195.2	2131.3	1854.2	1609.1	1587.8
62.5°	14599.1	6692.2	2024.7	2046.0	2035.4	1982.1	2056.7	2014.0	1683.7	1481.2	1459.9
65°	13799.9	6393.8	1811.6	1864.9	1907.5	1800.9	1896.8	1822.2	1534.5	1374.7	1342.7
67.5°	13693.3	6276.6	1598.4	1651.7	1726.3	1609.1	1673.0	1598.4	1396.0	1257.4	1236.1
70°	13480.2	6010.2	1406.6	1470.6	1502.5	1374.7	1459.9	1406.6	1257.4	1150.9	1129.6
72.5°	13586.8	5775.7	1204.2	1278.8	1289.4	1172.2	1257.4	1236.1	1108.3	1033.7	991.0
74°	*12990.0*	*4997.8*	*1086.9*	*1150.9*	*1129.6*	*1044.3*	*1118.9*	*1118.9*	*1001.7*	*948.4*	*895.1*
75°	12201.5	4433.0	1001.7	1065.6	1012.3	959.1	1033.7	1044.3	927.1	927.1	841.8
77.5°	8013.5	2973.1	788.6	831.2	809.9	777.9	820.5	809.9	724.6	703.3	650.0
80°	3921.5	1630.4	596.8	575.4	586.1	575.4	607.4	596.8	554.1	532.8	522.2
82.5°	735.3	543.5	394.3	383.6	362.3	341.0	383.6	383.6	511.5	575.4	575.4
85°	223.8	213.1	191.8	191.8	181.2	159.8	170.5	245.1	298.4	202.5	191.8
87.5°	95.9	95.9	85.3	74.6	53.3	53.3	42.6	42.6	42.6	42.6	42.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)