Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360685

Luminaire Tested: **GSS-SB6C-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360685
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	45360.1 lumens
Efficiency:	N/A
Efficacy:	151.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B5 - U0 - G5


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 22.3 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	22680.1	0.0	22680.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	22680.1	0.0	22680.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	45360.1	0.0	45360.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	865.0	1.9
10°-20°	2636.5	5.8
20°-30°	4406.7	9.7
30°-40°	6077.1	13.4
40°-50°	7449.7	16.4
50°-60°	8730.1	19.2
60°-70°	9694.6	21.4
70°-80°	5271.9	11.6
80°-90°	228.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	45360.1	100.0
0°-180°	45360.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3954.1	8.7			
FM	(30°-60°)	11128.5	24.5			
FH	(60°-80°)	7483.3	16.5			G3/7500
FVH	(80°-90°)	114.2	0.3			G2/225
BL	(0°-30°)	3954.1	8.7	B4/5000		
BM	(30°-60°)	11128.5	24.5	B5		
BH	(60°-80°)	7483.3	16.5	B5		G5
BVH	(80°-90°)	114.2	0.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1	8937.1
2.5°	8947.0	8947.0	8917.2	8956.9	8937.1	8947.0	8956.9	8947.0	8937.1	8947.0	8956.9
5°	8996.6	8976.8	8996.6	9016.5	8986.7	9006.6	8996.6	8947.0	8976.8	8976.8	8976.8
7.5°	9086.0	9105.9	9086.0	9135.7	9105.9	9165.5	9105.9	9066.2	9056.2	9046.3	9046.3
10°	9125.7	9125.7	9115.8	9205.2	9225.0	9284.6	9244.9	9185.3	9155.5	9115.8	9076.1
12.5°	9016.5	9036.4	9086.0	9254.8	9334.3	9453.4	9423.6	9304.5	9215.1	9185.3	9125.7
15°	8897.3	8917.2	9016.5	9225.0	9413.7	9592.4	9582.5	9433.6	9324.3	9244.9	9155.5
17.5°	8708.7	8738.5	8877.5	9195.2	9532.9	9731.5	9791.0	9642.1	9522.9	9393.8	9274.7
20°	8390.9	8390.9	8639.2	9046.3	9513.0	9959.9	10118.7	9999.6	9860.6	9652.0	9493.1
22.5°	8033.4	8053.3	8301.5	8837.8	9503.1	10158.5	10466.3	10337.2	10198.2	9969.8	9731.5
25°	7675.9	7675.9	7954.0	8559.7	9374.0	10297.5	10873.4	10803.9	10525.9	10317.3	10009.5
27.5°	7348.2	7348.2	7646.2	8281.7	9155.5	10337.2	11280.6	11280.6	10972.7	10664.9	10327.3
30°	6961.0	7060.3	7397.9	8063.2	8956.9	10267.7	11578.5	11767.1	11489.1	11091.9	10595.4
32.5°	6633.3	6702.8	7050.3	7755.4	8668.9	10188.2	11916.1	12382.8	12094.8	11548.7	10992.6
35°	6246.0	6236.1	6633.3	7328.4	8261.8	10009.5	12184.2	13117.6	12839.6	12253.7	11499.0
37.5°	5739.6	5739.6	6146.7	6822.0	7874.5	9701.7	12402.7	13931.9	13723.4	13058.0	12253.7
40°	5193.4	5253.0	5610.5	6295.7	7407.8	9334.3	12402.7	14597.2	14706.4	14021.3	13187.1
42.5°	4796.2	4816.1	5143.8	5789.2	6891.5	8857.6	12243.8	15173.1	15500.8	14924.9	13842.5
45°	4379.2	4428.8	4706.9	5302.7	6355.2	8291.6	11965.7	15818.6	16344.9	15947.7	14527.7
47.5°	3872.7	3922.4	4240.1	4845.9	5848.8	7675.9	11499.0	16493.8	17596.1	17308.1	15749.1
50°	3286.9	3326.6	3624.5	4269.9	5282.8	6970.9	10913.1	17000.3	18847.3	19135.2	17596.1
52.5°	2571.9	2601.7	2919.4	3545.0	4607.6	6295.7	10088.9	17308.1	20108.4	21121.3	20068.7
55°	1847.0	1896.6	2174.7	2691.0	3713.8	5392.0	9105.9	17467.0	21488.7	23474.7	23137.1
57.5°	1330.6	1350.5	1539.2	1936.4	2760.6	4329.5	7844.8	17198.9	22729.9	26284.9	26989.9
60°	1102.2	1102.2	1132.0	1320.7	1886.7	3058.5	6335.4	16205.9	23792.4	29124.9	31299.6
62.5°	1012.9	1012.9	1032.7	1062.5	1241.3	1986.0	4528.1	14190.1	23911.6	31855.7	36026.3
65°	923.5	923.5	943.4	963.2	1002.9	1290.9	2730.8	10386.8	21578.0	31885.4	38568.4
67.5°	844.1	844.1	854.0	863.9	883.8	943.4	1499.4	6295.7	17268.4	31041.4	39541.5
70°	764.6	764.6	764.6	754.7	784.5	794.4	993.0	3197.5	11548.7	28032.6	39074.8
72.5°	*675.2*	*675.2*	*665.3*	*645.5*	*655.4*	*655.4*	*734.8*	*1569.0*	*5997.8*	*22283.1*	*35281.5*
75°	575.9	585.9	546.2	526.3	516.4	526.3	585.9	893.7	2681.1	13514.8	26364.3
77.5°	486.6	506.4	446.9	407.1	397.2	397.2	456.8	556.1	1151.9	4905.5	11816.8
80°	367.4	377.3	327.7	288.0	288.0	278.0	337.6	407.1	546.2	1459.7	2651.3
82.5°	208.5	208.5	188.7	168.8	158.9	168.8	228.4	278.0	337.6	516.4	724.9
85°	49.7	49.7	59.6	69.5	69.5	89.4	129.1	149.0	178.7	208.5	278.0
87.5°	9.9	9.9	9.9	19.9	29.8	29.8	49.7	69.5	89.4	109.2	119.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360685
CATALOG NUMBER: GSS-SB6C-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	8937.1	8937.1	*8937.1*
2.5°	8956.9	8966.8	*8956.9*
5°	9016.5	8996.6	*8966.8*
7.5°	9026.4	9036.4	*9046.3*
10°	9066.2	9105.9	*9046.3*
12.5°	9105.9	9076.1	*9056.2*
15°	9135.7	9125.7	*9066.2*
17.5°	9244.9	9205.2	*9195.2*
20°	9413.7	9403.8	*9374.0*
22.5°	9612.3	9592.4	*9582.5*
25°	9900.3	9830.8	*9791.0*
27.5°	10138.6	10079.0	*10059.2*
30°	10376.9	10257.8	*10257.8*
32.5°	10585.5	10555.7	*10535.8*
35°	11082.0	10933.0	*10952.9*
37.5°	11687.7	11538.7	*11409.6*
40°	12541.7	12343.1	*12263.6*
42.5°	13087.8	12889.2	*12909.1*
45°	13395.7	13048.1	*12958.7*
47.5°	14229.8	13792.9	*13673.7*
50°	15580.3	15044.1	*14895.1*
52.5°	17764.9	16901.0	*16702.4*
55°	20505.6	19443.1	*19244.5*
57.5°	24259.2	22849.1	*22422.1*
60°	28827.0	27079.3	*26433.8*
62.5°	34318.3	32163.5	*31547.8*
65°	38449.2	36651.9	*35698.6*
67.5°	41755.9	40276.3	*39819.6*
70°	43722.1	43791.6	*43910.8*
72.5°	*41448.1*	*43354.7*	*44268.2*
75°	30376.1	31855.7	*33275.7*
77.5°	11737.3	10585.5	*10247.8*
80°	1896.6	1777.5	*1837.1*
82.5°	854.0	903.6	*953.3*
85°	556.1	645.5	*685.2*
87.5°	129.1	129.1	*129.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)