Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360677

Luminaire Tested: **GSS-SB4C-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360677
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	30241.4 lumens
Efficiency:	N/A
Efficacy:	148.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	15120.7	0.0	15120.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	15120.7	0.0	15120.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	30241.4	0.0	30241.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	576.7	1.9
10°-20°	1757.7	5.8
20°-30°	2937.9	9.7
30°-40°	4051.6	13.4
40°-50°	4966.7	16.4
50°-60°	5820.3	19.2
60°-70°	6463.3	21.4
70°-80°	3514.8	11.6
80°-90°	152.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	30241.4	100.0
0°-180°	30241.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2636.2	8.7			
FM	(30°-60°)	7419.3	24.5			
FH	(60°-80°)	4989.1	16.5			G2/5000
FVH	(80°-90°)	76.2	0.3			G1/100
BL	(0°-30°)	2636.2	8.7	B4/5000		
BM	(30°-60°)	7419.3	24.5	B4/8500		
BH	(60°-80°)	4989.1	16.5	B4/5000		G4/5000
BVH	(80°-90°)	76.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3	5958.3
2.5°	5964.9	5964.9	5945.1	5971.5	5958.3	5964.9	5971.5	5964.9	5958.3	5964.9	5971.5
5°	5998.0	5984.8	5998.0	6011.3	5991.4	6004.6	5998.0	5964.9	5984.8	5984.8	5984.8
7.5°	6057.6	6070.8	6057.6	6090.7	6070.8	6110.6	6070.8	6044.4	6037.7	6031.1	6031.1
10°	6084.1	6084.1	6077.5	6137.1	6150.3	6190.0	6163.5	6123.8	6103.9	6077.5	6051.0
12.5°	6011.3	6024.5	6057.6	6170.2	6223.1	6302.6	6282.7	6203.3	6143.7	6123.8	6084.1
15°	5931.8	5945.1	6011.3	6150.3	6276.1	6395.2	6388.6	6289.3	6216.5	6163.5	6103.9
17.5°	5806.0	5825.9	5918.6	6130.4	6355.5	6487.9	6527.7	6428.3	6348.9	6262.8	6183.4
20°	5594.2	5594.2	5759.7	6031.1	6342.3	6640.2	6746.1	6666.7	6574.0	6435.0	6329.0
22.5°	5355.9	5369.1	5534.6	5892.1	6335.7	6772.6	6977.8	6891.8	6799.1	6646.8	6487.9
25°	5117.5	5117.5	5302.9	5706.7	6249.6	6865.3	7249.3	7202.9	7017.6	6878.5	6673.3
27.5°	4899.0	4899.0	5097.7	5521.4	6103.9	6891.8	7520.7	7520.7	7315.5	7110.2	6885.1
30°	4640.9	4707.1	4932.1	5375.7	5971.5	6845.4	7719.3	7845.1	7659.7	7394.9	7063.9
32.5°	4422.4	4468.7	4700.4	5170.5	5779.6	6792.5	7944.4	8255.6	8063.6	7699.4	7328.7
35°	4164.2	4157.6	4422.4	4885.8	5508.1	6673.3	8123.2	8745.5	8560.1	8169.5	7666.3
37.5°	3826.6	3826.6	4098.0	4548.2	5249.9	6468.1	8268.8	9288.3	9149.3	8705.7	8169.5
40°	3462.4	3502.2	3740.5	4197.3	4938.8	6223.1	8268.8	9731.9	9804.7	9347.9	8791.8
42.5°	3197.6	3210.9	3429.3	3859.7	4594.5	5905.3	8162.9	10115.9	10334.3	9950.4	9228.7
45°	2919.6	2952.7	3138.0	3535.3	4237.0	5528.0	7977.5	10546.2	10897.1	10632.3	9685.6
47.5°	2581.9	2615.0	2826.9	3230.7	3899.4	5117.5	7666.3	10996.4	11731.2	11539.2	10499.9
50°	2191.3	2217.8	2416.4	2846.7	3522.0	4647.5	7275.7	11334.0	12565.4	12757.4	11731.2
52.5°	1714.7	1734.5	1946.4	2363.5	3071.8	4197.3	6726.3	11539.2	13406.2	14081.5	13379.7
55°	1231.4	1264.5	1449.9	1794.1	2476.0	3594.8	6070.8	11645.2	14326.4	15650.5	15425.4
57.5°	887.1	900.4	1026.2	1291.0	1840.5	2886.5	5230.1	11466.4	15153.9	17524.0	17994.1
60°	734.9	734.9	754.7	880.5	1257.9	2039.1	4223.8	10804.4	15862.3	19417.4	20867.3
62.5°	675.3	675.3	688.5	708.4	827.5	1324.1	3018.9	9460.5	15941.8	21238.0	24018.6
65°	615.7	615.7	628.9	642.2	668.7	860.6	1820.6	6924.9	14386.0	21257.9	25713.4
67.5°	562.7	562.7	569.3	576.0	589.2	628.9	999.7	4197.3	11512.8	20695.2	26362.2
70°	509.8	509.8	509.8	503.1	523.0	529.6	662.0	2131.7	7699.4	18689.2	26051.0
72.5°	*450.2*	*450.2*	*443.6*	*430.3*	*436.9*	*436.9*	*489.9*	*1046.0*	*3998.7*	*14856.0*	*23522.1*
75°	384.0	390.6	364.1	350.9	344.3	350.9	390.6	595.8	1787.5	9010.3	17577.0
77.5°	324.4	337.6	297.9	271.4	264.8	264.8	304.5	370.7	768.0	3270.4	7878.2
80°	245.0	251.6	218.5	192.0	192.0	185.4	225.1	271.4	364.1	973.2	1767.6
82.5°	139.0	139.0	125.8	112.5	105.9	112.5	152.3	185.4	225.1	344.3	483.3
85°	33.1	33.1	39.7	46.3	46.3	59.6	86.1	99.3	119.2	139.0	185.4
87.5°	6.6	6.6	6.6	13.2	19.9	19.9	33.1	46.3	59.6	72.8	79.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360677
CATALOG NUMBER: GSS-SB4C-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5958.3	5958.3	*5958.3*
2.5°	5971.5	5978.2	*5971.5*
5°	6011.3	5998.0	*5978.2*
7.5°	6017.9	6024.5	*6031.1*
10°	6044.4	6070.8	*6031.1*
12.5°	6070.8	6051.0	*6037.7*
15°	6090.7	6084.1	*6044.4*
17.5°	6163.5	6137.1	*6130.4*
20°	6276.1	6269.5	*6249.6*
22.5°	6408.5	6395.2	*6388.6*
25°	6600.5	6554.1	*6527.7*
27.5°	6759.4	6719.6	*6706.4*
30°	6918.3	6838.8	*6838.8*
32.5°	7057.3	7037.4	*7024.2*
35°	7388.3	7289.0	*7302.2*
37.5°	7792.1	7692.8	*7606.8*
40°	8361.5	8229.1	*8176.1*
42.5°	8725.6	8593.2	*8606.4*
45°	8930.8	8699.1	*8639.5*
47.5°	9486.9	9195.6	*9116.2*
50°	10387.3	10029.8	*9930.5*
52.5°	11843.8	11267.8	*11135.4*
55°	13671.0	12962.6	*12830.2*
57.5°	16173.5	15233.4	*14948.7*
60°	19218.8	18053.7	*17623.3*
62.5°	22879.9	21443.3	*21032.8*
65°	25633.9	24435.7	*23800.1*
67.5°	27838.5	26852.1	*26547.5*
70°	29149.3	29195.7	*29275.1*
72.5°	*27633.3*	*28904.4*	*29513.5*
75°	20251.6	21238.0	*22184.7*
77.5°	7825.2	7057.3	*6832.2*
80°	1264.5	1185.0	*1224.8*
82.5°	569.3	602.5	*635.6*
85°	370.7	430.3	*456.8*
87.5°	86.1	86.1	*86.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)