Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1364631

Luminaire Tested: **GSS-SB3A-750-U-SLR-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1364631
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3A-750-U-SLR-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 85W 70CRI 5000K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC AND HOUSE SIDE SHIELD
Light Source:	(78) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	10016 lumens
Efficiency:	N/A
Efficacy:	117.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B1 - U0 - G2


Input Watts (W):	85
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5.5 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1619.1	0.0	1619.1
	% Fixture	16.2	0.0	16.2
Street Side	Lumens	8396.9	0.0	8396.9
	% Fixture	83.8	0.0	83.8
Total	Lumens	10016.0	0.0	10016.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.4	1.7
10°-20°	460.2	4.6
20°-30°	659.2	6.6
30°-40°	826.8	8.3
40°-50°	1358.2	13.6
50°-60°	2450.9	24.5
60°-70°	2720.0	27.2
70°-80°	1228.9	12.3
80°-90°	145.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10016.0	100.0
0°-180°	10016.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	858.0	8.6			
FM	(30°-60°)	3803.4	38.0			
FH	(60°-80°)	3605.1	36.0			G2/5000
FVH	(80°-90°)	130.4	1.3			G2/225
BL	(0°-30°)	427.9	4.3	B1/500		
BM	(30°-60°)	832.6	8.3	B1/1000		
BH	(60°-80°)	343.9	3.4	B1/500		G1/500
BVH	(80°-90°)	14.9	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6
2.5°	1953.0	1951.2	1943.8	1897.6	1851.5	1811.5	1771.5	1731.6	1676.2	1633.1	1596.2
5°	2137.5	2127.7	2088.3	2017.6	1940.7	1873.0	1796.2	1722.3	1639.3	1571.6	1500.9
7.5°	2263.6	2253.8	2214.4	2097.6	1980.7	1897.6	1814.6	1737.7	1645.4	1556.3	1454.8
10°	2322.1	2311.0	2266.7	2140.6	2005.3	1903.8	1820.8	1750.0	1673.1	1583.9	1457.8
12.5°	2362.1	2348.5	2294.4	2149.8	2011.4	1910.0	1823.8	1756.2	1700.8	1648.5	1525.5
15°	2386.7	2374.4	2325.2	2174.5	2014.5	1900.7	1799.2	1734.6	1716.2	1725.4	1667.0
17.5°	2423.6	2411.9	2365.1	2205.2	2033.0	1885.3	1746.9	1676.2	1716.2	1799.2	1817.7
20°	2472.8	2460.5	2411.3	2245.2	2048.4	1839.2	1648.5	1580.9	1682.4	1820.8	1916.1
22.5°	2528.1	2518.3	2478.9	2291.3	2063.7	1771.5	1519.3	1488.6	1611.6	1759.2	1882.3
25°	2595.8	2586.6	2549.7	2355.9	2079.1	1679.3	1408.6	1414.8	1519.3	1636.2	1762.3
27.5°	2688.1	2679.5	2645.0	2435.9	2097.6	1583.9	1319.4	1350.2	1427.1	1507.0	1583.9
30°	2789.6	2782.8	2755.7	2531.2	2134.5	1494.7	1267.2	1285.6	1337.9	1402.5	1448.6
32.5°	2928.0	2916.9	2872.6	2620.4	2131.4	1427.1	1242.5	1224.1	1239.5	1291.8	1337.9
35°	3100.2	3091.6	3057.2	2712.7	2076.0	1365.6	1230.2	1165.7	1156.4	1187.2	1233.3
37.5°	3352.4	3345.0	3315.5	2863.4	1989.9	1288.7	1199.5	1104.1	1073.4	1094.9	1125.7
40°	3730.7	3711.6	3635.4	3035.6	1894.6	1211.8	1144.1	1030.3	987.3	1002.6	1036.5
42.5°	4244.3	4208.0	4062.9	3266.3	1765.4	1138.0	1061.1	956.5	910.4	919.6	950.4
45°	4902.5	4847.8	4628.8	3583.1	1630.1	1079.5	975.0	879.6	830.4	839.6	873.5
47.5°	5671.4	5596.4	5296.2	3915.2	1485.5	1045.7	907.3	802.7	765.8	787.4	821.2
50°	6578.7	6503.1	6200.4	4127.5	1368.6	1024.2	855.0	732.0	716.6	744.3	772.0
52.5°	7569.1	7461.4	7030.8	3992.1	1273.3	1005.7	836.6	682.8	688.9	710.5	738.1
55°	8531.7	8292.5	7335.3	3543.1	1150.3	984.2	848.9	645.9	661.3	688.9	710.5
57.5°	9159.2	8743.3	7080.0	2854.2	1021.1	959.6	858.1	627.4	639.7	670.5	695.1
60°	8611.7	8193.4	6520.3	2137.5	910.4	907.3	842.7	621.3	602.8	645.9	667.4
62.5°	7055.4	6711.0	5333.1	1365.6	805.8	808.9	808.9	618.2	541.3	596.7	615.1
65°	*4847.2*	*4631.9*	*3770.7*	*845.8*	*658.2*	*688.9*	*735.1*	*599.7*	*476.7*	*541.3*	*559.8*
67.5°	3186.3	3028.2	2395.9	522.9	507.5	565.9	636.7	562.8	427.5	485.9	498.2
70°	1728.5	1608.5	1128.7	344.5	332.2	442.9	501.3	476.7	384.5	433.7	446.0
72.5°	1141.1	1042.6	649.0	243.0	243.0	347.5	350.6	390.6	344.5	384.5	396.8
75°	858.1	770.1	418.3	169.2	187.6	221.4	273.7	279.9	289.1	326.0	341.4
77.5°	393.7	345.7	153.8	101.5	138.4	153.8	209.1	178.4	215.3	243.0	249.1
80°	227.6	199.3	86.1	67.7	89.2	98.4	172.2	104.6	129.2	172.2	181.5
82.5°	95.3	84.9	43.1	46.1	55.4	58.4	95.3	73.8	83.0	113.8	110.7
85°	27.7	27.7	27.7	30.8	33.8	33.8	55.4	52.3	49.2	52.3	52.3
87.5°	18.5	18.5	18.5	18.5	21.5	21.5	24.6	27.7	30.8	30.8	30.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6
2.5°	1580.9	1559.3	1531.7	1491.7	1485.5	1464.0	1448.6	1464.0	1479.4	1507.0	1510.1
5°	1464.0	1430.2	1365.6	1316.4	1261.0	1233.3	1230.2	1224.1	1242.5	1282.5	1307.1
7.5°	1399.4	1344.0	1227.2	1141.1	1064.2	1036.5	1015.0	1033.4	1030.3	1082.6	1104.1
10°	1384.0	1297.9	1134.9	1005.7	910.4	873.5	851.9	848.9	855.0	885.8	907.3
12.5°	1439.4	1328.7	1098.0	907.3	796.6	756.6	732.0	710.5	710.5	716.6	744.3
15°	1562.4	1430.2	1119.5	861.2	741.2	688.9	649.0	621.3	599.7	602.8	605.9
17.5°	1734.6	1577.8	1174.9	845.8	707.4	652.0	602.8	575.1	550.5	544.4	544.4
20°	1870.0	1719.3	1217.9	833.5	679.7	609.0	565.9	541.3	519.8	510.6	510.6
22.5°	1885.3	1777.7	1254.8	818.1	645.9	565.9	525.9	504.4	489.0	485.9	485.9
25°	1783.9	1731.6	1242.5	799.7	612.0	525.9	495.2	476.7	461.3	458.3	461.3
27.5°	1614.7	1587.0	1199.5	775.1	584.4	495.2	467.5	452.1	436.7	433.7	436.7
30°	1464.0	1433.2	1125.7	735.1	562.8	470.6	439.8	424.4	409.1	409.1	412.1
32.5°	1341.0	1310.2	1051.9	688.9	535.2	442.9	415.2	399.8	384.5	384.5	390.6
35°	1230.2	1205.6	993.4	642.8	507.5	418.3	387.5	375.2	362.9	359.8	366.0
37.5°	1134.9	1122.6	941.1	593.6	479.8	393.7	366.0	353.7	338.3	335.2	341.4
40°	1042.6	1036.5	882.7	550.5	446.0	369.1	341.4	329.1	310.6	310.6	316.8
42.5°	956.5	953.4	830.4	522.9	415.2	344.5	313.7	301.4	286.0	286.0	292.2
45°	888.9	885.8	781.2	507.5	384.5	316.8	289.1	273.7	261.4	264.5	270.7
47.5°	827.3	821.2	728.9	510.6	369.1	298.3	261.4	246.0	236.8	243.0	252.2
50°	778.1	772.0	692.0	513.6	344.5	273.7	239.9	224.5	218.4	227.6	236.8
52.5°	747.4	741.2	655.1	495.2	313.7	255.3	218.4	209.1	209.1	218.4	224.5
55°	716.6	710.5	593.6	455.2	279.9	236.8	203.0	196.8	196.8	206.1	212.2
57.5°	698.2	685.9	529.0	409.1	252.2	215.3	187.6	187.6	187.6	190.7	193.8
60°	670.5	639.7	461.3	350.6	230.7	193.8	175.3	172.2	172.2	169.2	172.2
62.5°	612.0	559.8	387.5	298.3	206.1	175.3	159.9	156.9	147.6	138.4	141.5
65°	*553.6*	*473.6*	*307.6*	*249.1*	*178.4*	*150.7*	*141.5*	*138.4*	*123.0*	*110.7*	*113.8*
67.5°	479.8	378.3	230.7	209.1	153.8	129.2	119.9	119.9	110.7	101.5	101.5
70°	427.5	295.3	193.8	156.9	123.0	101.5	101.5	107.6	98.4	86.1	86.1
72.5°	378.3	239.9	156.9	126.1	95.3	80.0	86.1	89.2	80.0	70.7	70.7
75°	322.9	187.6	123.0	98.4	70.7	61.5	64.6	70.7	64.6	55.4	58.4
77.5°	233.7	129.2	83.0	64.6	52.3	46.1	49.2	49.2	46.1	43.1	43.1
80°	163.0	86.1	55.4	43.1	36.9	33.8	33.8	30.8	30.8	33.8	33.8
82.5°	98.4	61.5	40.0	33.8	27.7	21.5	21.5	24.6	24.6	27.7	27.7
85°	43.1	36.9	27.7	24.6	18.5	15.4	18.5	18.5	21.5	24.6	24.6
87.5°	27.7	27.7	21.5	18.5	15.4	12.3	12.3	15.4	15.4	18.5	21.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6
2.5°	1522.4	1553.2	1590.1	1642.4	1688.5	1743.9	1799.2	1851.5	1900.7	1906.9	1928.4
5°	1325.6	1384.0	1457.8	1544.0	1648.5	1759.2	1866.9	1980.7	2073.0	2106.8	2156.0
7.5°	1122.6	1196.4	1304.1	1436.3	1583.9	1750.0	1916.1	2076.0	2214.4	2279.0	2343.6
10°	928.8	999.6	1131.8	1291.8	1482.4	1707.0	1928.4	2143.7	2312.9	2386.7	2448.2
12.5°	753.5	824.3	931.9	1116.4	1347.1	1617.8	1910.0	2168.3	2355.9	2432.8	2491.2
15°	615.1	673.6	775.1	947.3	1190.3	1494.7	1845.4	2149.8	2365.1	2439.0	2482.0
17.5°	541.3	556.7	621.3	778.1	1042.6	1384.0	1762.3	2125.2	2371.3	2439.0	2463.6
20°	510.6	510.6	522.9	605.9	864.2	1267.2	1700.8	2109.9	2380.5	2448.2	2445.1
22.5°	482.9	489.0	489.0	507.5	658.2	1104.1	1636.2	2103.7	2408.2	2460.5	2417.4
25°	458.3	467.5	467.5	473.6	516.7	910.4	1556.3	2116.0	2457.4	2485.1	2399.0
27.5°	436.7	446.0	446.0	452.1	461.3	676.6	1424.0	2119.1	2512.8	2515.8	2374.4
30°	415.2	424.4	430.6	430.6	436.7	498.2	1257.9	2100.6	2574.3	2555.8	2371.3
32.5°	390.6	402.9	406.0	412.1	415.2	433.7	1042.6	2069.9	2651.2	2611.2	2374.4
35°	369.1	384.5	387.5	387.5	393.7	412.1	833.5	2036.1	2755.7	2685.0	2386.7
37.5°	347.5	359.8	362.9	366.0	372.1	390.6	661.3	1986.8	2844.9	2777.3	2448.2
40°	322.9	338.3	341.4	344.5	350.6	369.1	569.0	1925.3	2980.3	2931.1	2540.5
42.5°	298.3	313.7	319.9	322.9	326.0	350.6	519.8	1882.3	3198.6	3146.3	2728.1
45°	276.8	292.2	298.3	298.3	304.5	338.3	476.7	1977.6	3500.0	3475.4	2980.3
47.5°	258.4	273.7	276.8	276.8	279.9	319.9	439.8	2232.9	3961.4	3896.8	3373.9
50°	243.0	255.3	261.4	255.3	258.4	304.5	461.3	2654.2	4551.9	4573.4	3952.2
52.5°	230.7	243.0	246.0	233.7	233.7	283.0	489.0	2998.7	5305.4	5502.3	4868.7
55°	215.3	227.6	230.7	215.3	215.3	249.1	424.4	3020.2	6163.5	6797.1	6062.0
57.5°	199.9	212.2	212.2	199.9	196.8	215.3	344.5	2678.9	6827.8	8264.2	7695.2
60°	181.5	193.8	190.7	184.5	178.4	196.8	316.8	2042.2	6738.7	9220.7	9568.2
62.5°	147.6	166.1	172.2	169.2	156.9	178.4	295.3	1331.7	5831.4	8390.3	9509.8
65°	*123.0*	*138.4*	*147.6*	*147.6*	*138.4*	*196.8*	*258.4*	*701.2*	*4668.8*	*7120.0*	*8384.1*
67.5°	107.6	123.0	129.2	126.1	119.9	175.3	163.0	338.3	3580.0	6135.8	7504.5
70°	95.3	107.6	113.8	104.6	98.4	141.5	116.9	199.9	2395.9	5120.9	6683.3
72.5°	76.9	89.2	95.3	86.1	76.9	104.6	89.2	132.3	1559.3	4364.3	5939.0
75°	61.5	73.8	76.9	70.7	61.5	76.9	70.7	92.3	1018.0	3610.8	5050.1
77.5°	46.1	52.3	58.4	55.4	46.1	55.4	49.2	64.6	581.3	2534.3	3543.1
80°	36.9	40.0	40.0	40.0	36.9	33.8	33.8	43.1	261.4	1248.7	1848.4
82.5°	30.8	33.8	33.8	30.8	27.7	24.6	21.5	24.6	76.9	559.8	851.9
85°	27.7	30.8	24.6	21.5	18.5	15.4	9.2	9.2	21.5	89.2	166.1
87.5°	21.5	18.5	15.4	12.3	6.2	3.1	3.1	0.0	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364631
CATALOG NUMBER: GSS-SB3A-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1731.6	1731.6	1731.6	*1731.6*	1731.6	1731.6	1731.6	1731.6	1731.6	1731.6
2.5°	1962.2	1993.0	2014.5	*2033.0*	2026.8	2011.4	1980.7	1959.2	1954.2	1953.0
5°	2220.6	2269.8	2312.9	*2306.7*	2312.9	2266.7	2220.6	2165.2	2143.1	2137.5
7.5°	2435.9	2497.4	2549.7	*2543.5*	2525.1	2472.8	2395.9	2312.9	2273.5	2263.6
10°	2552.8	2623.5	2666.6	*2651.2*	2620.4	2552.8	2475.9	2377.4	2333.2	2322.1
12.5°	2574.3	2620.4	2611.2	*2605.0*	2598.9	2565.1	2506.6	2417.4	2373.1	2362.1
15°	2518.9	2500.5	2448.2	*2435.9*	2482.0	2525.1	2512.8	2439.0	2397.1	2386.7
17.5°	2426.7	2331.3	2236.0	*2223.7*	2300.6	2420.5	2515.8	2472.8	2433.4	2423.6
20°	2325.2	2146.8	2042.2	*2020.7*	2116.0	2294.4	2482.0	2506.6	2479.6	2472.8
22.5°	2205.2	1996.1	1885.3	*1873.0*	1943.8	2152.9	2432.8	2543.5	2531.2	2528.1
25°	2100.6	1863.8	1759.2	*1740.8*	1833.1	2036.1	2383.6	2605.0	2597.7	2595.8
27.5°	2014.5	1768.5	1657.8	*1645.4*	1734.6	1937.6	2322.1	2657.3	2681.9	2688.1
30°	1946.9	1697.7	1587.0	*1571.6*	1670.1	1870.0	2279.0	2731.1	2777.9	2789.6
32.5°	1894.6	1657.8	1553.2	*1544.0*	1648.5	1842.3	2254.4	2808.0	2904.0	2928.0
35°	1876.1	1670.1	1599.3	*1620.8*	1700.8	1870.0	2272.9	2934.1	3067.0	3100.2
37.5°	1916.1	1805.4	1854.6	*1910.0*	1940.7	2002.2	2359.0	3137.1	3309.4	3352.4
40°	2045.3	2168.3	2399.0	*2506.6*	2494.3	2352.8	2555.8	3423.2	3669.2	3730.7
42.5°	2374.4	2774.2	3263.2	*3444.7*	3340.1	2912.6	2869.5	3893.7	4174.2	4244.3
45°	2863.4	3506.2	4308.9	*4718.0*	4358.1	3623.1	3364.7	4564.2	4834.9	4902.5
47.5°	3352.4	4324.3	5600.7	*6086.6*	5379.2	4327.4	4013.7	5366.9	5610.5	5671.4
50°	3850.7	5228.5	6889.4	*7538.3*	6397.3	5044.0	4702.6	6357.3	6534.4	6578.7
52.5°	4364.3	6037.4	8310.3	*8870.1*	7461.4	5597.6	5490.0	7436.8	7542.6	7569.1
55°	4936.3	6803.2	9734.3	*10186.4*	8430.2	6080.5	6412.6	8565.6	8538.5	8531.7
57.5°	5699.1	7609.1	10881.5	*11512.0*	9309.9	6732.5	7646.0	9820.4	9291.4	9159.2
60°	7030.8	8860.8	12308.6	*12994.4*	10487.8	7685.9	8553.3	9792.7	8847.9	8611.7
62.5°	8574.8	10066.5	13600.3	*14178.5*	11727.3	8633.2	7830.5	8224.2	7289.2	7055.4
65°	*7449.1*	*9854.2*	*13640.3*	*14233.9*	*11773.4*	*8055.0*	*5788.3*	*5831.4*	*5044.0*	*4847.2*
67.5°	6338.8	8734.7	12422.4	*12889.9*	10503.2	6658.7	3838.4	3804.5	3310.0	3186.3
70°	5643.7	7652.1	10706.2	*10303.3*	8830.1	5628.4	2549.7	2112.9	1805.4	1728.5
72.5°	5071.7	6071.2	8676.3	*7101.6*	7326.1	4579.6	1620.8	1439.4	1200.7	1141.1
75°	4591.9	5022.5	5413.1	*4908.7*	5203.9	3773.8	1374.8	1110.3	908.5	858.1
77.5°	3653.8	3909.1	3204.8	*3112.5*	3644.6	2685.0	682.8	467.5	408.4	393.7
80°	2174.5	1848.4	1817.7	*2073.0*	2426.7	1393.2	418.3	258.4	233.7	227.6
82.5°	1316.4	667.4	725.8	*916.5*	1291.8	633.6	249.1	110.7	98.4	95.3
85°	221.4	181.5	279.9	*267.6*	252.2	135.3	67.7	30.8	28.3	27.7
87.5°	6.2	9.2	12.3	*15.4*	15.4	15.4	15.4	15.4	17.8	18.5
90°	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)