Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1365016

Luminaire Tested: **GSS-SB3B-750-U-SLL**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1365016
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3B-750-U-SLL
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 109W 70CRI 5000K FIXTURE w/ 90° Spill Light Eliminator LEFT OPTIC
Light Source:	(78) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15845.1 lumens
Efficiency:	N/A
Efficacy:	145.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	109
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.4 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4262.7	0.0	4262.7
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	11582.4	0.0	11582.4
	% Fixture	73.1	0.0	73.1
Total	Lumens	15845.1	0.0	15845.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.5	1.6
10°-20°	764.5	4.8
20°-30°	1183.2	7.5
30°-40°	1468.0	9.3
40°-50°	2146.6	13.5
50°-60°	3362.5	21.2
60°-70°	3989.8	25.2
70°-80°	2327.0	14.7
80°-90°	354.0	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15845.1	100.0
0°-180°	15845.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1190.9	7.5			
FM	(30°-60°)	4820.4	30.4			
FH	(60°-80°)	5281.6	33.3			G3/7500
FVH	(80°-90°)	289.5	1.8			G3/500
BL	(0°-30°)	1006.3	6.4	B3/2500		
BM	(30°-60°)	2156.7	13.6	B2/2500		
BH	(60°-80°)	1035.2	6.5	B3/2500		G3/2500
BVH	(80°-90°)	64.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	*2526.5*	2526.5
2.5°	2730.0	2739.7	2749.3	2759.8	2770.7	2776.9	2783.1	2789.6	2795.8	*2801.7*	2795.8
5°	2916.0	2959.8	3003.2	3032.6	3062.1	3084.5	3107.0	3119.8	3133.0	*3134.9*	3133.0
7.5°	3103.9	3155.8	3207.8	3252.7	3297.7	3326.3	3355.0	3371.7	3388.7	*3394.5*	3388.7
10°	3222.1	3282.9	3344.2	3387.6	3431.4	3458.1	3484.4	3497.6	3510.8	*3514.7*	3510.8
12.5°	3282.2	3340.7	3399.2	3432.9	3466.2	3483.3	3499.9	3506.1	3511.6	*3506.9*	3511.6
15°	3311.2	3345.7	3379.8	3394.1	3408.1	3400.0	3391.4	3379.4	3367.4	*3359.7*	3367.4
17.5°	3319.0	3331.0	3343.4	3317.4	3291.8	3245.3	3198.8	3164.0	3129.1	*3103.9*	3129.1
20°	3344.2	3324.8	3305.4	3236.4	3167.8	3080.7	2993.5	2935.0	2876.1	*2840.4*	2876.1
22.5°	3371.3	3316.6	3262.0	3146.1	3030.3	2910.9	2792.0	2724.5	2657.5	*2619.5*	2657.5
25°	3413.9	3320.1	3226.0	3069.4	2913.3	2773.0	2633.1	2559.9	2487.0	*2445.2*	2487.0
27.5°	3475.9	3332.5	3189.2	2995.4	2801.7	2649.8	2497.5	2427.7	2358.0	*2321.2*	2358.0
30°	3563.1	3372.8	3182.2	2950.5	2718.3	2559.5	2400.6	2332.4	2263.8	*2224.3*	2263.8
32.5°	3669.7	3429.4	3189.2	2929.5	2669.9	2507.9	2346.3	2280.9	2215.7	*2181.6*	2215.7
35°	3849.9	3545.7	3241.5	2953.6	2666.0	2515.7	2365.7	2317.7	2270.0	*2251.4*	2270.0
37.5°	4078.5	3723.1	3367.4	3071.0	2774.5	2672.2	2569.9	2569.9	2569.9	*2584.7*	2569.9
40°	4415.6	4016.5	3617.4	3336.8	3056.6	3050.4	3045.0	3110.1	3175.6	*3204.7*	3175.6
42.5°	4888.4	4466.4	4044.8	3818.5	3592.2	3727.8	3863.4	4051.7	4240.1	*4363.3*	4240.1
45°	5475.4	5064.7	4653.9	4495.8	4338.1	4640.0	4941.5	5274.3	5607.2	*5843.6*	5607.2
47.5°	6037.3	5691.7	5345.6	5255.3	5165.4	5667.2	6169.1	6656.9	7144.8	*7432.3*	7144.8
50°	6688.3	6377.5	6066.4	6048.9	6031.5	6699.9	7368.4	7998.1	8627.8	*8978.5*	8627.8
52.5°	7523.4	7182.0	6840.2	6854.2	6867.4	7661.3	8455.3	9216.8	9978.2	*10373.5*	9978.2
55°	8521.2	8093.0	7664.8	7662.5	7660.2	8572.4	9485.3	10420.8	11357.0	*11884.8*	11357.0
57.5°	9538.4	9137.4	8736.3	8641.0	8545.2	9499.3	10452.9	11486.0	12519.5	*13074.4*	12519.5
60°	10301.8	10080.9	9860.0	9707.4	9555.1	10534.7	11514.7	12581.9	13648.7	*14202.0*	13648.7
62.5°	9986.0	10380.9	10775.7	10764.5	10753.2	11810.7	12868.2	13978.1	15088.6	*15585.4*	15088.6
65°	*8920.3*	*9550.0*	*10179.7*	*10613.0*	*11045.8*	*12324.2*	*13602.2*	*14758.5*	*15914.8*	*16422.4*	*15914.8*
67.5°	7920.6	8475.5	9030.8	9385.4	9739.9	11180.3	12621.0	13933.1	15245.2	*15767.5*	15245.2
70°	6963.5	7578.0	8192.6	8446.0	8699.5	9923.2	11146.6	12184.7	13222.4	*13427.0*	13222.4
72.5°	5977.3	6708.1	7439.3	7546.6	7654.0	8544.5	9435.0	9987.9	10540.9	*10094.5*	10540.9
75°	4894.2	5718.8	6543.0	6614.7	6686.4	6963.8	7241.7	7382.3	7523.4	*7269.6*	7523.4
77.5°	3255.0	3968.8	4683.0	4843.8	5004.6	5189.5	5374.7	5365.0	5355.3	*4998.8*	5355.3
80°	1910.4	2468.8	3027.2	3048.1	3069.0	3207.8	3346.1	3487.5	3629.0	*3402.3*	3629.0
82.5°	955.2	1261.7	1568.6	1615.9	1663.2	1748.0	1832.9	1872.4	1912.3	*1720.5*	1912.3
85°	217.0	296.8	376.7	453.8	530.9	620.0	709.1	699.1	689.0	*581.3*	689.0
87.5°	17.4	17.8	18.6	19.0	19.4	19.8	20.2	21.3	22.5	*23.3*	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2789.6	2783.1	2776.9	2770.7	2759.8	2749.3	2739.7	2730.0	2705.2	2680.8	2658.3
5°	3119.8	3107.0	3084.5	3062.1	3032.6	3003.2	2959.8	2916.0	2872.2	2828.8	2783.1
7.5°	3371.7	3355.0	3326.3	3297.7	3252.7	3207.8	3155.8	3103.9	3030.3	2956.7	2887.3
10°	3497.6	3484.4	3458.1	3431.4	3387.6	3344.2	3282.9	3222.1	3134.1	3045.8	2959.8
12.5°	3506.1	3499.9	3483.3	3466.2	3432.9	3399.2	3340.7	3282.2	3194.6	3107.0	3010.5
15°	3379.4	3391.4	3400.0	3408.1	3394.1	3379.8	3345.7	3311.2	3222.5	3134.1	3036.1
17.5°	3164.0	3198.8	3245.3	3291.8	3317.4	3343.4	3331.0	3319.0	3236.0	3153.5	3048.9
20°	2935.0	2993.5	3080.7	3167.8	3236.4	3305.4	3324.8	3344.2	3260.5	3176.8	3064.4
22.5°	2724.5	2792.0	2910.9	3030.3	3146.1	3262.0	3316.6	3371.3	3294.6	3218.2	3094.6
25°	2559.9	2633.1	2773.0	2913.3	3069.4	3226.0	3320.1	3413.9	3347.6	3281.4	3146.5
27.5°	2427.7	2497.5	2649.8	2801.7	2995.4	3189.2	3332.5	3475.9	3425.2	3374.4	3222.5
30°	2332.4	2400.6	2559.5	2718.3	2950.5	3182.2	3372.8	3563.1	3523.2	3483.7	3312.4
32.5°	2280.9	2346.3	2507.9	2669.9	2929.5	3189.2	3429.4	3669.7	3644.9	3620.1	3418.2
35°	2317.7	2365.7	2515.7	2666.0	2953.6	3241.5	3545.7	3849.9	3818.9	3787.9	3530.6
37.5°	2569.9	2569.9	2672.2	2774.5	3071.0	3367.4	3723.1	4078.5	4041.7	4004.9	3667.7
40°	3110.1	3045.0	3050.4	3056.6	3336.8	3617.4	4016.5	4415.6	4343.1	4270.3	3824.7
42.5°	4051.7	3863.4	3727.8	3592.2	3818.5	4044.8	4466.4	4888.4	4734.9	4581.1	3998.3
45°	5274.3	4941.5	4640.0	4338.1	4495.8	4653.9	5064.7	5475.4	5229.4	4983.3	4233.9
47.5°	6656.9	6169.1	5667.2	5165.4	5255.3	5345.6	5691.7	6037.3	5725.8	5414.2	4476.1
50°	7998.1	7368.4	6699.9	6031.5	6048.9	6066.4	6377.5	6688.3	6265.9	5843.6	4687.3
52.5°	9216.8	8455.3	7661.3	6867.4	6854.2	6840.2	7182.0	7523.4	6852.6	6181.5	4787.2
55°	10420.8	9485.3	8572.4	7660.2	7662.5	7664.8	8093.0	8521.2	7442.0	6362.8	4760.9
57.5°	11486.0	10452.9	9499.3	8545.2	8641.0	8736.3	9137.4	9538.4	7936.9	6335.7	4617.1
60°	12581.9	11514.7	10534.7	9555.1	9707.4	9860.0	10080.9	10301.8	8158.5	6014.8	4272.6
62.5°	13978.1	12868.2	11810.7	10753.2	10764.5	10775.7	10380.9	9986.0	7666.8	5347.6	3708.0
65°	*14758.5*	*13602.2*	*12324.2*	*11045.8*	*10613.0*	*10179.7*	*9550.0*	*8920.3*	*6612.8*	*4305.2*	*2908.6*
67.5°	13933.1	12621.0	11180.3	9739.9	9385.4	9030.8	8475.5	7920.6	5679.3	3437.9	2263.4
70°	12184.7	11146.6	9923.2	8699.5	8446.0	8192.6	7578.0	6963.5	4824.8	2686.2	1734.5
72.5°	9987.9	9435.0	8544.5	7654.0	7546.6	7439.3	6708.1	5977.3	4006.4	2035.2	1304.0
75°	7382.3	7241.7	6963.8	6686.4	6614.7	6543.0	5718.8	4894.2	3198.8	1503.5	966.4
77.5°	5365.0	5374.7	5189.5	5004.6	4843.8	4683.0	3968.8	3255.0	2098.7	942.4	624.7
80°	3487.5	3346.1	3207.8	3069.0	3048.1	3027.2	2468.8	1910.4	1203.2	496.0	345.3
82.5°	1872.4	1832.9	1748.0	1663.2	1615.9	1568.6	1261.7	955.2	603.0	251.1	185.6
85°	699.1	709.1	620.0	530.9	453.8	376.7	296.8	217.0	143.4	69.8	58.9
87.5°	21.3	20.2	19.8	19.4	19.0	18.6	17.8	17.4	17.1	16.3	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2635.8	2613.3	2590.5	2568.8	2546.7	2524.6	2505.2	2484.3	2463.8	2447.5	2431.6
5°	2737.7	2693.2	2648.6	2606.4	2564.5	2520.7	2483.1	2445.9	2409.5	2379.3	2349.1
7.5°	2817.9	2755.9	2693.9	2638.5	2582.7	2524.6	2479.3	2433.9	2389.0	2349.8	2310.3
10°	2873.3	2797.0	2720.3	2656.3	2592.4	2530.4	2482.0	2434.3	2387.0	2346.7	2306.4
12.5°	2914.0	2828.4	2742.8	2672.2	2602.1	2534.3	2487.0	2447.5	2408.3	2380.1	2352.2
15°	2938.1	2845.8	2753.2	2673.8	2594.3	2518.8	2476.9	2451.4	2425.8	2423.5	2421.1
17.5°	2944.3	2838.9	2733.8	2641.2	2549.0	2460.7	2425.0	2421.5	2418.0	2456.4	2494.8
20°	2952.0	2828.4	2704.8	2583.1	2461.4	2344.4	2321.9	2344.0	2365.7	2440.9	2515.7
22.5°	2971.4	2820.3	2669.1	2516.5	2363.8	2224.3	2203.0	2235.5	2267.7	2365.7	2463.8
25°	3011.7	2819.5	2627.3	2437.0	2246.7	2086.7	2084.8	2120.0	2155.3	2246.0	2336.7
27.5°	3071.0	2826.8	2582.7	2355.6	2128.2	1964.6	1974.3	2008.0	2042.1	2109.6	2177.0
30°	3140.7	2842.7	2545.1	2284.7	2024.7	1865.8	1876.3	1902.6	1929.0	1977.8	2026.6
32.5°	3216.3	2860.6	2505.2	2222.7	1940.6	1794.1	1794.1	1805.4	1816.6	1848.4	1880.2
35°	3273.6	2856.3	2439.3	2152.2	1864.7	1751.5	1727.5	1718.2	1708.9	1729.8	1750.7
37.5°	3330.6	2844.3	2358.0	2073.9	1790.3	1701.1	1655.4	1630.6	1605.0	1615.1	1624.4
40°	3379.0	2817.2	2255.3	1980.5	1705.8	1635.3	1577.9	1540.7	1503.5	1502.7	1501.6
42.5°	3414.7	2770.3	2125.5	1869.3	1612.8	1563.6	1492.7	1445.4	1398.1	1393.1	1388.0
45°	3484.4	2738.1	1991.8	1756.2	1521.0	1476.4	1405.9	1357.0	1309.0	1301.2	1293.5
47.5°	3537.9	2700.5	1863.1	1643.8	1425.2	1373.7	1307.8	1266.4	1224.5	1219.9	1214.8
50°	3530.9	2636.6	1741.8	1543.8	1345.4	1274.9	1209.8	1175.7	1141.2	1147.0	1152.8
52.5°	3392.6	2505.6	1619.0	1453.9	1289.6	1199.3	1129.6	1104.0	1078.0	1096.2	1114.1
55°	3158.9	2332.0	1504.3	1378.7	1252.4	1162.5	1080.4	1051.7	1023.0	1048.6	1074.2
57.5°	2898.5	2150.3	1402.0	1315.2	1228.4	1152.8	1052.1	1011.8	971.9	997.4	1023.0
60°	2530.4	1920.5	1310.5	1249.7	1188.9	1129.6	1028.8	978.4	928.1	945.1	961.8
62.5°	2068.5	1629.1	1189.6	1155.5	1121.8	1096.6	1000.5	934.7	868.8	871.1	872.7
65°	*1512.0*	*1280.3*	*1048.2*	*1040.8*	*1033.9*	*1026.9*	*947.4*	*876.5*	*806.0*	*798.3*	*790.5*
67.5°	1088.9	978.8	868.8	889.3	909.9	920.3	866.1	803.7	740.9	725.0	709.1
70°	782.8	744.0	705.3	735.9	766.5	763.4	737.0	699.8	662.6	652.6	642.5
72.5°	572.7	572.0	571.6	594.8	618.1	587.1	603.7	595.2	587.1	579.7	572.7
75°	429.4	426.6	424.3	451.8	479.7	492.1	503.0	498.3	494.1	488.6	483.6
77.5°	306.9	309.2	310.8	341.0	371.2	406.9	408.8	398.7	388.3	382.9	376.7
80°	194.5	196.9	198.4	230.2	261.6	311.9	310.0	297.6	284.8	280.6	275.9
82.5°	120.1	120.5	120.9	136.4	151.9	180.2	187.9	187.9	187.9	185.2	182.1
85°	48.4	50.8	53.5	63.6	73.6	89.1	93.8	94.6	94.9	90.7	86.0
87.5°	15.5	16.3	17.4	19.4	21.3	23.3	27.1	29.5	31.8	34.1	35.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2417.6	2403.3	2386.6	2369.6	2357.6	2345.2	2337.0	2328.9	2325.0	2321.2	2318.1
5°	2324.3	2298.7	2276.2	2253.3	2235.5	2217.3	2202.6	2187.5	2181.3	2174.7	2170.4
7.5°	2277.0	2243.6	2215.7	2187.5	2160.7	2134.4	2117.3	2100.3	2090.2	2080.1	2072.8
10°	2271.2	2235.9	2199.1	2162.3	2132.8	2103.4	2077.8	2053.0	2038.7	2024.7	2017.0
12.5°	2319.6	2287.1	2243.3	2199.1	2159.2	2119.6	2088.3	2056.9	2039.0	2022.0	2010.4
15°	2409.9	2398.7	2358.0	2317.3	2262.2	2206.8	2161.9	2116.5	2091.7	2066.2	2051.8
17.5°	2516.8	2538.9	2510.6	2482.0	2404.5	2327.0	2259.9	2193.3	2156.8	2120.4	2107.6
20°	2575.4	2635.0	2631.9	2629.2	2528.1	2426.6	2338.6	2250.6	2201.8	2153.7	2134.4
22.5°	2549.8	2635.8	2657.9	2679.6	2580.4	2480.8	2372.3	2263.8	2206.4	2148.7	2130.5
25°	2429.3	2521.9	2563.0	2604.0	2522.3	2440.5	2335.1	2230.1	2169.6	2108.8	2090.2
27.5°	2251.4	2325.8	2371.9	2418.0	2368.0	2318.1	2232.8	2147.5	2094.1	2040.2	2020.4
30°	2077.0	2127.4	2164.2	2201.0	2168.1	2135.1	2073.9	2013.1	1973.2	1933.6	1921.2
32.5°	1917.8	1955.0	1975.5	1995.6	1970.1	1944.5	1904.2	1863.9	1839.1	1814.3	1806.2
35°	1781.0	1811.6	1827.1	1842.6	1821.3	1800.0	1763.9	1728.3	1710.4	1692.6	1686.0
37.5°	1650.4	1676.0	1698.0	1720.5	1705.0	1689.5	1658.9	1628.3	1607.4	1585.7	1574.0
40°	1526.4	1550.8	1578.7	1606.2	1603.5	1600.4	1571.3	1542.3	1512.0	1482.2	1466.3
42.5°	1412.5	1436.9	1466.3	1495.8	1501.6	1507.4	1483.4	1459.0	1424.1	1389.2	1364.8
45°	1314.4	1336.1	1368.3	1400.8	1414.4	1428.0	1406.3	1384.2	1345.0	1305.9	1276.8
47.5°	1236.9	1259.4	1295.0	1331.1	1345.4	1360.1	1345.4	1331.1	1297.4	1263.3	1237.7
50°	1177.2	1201.3	1229.2	1257.5	1284.2	1310.5	1307.8	1305.1	1278.4	1251.6	1227.6
52.5°	1136.2	1158.6	1187.7	1216.8	1244.7	1273.0	1277.2	1281.9	1262.5	1243.1	1222.2
55°	1100.9	1127.6	1154.8	1181.9	1208.2	1234.2	1240.0	1245.8	1231.9	1217.5	1202.0
57.5°	1052.1	1081.1	1108.3	1135.4	1166.0	1196.6	1201.3	1205.9	1191.2	1176.1	1164.5
60°	991.6	1021.1	1049.4	1077.3	1108.3	1139.3	1145.5	1151.7	1140.0	1128.4	1117.6
62.5°	906.4	939.7	962.9	986.2	1015.6	1045.5	1054.4	1063.7	1058.3	1053.2	1040.8
65°	*822.3*	*854.4*	*872.7*	*891.3*	*916.8*	*942.4*	*951.3*	*960.2*	*957.5*	*955.2*	*946.3*
67.5°	738.6	768.0	783.1	798.3	815.7	833.1	843.2	853.3	848.2	842.8	833.5
70°	666.5	690.5	703.7	716.9	730.8	744.8	750.2	755.6	747.9	740.1	719.2
72.5°	590.9	609.2	620.4	631.6	644.8	658.0	661.1	664.6	652.6	640.2	615.7
75°	497.6	511.5	520.0	528.9	542.5	556.1	561.9	567.7	550.6	534.0	508.0
77.5°	389.4	402.2	410.4	418.5	429.7	441.0	442.5	444.9	430.1	415.4	399.9
80°	285.2	294.5	297.6	300.3	309.6	318.5	318.5	318.5	307.7	296.4	288.7
82.5°	180.2	178.3	174.4	170.5	179.8	189.1	192.2	195.7	190.7	186.0	177.5
85°	80.6	74.4	73.2	71.7	71.3	70.5	73.2	75.6	74.4	73.6	70.5
87.5°	38.0	39.5	38.4	36.8	35.3	34.1	31.0	27.9	25.6	23.3	21.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2315.3	2313.4	2315.3	2318.1	2321.2	2325.0	2328.9	2337.0	2345.2	2357.6	2369.6
5°	2166.1	2162.3	2166.1	2170.4	2174.7	2181.3	2187.5	2202.6	2217.3	2235.5	2253.3
7.5°	2065.4	2061.5	2065.4	2072.8	2080.1	2090.2	2100.3	2117.3	2134.4	2160.7	2187.5
10°	2009.2	2003.4	2009.2	2017.0	2024.7	2038.7	2053.0	2077.8	2103.4	2132.8	2162.3
12.5°	1998.7	1991.8	1998.7	2010.4	2022.0	2039.0	2056.9	2088.3	2119.6	2159.2	2199.1
15°	2037.5	2026.6	2037.5	2051.8	2066.2	2091.7	2116.5	2161.9	2206.8	2262.2	2317.3
17.5°	2094.5	2088.6	2094.5	2107.6	2120.4	2156.8	2193.3	2259.9	2327.0	2404.5	2482.0
20°	2115.0	2108.0	2115.0	2134.4	2153.7	2201.8	2250.6	2338.6	2426.6	2528.1	2629.2
22.5°	2111.9	2104.1	2111.9	2130.5	2148.7	2206.4	2263.8	2372.3	2480.8	2580.4	2679.6
25°	2071.2	2065.4	2071.2	2090.2	2108.8	2169.6	2230.1	2335.1	2440.5	2522.3	2604.0
27.5°	2000.3	1987.9	2000.3	2020.4	2040.2	2094.1	2147.5	2232.8	2318.1	2368.0	2418.0
30°	1908.5	1902.6	1908.5	1921.2	1933.6	1973.2	2013.1	2073.9	2135.1	2168.1	2201.0
32.5°	1798.0	1794.1	1798.0	1806.2	1814.3	1839.1	1863.9	1904.2	1944.5	1970.1	1995.6
35°	1679.8	1674.0	1679.8	1686.0	1692.6	1710.4	1728.3	1763.9	1800.0	1821.3	1842.6
37.5°	1562.4	1553.9	1562.4	1574.0	1585.7	1607.4	1628.3	1658.9	1689.5	1705.0	1720.5
40°	1450.0	1441.5	1450.0	1466.3	1482.2	1512.0	1542.3	1571.3	1600.4	1603.5	1606.2
42.5°	1340.8	1325.3	1340.8	1364.8	1389.2	1424.1	1459.0	1483.4	1507.4	1501.6	1495.8
45°	1247.8	1228.4	1247.8	1276.8	1305.9	1345.0	1384.2	1406.3	1428.0	1414.4	1400.8
47.5°	1212.1	1193.5	1212.1	1237.7	1263.3	1297.4	1331.1	1345.4	1360.1	1345.4	1331.1
50°	1203.2	1185.8	1203.2	1227.6	1251.6	1278.4	1305.1	1307.8	1310.5	1284.2	1257.5
52.5°	1201.3	1185.8	1201.3	1222.2	1243.1	1262.5	1281.9	1277.2	1273.0	1244.7	1216.8
55°	1186.5	1174.1	1186.5	1202.0	1217.5	1231.9	1245.8	1240.0	1234.2	1208.2	1181.9
57.5°	1152.8	1147.0	1152.8	1164.5	1176.1	1191.2	1205.9	1201.3	1196.6	1166.0	1135.4
60°	1106.3	1096.6	1106.3	1117.6	1128.4	1140.0	1151.7	1145.5	1139.3	1108.3	1077.3
62.5°	1028.8	1015.3	1028.8	1040.8	1053.2	1058.3	1063.7	1054.4	1045.5	1015.6	986.2
65°	*937.8*	*922.3*	*937.8*	*946.3*	*955.2*	*957.5*	*960.2*	*951.3*	*942.4*	*916.8*	*891.3*
67.5°	824.6	821.5	824.6	833.5	842.8	848.2	853.3	843.2	833.1	815.7	798.3
70°	698.3	674.3	698.3	719.2	740.1	747.9	755.6	750.2	744.8	730.8	716.9
72.5°	590.9	565.8	590.9	615.7	640.2	652.6	664.6	661.1	658.0	644.8	631.6
75°	482.4	465.0	482.4	508.0	534.0	550.6	567.7	561.9	556.1	542.5	528.9
77.5°	384.4	375.9	384.4	399.9	415.4	430.1	444.9	442.5	441.0	429.7	418.5
80°	280.9	275.1	280.9	288.7	296.4	307.7	318.5	318.5	318.5	309.6	300.3
82.5°	168.6	162.8	168.6	177.5	186.0	190.7	195.7	192.2	189.1	179.8	170.5
85°	67.8	65.9	67.8	70.5	73.6	74.4	75.6	73.2	70.5	71.3	71.7
87.5°	20.2	19.4	20.2	21.7	23.3	25.6	27.9	31.0	34.1	35.3	36.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2386.6	2403.3	2417.6	2431.6	2447.5	2463.8	2484.3	2505.2	2524.6	2546.7	2568.8
5°	2276.2	2298.7	2324.3	2349.1	2379.3	2409.5	2445.9	2483.1	2520.7	2564.5	2606.4
7.5°	2215.7	2243.6	2277.0	2310.3	2349.8	2389.0	2433.9	2479.3	2524.6	2582.7	2638.5
10°	2199.1	2235.9	2271.2	2306.4	2346.7	2387.0	2434.3	2482.0	2530.4	2592.4	2656.3
12.5°	2243.3	2287.1	2319.6	2352.2	2380.1	2408.3	2447.5	2487.0	2534.3	2602.1	2672.2
15°	2358.0	2398.7	2409.9	2421.1	2423.5	2425.8	2451.4	2476.9	2518.8	2594.3	2673.8
17.5°	2510.6	2538.9	2516.8	2494.8	2456.4	2418.0	2421.5	2425.0	2460.7	2549.0	2641.2
20°	2631.9	2635.0	2575.4	2515.7	2440.9	2365.7	2344.0	2321.9	2344.4	2461.4	2583.1
22.5°	2657.9	2635.8	2549.8	2463.8	2365.7	2267.7	2235.5	2203.0	2224.3	2363.8	2516.5
25°	2563.0	2521.9	2429.3	2336.7	2246.0	2155.3	2120.0	2084.8	2086.7	2246.7	2437.0
27.5°	2371.9	2325.8	2251.4	2177.0	2109.6	2042.1	2008.0	1974.3	1964.6	2128.2	2355.6
30°	2164.2	2127.4	2077.0	2026.6	1977.8	1929.0	1902.6	1876.3	1865.8	2024.7	2284.7
32.5°	1975.5	1955.0	1917.8	1880.2	1848.4	1816.6	1805.4	1794.1	1794.1	1940.6	2222.7
35°	1827.1	1811.6	1781.0	1750.7	1729.8	1708.9	1718.2	1727.5	1751.5	1864.7	2152.2
37.5°	1698.0	1676.0	1650.4	1624.4	1615.1	1605.0	1630.6	1655.4	1701.1	1790.3	2073.9
40°	1578.7	1550.8	1526.4	1501.6	1502.7	1503.5	1540.7	1577.9	1635.3	1705.8	1980.5
42.5°	1466.3	1436.9	1412.5	1388.0	1393.1	1398.1	1445.4	1492.7	1563.6	1612.8	1869.3
45°	1368.3	1336.1	1314.4	1293.5	1301.2	1309.0	1357.0	1405.9	1476.4	1521.0	1756.2
47.5°	1295.0	1259.4	1236.9	1214.8	1219.9	1224.5	1266.4	1307.8	1373.7	1425.2	1643.8
50°	1229.2	1201.3	1177.2	1152.8	1147.0	1141.2	1175.7	1209.8	1274.9	1345.4	1543.8
52.5°	1187.7	1158.6	1136.2	1114.1	1096.2	1078.0	1104.0	1129.6	1199.3	1289.6	1453.9
55°	1154.8	1127.6	1100.9	1074.2	1048.6	1023.0	1051.7	1080.4	1162.5	1252.4	1378.7
57.5°	1108.3	1081.1	1052.1	1023.0	997.4	971.9	1011.8	1052.1	1152.8	1228.4	1315.2
60°	1049.4	1021.1	991.6	961.8	945.1	928.1	978.4	1028.8	1129.6	1188.9	1249.7
62.5°	962.9	939.7	906.4	872.7	871.1	868.8	934.7	1000.5	1096.6	1121.8	1155.5
65°	*872.7*	*854.4*	*822.3*	*790.5*	*798.3*	*806.0*	*876.5*	*947.4*	*1026.9*	*1033.9*	*1040.8*
67.5°	783.1	768.0	738.6	709.1	725.0	740.9	803.7	866.1	920.3	909.9	889.3
70°	703.7	690.5	666.5	642.5	652.6	662.6	699.8	737.0	763.4	766.5	735.9
72.5°	620.4	609.2	590.9	572.7	579.7	587.1	595.2	603.7	587.1	618.1	594.8
75°	520.0	511.5	497.6	483.6	488.6	494.1	498.3	503.0	492.1	479.7	451.8
77.5°	410.4	402.2	389.4	376.7	382.9	388.3	398.7	408.8	406.9	371.2	341.0
80°	297.6	294.5	285.2	275.9	280.6	284.8	297.6	310.0	311.9	261.6	230.2
82.5°	174.4	178.3	180.2	182.1	185.2	187.9	187.9	187.9	180.2	151.9	136.4
85°	73.2	74.4	80.6	86.0	90.7	94.9	94.6	93.8	89.1	73.6	63.6
87.5°	38.4	39.5	38.0	35.7	34.1	31.8	29.5	27.1	23.3	21.3	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365016
CATALOG NUMBER: GSS-SB3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5	2526.5
2.5°	2590.5	2613.3	2635.8	2658.3	2680.8	2705.2	2730.0
5°	2648.6	2693.2	2737.7	2783.1	2828.8	2872.2	2916.0
7.5°	2693.9	2755.9	2817.9	2887.3	2956.7	3030.3	3103.9
10°	2720.3	2797.0	2873.3	2959.8	3045.8	3134.1	3222.1
12.5°	2742.8	2828.4	2914.0	3010.5	3107.0	3194.6	3282.2
15°	2753.2	2845.8	2938.1	3036.1	3134.1	3222.5	3311.2
17.5°	2733.8	2838.9	2944.3	3048.9	3153.5	3236.0	3319.0
20°	2704.8	2828.4	2952.0	3064.4	3176.8	3260.5	3344.2
22.5°	2669.1	2820.3	2971.4	3094.6	3218.2	3294.6	3371.3
25°	2627.3	2819.5	3011.7	3146.5	3281.4	3347.6	3413.9
27.5°	2582.7	2826.8	3071.0	3222.5	3374.4	3425.2	3475.9
30°	2545.1	2842.7	3140.7	3312.4	3483.7	3523.2	3563.1
32.5°	2505.2	2860.6	3216.3	3418.2	3620.1	3644.9	3669.7
35°	2439.3	2856.3	3273.6	3530.6	3787.9	3818.9	3849.9
37.5°	2358.0	2844.3	3330.6	3667.7	4004.9	4041.7	4078.5
40°	2255.3	2817.2	3379.0	3824.7	4270.3	4343.1	4415.6
42.5°	2125.5	2770.3	3414.7	3998.3	4581.1	4734.9	4888.4
45°	1991.8	2738.1	3484.4	4233.9	4983.3	5229.4	5475.4
47.5°	1863.1	2700.5	3537.9	4476.1	5414.2	5725.8	6037.3
50°	1741.8	2636.6	3530.9	4687.3	5843.6	6265.9	6688.3
52.5°	1619.0	2505.6	3392.6	4787.2	6181.5	6852.6	7523.4
55°	1504.3	2332.0	3158.9	4760.9	6362.8	7442.0	8521.2
57.5°	1402.0	2150.3	2898.5	4617.1	6335.7	7936.9	9538.4
60°	1310.5	1920.5	2530.4	4272.6	6014.8	8158.5	10301.8
62.5°	1189.6	1629.1	2068.5	3708.0	5347.6	7666.8	9986.0
65°	*1048.2*	*1280.3*	*1512.0*	*2908.6*	*4305.2*	*6612.8*	*8920.3*
67.5°	868.8	978.8	1088.9	2263.4	3437.9	5679.3	7920.6
70°	705.3	744.0	782.8	1734.5	2686.2	4824.8	6963.5
72.5°	571.6	572.0	572.7	1304.0	2035.2	4006.4	5977.3
75°	424.3	426.6	429.4	966.4	1503.5	3198.8	4894.2
77.5°	310.8	309.2	306.9	624.7	942.4	2098.7	3255.0
80°	198.4	196.9	194.5	345.3	496.0	1203.2	1910.4
82.5°	120.9	120.5	120.1	185.6	251.1	603.0	955.2
85°	53.5	50.8	48.4	58.9	69.8	143.4	217.0
87.5°	17.4	16.3	15.5	15.9	16.3	17.1	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7




Test Conditions

Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)