Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359149

Luminaire Tested: **GSS-SB6C-740-U-T2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359149
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-740-U-T2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 4000K FIXTURE w/ TYPE II DISTRIBUTION OPTIC
Light Source:	(156) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	44715 lumens
Efficiency:	N/A
Efficacy:	149.0 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B4 - U0 - G5


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 19.9 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10245.3	0.0	10245.3
	% Fixture	22.9	0.0	22.9
Street Side	Lumens	34469.7	0.0	34469.7
	% Fixture	77.1	0.0	77.1
Total	Lumens	44715.0	0.0	44715.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	637.3	1.4
10°-20°	1918.6	4.3
20°-30°	3241.6	7.2
30°-40°	5000.9	11.2
40°-50°	7637.2	17.1
50°-60°	10559.5	23.6
60°-70°	10671.2	23.9
70°-80°	4694.9	10.5
80°-90°	353.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	44715.0	100.0
0°-180°	44715.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3488.6	7.8			
FM	(30°-60°)	18281.6	40.9			
FH	(60°-80°)	12520.3	28.0			G5
FVH	(80°-90°)	179.2	0.4			G2/225
BL	(0°-30°)	2308.9	5.2	B3/2500		
BM	(30°-60°)	4916.0	11.0	B3/5000		
BH	(60°-80°)	2845.8	6.4	B4/5000		G4/5000
BVH	(80°-90°)	174.5	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	*6669.3*	6669.3
2.5°	6978.9	7088.7	7088.7	7038.8	7018.8	7008.8	6938.9	6859.0	6829.1	*6779.2*	6749.2
5°	7408.2	7408.2	7428.1	7378.2	7408.2	7368.2	7268.4	7168.6	7048.7	*6958.9*	6919.0
7.5°	7448.1	7528.0	7577.9	7577.9	7637.8	7647.8	7597.9	7488.0	7338.3	*7198.5*	7128.6
10°	7488.0	7557.9	7557.9	7637.8	7767.6	7867.4	7897.4	7857.5	7617.8	*7518.0*	7378.2
12.5°	7398.2	7478.1	7508.0	7667.8	7847.5	8037.2	8176.9	8196.9	8047.1	*7867.4*	7657.8
15°	7088.7	7158.6	7278.4	7518.0	7837.5	8127.0	8396.6	8546.4	8376.6	*8246.8*	7957.3
17.5°	6669.3	6709.3	6909.0	7218.5	7657.8	8147.0	8616.2	8905.8	8865.8	*8696.1*	8356.7
20°	6629.4	6669.3	6729.3	6958.9	7468.1	8077.1	8756.0	9315.1	9424.9	*9165.4*	8746.0
22.5°	6968.9	7008.8	7008.8	7038.8	7358.2	8017.2	8895.8	9754.4	10004.0	*9784.4*	9245.2
25°	7438.1	7518.0	7428.1	7358.2	7468.1	8057.1	8975.7	10253.6	10742.8	*10473.3*	9804.3
27.5°	8107.1	8097.1	8017.2	7807.5	7777.6	8176.9	9195.3	10643.0	11451.7	*11172.2*	10383.4
30°	9035.6	9085.5	8905.8	8466.5	8266.8	8446.5	9494.8	10962.5	12200.5	*11970.9*	10932.5
32.5°	10083.9	10063.9	9844.3	9424.9	8935.7	8885.8	9774.4	11302.0	13059.1	*12769.6*	11621.4
35°	11212.1	11192.1	11122.2	10403.4	9764.4	9494.8	10223.7	11691.3	14057.5	*13817.9*	12430.1
37.5°	12230.5	12320.3	12530.0	11371.8	10692.9	10293.6	10802.7	12340.3	15335.5	*14986.1*	13408.6
40°	13099.1	13258.8	13458.5	12410.2	11561.5	11222.1	11571.5	13398.6	16703.3	*16493.7*	14586.7
42.5°	13897.8	14007.6	13987.7	13348.7	12619.8	12240.5	12540.0	14496.8	18470.5	*18320.7*	16034.4
45°	14876.2	14996.1	14946.1	14337.1	13608.3	13268.8	13807.9	15784.8	20147.8	*20167.8*	17402.2
47.5°	15834.7	15954.5	15924.6	15365.5	14666.6	14387.0	15125.8	17302.4	21765.2	*22034.8*	18889.8
50°	16733.3	16843.1	16903.0	16553.6	15944.5	15645.0	16413.8	18730.1	23332.7	*23941.8*	20307.6
52.5°	16982.9	17122.7	17532.0	17661.8	17392.2	17032.8	17591.9	20097.9	24680.6	*25589.1*	21675.4
55°	16164.2	16403.8	17282.4	17941.3	18740.1	18780.0	18819.9	21425.8	25858.7	*27076.8*	22923.4
57.5°	14736.5	14776.4	15804.8	17142.6	19039.6	20736.9	20936.6	22973.3	27006.9	*28524.4*	24161.4
60°	11571.5	11361.9	13029.2	15295.6	17961.3	21515.6	24311.2	25369.5	28434.6	*30271.7*	25649.0
62.5°	6200.1	6220.1	7597.9	10413.4	14876.2	20756.9	27206.6	28943.8	30521.3	*32538.0*	27855.5
65°	3893.8	4043.5	4822.3	6070.3	9005.6	16493.7	27386.3	33696.2	33826.0	*35832.8*	30621.1
67.5°	*2845.5*	*2885.4*	*3544.3*	*4452.9*	*5161.8*	*9674.5*	*22044.8*	*33756.1*	*36212.2*	*38149.1*	*31799.2*
70°	2116.6	2136.6	2605.8	3354.6	3764.0	4532.8	14047.6	29213.3	34974.1	*35932.6*	28853.9
72.5°	1547.5	1557.5	1807.1	2466.1	2965.3	2695.7	6599.5	21046.4	30371.5	*32078.8*	25958.5
75°	1088.3	1108.2	1287.9	1707.3	1996.8	1877.0	2516.0	13159.0	21805.2	*21615.5*	18131.0
77.5°	818.7	828.7	948.5	1208.1	1357.8	1228.0	1417.7	6150.2	7787.6	*7028.8*	5720.9
80°	599.0	629.0	688.9	758.8	908.5	788.7	798.7	1727.2	1877.0	*1647.4*	1477.6
82.5°	319.5	359.4	459.3	459.3	529.2	469.3	419.3	768.8	808.7	*758.8*	658.9
85°	99.8	99.8	109.8	139.8	209.7	209.7	209.7	259.6	269.6	*269.6*	229.6
87.5°	20.0	20.0	20.0	20.0	30.0	39.9	59.9	79.9	89.9	*99.8*	99.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359149
CATALOG NUMBER: GSS-SB6C-740-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3	6669.3
2.5°	6729.3	6659.4	6589.5	6469.7	6409.8	6319.9	6240.0	6200.1	6170.1	6160.2	6160.2
5°	6859.0	6749.2	6529.6	6319.9	6130.2	5960.5	5830.7	5730.8	5670.9	5621.0	5621.0
7.5°	6988.8	6839.1	6509.6	6140.2	5870.6	5661.0	5481.2	5421.3	5401.4	5351.5	5321.5
10°	7208.5	6968.9	6479.7	5950.5	5571.1	5391.4	5311.5	5291.5	5301.5	5311.5	5311.5
12.5°	7378.2	7118.6	6399.8	5710.9	5341.5	5241.6	5251.6	5301.5	5381.4	5371.4	5351.5
15°	7617.8	7228.5	6240.0	5431.3	5161.8	5161.8	5261.6	5371.4	5451.3	5501.2	5471.3
17.5°	7897.4	7358.2	6000.4	5171.7	5012.0	5101.9	5311.5	5421.3	5561.1	5591.1	5571.1
20°	8246.8	7468.1	5730.8	4922.1	4912.2	5101.9	5281.6	5441.3	5551.1	5581.1	5601.1
22.5°	8586.3	7567.9	5381.4	4742.4	4802.3	5041.9	5211.7	5381.4	5431.3	5461.3	5471.3
25°	8935.7	7667.8	5061.9	4602.6	4722.5	4962.1	5101.9	5171.7	5181.7	5161.8	5161.8
27.5°	9315.1	7677.7	4742.4	4492.8	4632.6	4842.3	4922.1	4942.1	4902.2	4762.4	4722.5
30°	9714.5	7577.9	4482.8	4393.0	4532.8	4702.5	4762.4	4702.5	4562.7	4363.0	4343.1
32.5°	10044.0	7428.1	4293.1	4273.2	4422.9	4572.7	4572.7	4462.9	4253.2	4053.5	4043.5
35°	10543.2	7218.5	4103.4	4193.3	4323.1	4393.0	4413.0	4253.2	4023.6	3833.9	3813.9
37.5°	11032.4	7038.8	4023.6	4093.5	4213.3	4273.2	4213.3	4053.5	3903.8	3744.0	3744.0
40°	11791.2	6928.9	3923.7	4023.6	4123.4	4133.4	4023.6	3903.8	3923.7	3833.9	3823.9
42.5°	12619.8	6919.0	3883.8	3953.7	4023.6	4003.6	3843.9	3843.9	3873.8	3704.1	3664.1
45°	13568.3	7058.7	3883.8	3853.8	3893.8	3833.9	3744.0	3724.1	3654.2	3404.6	3394.6
47.5°	14556.8	7398.2	3903.8	3714.1	3704.1	3684.1	3644.2	3574.3	3364.6	3155.0	3125.0
50°	15335.5	7867.4	3963.7	3534.4	3494.4	3564.3	3494.4	3374.6	3135.0	2935.3	2905.4
52.5°	16264.0	8336.7	3923.7	3314.7	3264.8	3444.5	3374.6	3204.9	3025.2	2905.4	2875.4
55°	17242.5	8825.9	3764.0	3015.2	3055.1	3294.7	3274.8	3085.1	2865.4	2705.7	2685.7
57.5°	18220.9	9444.9	3494.4	2755.6	2905.4	3204.9	3125.0	2895.4	2745.6	2635.8	2615.8
60°	19718.5	10333.5	3105.0	2486.0	2755.6	3015.2	2885.4	2815.5	2655.8	2565.9	2516.0
62.5°	21655.4	11811.1	2595.9	2236.4	2545.9	2785.6	2775.6	2695.7	2555.9	2456.1	2426.1
65°	24411.0	13218.9	2126.6	1996.8	2276.4	2506.0	2625.8	2555.9	2416.1	2306.3	2296.3
67.5°	*24940.2*	*11811.1*	*1767.2*	*1747.2*	*1976.8*	*2236.4*	*2466.1*	*2416.1*	*2196.5*	*2056.7*	*2036.7*
70°	21705.3	8436.5	1487.6	1507.6	1727.2	1956.9	2206.5	2086.7	1907.0	1827.1	1817.1
72.5°	19269.2	7248.4	1248.0	1287.9	1447.7	1657.4	1807.1	1847.1	1717.3	1647.4	1617.4
75°	13887.8	5431.3	1008.4	1058.3	1168.1	1287.9	1567.5	1637.4	1517.6	1447.7	1397.8
77.5°	5151.8	2266.4	748.8	798.7	878.6	1048.3	1268.0	1417.7	1327.9	1377.8	1238.0
80°	1238.0	798.7	549.1	539.1	619.0	788.7	1008.4	1118.2	1028.4	978.4	848.6
82.5°	539.1	389.4	359.4	359.4	379.4	519.2	668.9	788.7	768.8	639.0	609.0
85°	199.7	169.7	169.7	179.7	179.7	239.6	359.4	419.3	379.4	329.5	319.5
87.5°	89.9	89.9	69.9	59.9	49.9	49.9	59.9	39.9	30.0	20.0	20.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)