Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360785

Luminaire Tested: **GSS-SB1C-750-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360785
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1C-750-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 52W 70CRI 5000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7072.6 lumens
Efficiency:	N/A
Efficacy:	136.0 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	52
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3536.3	0.0	3536.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3536.3	0.0	3536.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	7072.6	0.0	7072.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	1.9
10°-20°	411.1	5.8
20°-30°	687.1	9.7
30°-40°	947.6	13.4
40°-50°	1161.6	16.4
50°-60°	1361.2	19.2
60°-70°	1511.6	21.4
70°-80°	822.0	11.6
80°-90°	35.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7072.6	100.0
0°-180°	7072.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	616.5	8.7			
FM	(30°-60°)	1735.2	24.5			
FH	(60°-80°)	1166.8	16.5			G1/1800
FVH	(80°-90°)	17.8	0.3			G1/100
BL	(0°-30°)	616.5	8.7	B2/1000		
BM	(30°-60°)	1735.2	24.5	B2/2500		
BH	(60°-80°)	1166.8	16.5	B3/2500		G3/2500
BVH	(80°-90°)	17.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5	1393.5
2.5°	1395.0	1395.0	1390.4	1396.6	1393.5	1395.0	1396.6	1395.0	1393.5	1395.0	1396.6
5°	1402.8	1399.7	1402.8	1405.9	1401.2	1404.3	1402.8	1395.0	1399.7	1399.7	1399.7
7.5°	1416.7	1419.8	1416.7	1424.5	1419.8	1429.1	1419.8	1413.6	1412.1	1410.5	1410.5
10°	1422.9	1422.9	1421.4	1435.3	1438.4	1447.7	1441.5	1432.2	1427.6	1421.4	1415.2
12.5°	1405.9	1409.0	1416.7	1443.0	1455.4	1474.0	1469.4	1450.8	1436.8	1432.2	1422.9
15°	1387.3	1390.4	1405.9	1438.4	1467.8	1495.7	1494.1	1470.9	1453.9	1441.5	1427.6
17.5°	1357.9	1362.5	1384.2	1433.7	1486.4	1517.4	1526.6	1503.4	1484.8	1464.7	1446.1
20°	1308.3	1308.3	1347.0	1410.5	1483.3	1553.0	1577.7	1559.2	1537.5	1505.0	1480.2
22.5°	1252.6	1255.7	1294.4	1378.0	1481.7	1583.9	1631.9	1611.8	1590.1	1554.5	1517.4
25°	1196.9	1196.9	1240.2	1334.7	1461.6	1605.6	1695.4	1684.6	1641.2	1608.7	1560.7
27.5°	1145.8	1145.8	1192.2	1291.3	1427.6	1611.8	1758.9	1758.9	1710.9	1662.9	1610.3
30°	1085.4	1100.9	1153.5	1257.2	1396.6	1601.0	1805.3	1834.8	1791.4	1729.5	1652.1
32.5°	1034.3	1045.1	1099.3	1209.2	1351.7	1588.6	1858.0	1930.8	1885.9	1800.7	1714.0
35°	973.9	972.3	1034.3	1142.7	1288.2	1560.7	1899.8	2045.3	2002.0	1910.6	1793.0
37.5°	894.9	894.9	958.4	1063.7	1227.8	1512.7	1933.9	2172.3	2139.8	2036.0	1910.6
40°	809.8	819.1	874.8	981.6	1155.0	1455.4	1933.9	2276.0	2293.1	2186.2	2056.2
42.5°	747.8	750.9	802.0	902.7	1074.5	1381.1	1909.1	2365.8	2416.9	2327.1	2158.4
45°	682.8	690.6	733.9	826.8	990.9	1292.8	1865.7	2466.5	2548.5	2486.6	2265.2
47.5°	603.8	611.6	661.1	755.6	912.0	1196.9	1793.0	2571.8	2743.6	2698.7	2455.6
50°	512.5	518.7	565.1	665.8	823.7	1086.9	1701.6	2650.7	2938.7	2983.6	2743.6
52.5°	401.0	405.7	455.2	552.8	718.4	981.6	1573.1	2698.7	3135.4	3293.3	3129.2
55°	288.0	295.7	339.1	419.6	579.1	840.7	1419.8	2723.5	3350.6	3660.2	3607.6
57.5°	207.5	210.6	240.0	301.9	430.4	675.1	1223.2	2681.7	3544.1	4098.4	4208.3
60°	171.9	171.9	176.5	205.9	294.2	476.9	987.8	2526.9	3709.8	4541.2	4880.3
62.5°	157.9	157.9	161.0	165.7	193.5	309.7	706.0	2212.6	3728.4	4967.0	5617.3
65°	144.0	144.0	147.1	150.2	156.4	201.3	425.8	1619.5	3364.5	4971.7	6013.7
67.5°	131.6	131.6	133.2	134.7	137.8	147.1	233.8	981.6	2692.5	4840.1	6165.4
70°	119.2	119.2	119.2	117.7	122.3	123.9	154.8	498.6	1800.7	4370.9	6092.6
72.5°	*105.3*	*105.3*	*103.7*	*100.6*	*102.2*	*102.2*	*114.6*	*244.6*	*935.2*	*3474.4*	*5501.2*
75°	89.8	91.4	85.2	82.1	80.5	82.1	91.4	139.3	418.0	2107.3	4110.8
77.5°	75.9	79.0	69.7	63.5	61.9	61.9	71.2	86.7	179.6	764.9	1842.5
80°	57.3	58.8	51.1	44.9	44.9	43.4	52.6	63.5	85.2	227.6	413.4
82.5°	32.5	32.5	29.4	26.3	24.8	26.3	35.6	43.4	52.6	80.5	113.0
85°	7.7	7.7	9.3	10.8	10.8	13.9	20.1	23.2	27.9	32.5	43.4
87.5°	1.5	1.5	1.5	3.1	4.6	4.6	7.7	10.8	13.9	17.0	18.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360785
CATALOG NUMBER: GSS-SB1C-750-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1393.5	1393.5	*1393.5*
2.5°	1396.6	1398.1	*1396.6*
5°	1405.9	1402.8	*1398.1*
7.5°	1407.4	1409.0	*1410.5*
10°	1413.6	1419.8	*1410.5*
12.5°	1419.8	1415.2	*1412.1*
15°	1424.5	1422.9	*1413.6*
17.5°	1441.5	1435.3	*1433.7*
20°	1467.8	1466.3	*1461.6*
22.5°	1498.8	1495.7	*1494.1*
25°	1543.7	1532.8	*1526.6*
27.5°	1580.8	1571.5	*1568.4*
30°	1618.0	1599.4	*1599.4*
32.5°	1650.5	1645.9	*1642.8*
35°	1727.9	1704.7	*1707.8*
37.5°	1822.4	1799.1	*1779.0*
40°	1955.5	1924.6	*1912.2*
42.5°	2040.7	2009.7	*2012.8*
45°	2088.7	2034.5	*2020.6*
47.5°	2218.7	2150.6	*2132.0*
50°	2429.3	2345.7	*2322.5*
52.5°	2769.9	2635.2	*2604.3*
55°	3197.3	3031.6	*3000.6*
57.5°	3782.6	3562.7	*3496.1*
60°	4494.8	4222.3	*4121.6*
62.5°	5351.0	5015.0	*4919.0*
65°	5995.1	5714.9	*5566.2*
67.5°	6510.7	6280.0	*6208.8*
70°	6817.3	6828.1	*6846.7*
72.5°	*6462.7*	*6760.0*	*6902.4*
75°	4736.3	4967.0	*5188.4*
77.5°	1830.1	1650.5	*1597.9*
80°	295.7	277.1	*286.4*
82.5°	133.2	140.9	*148.6*
85°	86.7	100.6	*106.8*
87.5°	20.1	20.1	*20.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)