Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363879

Luminaire Tested: **GSS-SB1A-760-U-SL3-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363879
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1A-760-U-SL3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 31W 70CRI 5700K FIXTURE w/ TYPE III SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(26) 5700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Luminaire Equipment:

Sample No.	Condition	Description
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3070.9 lumens
Efficiency:	N/A
Efficacy:	99.1 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B0 - U0 - G1


Input Watts (W):	31
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.4%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 1.8 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	275.1	0.0	275.1
	% Fixture	9.0	0.0	9.0
Street Side	Lumens	2795.8	0.0	2795.8
	% Fixture	91.0	0.0	91.0
Total	Lumens	3070.9	0.0	3070.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.5
10°-20°	131.3	4.3
20°-30°	199.3	6.5
30°-40°	288.7	9.4
40°-50°	431.1	14.0
50°-60°	624.2	20.3
60°-70°	756.2	24.6
70°-80°	546.2	17.8
80°-90°	47.9	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3070.9	100.0
0°-180°	3070.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	291.4	9.5			
FM	(30°-60°)	1214.7	39.6			
FH	(60°-80°)	1245.9	40.6			G1/1800
FVH	(80°-90°)	43.7	1.4			G1/100
BL	(0°-30°)	85.0	2.8	B0/110		
BM	(30°-60°)	129.4	4.2	B0/220		
BH	(60°-80°)	56.5	1.8	B0/110		G0/110
BVH	(80°-90°)	4.2	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°	85°
0°	494	494	494	494	494	494	494	*494*	494	494	494
2.5°	594	596	589	585	577	564	551	*551*	536	522	504
5°	682	676	673	663	648	632	609	*603*	579	549	513
7.5°	749	742	739	730	713	692	661	*656*	621	577	525
10°	790	785	785	778	765	743	712	*705*	663	603	533
12.5°	772	770	782	798	804	791	758	*749*	701	632	543
15°	690	688	710	752	803	825	800	*792*	742	662	553
17.5°	611	608	629	671	747	829	844	*834*	783	692	564
20°	566	563	577	611	680	797	867	*869*	828	725	575
22.5°	550	549	556	579	628	742	876	*888*	877	763	591
25°	557	553	555	564	599	698	871	*894*	918	809	612
27.5°	575	572	569	569	587	666	858	*896*	960	859	630
30°	605	601	592	581	587	646	843	*891*	996	913	655
32.5°	673	670	644	609	601	641	826	*882*	1035	977	684
35°	740	737	719	669	625	645	815	*876*	1083	1055	718
37.5°	770	765	751	724	681	668	818	*883*	1152	1141	760
40°	808	800	779	754	735	721	842	*907*	1229	1240	806
42.5°	864	855	824	789	767	795	888	*950*	1324	1350	862
45°	941	929	889	843	816	832	950	*1011*	1430	1475	927
47.5°	1011	1008	963	910	878	857	1017	*1082*	1542	1615	994
50°	1077	1066	1022	970	943	908	1091	*1161*	1654	1743	1066
52.5°	1149	1137	1077	1018	991	983	1187	*1255*	1752	1878	1139
55°	1205	1188	1122	1073	1030	1057	1290	*1368*	1839	2000	1213
57.5°	1275	1253	1159	1123	1090	1132	1406	*1481*	1930	2103	1287
60°	1336	1319	1228	1183	1152	1217	1519	*1585*	2001	2191	1355
62.5°	1150	1148	1172	1307	1261	1346	1640	*1698*	2044	2250	1383
65°	816	822	889	1309	1473	1562	1799	*1837*	2046	2183	1328
67.5°	519	513	596	1096	1481	1988	2041	*2003*	1954	2111	1335
70°	311	313	341	795	1221	2085	2379	*2281*	2009	2164	1341
72.5°	169	173	213	390	809	1659	2737	*2751*	2197	2189	1318
73°	*154*	*155*	*191*	*326*	*700*	*1577*	*2720*	*2777*	*2235*	*2196*	*1303*
75°	102	102	130	185	307	1226	2258	*2510*	2364	2124	1186
77.5°	63	67	90	128	112	617	1328	*1536*	2108	1598	745
80°	23	25	56	84	65	234	557	*639*	977	811	269
82.5°	12	13	35	43	35	61	249	*266*	394	211	50
85°	6	7	15	18	14	20	62	*58*	89	28	14
87.5°	0	0	1	2	3	4	6	*6*	7	8	8
90°	0	0	0	0	0	0	0	*0*	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363879
CATALOG NUMBER: GSS-SB1A-760-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	494	494	494	494	494	494	494	494	494	494	494
2.5°	493	485	466	447	433	418	404	392	385	382	385
5°	494	477	438	399	361	330	301	280	265	260	258
7.5°	494	466	405	341	285	244	215	202	195	194	194
10°	493	453	368	284	220	192	183	181	181	181	182
12.5°	492	441	326	229	185	176	173	173	174	175	176
15°	490	423	282	191	172	169	167	167	168	170	170
17.5°	488	405	239	174	166	163	162	161	163	165	165
20°	484	382	203	165	160	158	157	156	157	159	160
22.5°	479	353	179	159	155	152	151	150	150	154	154
25°	474	321	165	153	149	146	144	143	144	147	147
27.5°	464	286	156	148	144	140	138	136	137	140	140
30°	449	249	151	143	138	133	130	128	129	132	133
32.5°	427	217	149	139	133	126	122	119	120	124	124
35°	404	194	148	135	127	120	113	109	111	115	116
37.5°	380	181	148	133	123	114	104	100	101	105	106
40°	359	175	149	131	118	107	96	91	93	98	97
42.5°	351	174	149	126	113	100	88	83	85	88	89
45°	360	178	147	121	106	92	82	77	78	80	82
47.5°	391	183	144	115	100	86	76	72	70	73	74
50°	434	186	139	109	95	80	71	66	64	65	66
52.5°	483	186	134	103	90	74	67	62	58	59	59
55°	532	184	121	98	85	70	63	56	53	53	52
57.5°	583	181	105	91	79	65	58	52	48	46	46
60°	633	177	96	84	72	61	53	48	43	40	39
62.5°	659	166	86	75	65	55	48	43	37	33	32
65°	645	143	74	67	59	49	43	38	31	26	26
67.5°	660	120	63	57	51	42	36	33	27	23	23
70°	665	94	53	49	44	35	31	29	24	20	19
72.5°	628	70	43	41	36	27	26	24	20	16	16
73°	*613*	*65*	*41*	*39*	*34*	*26*	*25*	*23*	*19*	*16*	*15*
75°	540	50	34	32	27	22	21	19	16	13	13
77.5°	358	36	26	24	20	17	16	14	12	10	10
80°	132	24	19	17	15	14	12	10	8	8	7
82.5°	27	16	14	12	11	10	8	7	6	6	6
85°	11	10	8	8	8	7	6	6	5	5	4
87.5°	7	6	6	5	5	4	4	4	4	4	4
90°	0	0	0	0	0	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ

Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-757-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571
CIE u':	0.2033
CIE v':	0.4806
Duv:	0.0041
CIE x:	0.3308
CIE y:	0.3476
CIE z:	0.3216
Peak Wavelength (nm):	442
Dominant Wavelength (nm):	544
Purity:	3.635698
Rf:	70.4
Rg:	97.1

CRI (Ra):	69.9
R1:	68.8
R2:	72.5
R3:	76.8
R4:	72.0
R5:	70.9
R6:	65.6
R7:	75.5
R8:	56.8
R9:	-35.4
R10:	36.7
R11:	73.9
R12:	47.8
R13:	68.0
R14:	87.0
R15:	59.8



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5571K
CIE x = 0.3308
CIE y = 0.3476
Duv = 0.0041

Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.84**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-7

TM-30-18


Summary


R_f = 70.4
R_g = 97.1
CIE R_a = 69.9
R_9 = -35.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-7

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-7

TM-30-18

Measure Comparisons





(END OF REPORT)