Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1366183

Luminaire Tested: **GSS-SB1A-760-U-T2R-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1366183
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1A-760-U-T2R-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 31W 70CRI 5700K FIXTURE w/ TYPE II ROADWAY DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(26) 5700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Luminaire Equipment:

Sample No.	Condition	Description
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3631.7 lumens
Efficiency:	N/A
Efficacy:	117.2 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type II - Short
BUG Rating:	B0 - U0 - G1


Input Watts (W):	31
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.4%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.6 fc
Type II - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	261.7	0.0	261.7
	% Fixture	7.2	0.0	7.2
Street Side	Lumens	3370.0	0.0	3370.0
	% Fixture	92.8	0.0	92.8
Total	Lumens	3631.7	0.0	3631.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	1.2
10°-20°	151.5	4.2
20°-30°	295.5	8.1
30°-40°	519.0	14.3
40°-50°	759.3	20.9
50°-60°	881.1	24.3
60°-70°	694.4	19.1
70°-80°	276.0	7.6
80°-90°	12.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3631.7	100.0
0°-180°	3631.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	429.5	11.8			
FM	(30°-60°)	2017.5	55.6			
FH	(60°-80°)	912.2	25.1			G1/1800
FVH	(80°-90°)	10.9	0.3			G1/100
BL	(0°-30°)	59.9	1.7	B0/110		
BM	(30°-60°)	142.0	3.9	B0/220		
BH	(60°-80°)	58.2	1.6	B0/110		G0/110
BVH	(80°-90°)	1.6	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1
Type II Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	76°	85°
0°	406	406	406	406	406	406	406	406	406	*406*	406
2.5°	582	579	579	568	552	535	511	484	457	*456*	426
5°	722	718	713	700	679	651	619	572	516	*514*	455
7.5°	813	814	807	801	787	757	716	658	585	*576*	493
10°	895	890	889	888	878	849	810	742	653	*644*	535
12.5°	946	944	951	957	955	943	898	830	725	*714*	577
15°	962	964	981	1000	1016	1020	982	912	793	*786*	625
17.5°	950	953	977	1011	1050	1080	1063	989	866	*853*	668
20°	955	958	980	1012	1063	1114	1129	1071	931	*917*	718
22.5°	1039	1043	1048	1048	1083	1138	1172	1148	1005	*991*	773
25°	1223	1220	1193	1149	1150	1174	1211	1212	1080	*1063*	823
27.5°	1406	1414	1379	1314	1263	1240	1256	1269	1152	*1135*	879
30°	1575	1570	1533	1466	1402	1349	1315	1322	1229	*1216*	935
32.5°	1708	1710	1668	1594	1524	1478	1408	1379	1304	*1294*	995
35°	1820	1814	1763	1691	1626	1596	1522	1441	1390	*1377*	1058
37.5°	1927	1923	1860	1764	1705	1691	1649	1523	1479	*1469*	1138
40°	1999	1995	1941	1847	1776	1764	1762	1625	1575	*1568*	1220
42.5°	2016	2011	1973	1903	1840	1827	1870	1736	1695	*1683*	1316
45°	1982	1987	1961	1919	1889	1874	1959	1857	1818	*1811*	1419
47.5°	1884	1886	1884	1897	1903	1930	2041	1988	1961	*1962*	1551
50°	1706	1703	1734	1806	1877	1970	2147	2159	2185	*2179*	1748
52.5°	1358	1363	1497	1629	1802	1966	2227	2373	2479	*2479*	1961
55°	1095	1099	1187	1410	1650	1923	2271	2483	2673	*2672*	2113
57.5°	895	902	972	1148	1423	1799	2289	2569	2840	*2858*	2269
60°	501	540	679	910	1172	1606	2261	2642	3022	*3043*	2428
62.5°	227	232	295	562	913	1360	2131	2624	3186	*3202*	2480
63°	*206*	*214*	*256*	*514*	*861*	*1305*	*2098*	*2611*	*3183*	*3214*	*2476*
65°	162	167	178	332	577	1071	1876	2397	3141	*3178*	2388
67.5°	133	133	142	207	319	737	1391	2093	3097	*3140*	2276
70°	113	113	119	146	190	356	1001	1791	2835	*2870*	1981
72.5°	82	86	95	114	131	201	514	1375	2426	*2457*	1662
75°	67	69	77	87	90	121	181	1024	1909	*1921*	1153
77.5°	35	38	63	71	69	74	88	558	928	*865*	374
80°	15	15	45	46	49	35	42	128	266	*248*	76
82.5°	4	5	36	32	33	16	18	41	68	*64*	22
85°	2	3	9	8	10	6	8	16	12	*12*	9
87.5°	0	0	1	1	1	2	3	5	6	*6*	6
90°	0	0	0	0	0	0	0	0	0	*0*	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366183
CATALOG NUMBER: GSS-SB1A-760-U-T2R-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	406	406	406	406	406	406	406	406	406	406	406
2.5°	410	393	362	334	306	280	259	249	235	237	235
5°	421	387	322	264	221	187	165	153	143	141	143
7.5°	438	385	288	211	162	140	131	127	124	123	124
10°	460	386	257	171	137	127	121	117	114	114	113
12.5°	484	387	226	145	125	118	112	108	105	104	104
15°	507	387	200	130	117	110	105	100	97	95	96
17.5°	530	385	175	121	110	103	97	92	89	87	87
20°	556	383	153	113	103	96	89	85	82	80	80
22.5°	583	379	136	105	95	88	82	77	74	72	72
25°	609	375	121	98	89	81	75	70	66	65	65
27.5°	637	370	110	91	82	75	68	63	60	59	59
30°	671	373	106	84	76	69	63	58	55	55	55
32.5°	703	375	111	81	70	63	57	53	51	51	51
35°	739	379	116	84	66	58	53	50	47	47	47
37.5°	781	380	120	88	65	54	51	47	45	45	45
40°	853	396	120	91	65	50	46	43	41	41	41
42.5°	942	446	118	92	66	49	43	41	39	39	39
45°	1036	504	131	87	66	49	40	40	37	37	37
47.5°	1146	562	144	79	67	49	39	36	35	35	35
50°	1289	600	148	70	65	49	37	35	33	34	34
52.5°	1400	599	143	61	61	48	35	34	33	33	33
55°	1492	583	117	52	54	41	34	34	32	32	32
57.5°	1564	533	84	44	45	34	33	33	32	31	31
60°	1597	452	58	38	37	31	31	31	30	29	29
62.5°	1538	370	42	33	30	28	29	29	27	25	24
63°	*1505*	*353*	*40*	*32*	*29*	*28*	*29*	*29*	*27*	*24*	*23*
65°	1396	285	35	29	26	25	27	26	23	18	18
67.5°	1249	189	30	26	23	22	23	23	20	16	15
70°	1065	119	25	21	19	17	18	20	17	13	12
72.5°	874	83	20	17	15	12	15	17	14	10	10
75°	589	53	16	13	11	10	12	13	11	7	7
77.5°	186	27	13	10	8	7	8	9	6	4	4
80°	41	16	9	7	6	5	5	3	2	2	1
82.5°	15	10	7	5	4	3	2	2	1	0	0
85°	8	6	4	3	3	2	2	1	0	0	0
87.5°	5	4	3	3	2	2	1	1	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ

Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-757-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571
CIE u':	0.2033
CIE v':	0.4806
Duv:	0.0041
CIE x:	0.3308
CIE y:	0.3476
CIE z:	0.3216
Peak Wavelength (nm):	442
Dominant Wavelength (nm):	544
Purity:	3.635698
Rf:	70.4
Rg:	97.1

CRI (Ra):	69.9
R1:	68.8
R2:	72.5
R3:	76.8
R4:	72.0
R5:	70.9
R6:	65.6
R7:	75.5
R8:	56.8
R9:	-35.4
R10:	36.7
R11:	73.9
R12:	47.8
R13:	68.0
R14:	87.0
R15:	59.8



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5571K
CIE x = 0.3308
CIE y = 0.3476
Duv = 0.0041

Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.84**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-7

TM-30-18


Summary


R_f = 70.4
R_g = 97.1
CIE R_a = 69.9
R_9 = -35.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-7

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-7

TM-30-18

Measure Comparisons





(END OF REPORT)