Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1501628

Luminaire Tested: GSS-SB4D-927-U-T2LG

Issue Date: 07/20/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1501628
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	7/20/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4D-927-U-T2LG
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 238W 90CRI 2700K FIXTURE w/ TYPE II LOW GLARE DISTRIBUTION FIXTURE
Light Source:	(104) 2700K CCT, 90 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	19414 lumens
Efficiency:	N/A
Efficacy:	81.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	238
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	--
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

Iso-Footcandle Lines of Horizontal Illumination




Based on 25 foot mounting height. Maximum calculated value = 7.5 fc
Type II - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5220.7	0.0	5220.7
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	14193.4	0.0	14193.4
	% Fixture	73.1	0.0	73.1
Total	Lumens	19414.0	0.0	19414.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.7	1.5
10°-20°	844.3	4.3
20°-30°	1599.2	8.2
30°-40°	2819.3	14.5
40°-50°	4169.5	21.5
50°-60°	4896.1	25.2
60°-70°	3547.4	18.3
70°-80°	1094.0	5.6
80°-90°	150.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19414.0	100.0
0°-180°	19414.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1587.4	8.2			
FM	(30°-60°)	9010.2	46.4			
FH	(60°-80°)	3514.5	18.1			G2/5000
FVH	(80°-90°)	81.2	0.4			G1/100
BL	(0°-30°)	1149.8	5.9	B3/2500		
BM	(30°-60°)	2874.7	14.8	B3/5000		
BH	(60°-80°)	1126.9	5.8	B3/2500		G3/2500
BVH	(80°-90°)	69.4	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type II Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	67°	75°	85°
0°	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6
2.5°	3185.6	3194.4	3181.1	3190.0	3190.0	3176.7	3172.3	3154.6	3163.4	3159.0	3154.6
5°	3260.8	3265.2	3256.4	3269.6	3269.6	3274.1	3269.6	3247.5	3247.5	3247.5	3238.7
7.5°	3238.7	3238.7	3243.1	3287.3	3331.6	3389.1	3389.1	3380.2	3389.1	3384.7	3344.9
10°	3052.8	3070.5	3110.4	3221.0	3327.2	3451.0	3535.1	3561.6	3561.6	3566.1	3499.7
12.5°	2721.0	2734.3	2827.2	2995.3	3216.5	3442.2	3645.7	3778.4	3791.7	3813.8	3725.3
15°	2424.6	2433.4	2499.8	2672.3	2924.5	3322.7	3707.7	3982.0	4026.2	4119.1	3986.4
17.5°	2451.1	2446.7	2464.4	2530.8	2712.2	3128.1	3694.4	4220.9	4300.5	4464.2	4349.2
20°	2610.4	2610.4	2623.7	2636.9	2703.3	2986.5	3597.0	4415.6	4570.4	4889.0	4756.2
22.5°	2862.6	2862.6	2858.2	2880.3	2880.3	3048.4	3601.5	4561.6	4791.6	5362.4	5234.1
25°	3212.1	3194.4	3194.4	3203.3	3163.4	3282.9	3712.1	4712.0	5012.9	5924.3	5813.7
27.5°	3605.9	3619.2	3610.3	3579.3	3526.3	3619.2	3977.5	4946.5	5260.6	6517.1	6472.9
30°	4035.1	4039.5	4048.3	4030.6	3986.4	4052.8	4393.4	5300.4	5588.0	7136.6	7233.9
32.5°	4455.4	4517.3	4495.2	4451.0	4468.6	4588.1	4906.7	5778.3	6074.7	7711.7	8056.8
35°	4990.7	5012.9	5101.3	4937.6	4942.1	5145.6	5561.5	6406.5	6694.1	8309.0	8879.8
37.5°	5769.4	5809.2	5769.4	5512.8	5473.0	5756.2	6198.6	7026.0	7233.9	8760.3	9645.2
40°	6534.8	6583.5	6649.9	6349.0	6096.8	6331.3	6800.3	7499.4	7716.2	9008.1	10154.0
42.5°	7167.5	7247.2	7176.4	7087.9	6857.8	6902.1	7220.6	7866.6	8083.4	9322.2	10667.2
45°	7702.9	7716.2	7747.1	7685.2	7570.2	7530.3	7579.0	8189.6	8428.5	9463.8	10919.4
47.5°	7924.1	7981.6	8008.2	8114.4	8233.8	8154.2	7884.3	8340.0	8556.8	9455.0	10999.1
50°	7804.7	7862.2	8003.7	8255.9	8543.5	8685.1	8242.7	8548.0	8791.3	9614.2	11162.8
52.5°	7490.5	7552.5	7782.5	8070.1	8552.4	8875.4	8747.0	8981.5	9216.0	9897.4	11437.1
55°	6729.5	6822.4	7145.4	7623.2	8286.9	8773.6	9278.0	9618.7	9875.3	10238.1	11720.2
57.5°	5623.4	5720.8	6083.6	6800.3	7795.8	8353.3	9432.8	10813.2	10928.3	10645.1	11746.8
60°	*4212.0*	*4291.7*	*4804.9*	*5380.1*	*6548.1*	*7583.4*	*9344.3*	*11945.9*	*12237.9*	*10574.3*	*10901.7*
62.5°	3336.0	3433.3	3889.1	4154.5	4990.7	6265.0	9034.6	12260.0	12512.2	9990.3	9724.8
65°	2606.0	2672.3	3097.1	3477.6	3681.1	4278.4	7742.7	10724.8	10950.4	9039.1	8025.9
67.5°	1721.1	1822.9	2327.2	2849.3	2955.5	2721.0	5327.0	8251.5	8357.7	7185.2	6034.9
70°	1234.4	1283.1	1659.2	2216.6	2375.9	1822.9	2902.4	6247.3	6278.2	4822.6	4066.0
72.5°	840.6	849.5	1128.2	1699.0	1893.6	1322.9	1597.2	4114.7	4008.5	2380.3	2327.2
75°	570.7	579.6	721.2	1132.6	1340.6	920.3	1039.7	2243.2	2154.7	1314.0	1411.4
77.5°	384.9	393.8	495.5	761.0	893.7	637.1	761.0	1185.7	1163.6	871.6	756.6
80°	292.0	305.3	367.2	486.7	623.8	371.7	433.6	561.9	570.7	464.6	384.9
82.5°	163.7	181.4	221.2	247.8	402.6	207.9	207.9	336.3	323.0	287.6	207.9
85°	70.8	75.2	88.5	92.9	163.7	88.5	75.2	146.0	150.4	141.6	66.4
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	17.7	17.7	17.7	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6
2.5°	3132.5	3159.0	3132.5	3119.2	3119.2	3097.1	3088.2	3088.2	3057.3	3070.5	3061.7
5°	3203.3	3212.1	3181.1	3141.3	3088.2	3044.0	2982.0	2902.4	2853.7	2849.3	2853.7
7.5°	3313.9	3318.3	3234.2	3145.8	3013.0	2853.7	2663.5	2508.6	2371.5	2349.4	2375.9
10°	3468.7	3459.9	3336.0	3128.1	2849.3	2513.1	2221.1	2079.5	1999.8	1995.4	1991.0
12.5°	3676.7	3619.2	3428.9	3052.8	2566.2	2176.8	2026.4	2017.5	2039.7	2057.3	2061.8
15°	3915.6	3840.4	3504.1	2906.8	2278.6	2052.9	2061.8	2137.0	2163.5	2181.2	2181.2
17.5°	4212.0	4114.7	3588.2	2698.9	2132.6	2079.5	2141.4	2212.2	2256.4	2274.1	2269.7
20°	4605.8	4402.3	3654.6	2499.8	2092.7	2123.7	2176.8	2247.6	2291.8	2314.0	2314.0
22.5°	4999.6	4747.4	3667.8	2362.6	2092.7	2128.1	2176.8	2247.6	2296.3	2318.4	2314.0
25°	5534.9	5189.8	3672.3	2265.3	2097.2	2106.0	2150.3	2212.2	2283.0	2305.1	2314.0
27.5°	6105.7	5676.5	3694.4	2243.2	2079.5	2075.0	2106.0	2163.5	2234.3	2291.8	2296.3
30°	6813.6	6225.1	3703.2	2265.3	2083.9	2026.4	2048.5	2106.0	2181.2	2238.7	2256.4
32.5°	7508.2	6733.9	3685.5	2314.0	2092.7	1995.4	1999.8	2035.2	2114.9	2154.7	2185.7
35°	8242.7	7273.7	3654.6	2380.3	2097.2	1982.1	1942.3	1960.0	2013.1	2017.5	2030.8
37.5°	8817.8	7676.3	3561.6	2468.8	2106.0	1933.5	1853.8	1840.6	1818.4	1774.2	1783.0
40°	9291.3	7946.2	3406.8	2513.1	2083.9	1875.9	1743.2	1681.3	1597.2	1530.8	1544.1
42.5°	9631.9	8127.6	3221.0	2521.9	2048.5	1778.6	1614.9	1508.7	1415.8	1345.0	1349.4
45°	9782.4	8109.9	3021.9	2455.5	1964.4	1659.2	1495.4	1393.7	1291.9	1216.7	1207.9
47.5°	9786.8	7937.4	2747.6	2296.3	1822.9	1522.0	1384.8	1274.2	1190.2	1137.1	1132.6
50°	9822.2	7840.0	2490.9	2066.2	1637.0	1376.0	1287.5	1176.9	1128.2	1053.0	1030.9
52.5°	10043.4	7999.3	2314.0	1814.0	1464.5	1269.8	1203.4	1106.1	1026.5	977.8	973.4
55°	10401.8	8273.6	2216.6	1623.8	1300.8	1168.0	1123.8	1039.7	968.9	920.3	907.0
57.5°	10446.0	8415.2	2101.6	1446.8	1168.0	1088.4	1070.7	977.8	876.0	840.6	827.4
60°	*9826.6*	*8176.3*	*1960.0*	*1283.1*	*1070.7*	*1026.5*	*1017.6*	*893.7*	*809.7*	*765.4*	*747.7*
62.5°	8981.5	7579.0	1743.2	1132.6	995.5	964.5	929.1	831.8	725.6	676.9	663.7
65°	7340.1	6371.1	1482.2	1030.9	920.3	884.9	876.0	743.3	672.5	646.0	641.5
67.5°	5561.5	5119.0	1305.2	955.7	840.6	827.4	796.4	752.1	721.2	690.2	681.4
70°	3933.3	3694.4	1110.5	858.3	761.0	738.9	867.2	818.5	707.9	668.1	663.7
72.5°	2384.8	2318.4	960.1	769.8	654.8	690.2	800.8	738.9	637.1	588.4	570.7
75°	1504.3	1376.0	805.2	654.8	522.1	561.9	699.1	659.2	548.6	500.0	486.7
77.5°	818.5	761.0	606.1	535.4	411.5	455.7	610.6	544.2	438.0	477.8	424.7
80°	358.4	398.2	402.6	309.7	274.3	336.3	438.0	424.7	336.3	340.7	283.2
82.5°	172.6	225.6	261.0	212.4	154.9	199.1	292.0	243.3	225.6	212.4	203.5
85°	53.1	84.1	115.0	101.8	70.8	84.1	137.2	132.7	159.3	137.2	128.3
87.5°	17.7	17.7	13.3	13.3	13.3	17.7	22.1	13.3	4.4	4.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6
2.5°	3057.3	3061.7	3061.7	3066.1	3066.1	3079.4	3097.1	3114.8	3101.5	3119.2	3123.6
5°	2844.9	2867.0	2884.7	2951.1	3004.2	3048.4	3097.1	3141.3	3154.6	3163.4	3185.6
7.5°	2344.9	2406.9	2521.9	2672.3	2840.5	3004.2	3114.8	3229.8	3247.5	3269.6	3300.6
10°	1995.4	2022.0	2101.6	2256.4	2557.3	2880.3	3150.2	3331.6	3406.8	3451.0	3482.0
12.5°	2052.9	2035.2	2022.0	2044.1	2238.7	2654.6	3128.1	3477.6	3619.2	3667.8	3707.7
15°	2190.1	2172.4	2123.7	2061.8	2083.9	2415.7	3052.8	3614.7	3840.4	3920.0	4004.1
17.5°	2269.7	2252.0	2212.2	2145.8	2088.3	2216.6	2911.3	3738.6	4189.9	4287.2	4406.7
20°	2314.0	2296.3	2256.4	2190.1	2123.7	2141.4	2729.9	3893.5	4588.1	4743.0	4919.9
22.5°	2322.8	2300.7	2256.4	2190.1	2150.3	2137.0	2557.3	3986.4	5017.3	5256.2	5459.7
25°	2318.4	2278.6	2221.1	2172.4	2150.3	2145.8	2437.8	4039.5	5481.8	5862.3	6092.4
27.5°	2287.4	2238.7	2181.2	2145.8	2137.0	2163.5	2384.8	4101.4	6026.0	6512.7	6879.9
30°	2252.0	2181.2	2110.4	2097.2	2119.3	2203.4	2429.0	4123.5	6596.8	7220.6	7596.7
32.5°	2159.1	2106.0	2035.2	2030.8	2083.9	2234.3	2530.8	4092.6	7101.2	7928.5	8401.9
35°	2026.4	1995.4	1955.6	1968.9	2052.9	2260.9	2601.6	3995.2	7561.3	8587.8	9140.8
37.5°	1791.9	1814.0	1836.1	1867.1	1973.3	2256.4	2632.5	3840.4	7941.8	9114.3	9822.2
40°	1530.8	1606.1	1676.8	1756.5	1898.1	2221.1	2641.4	3650.1	8163.0	9512.5	10428.3
42.5°	1367.1	1437.9	1526.4	1641.5	1796.3	2141.4	2632.5	3437.8	8233.8	9786.8	10813.2
45°	1216.7	1300.8	1411.4	1530.8	1707.8	2026.4	2552.9	3207.7	8269.2	9915.1	10976.9
47.5°	1137.1	1185.7	1287.5	1407.0	1592.8	1884.8	2398.0	3039.6	8216.1	9941.6	11176.0
50°	1044.2	1110.5	1176.9	1291.9	1473.3	1707.8	2212.2	2942.2	8304.6	10202.7	11490.2
52.5°	973.4	1008.8	1079.6	1185.7	1318.5	1544.1	2035.2	2862.6	8548.0	10468.1	11817.6
55°	920.3	960.1	1004.3	1092.8	1194.6	1380.4	1853.8	2743.1	8831.1	10751.3	12145.0
57.5°	836.2	862.8	924.7	1017.6	1084.0	1221.1	1641.5	2601.6	8809.0	10530.1	11578.7
60°	*761.0*	*787.5*	*853.9*	*946.8*	*986.6*	*1079.6*	*1433.5*	*2420.1*	*8384.2*	*9808.9*	*10534.5*
62.5°	676.9	707.9	787.5	853.9	889.3	960.1	1216.7	2088.3	7499.4	8724.9	9313.4
65°	641.5	659.2	712.3	792.0	787.5	853.9	1026.5	1641.5	6034.9	6667.6	7202.9
67.5°	681.4	707.9	699.1	721.2	707.9	743.3	920.3	1318.5	4743.0	5021.7	5331.4
70°	672.5	734.5	765.4	721.2	619.4	659.2	796.4	1053.0	3393.5	3367.0	3353.7
72.5°	588.4	650.4	738.9	783.1	606.1	548.6	690.2	911.4	2176.8	2168.0	1960.0
75°	500.0	544.2	650.4	707.9	522.1	442.4	592.9	774.3	1300.8	1318.5	1176.9
77.5°	460.1	438.0	544.2	623.8	424.7	340.7	477.8	584.0	716.8	725.6	672.5
80°	331.8	318.6	407.0	455.7	323.0	243.3	269.9	362.8	384.9	345.1	358.4
82.5°	212.4	216.8	243.3	292.0	199.1	132.7	185.8	243.3	207.9	168.1	199.1
85°	137.2	154.9	128.3	150.4	61.9	61.9	79.6	106.2	70.8	48.7	53.1
87.5°	0.0	0.0	8.8	17.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501628
CATALOG NUMBER: GSS-SB4D-927-U-T2LG

CANDELA DISTRIBUTION (continued):

	285°	293°	295°	305°	315°	325°	335°	345°	355°	360°
0°	3123.6	3123.6	*3123.6*	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6	3123.6
2.5°	3136.9	3132.5	*3132.5*	3141.3	3163.4	3172.3	3185.6	3181.1	3194.4	3185.6
5°	3198.8	3203.3	*3216.5*	3221.0	3234.2	3251.9	3256.4	3251.9	3260.8	3260.8
7.5°	3322.7	3340.4	*3331.6*	3353.7	3336.0	3313.9	3278.5	3251.9	3229.8	3238.7
10°	3530.7	3521.8	*3517.4*	3477.6	3397.9	3282.9	3190.0	3088.2	3070.5	3052.8
12.5°	3760.7	3751.9	*3751.9*	3614.7	3389.1	3150.2	2937.8	2778.5	2725.4	2721.0
15°	4083.7	4026.2	*3973.1*	3685.5	3234.2	2827.2	2579.4	2455.5	2424.6	2424.6
17.5°	4486.3	4335.9	*4247.4*	3632.4	2982.0	2614.8	2468.8	2437.8	2429.0	2451.1
20°	4986.3	4605.8	*4477.5*	3513.0	2889.1	2641.4	2570.6	2575.0	2579.4	2610.4
22.5°	5534.9	4853.6	*4641.2*	3513.0	2982.0	2809.5	2774.1	2822.8	2836.0	2862.6
25°	6145.5	5074.8	*4787.2*	3698.8	3256.4	3128.1	3083.8	3132.5	3167.9	3212.1
27.5°	6831.3	5304.9	*5039.4*	4035.1	3610.3	3530.7	3482.0	3504.1	3552.8	3605.9
30°	7446.3	5689.8	*5424.3*	4548.3	4092.6	3995.2	3911.2	3946.6	3999.7	4035.1
32.5°	7990.5	6158.8	*5933.1*	5088.1	4645.6	4477.5	4384.6	4375.7	4481.9	4455.4
35°	8490.4	6711.8	*6495.0*	5703.1	5207.5	4999.6	4875.7	5035.0	4964.2	4990.7
37.5°	8884.2	7287.0	*7114.4*	6291.5	5791.5	5508.4	5433.2	5627.8	5738.5	5769.4
40°	9207.2	7787.0	*7605.6*	6875.5	6326.9	6119.0	6238.4	6561.4	6548.1	6534.8
42.5°	9455.0	8216.1	*8017.0*	7318.0	6840.1	6879.9	6972.9	7189.7	7242.8	7167.5
45°	9565.6	8486.0	*8326.7*	7667.5	7424.2	7654.2	7694.0	7787.0	7751.6	7702.9
47.5°	9693.9	8724.9	*8556.8*	7986.1	8056.8	8282.5	8202.8	8127.6	7999.3	7924.1
50°	9910.7	9008.1	*8866.5*	8450.6	8707.2	8632.0	8322.3	8154.2	7893.1	7804.7
52.5°	10322.1	9543.4	*9437.3*	9185.1	9012.5	8578.9	8202.8	7902.0	7610.0	7490.5
55°	10689.4	10269.0	*10207.1*	9870.8	8919.6	8300.2	7795.8	7331.2	6831.3	6729.5
57.5°	10901.7	11472.5	*11543.3*	10162.9	8494.9	7667.5	6924.2	6180.9	5707.5	5623.4
60°	*10269.0*	*12773.3*	*12808.7*	*10105.3*	*7729.4*	*6526.0*	*5393.3*	*4866.8*	*4358.0*	*4212.0*
62.5°	9397.4	12503.4	*12472.4*	9760.2	6154.3	4760.7	4097.0	3849.2	3455.5	3336.0
65°	8079.0	10415.0	*10450.4*	8432.9	4092.6	3442.2	3442.2	3128.1	2690.0	2606.0
67.5°	6583.5	8030.3	*7950.7*	5468.6	2513.1	2756.4	2889.1	2437.8	1822.9	1721.1
70°	4278.4	6132.2	*6021.6*	3154.6	1579.5	2296.3	2274.1	1831.7	1305.2	1234.4
72.5°	1840.6	3543.9	*3769.6*	1610.5	1190.2	1849.4	1814.0	1283.1	871.6	840.6
75°	1110.5	1783.0	*1942.3*	1026.5	867.2	1393.7	1256.5	814.1	592.9	570.7
77.5°	703.5	977.8	*968.9*	769.8	650.4	942.4	845.1	561.9	402.6	384.9
80°	407.0	482.3	*500.0*	482.3	438.0	672.5	539.8	407.0	314.1	292.0
82.5°	261.0	300.9	*305.3*	234.5	243.3	433.6	292.0	238.9	181.4	163.7
85°	115.0	128.3	*123.9*	79.6	79.6	177.0	101.8	97.3	70.8	70.8
87.5°	4.4	8.8	*4.4*	4.4	4.4	17.7	8.8	13.3	13.3	13.3
90°	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2106-271-1

Luminaire Tested: GFLD-SA1-A-927-U-WR-X-BK

Test Date: 06/16/2021

Report Generated By FNC07603 / LDUCLS01DT446
Version: v6.09

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Test Information


Test Method:	LM-79-08
Report Number:	SP1-2106-271-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1
Measurement Geometry:	4π
Issue Date:	06/16/2021
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	**GFLD-SA1-A-927-U-WR-X-BK**
Description:	MCGRAW EDISON

N6, BLACK

Spectral Parameters

CCT (K):	2747	CRI (Ra):	92.5		
CIE u':	0.2598	R1:	92.3	R9:	58.3
CIE v':	0.5293	R2:	95.5	R10:	88.5
Duv:	0.0020	R3:	97.5	R11:	93.7
CIE x:	0.4594	R4:	93.1	R12:	84.9
CIE y:	0.4160	R5:	91.8	R13:	93.0
CIE z:	0.1246	R6:	95.1	R14:	97.8
Peak Wavelength (nm):	624	R7:	92.9		
Dominant Wavelength (nm):	583	R8:	81.7		
Purity:	63				

Rf:	93.1
Rg:	98.2



Test Conditions

Stabilization Time:	198M
Operation Time:	12H
Room Temperature (°C) / RH%:	24.3/43%
Sphere Temperature (°C):	24.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	1/31/2021	7/31/2021
Power Meter	XITRON 2801 IN0071	12/1/2020	12/1/2021
AC Power Source	CHROMA 61603 IN0063	12/1/2020	12/1/2021
DC Power Source	AGILENT E3634A IN0208	12/1/2020	12/1/2021
Sphere Thermometer	ONSET IN0085	12/1/2020	12/1/2021
Room Thermometer	ONSET IN0046	12/1/2020	12/1/2021


Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2747K
CIE x = 0.4594
CIE y = 0.4160
Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

Photopic Flux vs. Wavelength




######

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	649	NR	490	9819	NR	620	37806	NR	750	3792	NR	880	778	NR
365	535	NR	495	10995	NR	625	38173	NR	755	3383	NR	885	829	NR
370	546	NR	500	12186	NR	630	37677	NR	760	3071	NR	890	745	NR
375	624	NR	505	13274	NR	635	36852	NR	765	2656	NR	895	648	NR
380	611	NR	510	14396	NR	640	35711	NR	770	2297	NR	900	661	NR
385	569	NR	515	15467	NR	645	34820	NR	775	2076	NR	905	740	NR
390	512	NR	520	16543	NR	650	33278	NR	780	1860	NR	910	635	NR
395	465	NR	525	17716	NR	655	31397	NR	785	1717	NR	915	683	NR
400	418	NR	530	18837	NR	660	29663	NR	790	1494	NR	920	620	NR
405	411	NR	535	19916	NR	665	27479	NR	795	1276	NR	925	580	NR
410	439	NR	540	20679	NR	670	25115	NR	800	1183	NR	930	717	NR
415	565	NR	545	21563	NR	675	22916	NR	805	1161	NR	935	780	NR
420	866	NR	550	22521	NR	680	20799	NR	810	1065	NR	940	630	NR
425	1393	NR	555	23411	NR	685	18810	NR	815	970	NR	945	433	NR
430	2399	NR	560	24238	NR	690	16831	NR	820	1013	NR	950	676	NR
435	4305	NR	565	25148	NR	695	14867	NR	825	970	NR	955	802	NR
440	7544	NR	570	26216	NR	700	13210	NR	830	769	NR	960	645	NR
445	11003	NR	575	27219	NR	705	11593	NR	835	894	NR	965	620	NR
450	11015	NR	580	28466	NR	710	10403	NR	840	893	NR	970	474	NR
455	8956	NR	585	29834	NR	715	9162	NR	845	864	NR	975	478	NR
460	8133	NR	590	31413	NR	720	8146	NR	850	828	NR	980	905	NR
465	7252	NR	595	32655	NR	725	7155	NR	855	921	NR	985	639	NR
470	6556	NR	600	34084	NR	730	6272	NR	860	633	NR	990	838	NR
475	6915	NR	605	35555	NR	735	5418	NR	865	816	NR	995	621	NR
480	7734	NR	610	36593	NR	740	4870	NR	870	767	NR	1000	903	NR
485	8748	NR	615	37350	NR	745	4295	NR	875	601	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: 2290.1 **S/P: 1.28**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	649	NR	490	9819	NR	620	37806	NR	750	3792	NR	880	778	NR
365	535	NR	495	10995	NR	625	38173	NR	755	3383	NR	885	829	NR
370	546	NR	500	12186	NR	630	37677	NR	760	3071	NR	890	745	NR
375	624	NR	505	13274	NR	635	36852	NR	765	2656	NR	895	648	NR
380	611	NR	510	14396	NR	640	35711	NR	770	2297	NR	900	661	NR
385	569	NR	515	15467	NR	645	34820	NR	775	2076	NR	905	740	NR
390	512	NR	520	16543	NR	650	33278	NR	780	1860	NR	910	635	NR
395	465	NR	525	17716	NR	655	31397	NR	785	1717	NR	915	683	NR
400	418	NR	530	18837	NR	660	29663	NR	790	1494	NR	920	620	NR
405	411	NR	535	19916	NR	665	27479	NR	795	1276	NR	925	580	NR
410	439	NR	540	20679	NR	670	25115	NR	800	1183	NR	930	717	NR
415	565	NR	545	21563	NR	675	22916	NR	805	1161	NR	935	780	NR
420	866	NR	550	22521	NR	680	20799	NR	810	1065	NR	940	630	NR
425	1393	NR	555	23411	NR	685	18810	NR	815	970	NR	945	433	NR
430	2399	NR	560	24238	NR	690	16831	NR	820	1013	NR	950	676	NR
435	4305	NR	565	25148	NR	695	14867	NR	825	970	NR	955	802	NR
440	7544	NR	570	26216	NR	700	13210	NR	830	769	NR	960	645	NR
445	11003	NR	575	27219	NR	705	11593	NR	835	894	NR	965	620	NR
450	11015	NR	580	28466	NR	710	10403	NR	840	893	NR	970	474	NR
455	8956	NR	585	29834	NR	715	9162	NR	845	864	NR	975	478	NR
460	8133	NR	590	31413	NR	720	8146	NR	850	828	NR	980	905	NR
465	7252	NR	595	32655	NR	725	7155	NR	855	921	NR	985	639	NR
470	6556	NR	600	34084	NR	730	6272	NR	860	633	NR	990	838	NR
475	6915	NR	605	35555	NR	735	5418	NR	865	816	NR	995	621	NR
480	7734	NR	610	36593	NR	740	4870	NR	870	767	NR	1000	903	NR
485	8748	NR	615	37350	NR	745	4295	NR	875	601	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: 849.3 **S/P: 0.48**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	649	NR	490	9819	NR	620	37806	NR	750	3792	NR	880	778	NR
365	535	NR	495	10995	NR	625	38173	NR	755	3383	NR	885	829	NR
370	546	NR	500	12186	NR	630	37677	NR	760	3071	NR	890	745	NR
375	624	NR	505	13274	NR	635	36852	NR	765	2656	NR	895	648	NR
380	611	NR	510	14396	NR	640	35711	NR	770	2297	NR	900	661	NR
385	569	NR	515	15467	NR	645	34820	NR	775	2076	NR	905	740	NR
390	512	NR	520	16543	NR	650	33278	NR	780	1860	NR	910	635	NR
395	465	NR	525	17716	NR	655	31397	NR	785	1717	NR	915	683	NR
400	418	NR	530	18837	NR	660	29663	NR	790	1494	NR	920	620	NR
405	411	NR	535	19916	NR	665	27479	NR	795	1276	NR	925	580	NR
410	439	NR	540	20679	NR	670	25115	NR	800	1183	NR	930	717	NR
415	565	NR	545	21563	NR	675	22916	NR	805	1161	NR	935	780	NR
420	866	NR	550	22521	NR	680	20799	NR	810	1065	NR	940	630	NR
425	1393	NR	555	23411	NR	685	18810	NR	815	970	NR	945	433	NR
430	2399	NR	560	24238	NR	690	16831	NR	820	1013	NR	950	676	NR
435	4305	NR	565	25148	NR	695	14867	NR	825	970	NR	955	802	NR
440	7544	NR	570	26216	NR	700	13210	NR	830	769	NR	960	645	NR
445	11003	NR	575	27219	NR	705	11593	NR	835	894	NR	965	620	NR
450	11015	NR	580	28466	NR	710	10403	NR	840	893	NR	970	474	NR
455	8956	NR	585	29834	NR	715	9162	NR	845	864	NR	975	478	NR
460	8133	NR	590	31413	NR	720	8146	NR	850	828	NR	980	905	NR
465	7252	NR	595	32655	NR	725	7155	NR	855	921	NR	985	639	NR
470	6556	NR	600	34084	NR	730	6272	NR	860	633	NR	990	838	NR
475	6915	NR	605	35555	NR	735	5418	NR	865	816	NR	995	621	NR
480	7734	NR	610	36593	NR	740	4870	NR	870	767	NR	1000	903	NR
485	8748	NR	615	37350	NR	745	4295	NR	875	601	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-1

TM-30-18


Summary


R_f = 93.1
R_g = 98.2
CIE R_a = 92.5
R_9 = 58.3


Spectral Power Distribution Comparison




Color Vector Graphics










Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 98	CES76 = 91
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 91
CES03 = 32	CES28 = 97	CES53 = 96	CES78 = 90
CES04 = 70	CES29 = 95	CES54 = 96	CES79 = 94
CES05 = 51	CES30 = 98	CES55 = 96	CES80 = 94
CES06 = 52	CES31 = 96	CES56 = 95	CES81 = 83
CES07 = 44	CES32 = 91	CES57 = 94	CES82 = 97
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 97	CES84 = 96
CES10 = 76	CES35 = 98	CES60 = 96	CES85 = 85
CES11 = 59	CES36 = 91	CES61 = 95	CES86 = 84
CES12 = 66	CES37 = 95	CES62 = 95	CES87 = 93
CES13 = 44	CES38 = 96	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 99	CES64 = 93	CES89 = 86
CES15 = 72	CES40 = 98	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 91	CES91 = 86
CES17 = 50	CES42 = 97	CES67 = 91	CES92 = 83
CES18 = 57	CES43 = 97	CES68 = 92	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 80
CES20 = 68	CES45 = 99	CES70 = 90	CES95 = 87
CES21 = 87	CES46 = 96	CES71 = 90	CES96 = 93
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 93	CES73 = 87	CES98 = 94
CES24 = 91	CES49 = 97	CES74 = 92	CES99 = 91
CES25 = 72	CES50 = 98	CES75 = 90	





Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-1

TM-30-18

Color Rendition by Hue-Angle Bin









Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-1

TM-30-18

Measure Comparisons





(END OF REPORT)