Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1502059

Luminaire Tested: GSS-SB4C-935-U-T2LG-HSS

Issue Date: 07/20/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1502059
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	7/20/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-935-U-T2LG-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 90CRI 3500K FIXTURE w/ TYPE II LOW GLARE DISTRIBUTION FIXTURE W/ HOUSE SIDE SHIELD
Light Source:	(104) 3500K CCT, 90 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	16337 lumens
Efficiency:	N/A
Efficacy:	80.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 25 foot mounting height. Maximum calculated value = 7.4 fc
Type II - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2549.0	0.0	2549.0
	% Fixture	15.6	0.0	15.6
Street Side	Lumens	13788.0	0.0	13788.0
	% Fixture	84.4	0.0	84.4
Total	Lumens	16337.0	0.0	16337.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.5	1.6
10°-20°	638.5	3.9
20°-30°	1192.0	7.3
30°-40°	2363.9	14.5
40°-50°	3768.9	23.1
50°-60°	4502.9	27.6
60°-70°	2951.9	18.1
70°-80°	618.5	3.8
80°-90°	46.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16337.0	100.0
0°-180°	16337.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1467.4	9.0			
FM	(30°-60°)	9059.5	55.5			
FH	(60°-80°)	3218.3	19.7			G2/5000
FVH	(80°-90°)	42.9	0.3			G1/100
BL	(0°-30°)	616.7	3.8	B2/1000		
BM	(30°-60°)	1576.3	9.6	B2/2500		
BH	(60°-80°)	352.1	2.2	B1/500		G1/500
BVH	(80°-90°)	3.9	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type II Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	67°	75°	85°
0°	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0
2.5°	2941.8	2932.7	2918.9	2923.5	2918.9	2900.6	2873.2	2850.3	2868.6	2841.2	2822.9
5°	3028.7	3028.7	3019.6	3019.6	3024.2	3015.0	2996.7	2964.7	2969.3	2946.4	2886.9
7.5°	3028.7	3015.0	3037.9	3060.8	3102.0	3124.8	3134.0	3115.7	3124.8	3079.1	3001.3
10°	2850.3	2841.2	2900.6	2987.6	3106.5	3211.8	3280.4	3285.0	3298.7	3252.9	3161.4
12.5°	2470.6	2452.3	2571.2	2735.9	2978.4	3220.9	3413.1	3486.3	3518.3	3500.0	3371.9
15°	2118.3	2141.2	2223.5	2402.0	2726.8	3097.4	3486.3	3728.7	3774.5	3797.4	3646.4
17.5°	2081.7	2086.3	2113.7	2200.6	2447.7	2896.1	3495.4	3980.4	4044.4	4145.1	3939.2
20°	2182.3	2173.2	2200.6	2228.1	2347.1	2717.6	3408.5	4222.9	4346.4	4561.4	4337.2
22.5°	2369.9	2369.9	2383.7	2402.0	2461.4	2703.9	3371.9	4447.0	4657.5	5096.7	4835.9
25°	2685.6	2649.0	2658.2	2635.3	2685.6	2868.6	3454.2	4625.5	4913.7	5691.5	5430.7
27.5°	3175.2	3188.9	3106.5	2983.0	3010.4	3166.0	3655.5	4826.8	5179.1	6309.1	6034.6
30°	3852.3	3829.4	3779.1	3536.6	3426.8	3564.0	4026.1	5156.2	5535.9	7091.5	6839.8
32.5°	4383.0	4447.0	4360.1	4190.8	4021.6	4062.7	4547.7	5686.9	5970.6	7809.8	7672.5
35°	5023.5	5023.5	5041.8	4803.9	4689.5	4680.4	5201.9	6263.4	6547.0	8459.5	8555.5
37.5°	5888.2	5828.7	5728.1	5462.7	5375.8	5490.2	5815.0	6858.1	7164.7	8985.6	9241.8
40°	6615.7	6656.8	6643.1	6258.8	6089.5	6213.1	6501.3	7366.0	7603.9	9324.2	9795.4
42.5°	7329.4	7352.3	7292.8	7109.8	6862.7	6871.9	7109.8	7750.3	7992.8	9649.0	10317.0
45°	7864.7	7860.1	7818.9	7773.2	7626.8	7475.8	7517.0	8175.8	8386.2	9754.2	10600.6
47.5°	8034.0	8070.6	8107.2	8235.3	8335.9	8098.0	7887.6	8404.5	8596.7	9735.9	10705.8
50°	7878.4	7956.2	8134.6	8326.8	8669.9	8651.6	8198.7	8651.6	8839.2	9836.6	10829.4
52.5°	7530.7	7608.5	7846.4	8194.1	8711.1	8967.3	8775.1	9067.9	9287.6	10092.8	11085.6
55°	6720.9	6752.9	7242.5	7700.0	8505.2	8830.0	9392.8	9772.5	9955.5	10403.9	11424.1
57.5°	5471.9	5549.7	6030.0	6775.8	7928.7	8468.6	9745.1	10975.8	10971.2	10701.3	11497.4
60°	*3600.6*	*3829.4*	*4611.8*	*5435.3*	*6812.4*	*7759.5*	*9722.2*	*12384.9*	*12526.8*	*10408.5*	*10614.3*
62.5°	2749.7	2845.7	3289.5	3975.8	5041.8	6432.7	9571.2	12805.8	12915.6	9621.5	9292.1
65°	2068.0	2186.9	2612.4	3225.5	3559.5	4360.1	8583.0	11131.3	11282.3	8587.6	7224.2
67.5°	1267.3	1363.4	1930.7	2649.0	2694.8	2708.5	5792.1	8432.0	8486.9	6926.8	4863.4
70°	846.4	942.5	1335.9	2035.9	2145.7	1560.1	3179.7	6382.3	6377.8	4739.9	2955.5
72.5°	489.5	535.3	846.4	1500.6	1688.2	992.8	1587.6	4058.2	3879.7	2228.1	1381.7
75°	279.1	311.1	466.7	965.4	1185.0	631.4	626.8	2173.2	1921.6	1148.4	754.9
77.5°	169.3	183.0	256.2	631.4	713.7	425.5	347.7	1011.1	974.5	672.5	398.0
80°	82.4	96.1	155.6	370.6	457.5	228.8	210.5	398.0	425.5	370.6	210.5
82.5°	27.5	36.6	86.9	141.8	297.4	91.5	86.9	219.6	233.3	219.6	100.7
85°	13.7	18.3	41.2	45.8	114.4	45.8	32.0	96.1	119.0	73.2	41.2
87.5°	0.0	4.6	4.6	4.6	4.6	4.6	4.6	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0
2.5°	2809.1	2800.0	2781.7	2749.7	2745.1	2722.2	2685.6	2662.7	2644.4	2658.2	2662.7
5°	2859.5	2836.6	2781.7	2694.8	2603.3	2511.8	2424.8	2324.2	2255.5	2246.4	2228.1
7.5°	2951.0	2905.2	2786.3	2617.0	2383.7	2164.0	1907.8	1660.8	1537.3	1518.9	1477.8
10°	3097.4	3019.6	2822.9	2479.7	2031.4	1573.9	1185.0	919.6	768.6	741.2	750.3
12.5°	3271.2	3161.4	2827.4	2246.4	1546.4	974.5	672.5	571.9	539.9	526.1	526.1
15°	3495.4	3335.3	2822.9	1944.4	1043.1	626.8	539.9	498.7	485.0	475.8	475.8
17.5°	3779.1	3568.6	2790.8	1491.5	704.6	544.4	494.1	462.1	443.8	439.2	439.2
20°	4113.1	3829.4	2717.6	1111.8	590.2	507.8	466.7	425.5	411.8	402.6	402.6
22.5°	4538.5	4145.1	2575.8	864.7	558.2	485.0	439.2	393.5	379.7	370.6	370.6
25°	5032.7	4547.7	2388.2	777.8	553.6	466.7	411.8	366.0	352.3	347.7	343.1
27.5°	5618.3	4977.8	2214.4	782.4	562.7	452.9	384.3	343.1	329.4	315.7	320.3
30°	6309.1	5421.6	2072.5	837.3	571.9	439.2	366.0	329.4	315.7	297.4	297.4
32.5°	6990.8	5943.1	2058.8	937.9	603.9	430.1	347.7	311.1	297.4	283.7	283.7
35°	7690.8	6418.9	2136.6	1070.6	668.0	416.3	324.8	292.8	279.1	269.9	265.4
37.5°	8358.8	6798.7	2209.8	1152.9	631.4	356.9	297.4	269.9	256.2	237.9	237.9
40°	8802.6	7004.6	2223.5	1088.9	521.6	320.3	269.9	242.5	224.2	215.0	210.5
42.5°	9127.4	7137.2	2068.0	883.0	452.9	292.8	247.1	219.6	205.9	196.7	196.7
45°	9260.1	7091.5	1802.6	672.5	416.3	269.9	224.2	201.3	192.2	183.0	183.0
47.5°	9241.8	6881.0	1532.7	539.9	379.7	247.1	210.5	192.2	183.0	173.9	169.3
50°	9209.8	6684.3	1258.2	480.4	338.6	233.3	196.7	183.0	169.3	160.1	155.6
52.5°	9420.2	6620.2	1043.1	439.2	315.7	224.2	192.2	173.9	160.1	151.0	151.0
55°	9630.7	6647.7	819.0	411.8	292.8	219.6	187.6	169.3	155.6	141.8	141.8
57.5°	9617.0	6528.7	622.2	384.3	274.5	215.0	183.0	164.7	141.8	132.7	132.7
60°	*8743.1*	*5824.2*	*485.0*	*352.3*	*251.6*	*201.3*	*169.3*	*155.6*	*132.7*	*119.0*	*119.0*
62.5°	7393.4	4579.7	398.0	311.1	224.2	183.0	155.6	141.8	119.0	96.1	96.1
65°	5462.7	3303.3	320.3	269.9	205.9	160.1	141.8	123.5	96.1	77.8	73.2
67.5°	3696.7	2031.4	256.2	224.2	183.0	137.3	119.0	105.2	86.9	64.1	59.5
70°	2191.5	1079.7	187.6	155.6	137.3	100.7	100.7	91.5	73.2	54.9	50.3
72.5°	1043.1	375.2	137.3	114.4	105.2	73.2	77.8	77.8	59.5	41.2	36.6
75°	530.7	183.0	91.5	82.4	68.6	54.9	64.1	59.5	41.2	27.5	27.5
77.5°	302.0	128.1	64.1	54.9	45.8	36.6	41.2	36.6	22.9	13.7	13.7
80°	169.3	91.5	41.2	36.6	27.5	22.9	22.9	18.3	13.7	4.6	4.6
82.5°	64.1	54.9	27.5	18.3	13.7	13.7	9.2	9.2	4.6	0.0	0.0
85°	27.5	13.7	13.7	9.2	9.2	4.6	4.6	4.6	0.0	0.0	0.0
87.5°	4.6	4.6	4.6	4.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0
2.5°	2626.1	2635.3	2644.4	2681.0	2690.2	2717.6	2740.5	2768.0	2772.5	2809.1	2809.1
5°	2264.7	2260.1	2337.9	2452.3	2525.5	2626.1	2703.9	2786.3	2832.0	2891.5	2918.9
7.5°	1500.6	1615.0	1788.9	1990.2	2251.0	2493.5	2676.5	2836.6	2946.4	3015.0	3042.5
10°	745.7	809.8	992.8	1322.2	1766.0	2260.1	2649.0	2946.4	3124.8	3202.6	3252.9
12.5°	526.1	539.9	571.9	750.3	1175.8	1875.8	2562.1	3065.4	3312.4	3458.8	3522.9
15°	471.2	480.4	494.1	544.4	727.4	1400.0	2406.5	3198.0	3605.2	3774.5	3856.9
17.5°	434.6	439.2	452.9	494.1	571.9	951.6	2154.9	3339.9	3957.5	4163.4	4318.9
20°	402.6	402.6	416.3	466.7	530.7	732.0	1793.5	3500.0	4405.9	4703.3	4858.8
22.5°	366.0	375.2	384.3	439.2	517.0	668.0	1454.9	3623.5	4904.6	5266.0	5449.0
25°	338.6	347.7	356.9	411.8	503.3	668.0	1258.2	3701.3	5462.7	5892.8	6144.4
27.5°	315.7	324.8	338.6	393.5	489.5	695.4	1180.4	3724.2	6071.2	6629.4	6968.0
30°	297.4	306.5	320.3	379.7	498.7	727.4	1207.8	3692.1	6688.9	7388.9	7791.5
32.5°	279.1	288.2	302.0	366.0	498.7	768.6	1299.3	3628.1	7288.2	8148.3	8642.5
35°	265.4	269.9	274.5	329.4	452.9	764.0	1413.7	3564.0	7892.1	8898.7	9475.1
37.5°	237.9	242.5	251.6	283.7	361.4	695.4	1436.6	3486.3	8367.9	9530.0	10166.0
40°	210.5	219.6	228.8	260.8	302.0	562.7	1335.9	3321.6	8619.6	10015.0	10788.2
42.5°	192.2	196.7	205.9	237.9	279.1	448.4	1120.9	3033.3	8843.8	10344.4	11241.1
45°	178.4	183.0	192.2	215.0	260.8	388.9	883.0	2681.0	8862.1	10449.6	11460.7
47.5°	164.7	169.3	173.9	196.7	251.6	347.7	677.1	2360.8	8857.5	10586.9	11648.3
50°	155.6	160.1	169.3	187.6	237.9	311.1	558.2	2100.0	9049.6	10884.3	12028.1
52.5°	151.0	151.0	164.7	183.0	224.2	283.7	466.7	1866.7	9150.3	11177.1	12302.6
55°	141.8	146.4	155.6	173.9	210.5	269.9	398.0	1573.9	9196.1	11323.5	12352.9
57.5°	132.7	137.3	151.0	164.7	201.3	256.2	343.1	1175.8	8541.8	10559.4	11511.1
60°	*119.0*	*128.1*	*146.4*	*160.1*	*187.6*	*233.3*	*302.0*	*796.1*	*7205.9*	*9177.7*	*9973.8*
62.5°	96.1	114.4	132.7	141.8	169.3	196.7	256.2	530.7	5755.5	7594.7	8500.6
65°	73.2	96.1	109.8	123.5	141.8	164.7	215.0	361.4	3838.6	5110.4	6130.7
67.5°	64.1	82.4	91.5	100.7	119.0	141.8	173.9	251.6	2328.8	3069.9	4076.5
70°	50.3	68.6	77.8	73.2	91.5	109.8	123.5	169.3	1189.5	1665.4	2319.6
72.5°	36.6	54.9	59.5	59.5	54.9	77.8	91.5	119.0	517.0	809.8	1052.3
75°	27.5	36.6	41.2	36.6	32.0	50.3	64.1	77.8	338.6	485.0	613.1
77.5°	13.7	13.7	22.9	22.9	13.7	27.5	32.0	45.8	192.2	283.7	352.3
80°	4.6	0.0	0.0	4.6	0.0	9.2	13.7	22.9	100.7	151.0	219.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.6	50.3	45.8	114.4
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.2	27.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1502059
CATALOG NUMBER: GSS-SB4C-935-U-T2LG-HSS

CANDELA DISTRIBUTION (continued):

	285°	293°	295°	305°	315°	325°	335°	345°	355°	360°
0°	2800.0	*2800.0*	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0	2800.0
2.5°	2832.0	*2832.0*	2850.3	2877.8	2891.5	2900.6	2905.2	2914.4	2951.0	2941.8
5°	2951.0	*2960.1*	2973.8	3001.3	3033.3	3024.2	3024.2	3024.2	3047.0	3028.7
7.5°	3106.5	*3134.0*	3138.6	3170.6	3147.7	3102.0	3074.5	3033.3	3028.7	3028.7
10°	3358.2	*3349.0*	3349.0	3307.8	3225.5	3092.8	2973.8	2891.5	2845.7	2850.3
12.5°	3628.1	*3591.5*	3596.1	3445.1	3211.8	2918.9	2676.5	2498.0	2484.3	2470.6
15°	3962.1	*3866.0*	3847.7	3500.0	3005.9	2557.5	2319.6	2177.8	2132.0	2118.3
17.5°	4437.9	*4195.4*	4108.5	3403.9	2735.9	2333.3	2154.9	2090.8	2086.3	2081.7
20°	4941.2	*4460.8*	4296.1	3262.1	2644.4	2337.9	2205.2	2186.9	2177.8	2182.3
22.5°	5526.8	*4630.1*	4419.6	3285.0	2726.8	2488.9	2383.7	2369.9	2360.8	2369.9
25°	6130.7	*4826.8*	4566.0	3468.0	2973.8	2768.0	2644.4	2617.0	2644.4	2685.6
27.5°	6739.2	*5092.1*	4854.2	3829.4	3371.9	3147.7	3028.7	3129.4	3170.6	3175.2
30°	7279.1	*5462.7*	5243.1	4337.2	3824.8	3600.6	3623.5	3751.6	3801.9	3852.3
32.5°	7773.2	*5956.8*	5787.6	4913.7	4410.4	4277.8	4264.0	4360.1	4415.0	4383.0
35°	8271.9	*6601.9*	6437.2	5540.5	5128.7	5018.9	4904.6	5092.1	5073.8	5023.5
37.5°	8743.1	*7251.6*	7100.6	6213.1	5787.6	5595.4	5577.1	5746.4	5897.4	5888.2
40°	9081.7	*7777.8*	7594.7	6881.0	6478.4	6313.7	6409.8	6702.6	6666.0	6615.7
42.5°	9392.8	*8226.1*	8061.4	7466.6	7045.7	7118.9	7205.9	7402.6	7379.7	7329.4
45°	9539.2	*8610.4*	8468.6	7910.4	7704.6	7937.9	7933.3	8006.5	7883.0	7864.7
47.5°	9745.1	*8884.9*	8738.5	8308.5	8491.5	8587.6	8317.6	8239.8	8125.5	8034.0
50°	10124.8	*9310.4*	9164.0	8912.4	9067.9	8770.6	8441.2	8271.9	8038.5	7878.4
52.5°	10568.6	*9955.5*	9827.4	9726.8	9292.1	8679.1	8258.1	7951.6	7668.0	7530.7
55°	11126.8	*10907.2*	10815.7	10262.1	9090.8	8303.9	7809.8	7237.9	6849.0	6720.9
57.5°	11309.8	*12302.6*	12270.6	10349.0	8528.1	7622.2	6730.0	5956.8	5554.2	5471.9
60°	*10769.9*	*13396.0*	*13281.7*	*10202.6*	*7507.8*	*6185.6*	*5142.5*	*4351.0*	*3696.7*	*3600.6*
62.5°	10079.1	*12558.8*	12517.6	9466.0	5718.9	4433.3	3843.1	3102.0	2822.9	2749.7
65°	8633.3	*10275.8*	10294.1	7594.7	3618.9	3184.3	3156.9	2466.0	2122.9	2068.0
67.5°	6647.7	*7883.0*	7754.9	4776.5	2109.1	2548.4	2520.9	1802.6	1303.9	1267.3
70°	3884.3	*5869.9*	5664.0	2484.3	1395.4	2127.4	1939.9	1267.3	887.6	846.4
72.5°	1715.7	*3230.1*	3468.0	1093.5	983.7	1692.8	1400.0	777.8	498.7	489.5
75°	951.6	*1601.3*	1674.5	475.8	690.8	1203.3	846.4	434.6	283.7	279.1
77.5°	571.9	*709.1*	690.8	306.5	517.0	768.6	512.4	247.1	178.4	169.3
80°	320.3	*324.8*	274.5	224.2	306.5	430.1	288.2	155.6	82.4	82.4
82.5°	196.7	*178.4*	141.8	68.6	82.4	260.8	105.2	86.9	27.5	27.5
85°	82.4	*54.9*	36.6	13.7	32.0	68.6	36.6	41.2	13.7	13.7
87.5°	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2106-271-3

Luminaire Tested: GFLD-SA1-A-935-U-WR-X-BK

Test Date: 06/15/2021

Report Generated By FNC07603 / LDUCLS01DT446
Version: v6.09

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Test Information


Test Method:	LM-79-08
Report Number:	SP1-2106-271-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1
Measurement Geometry:	4π
Issue Date:	06/15/2021
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	**GFLD-SA1-A-935-U-WR-X-BK**
Description:	MCGRAW EDISON

N6, BLACK

Spectral Parameters

CCT (K):	3364	CRI (Ra):	92.0		
CIE u':	0.2376	R1:	91.7	R9:	59.7
CIE v':	0.5188	R2:	94.0	R10:	85.2
Duv:	0.0036	R3:	95.5	R11:	92.8
CIE x:	0.4173	R4:	93.0	R12:	78.2
CIE y:	0.4050	R5:	90.9	R13:	92.0
CIE z:	0.1777	R6:	92.2	R14:	96.9
Peak Wavelength (nm):	622	R7:	94.8		
Dominant Wavelength (nm):	580	R8:	84.1		
Purity:	46.9				

Rf:	92.6
Rg:	98.3



Test Conditions

Stabilization Time:	76M
Operation Time:	12H
Room Temperature (°C) / RH%:	24.8/44%
Sphere Temperature (°C):	24.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	1/31/2021	7/31/2021
Power Meter	XITRON 2801 IN0071	12/1/2020	12/1/2021
AC Power Source	CHROMA 61603 IN0063	12/1/2020	12/1/2021
DC Power Source	AGILENT E3634A IN0208	12/1/2020	12/1/2021
Sphere Thermometer	ONSET IN0085	12/1/2020	12/1/2021
Room Thermometer	ONSET IN0046	12/1/2020	12/1/2021


Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3364K
CIE x = 0.4173
CIE y = 0.4050
Duv = 0.0036

Point lies inside the ANSI 3500K 4-step quadrangle

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

Photopic Flux vs. Wavelength




######

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	792	NR	490	14205	NR	620	36151	NR	750	3427	NR	880	712	NR
365	640	NR	495	15647	NR	625	36077	NR	755	3047	NR	885	942	NR
370	630	NR	500	17088	NR	630	35451	NR	760	2790	NR	890	952	NR
375	684	NR	505	18475	NR	635	34417	NR	765	2433	NR	895	764	NR
380	731	NR	510	19780	NR	640	33166	NR	770	2178	NR	900	743	NR
385	664	NR	515	21055	NR	645	32124	NR	775	1893	NR	905	776	NR
390	595	NR	520	22268	NR	650	30559	NR	780	1724	NR	910	659	NR
395	520	NR	525	23497	NR	655	28656	NR	785	1549	NR	915	701	NR
400	491	NR	530	24653	NR	660	27033	NR	790	1451	NR	920	728	NR
405	489	NR	535	25661	NR	665	25030	NR	795	1317	NR	925	793	NR
410	585	NR	540	26289	NR	670	22820	NR	800	1124	NR	930	877	NR
415	826	NR	545	26945	NR	675	20678	NR	805	1116	NR	935	923	NR
420	1336	NR	550	27713	NR	680	18748	NR	810	1105	NR	940	1001	NR
425	2406	NR	555	28230	NR	685	16904	NR	815	1073	NR	945	604	NR
430	4355	NR	560	28678	NR	690	15203	NR	820	977	NR	950	424	NR
435	7911	NR	565	29242	NR	695	13356	NR	825	882	NR	955	550	NR
440	13821	NR	570	29806	NR	700	11948	NR	830	875	NR	960	709	NR
445	19836	NR	575	30322	NR	705	10482	NR	835	944	NR	965	755	NR
450	19902	NR	580	31125	NR	710	9351	NR	840	956	NR	970	426	NR
455	15697	NR	585	31838	NR	715	8217	NR	845	875	NR	975	556	NR
460	13589	NR	590	32845	NR	720	7313	NR	850	801	NR	980	1040	NR
465	11857	NR	595	33487	NR	725	6460	NR	855	890	NR	985	833	NR
470	10336	NR	600	34359	NR	730	5680	NR	860	706	NR	990	964	NR
475	10504	NR	605	35281	NR	735	4904	NR	865	902	NR	995	953	NR
480	11526	NR	610	35679	NR	740	4372	NR	870	879	NR	1000	950	NR
485	12831	NR	615	36113	NR	745	3858	NR	875	769	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: 3109.5 **S/P: 1.54**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	792	NR	490	14205	NR	620	36151	NR	750	3427	NR	880	712	NR
365	640	NR	495	15647	NR	625	36077	NR	755	3047	NR	885	942	NR
370	630	NR	500	17088	NR	630	35451	NR	760	2790	NR	890	952	NR
375	684	NR	505	18475	NR	635	34417	NR	765	2433	NR	895	764	NR
380	731	NR	510	19780	NR	640	33166	NR	770	2178	NR	900	743	NR
385	664	NR	515	21055	NR	645	32124	NR	775	1893	NR	905	776	NR
390	595	NR	520	22268	NR	650	30559	NR	780	1724	NR	910	659	NR
395	520	NR	525	23497	NR	655	28656	NR	785	1549	NR	915	701	NR
400	491	NR	530	24653	NR	660	27033	NR	790	1451	NR	920	728	NR
405	489	NR	535	25661	NR	665	25030	NR	795	1317	NR	925	793	NR
410	585	NR	540	26289	NR	670	22820	NR	800	1124	NR	930	877	NR
415	826	NR	545	26945	NR	675	20678	NR	805	1116	NR	935	923	NR
420	1336	NR	550	27713	NR	680	18748	NR	810	1105	NR	940	1001	NR
425	2406	NR	555	28230	NR	685	16904	NR	815	1073	NR	945	604	NR
430	4355	NR	560	28678	NR	690	15203	NR	820	977	NR	950	424	NR
435	7911	NR	565	29242	NR	695	13356	NR	825	882	NR	955	550	NR
440	13821	NR	570	29806	NR	700	11948	NR	830	875	NR	960	709	NR
445	19836	NR	575	30322	NR	705	10482	NR	835	944	NR	965	755	NR
450	19902	NR	580	31125	NR	710	9351	NR	840	956	NR	970	426	NR
455	15697	NR	585	31838	NR	715	8217	NR	845	875	NR	975	556	NR
460	13589	NR	590	32845	NR	720	7313	NR	850	801	NR	980	1040	NR
465	11857	NR	595	33487	NR	725	6460	NR	855	890	NR	985	833	NR
470	10336	NR	600	34359	NR	730	5680	NR	860	706	NR	990	964	NR
475	10504	NR	605	35281	NR	735	4904	NR	865	902	NR	995	953	NR
480	11526	NR	610	35679	NR	740	4372	NR	870	879	NR	1000	950	NR
485	12831	NR	615	36113	NR	745	3858	NR	875	769	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1210.8 **S/P: 0.6**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	792	NR	490	14205	NR	620	36151	NR	750	3427	NR	880	712	NR
365	640	NR	495	15647	NR	625	36077	NR	755	3047	NR	885	942	NR
370	630	NR	500	17088	NR	630	35451	NR	760	2790	NR	890	952	NR
375	684	NR	505	18475	NR	635	34417	NR	765	2433	NR	895	764	NR
380	731	NR	510	19780	NR	640	33166	NR	770	2178	NR	900	743	NR
385	664	NR	515	21055	NR	645	32124	NR	775	1893	NR	905	776	NR
390	595	NR	520	22268	NR	650	30559	NR	780	1724	NR	910	659	NR
395	520	NR	525	23497	NR	655	28656	NR	785	1549	NR	915	701	NR
400	491	NR	530	24653	NR	660	27033	NR	790	1451	NR	920	728	NR
405	489	NR	535	25661	NR	665	25030	NR	795	1317	NR	925	793	NR
410	585	NR	540	26289	NR	670	22820	NR	800	1124	NR	930	877	NR
415	826	NR	545	26945	NR	675	20678	NR	805	1116	NR	935	923	NR
420	1336	NR	550	27713	NR	680	18748	NR	810	1105	NR	940	1001	NR
425	2406	NR	555	28230	NR	685	16904	NR	815	1073	NR	945	604	NR
430	4355	NR	560	28678	NR	690	15203	NR	820	977	NR	950	424	NR
435	7911	NR	565	29242	NR	695	13356	NR	825	882	NR	955	550	NR
440	13821	NR	570	29806	NR	700	11948	NR	830	875	NR	960	709	NR
445	19836	NR	575	30322	NR	705	10482	NR	835	944	NR	965	755	NR
450	19902	NR	580	31125	NR	710	9351	NR	840	956	NR	970	426	NR
455	15697	NR	585	31838	NR	715	8217	NR	845	875	NR	975	556	NR
460	13589	NR	590	32845	NR	720	7313	NR	850	801	NR	980	1040	NR
465	11857	NR	595	33487	NR	725	6460	NR	855	890	NR	985	833	NR
470	10336	NR	600	34359	NR	730	5680	NR	860	706	NR	990	964	NR
475	10504	NR	605	35281	NR	735	4904	NR	865	902	NR	995	953	NR
480	11526	NR	610	35679	NR	740	4372	NR	870	879	NR	1000	950	NR
485	12831	NR	615	36113	NR	745	3858	NR	875	769	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-3

TM-30-18


Summary


R_f = 92.6
R_g = 98.3
CIE R_a = 92.0
R_9 = 59.7


Spectral Power Distribution Comparison




Color Vector Graphics










Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 93	CES52 = 98	CES77 = 91
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 87
CES04 = 70	CES29 = 96	CES54 = 95	CES79 = 96
CES05 = 50	CES30 = 97	CES55 = 94	CES80 = 95
CES06 = 51	CES31 = 96	CES56 = 94	CES81 = 88
CES07 = 42	CES32 = 92	CES57 = 93	CES82 = 98
CES08 = 41	CES33 = 98	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 95	CES59 = 96	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 94	CES85 = 86
CES11 = 58	CES36 = 87	CES61 = 93	CES86 = 87
CES12 = 64	CES37 = 95	CES62 = 91	CES87 = 92
CES13 = 43	CES38 = 92	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 89	CES91 = 80
CES17 = 49	CES42 = 96	CES67 = 88	CES92 = 82
CES18 = 56	CES43 = 97	CES68 = 90	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 82
CES20 = 66	CES45 = 98	CES70 = 88	CES95 = 85
CES21 = 86	CES46 = 97	CES71 = 85	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 95	CES97 = 96
CES23 = 91	CES48 = 93	CES73 = 84	CES98 = 94
CES24 = 90	CES49 = 97	CES74 = 94	CES99 = 91
CES25 = 71	CES50 = 98	CES75 = 86	





Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-3

TM-30-18

Color Rendition by Hue-Angle Bin









Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-3

TM-30-18

Measure Comparisons





(END OF REPORT)