

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197710

Luminaire Tested: **TT-C3-LED-E1-5MQ-PM-CG**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197710  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115348)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-5MQ-PM-CG  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
MEDIUM DISTRIBUTION WITH CLEAR GLASS LENS  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5555.3 lumens  
Efficiency: N/A  
Efficacy: 123.5 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197710

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.8 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197710  
CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 61-Deg Vertical

REPORT NUMBER: P197710

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2777.6	0.0	2777.6
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2777.6	0.0	2777.6
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	5555.3	0.0	5555.3
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.7	1.8
10°-20°	303.6	5.5
20°-30°	488.4	8.8
30°-40°	647.0	11.6
40°-50°	817.1	14.7
50°-60°	979.1	17.6
60°-70°	1070.5	19.3
70°-80°	857.0	15.4
80°-90°	289.9	5.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5555.3	100.0
0°-180°	5555.3	100.0



REPORT NUMBER: P197710


CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	447.3	8.1			
FM (30°-60°)	1221.6	22.0			
FH (60°-80°)	963.7	17.3			G1/1800
FVH (80°-90°)	145.0	2.6			G2/225
BL (0°-30°)	447.3	8.1	B1/500		
BM (30°-60°)	1221.6	22.0	B2/2500		
BH (60°-80°)	963.7	17.3	B2/1000		G1/1800
BVH (80°-90°)	145.0	2.6			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type V Short





REPORT NUMBER: P197710

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3
2.5°	1077.3	1076.3	1077.3	1077.3	1077.3	1077.3	1077.3	1077.3	1077.3	1077.3	1077.3
5°	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3
7.5°	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1076.3	1075.2	1076.3
10°	1073.2	1073.2	1073.2	1073.2	1074.2	1074.2	1074.2	1074.2	1074.2	1074.2	1074.2
12.5°	1071.1	1071.1	1071.1	1071.1	1072.2	1072.2	1072.2	1072.2	1073.2	1073.2	1072.2
15°	1069.0	1068.0	1068.0	1069.0	1069.0	1070.1	1070.1	1070.1	1071.1	1070.1	1070.1
17.5°	1066.9	1065.9	1066.9	1068.0	1068.0	1069.0	1070.1	1070.1	1071.1	1071.1	1071.1
20°	1070.1	1069.0	1070.1	1071.1	1072.2	1074.2	1075.2	1076.3	1077.3	1078.4	1078.4
22.5°	1063.9	1062.9	1063.9	1063.9	1065.0	1065.9	1068.0	1069.0	1070.1	1070.1	1070.1
25°	1054.6	1054.6	1055.6	1055.6	1056.7	1057.6	1058.7	1059.7	1059.7	1060.8	1059.7
27.5°	1044.2	1044.2	1045.3	1045.3	1047.4	1047.4	1048.4	1049.3	1050.4	1050.4	1050.4
30°	1031.9	1031.9	1032.8	1033.8	1035.9	1037.0	1038.0	1039.1	1040.1	1040.1	1040.1
32.5°	1020.4	1019.4	1020.4	1022.5	1025.6	1027.7	1029.8	1030.8	1030.8	1030.8	1031.9
35°	1011.1	1012.1	1014.2	1016.2	1020.4	1022.5	1024.5	1027.7	1028.7	1028.7	1028.7
37.5°	1013.2	1014.2	1017.3	1021.5	1026.6	1032.8	1037.0	1041.1	1044.2	1043.2	1042.1
40°	1026.6	1028.7	1033.8	1040.1	1048.4	1056.7	1062.9	1068.0	1071.1	1072.2	1071.1
42.5°	1028.7	1030.8	1034.9	1044.2	1053.5	1062.9	1071.1	1076.3	1080.5	1081.5	1080.5
45°	1027.7	1027.7	1033.8	1044.2	1053.5	1062.9	1073.2	1080.5	1084.6	1084.6	1084.6
47.5°	1020.4	1023.6	1027.7	1038.0	1050.4	1059.7	1070.1	1077.3	1082.5	1085.6	1082.5
50°	1020.4	1020.4	1027.7	1034.9	1046.3	1062.9	1077.3	1084.6	1089.8	1088.7	1089.8
52.5°	1018.3	1024.5	1028.7	1039.1	1059.7	1076.3	1087.7	1098.1	1105.3	1106.4	1104.3
55°	1037.0	1038.0	1047.4	1066.9	1086.7	1105.3	1125.9	1141.4	1153.9	1161.2	1150.8
57.5°	1051.4	1046.3	1065.0	1081.5	1104.3	1132.2	1163.3	1175.6	1184.9	1182.8	1186.0
60°	1031.9	1039.1	1052.5	1070.1	1106.4	1134.2	1150.8	1164.3	1175.6	1178.8	1174.6
61°	1022.5	1034.9	1041.1	1065.0	1103.2	1124.0	1141.4	1160.1	1180.9	1188.1	1178.8
62.5°	1007.0	1026.6	1024.5	1062.9	1086.7	1110.4	1143.5	1165.4	1179.8	1181.9	1179.8
65°	1007.9	1004.9	1028.7	1056.7	1080.5	1122.9	1150.8	1164.3	1172.6	1176.7	1174.6
67.5°	974.8	964.6	993.5	1013.2	1053.5	1086.7	1113.6	1133.2	1145.6	1149.7	1144.6
70°	898.4	905.6	926.2	956.3	989.4	1029.8	1054.6	1080.5	1090.7	1091.8	1091.8
72.5°	824.8	829.0	849.6	877.6	915.8	951.1	975.9	996.6	1006.0	1007.0	1009.0
75°	727.5	731.6	755.5	781.4	819.7	849.6	867.2	892.1	905.6	916.9	907.6
77.5°	614.7	622.0	640.6	668.5	703.8	720.3	751.3	780.4	789.7	792.7	789.7
80°	487.5	496.8	513.4	550.6	566.1	593.0	623.0	635.4	643.7	645.8	646.9
82.5°	350.8	358.1	375.7	401.5	419.2	440.8	461.6	477.1	486.4	484.3	483.3
85°	207.0	209.1	227.7	245.3	258.7	272.1	288.7	300.1	302.2	306.3	305.2
87.5°	62.1	63.1	71.4	80.7	87.0	93.2	103.5	116.9	120.1	111.8	112.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197710

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM-CG

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3
2.5°	1077.3	1077.3	1077.3	1077.3	1077.3	1077.3	1076.3	1077.3
5°	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3	1076.3
7.5°	1076.3	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2	1075.2
10°	1074.2	1074.2	1074.2	1074.2	1073.2	1073.2	1073.2	1073.2
12.5°	1072.2	1072.2	1072.2	1072.2	1071.1	1071.1	1071.1	1071.1
15°	1070.1	1070.1	1070.1	1070.1	1069.0	1069.0	1069.0	1069.0
17.5°	1071.1	1070.1	1069.0	1069.0	1068.0	1066.9	1066.9	1066.9
20°	1077.3	1076.3	1074.2	1072.2	1071.1	1070.1	1070.1	1070.1
22.5°	1069.0	1068.0	1065.9	1065.0	1065.0	1063.9	1062.9	1062.9
25°	1059.7	1057.6	1057.6	1056.7	1056.7	1054.6	1054.6	1053.5
27.5°	1049.3	1048.4	1047.4	1046.3	1046.3	1045.3	1044.2	1043.2
30°	1040.1	1038.0	1035.9	1034.9	1033.8	1032.8	1032.8	1032.8
32.5°	1030.8	1028.7	1027.7	1024.5	1022.5	1021.5	1020.4	1020.4
35°	1027.7	1024.5	1022.5	1019.4	1016.2	1014.2	1013.2	1011.1
37.5°	1040.1	1035.9	1032.8	1027.7	1020.4	1017.3	1014.2	1013.2
40°	1066.9	1062.9	1056.7	1048.4	1040.1	1033.8	1028.7	1026.6
42.5°	1076.3	1071.1	1062.9	1054.6	1044.2	1034.9	1030.8	1028.7
45°	1079.4	1074.2	1062.9	1052.5	1043.2	1034.9	1028.7	1026.6
47.5°	1076.3	1069.0	1058.7	1050.4	1037.0	1026.6	1022.5	1019.4
50°	1083.5	1077.3	1063.9	1045.3	1033.8	1027.7	1020.4	1019.4
52.5°	1098.1	1086.7	1074.2	1060.8	1039.1	1026.6	1022.5	1017.3
55°	1141.4	1125.9	1104.3	1082.5	1069.0	1049.3	1037.0	1037.0
57.5°	1174.6	1162.2	1134.2	1105.3	1080.5	1065.9	1047.4	1048.4
60°	1165.4	1148.8	1135.3	1106.4	1071.1	1051.4	1044.2	1030.8
61°	1164.3	1141.4	1122.9	1100.1	1070.1	1039.1	1037.0	1019.4
62.5°	1166.3	1145.6	1110.4	1086.7	1063.9	1023.6	1022.5	1006.0
65°	1164.3	1144.6	1127.0	1082.5	1051.4	1034.9	999.7	1013.2
67.5°	1132.2	1114.6	1082.5	1057.6	1010.0	989.4	969.7	969.7
70°	1081.5	1055.6	1024.5	993.5	961.4	926.2	908.6	898.4
72.5°	996.6	974.8	950.0	916.9	877.6	845.5	829.0	821.8
75°	890.1	866.2	844.5	819.7	778.3	751.3	733.7	728.6
77.5°	778.3	757.5	719.3	695.5	667.5	636.5	621.0	614.7
80°	635.4	624.0	597.2	558.8	545.4	507.1	496.8	487.5
82.5°	477.1	464.6	439.8	413.0	396.4	374.6	356.0	354.0
85°	300.1	291.8	276.3	256.6	236.0	223.5	207.0	211.2
87.5°	111.8	106.6	97.2	84.9	75.6	67.3	59.0	62.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)