Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360404

Luminaire Tested: **GSS-SB2B-750-U-T3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360404
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2B-750-U-T3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 74W 70CRI 5000K FIXTURE w/ TYPE III DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	8045.6 lumens
Efficiency:	N/A
Efficacy:	108.7 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B1 - U0 - G2


Input Watts (W):	74
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.7 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	962.0	0.0	962.0
	% Fixture	12.0	0.0	12.0
Street Side	Lumens	7083.6	0.0	7083.6
	% Fixture	88.0	0.0	88.0
Total	Lumens	8045.6	0.0	8045.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	1.3
10°-20°	268.2	3.3
20°-30°	478.1	5.9
30°-40°	855.7	10.6
40°-50°	1347.9	16.8
50°-60°	1960.5	24.4
60°-70°	2133.0	26.5
70°-80°	861.7	10.7
80°-90°	36.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8045.6	100.0
0°-180°	8045.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	567.3	7.1			
FM	(30°-60°)	3632.0	45.1			
FH	(60°-80°)	2854.9	35.5			G2/5000
FVH	(80°-90°)	29.4	0.4			G1/100
BL	(0°-30°)	283.3	3.5	B1/500		
BM	(30°-60°)	532.0	6.6	B1/1000		
BH	(60°-80°)	139.8	1.7	B1/500		G1/500
BVH	(80°-90°)	6.8	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	51°	55°	65°	75°	85°
0°	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5
2.5°	1152.1	1149.7	1152.1	1142.5	1147.3	1149.7	1154.5	1147.3	1144.9	1147.3	1144.9
5°	1147.3	1144.9	1147.3	1149.7	1154.5	1161.7	1159.3	1159.3	1164.2	1154.5	1154.5
7.5°	1106.3	1103.9	1118.4	1123.2	1142.5	1159.3	1178.6	1171.4	1181.0	1178.6	1171.4
10°	1055.7	1048.5	1062.9	1089.4	1118.4	1161.7	1181.0	1185.8	1207.5	1217.2	1212.4
12.5°	1026.8	1019.5	1038.8	1058.1	1103.9	1156.9	1190.7	1202.7	1226.8	1246.1	1250.9
15°	1005.1	1012.3	1031.6	1067.7	1111.1	1166.6	1195.5	1219.6	1270.2	1289.5	1289.5
17.5°	1019.5	1017.1	1034.0	1070.2	1123.2	1178.6	1222.0	1246.1	1306.4	1332.9	1330.5
20°	1161.7	1147.3	1144.9	1125.6	1142.5	1207.5	1260.6	1284.7	1342.5	1378.7	1376.3
22.5°	1344.9	1359.4	1320.8	1277.4	1224.4	1246.1	1301.5	1335.3	1393.1	1431.7	1417.2
25°	1593.2	1585.9	1559.4	1472.7	1376.3	1330.5	1359.4	1393.1	1465.4	1496.8	1472.7
27.5°	1855.9	1824.6	1790.8	1670.3	1542.6	1458.2	1463.0	1484.7	1569.1	1588.4	1532.9
30°	2137.9	2142.7	2087.3	1923.4	1747.4	1619.7	1610.0	1619.7	1687.2	1684.8	1607.6
32.5°	2460.9	2448.8	2395.8	2219.8	2024.6	1814.9	1790.8	1773.9	1802.9	1776.4	1687.2
35°	2687.4	2699.5	2641.6	2525.9	2330.7	2070.4	2012.6	1971.6	1942.7	1913.7	1817.3
37.5°	2889.9	2875.4	2841.7	2776.6	2586.2	2347.6	2236.7	2200.6	2137.9	2058.4	1969.2
40°	2935.7	2928.5	2911.6	2914.0	2791.1	2605.5	2525.9	2460.9	2352.4	2287.3	2171.6
42.5°	2928.5	2952.6	2957.4	2976.7	2906.8	2861.0	2779.0	2716.4	2615.1	2535.6	2415.1
45°	2967.0	3008.0	3041.7	3058.6	3012.8	3008.0	3017.6	2988.7	2918.8	2836.9	2699.5
47.5°	3044.1	3114.0	3167.1	3203.2	3193.6	3273.1	3222.5	3215.3	3244.2	3164.7	3027.3
50°	3188.8	3208.0	3333.4	3386.4	3475.6	3591.3	3492.5	3516.6	3574.4	3581.6	3328.6
52.5°	3297.2	3314.1	3439.4	3596.1	3793.7	3921.5	3832.3	3829.9	3933.5	3962.4	3620.2
55°	3326.1	3364.7	3526.2	3798.6	4169.7	4299.9	4237.2	4215.5	4352.9	4403.5	3878.1
57.5°	3285.2	3299.6	3531.0	3923.9	4442.1	4724.1	4743.4	4675.9	4801.2	4813.3	4068.5
60°	2841.7	2904.4	3309.3	4003.4	4673.5	5184.4	5285.7	5247.1	5256.8	5235.1	4210.7
62.5°	1964.4	1976.4	2571.7	3919.1	4863.9	5649.6	5818.3	5789.4	5707.5	5502.6	4138.4
65°	935.2	1000.3	1381.1	3316.5	4890.4	6003.9	6331.7	6351.0	5970.2	5505.0	3858.8
67.5°	643.5	645.9	735.1	2340.4	4148.0	6105.2	6606.5	6517.3	5946.1	5454.4	3516.6
70°	407.3	378.4	424.2	1335.3	2803.1	4794.0	5893.1	6206.4	5844.9	5124.2	2971.8
72.5°	161.5	173.5	200.1	438.7	1373.8	2730.8	3849.2	4724.1	5271.2	4432.4	2321.1
75°	72.3	77.1	101.2	183.2	354.3	1113.5	1489.5	2087.3	4217.9	3499.7	1643.8
77.5°	48.2	50.6	65.1	106.1	161.5	310.9	544.7	638.7	2528.4	1913.7	771.3
80°	28.9	31.3	43.4	65.1	89.2	110.9	166.3	192.8	667.6	633.9	212.1
82.5°	19.3	16.9	28.9	36.2	53.0	45.8	53.0	62.7	183.2	161.5	57.8
85°	7.2	7.2	12.1	14.5	19.3	24.1	21.7	26.5	43.4	43.4	26.5
87.5°	0.0	0.0	2.4	2.4	7.2	9.6	12.1	12.1	16.9	16.9	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360404
CATALOG NUMBER: GSS-SB2B-750-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5	1142.5
2.5°	1147.3	1140.0	1142.5	1137.6	1140.0	1135.2	1125.6	1135.2	1128.0	1128.0	1135.2
5°	1154.5	1152.1	1144.9	1132.8	1125.6	1108.7	1082.2	1070.2	1058.1	1050.9	1055.7
7.5°	1178.6	1169.0	1156.9	1128.0	1089.4	1038.8	985.8	925.5	879.7	874.9	858.0
10°	1209.9	1200.3	1173.8	1108.7	1029.2	884.6	768.9	689.3	641.1	609.8	597.7
12.5°	1250.9	1238.9	1190.7	1079.8	884.6	682.1	544.7	486.9	470.0	462.8	460.4
15°	1289.5	1275.0	1190.7	985.8	715.8	513.4	443.5	429.0	426.6	429.0	426.6
17.5°	1325.6	1306.4	1178.6	858.0	549.5	433.8	417.0	409.7	407.3	404.9	404.9
20°	1369.0	1337.7	1144.9	718.3	453.1	412.2	404.9	395.3	395.3	385.6	388.1
22.5°	1410.0	1366.6	1079.8	578.5	417.0	400.1	392.9	383.2	378.4	371.2	371.2
25°	1451.0	1395.5	1002.7	479.6	395.3	388.1	380.8	371.2	359.1	349.5	349.5
27.5°	1511.2	1434.1	911.1	438.7	383.2	371.2	363.9	351.9	337.4	325.4	325.4
30°	1578.7	1487.1	836.4	431.4	378.4	349.5	337.4	318.2	308.5	298.9	298.9
32.5°	1660.7	1559.4	780.9	443.5	366.4	320.6	301.3	282.0	274.8	274.8	274.8
35°	1781.2	1665.5	720.7	445.9	351.9	291.6	260.3	241.0	241.0	250.7	250.7
37.5°	1942.7	1781.2	689.3	441.1	339.8	262.7	226.6	212.1	209.7	219.3	219.3
40°	2128.3	1908.9	701.4	424.2	323.0	233.8	200.1	188.0	185.6	188.0	190.4
42.5°	2330.7	2046.3	730.3	400.1	294.1	209.7	180.8	173.5	171.1	171.1	171.1
45°	2545.2	2140.3	759.2	376.0	265.1	190.4	168.7	163.9	161.5	161.5	161.5
47.5°	2750.1	2215.0	739.9	354.3	241.0	178.4	159.1	159.1	156.7	156.7	156.7
50°	2926.0	2207.8	658.0	332.6	214.5	168.7	154.3	151.8	151.8	149.4	149.4
52.5°	3024.9	2060.8	530.3	308.5	190.4	159.1	149.4	147.0	144.6	142.2	142.2
55°	3063.4	1865.5	412.2	272.4	173.5	151.8	144.6	142.2	137.4	135.0	132.6
57.5°	2995.9	1578.7	318.2	216.9	159.1	142.2	137.4	135.0	130.2	122.9	120.5
60°	2858.6	1265.4	238.6	166.3	142.2	130.2	130.2	127.7	118.1	106.1	103.6
62.5°	2617.5	908.7	180.8	135.0	122.9	118.1	122.9	118.1	103.6	86.8	84.4
65°	2277.7	561.6	139.8	115.7	108.5	103.6	110.9	106.1	89.2	69.9	65.1
67.5°	*1904.1*	*286.8*	*108.5*	*98.8*	*91.6*	*86.8*	*94.0*	*94.0*	*77.1*	*57.8*	*55.4*
70°	1470.3	159.1	86.8	81.9	74.7	67.5	79.5	81.9	67.5	50.6	48.2
72.5°	1091.8	101.2	69.9	67.5	57.8	48.2	65.1	69.9	57.8	38.6	36.2
75°	713.4	79.5	53.0	53.0	41.0	38.6	55.4	60.3	50.6	28.9	28.9
77.5°	342.3	60.3	41.0	36.2	28.9	28.9	48.2	50.6	36.2	21.7	21.7
80°	113.3	41.0	28.9	24.1	19.3	19.3	38.6	28.9	19.3	16.9	16.9
82.5°	38.6	26.5	19.3	16.9	14.5	12.1	12.1	14.5	14.5	12.1	12.1
85°	19.3	16.9	14.5	12.1	9.6	9.6	9.6	9.6	12.1	12.1	12.1
87.5°	12.1	12.1	9.6	7.2	7.2	7.2	7.2	7.2	9.6	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)