Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1365404

Luminaire Tested: **GSS-SB4B-750-U-SLL-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1365404
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4B-750-U-SLL-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 148W 70CRI 5000K FIXTURE w/ 90° Spill Light Eliminator LETT OPTIC OPTIC AND HOUSE SIDE SHIELD
Light Source:	(104) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17554.8 lumens
Efficiency:	N/A
Efficacy:	118.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G3


Input Watts (W):	148
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.1 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3948.9	0.0	3948.9
	% Fixture	22.5	0.0	22.5
Street Side	Lumens	13605.9	0.0	13605.9
	% Fixture	77.5	0.0	77.5
Total	Lumens	17554.8	0.0	17554.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.5	1.7
10°-20°	806.1	4.6
20°-30°	1154.6	6.6
30°-40°	1448.3	8.3
40°-50°	2379.1	13.6
50°-60°	4295.6	24.5
60°-70°	4768.8	27.2
70°-80°	2155.6	12.3
80°-90°	255.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17554.8	100.0
0°-180°	17554.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1268.2	7.2			
FM	(30°-60°)	5913.6	33.7			
FH	(60°-80°)	6205.1	35.3			G3/7500
FVH	(80°-90°)	219.1	1.2			G2/225
BL	(0°-30°)	984.1	5.6	B2/1000		
BM	(30°-60°)	2209.5	12.6	B2/2500		
BH	(60°-80°)	719.3	4.1	B2/1000		G2/1000
BVH	(80°-90°)	36.1	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8
2.5°	3339.9	3383.0	3377.6	3436.8	3490.7	3528.4	3560.7	3550.0	3523.0	3469.1	3431.4
5°	3690.0	3722.3	3776.2	3889.3	3975.5	4050.9	4040.2	4050.9	3970.1	3889.3	3792.4
7.5°	3991.7	4029.4	4104.8	4266.4	4374.1	4465.7	4454.9	4422.6	4331.0	4196.4	4050.9
10°	4180.2	4207.2	4288.0	4471.1	4595.0	4670.4	4643.5	4589.6	4471.1	4336.4	4164.1
12.5°	4261.0	4293.3	4363.4	4508.8	4589.6	4573.5	4562.7	4551.9	4492.7	4390.3	4234.1
15°	4271.8	4293.3	4347.2	4411.9	4379.5	4288.0	4266.4	4347.2	4422.6	4401.1	4271.8
17.5°	4271.8	4304.1	4314.9	4250.2	4083.3	3916.3	3894.7	4029.4	4239.5	4406.5	4331.0
20°	4288.0	4304.1	4282.6	4072.5	3760.0	3576.9	3539.2	3706.2	4018.6	4347.2	4390.3
22.5°	4309.5	4325.7	4234.1	3862.4	3496.1	3302.2	3280.6	3404.5	3770.8	4261.0	4454.9
25°	4352.6	4341.8	4201.8	3679.2	3264.4	3081.3	3049.0	3210.6	3566.1	4174.8	4562.7
27.5°	4406.5	4358.0	4158.7	3528.4	3097.5	2903.5	2882.0	3038.2	3393.7	4067.1	4654.3
30°	4476.5	4428.0	4153.3	3409.9	2973.6	2779.6	2752.7	2925.1	3275.2	3991.7	4783.5
32.5°	4573.5	4503.4	4158.7	3318.3	2903.5	2720.4	2704.2	2887.4	3226.7	3948.6	4918.2
35°	4702.7	4600.4	4180.2	3286.0	2925.1	2801.2	2838.9	2978.9	3275.2	3980.9	5139.1
37.5°	4864.3	4767.4	4288.0	3356.0	3162.1	3248.3	3345.2	3399.1	3506.9	4131.7	5494.6
40°	5133.7	4999.0	4449.6	3582.3	3797.7	4201.8	4390.3	4368.8	4121.0	4476.5	5995.6
42.5°	5510.8	5386.9	4778.2	4158.7	4859.0	5715.5	6033.3	5850.1	5101.4	5026.0	6819.8
45°	6087.2	5882.5	5219.9	5015.2	6141.0	7547.0	8263.5	7633.2	6345.7	5893.2	7994.1
47.5°	6825.2	6620.5	5909.4	5871.7	7573.9	9809.5	10660.6	9421.6	7579.3	7029.9	9400.1
50°	8010.3	7784.0	6922.1	6744.4	9157.7	12066.6	13203.2	11204.7	8834.5	8236.5	11134.7
52.5°	9637.1	9486.3	8527.4	7644.0	10574.4	14555.3	15535.8	13068.6	9804.1	9615.6	13025.5
55°	11905.0	11759.6	10617.5	8645.9	11915.8	17049.5	17841.3	14765.4	10649.9	11231.6	15002.4
57.5°	14474.5	14716.9	13478.0	9981.9	13327.1	19058.8	20163.1	16306.1	11791.9	13391.8	17200.3
60°	16149.9	16914.8	16758.6	12314.4	15519.6	21558.3	22759.6	18369.2	13461.8	14980.9	17151.8
62.5°	14695.4	15460.3	16656.2	15018.6	17631.2	23820.8	24833.5	20540.2	15121.0	13715.0	14404.5
65°	12470.6	13424.1	14684.6	13047.0	17259.6	23890.8	24930.5	20621.0	14108.2	10138.1	10213.5
67.5°	10746.8	11592.6	13144.0	11102.4	15298.7	21757.6	22576.4	18396.2	11662.6	6722.8	6663.6
70°	8969.1	9744.9	11705.7	9884.9	13402.5	18751.7	18046.0	15465.7	9858.0	4465.7	3700.8
72.5°	7644.0	8360.4	10402.1	8883.0	10633.7	15196.4	12438.3	12831.5	8021.1	2838.9	2521.1
75°	6324.2	6981.4	8845.3	8042.6	8796.8	9480.9	8597.5	9114.6	6609.7	2407.9	1944.7
77.5°	4438.8	4848.2	6205.7	6399.6	6846.7	5613.1	5451.5	6383.4	4702.7	1195.9	818.8
80°	2187.1	2440.3	3237.5	3808.5	3237.5	3183.6	3630.8	4250.2	2440.3	732.6	452.5
82.5°	980.4	1163.6	1492.2	2305.6	1169.0	1271.3	1605.3	2262.5	1109.7	436.3	193.9
85°	156.2	172.4	290.9	387.9	317.8	490.2	468.7	441.7	237.0	118.5	53.9
87.5°	5.4	5.4	5.4	10.8	16.2	21.5	26.9	26.9	26.9	26.9	26.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8
2.5°	3420.7	3404.5	3323.7	3242.9	3172.9	3102.8	3032.8	2935.8	2860.4	2795.8	2768.9
5°	3743.9	3657.7	3533.8	3399.1	3280.6	3145.9	3016.7	2871.2	2752.7	2628.8	2564.2
7.5°	3964.7	3878.6	3673.8	3469.1	3323.7	3178.3	3043.6	2882.0	2725.8	2548.0	2451.0
10°	4067.1	3970.1	3749.3	3512.2	3334.5	3189.0	3065.1	2930.5	2774.2	2553.4	2424.1
12.5°	4137.1	4018.6	3765.4	3523.0	3345.2	3194.4	3075.9	2978.9	2887.4	2671.9	2521.1
15°	4180.2	4072.5	3808.5	3528.4	3329.1	3151.3	3038.2	3005.9	3022.0	2919.7	2736.5
17.5°	4244.9	4142.5	3862.4	3560.7	3302.2	3059.7	2935.8	3005.9	3151.3	3183.6	3038.2
20°	4331.0	4223.3	3932.4	3587.7	3221.4	2887.4	2768.9	2946.6	3189.0	3356.0	3275.2
22.5°	4428.0	4341.8	4013.2	3614.6	3102.8	2661.1	2607.2	2822.7	3081.3	3296.8	3302.2
25°	4546.5	4465.7	4126.3	3641.5	2941.2	2467.2	2478.0	2661.1	2865.8	3086.7	3124.4
27.5°	4708.1	4632.7	4266.4	3673.8	2774.2	2311.0	2364.8	2499.5	2639.6	2774.2	2828.1
30°	4885.9	4826.6	4433.4	3738.5	2618.0	2219.4	2251.7	2343.3	2456.4	2537.2	2564.2
32.5°	5128.3	5031.3	4589.6	3733.1	2499.5	2176.3	2144.0	2170.9	2262.5	2343.3	2348.7
35°	5430.0	5354.6	4751.2	3636.1	2391.8	2154.8	2041.6	2025.5	2079.3	2160.1	2154.8
37.5°	5871.7	5807.1	5015.2	3485.3	2257.1	2100.9	1933.9	1880.0	1917.7	1971.6	1987.8
40°	6534.3	6367.3	5316.8	3318.3	2122.4	2003.9	1804.6	1729.2	1756.1	1815.4	1826.2
42.5°	7433.9	7116.1	5720.9	3092.1	1993.1	1858.5	1675.3	1594.5	1610.7	1664.5	1675.3
45°	8586.7	8107.2	6275.7	2855.0	1890.8	1707.6	1540.6	1454.5	1470.6	1529.9	1556.8
47.5°	9933.4	9276.2	6857.5	2601.9	1831.5	1589.1	1406.0	1341.3	1379.0	1438.3	1449.1
50°	11522.5	10859.9	7229.2	2397.2	1793.8	1497.6	1282.1	1255.1	1303.6	1352.1	1362.9
52.5°	13257.1	12314.4	6992.2	2230.2	1761.5	1465.2	1195.9	1206.7	1244.4	1292.9	1309.0
55°	14943.2	12847.7	6205.7	2014.7	1723.8	1486.8	1131.2	1158.2	1206.7	1244.4	1255.1
57.5°	16042.1	12400.6	4999.0	1788.4	1680.7	1502.9	1098.9	1120.5	1174.3	1217.4	1222.8
60°	15083.3	11420.2	3743.9	1594.5	1589.1	1476.0	1088.1	1055.8	1131.2	1169.0	1174.3
62.5°	12357.5	9340.8	2391.8	1411.4	1416.7	1416.7	1082.8	948.1	1045.1	1077.4	1072.0
65°	*8489.7*	*6604.3*	*1481.4*	*1152.8*	*1206.7*	*1287.5*	*1050.4*	*835.0*	*948.1*	*980.4*	*969.6*
67.5°	5580.8	4196.4	915.8	888.8	991.2	1115.1	985.8	748.8	851.1	872.7	840.4
70°	3027.4	1977.0	603.3	581.8	775.7	878.1	835.0	673.4	759.5	781.1	748.8
72.5°	1998.5	1136.6	425.6	425.6	608.7	614.1	684.1	603.3	673.4	694.9	662.6
75°	1502.9	732.6	296.3	328.6	387.9	479.4	490.2	506.4	571.0	597.9	565.6
77.5°	689.5	269.3	177.8	242.4	269.3	366.3	312.4	377.1	425.6	436.3	409.4
80°	398.6	150.8	118.5	156.2	172.4	301.7	183.2	226.2	301.7	317.8	285.5
82.5°	167.0	75.4	80.8	97.0	102.4	167.0	129.3	145.4	199.3	193.9	172.4
85°	48.5	48.5	53.9	59.3	59.3	97.0	91.6	86.2	91.6	91.6	75.4
87.5°	32.3	32.3	32.3	37.7	37.7	43.1	48.5	53.9	53.9	53.9	48.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8
2.5°	2731.1	2682.7	2612.6	2601.9	2564.2	2537.2	2564.2	2591.1	2639.6	2645.0	2666.5
5°	2504.9	2391.8	2305.6	2208.6	2160.1	2154.8	2144.0	2176.3	2246.3	2289.4	2321.7
7.5°	2354.1	2149.4	1998.5	1863.9	1815.4	1777.7	1810.0	1804.6	1896.2	1933.9	1966.2
10°	2273.3	1987.8	1761.5	1594.5	1529.9	1492.2	1486.8	1497.6	1551.4	1589.1	1626.8
12.5°	2327.1	1923.1	1589.1	1395.2	1325.2	1282.1	1244.4	1244.4	1255.1	1303.6	1319.8
15°	2504.9	1960.8	1508.3	1298.2	1206.7	1136.6	1088.1	1050.4	1055.8	1061.2	1077.4
17.5°	2763.5	2057.8	1481.4	1239.0	1142.0	1055.8	1007.3	964.3	953.5	953.5	948.1
20°	3011.3	2133.2	1459.8	1190.5	1066.6	991.2	948.1	910.4	894.2	894.2	894.2
22.5°	3113.6	2197.8	1432.9	1131.2	991.2	921.2	883.4	856.5	851.1	851.1	845.7
25°	3032.8	2176.3	1400.6	1072.0	921.2	867.3	835.0	808.0	802.6	808.0	802.6
27.5°	2779.6	2100.9	1357.5	1023.5	867.3	818.8	791.9	764.9	759.5	764.9	764.9
30°	2510.3	1971.6	1287.5	985.8	824.2	770.3	743.4	716.5	716.5	721.8	727.2
32.5°	2294.8	1842.3	1206.7	937.3	775.7	727.2	700.3	673.4	673.4	684.1	684.1
35°	2111.7	1740.0	1125.9	888.8	732.6	678.7	657.2	635.7	630.3	641.0	646.4
37.5°	1966.2	1648.4	1039.7	840.4	689.5	641.0	619.5	592.6	587.2	597.9	608.7
40°	1815.4	1546.0	964.3	781.1	646.4	597.9	576.4	544.1	544.1	554.8	565.6
42.5°	1669.9	1454.5	915.8	727.2	603.3	549.5	527.9	501.0	501.0	511.8	522.5
45°	1551.4	1368.3	888.8	673.4	554.8	506.4	479.4	457.9	463.3	474.0	484.8
47.5°	1438.3	1276.7	894.2	646.4	522.5	457.9	431.0	414.8	425.6	441.7	452.5
50°	1352.1	1212.0	899.6	603.3	479.4	420.2	393.2	382.5	398.6	414.8	425.6
52.5°	1298.2	1147.4	867.3	549.5	447.1	382.5	366.3	366.3	382.5	393.2	404.0
55°	1244.4	1039.7	797.3	490.2	414.8	355.5	344.8	344.8	360.9	371.7	377.1
57.5°	1201.3	926.5	716.5	441.7	377.1	328.6	328.6	328.6	334.0	339.4	350.1
60°	1120.5	808.0	614.1	404.0	339.4	307.1	301.7	301.7	296.3	301.7	317.8
62.5°	980.4	678.7	522.5	360.9	307.1	280.1	274.7	258.6	242.4	247.8	258.6
65°	*829.6*	*538.7*	*436.3*	*312.4*	*264.0*	*247.8*	*242.4*	*215.5*	*193.9*	*199.3*	*215.5*
67.5°	662.6	404.0	366.3	269.3	226.2	210.1	210.1	193.9	177.8	177.8	188.5
70°	517.1	339.4	274.7	215.5	177.8	177.8	188.5	172.4	150.8	150.8	167.0
72.5°	420.2	274.7	220.9	167.0	140.1	150.8	156.2	140.1	123.9	123.9	134.7
75°	328.6	215.5	172.4	123.9	107.7	113.1	123.9	113.1	97.0	102.4	107.7
77.5°	226.2	145.4	113.1	91.6	80.8	86.2	86.2	80.8	75.4	75.4	80.8
80°	150.8	97.0	75.4	64.6	59.3	59.3	53.9	53.9	59.3	59.3	64.6
82.5°	107.7	70.0	59.3	48.5	37.7	37.7	43.1	43.1	48.5	48.5	53.9
85°	64.6	48.5	43.1	32.3	26.9	32.3	32.3	37.7	43.1	43.1	48.5
87.5°	48.5	37.7	32.3	26.9	21.5	21.5	26.9	26.9	32.3	37.7	37.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365404
CATALOG NUMBER: GSS-SB4B-750-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8	3032.8
2.5°	2720.4	2785.0	2876.6	2957.4	3054.4	3151.3	3242.9	3329.1	3334.5	3339.9
5°	2424.1	2553.4	2704.2	2887.4	3081.3	3269.8	3469.1	3630.8	3668.5	3690.0
7.5°	2095.5	2284.0	2515.7	2774.2	3065.1	3356.0	3636.1	3878.6	3970.1	3991.7
10°	1750.7	1982.4	2262.5	2596.5	2989.7	3377.6	3754.7	4050.9	4158.7	4180.2
12.5°	1443.7	1632.2	1955.4	2359.5	2833.5	3345.2	3797.7	4126.3	4234.1	4261.0
15°	1179.7	1357.5	1659.2	2084.7	2618.0	3232.1	3765.4	4142.5	4250.2	4271.8
17.5°	975.0	1088.1	1362.9	1826.2	2424.1	3086.7	3722.3	4153.3	4255.6	4271.8
20°	894.2	915.8	1061.2	1513.7	2219.4	2978.9	3695.4	4169.4	4271.8	4288.0
22.5°	856.5	856.5	888.8	1152.8	1933.9	2865.8	3684.6	4217.9	4293.3	4309.5
25°	818.8	818.8	829.6	905.0	1594.5	2725.8	3706.2	4304.1	4352.6	4352.6
27.5°	781.1	781.1	791.9	808.0	1185.1	2494.1	3711.6	4401.1	4422.6	4406.5
30°	743.4	754.2	754.2	764.9	872.7	2203.2	3679.2	4508.8	4508.8	4476.5
32.5°	705.7	711.1	721.8	727.2	759.5	1826.2	3625.4	4643.5	4616.6	4573.5
35°	673.4	678.7	678.7	689.5	721.8	1459.8	3566.1	4826.6	4751.2	4702.7
37.5°	630.3	635.7	641.0	651.8	684.1	1158.2	3479.9	4982.9	4929.0	4864.3
40°	592.6	597.9	603.3	614.1	646.4	996.6	3372.2	5219.9	5209.1	5133.7
42.5°	549.5	560.2	565.6	571.0	614.1	910.4	3296.8	5602.4	5602.4	5510.8
45°	511.8	522.5	522.5	533.3	592.6	835.0	3463.8	6130.3	6173.4	6087.2
47.5°	479.4	484.8	484.8	490.2	560.2	770.3	3910.9	6938.3	6884.4	6825.2
50°	447.1	457.9	447.1	452.5	533.3	808.0	4648.9	7972.6	8112.6	8010.3
52.5°	425.6	431.0	409.4	409.4	495.6	856.5	5252.2	9292.4	9761.0	9637.1
55°	398.6	404.0	377.1	377.1	436.3	743.4	5289.9	10795.3	11824.2	11905.0
57.5°	371.7	371.7	350.1	344.8	377.1	603.3	4692.0	11958.9	14291.4	14474.5
60°	339.4	334.0	323.2	312.4	344.8	554.8	3576.9	11802.6	15514.2	16149.9
62.5°	290.9	301.7	296.3	274.7	312.4	517.1	2332.5	10213.5	14135.2	14695.4
65°	*242.4*	*258.6*	*258.6*	*242.4*	*344.8*	*452.5*	*1228.2*	*8177.3*	*11797.3*	*12470.6*
67.5°	215.5	226.2	220.9	210.1	307.1	285.5	592.6	6270.3	10100.4	10746.8
70°	188.5	199.3	183.2	172.4	247.8	204.7	350.1	4196.4	8338.9	8969.1
72.5°	156.2	167.0	150.8	134.7	183.2	156.2	231.6	2731.1	6943.7	7644.0
75°	129.3	134.7	123.9	107.7	134.7	123.9	161.6	1783.1	5807.1	6324.2
77.5°	91.6	102.4	97.0	80.8	97.0	86.2	113.1	1018.1	4050.9	4438.8
80°	70.0	70.0	70.0	64.6	59.3	59.3	75.4	457.9	1966.2	2187.1
82.5°	59.3	59.3	53.9	48.5	43.1	37.7	43.1	134.7	926.5	980.4
85°	53.9	43.1	37.7	32.3	26.9	16.2	16.2	37.7	188.5	156.2
87.5°	32.3	26.9	21.5	10.8	5.4	5.4	0.0	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)