

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197805

Luminaire Tested: **TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115528)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
WIDE DISTRIBUTION WITH CLEAR GLASS LENS AND LumaWatt WIRELESS SENSOR
Light Source: (168) 3000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4324.5 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197805

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P197805

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 59-Deg Vertical

REPORT NUMBER: P197805

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2162.2	0.0	2162.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2162.2	0.0	2162.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	4324.5	0.0	4324.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.8	0.8
10°-20°	120.8	2.8
20°-30°	243.1	5.6
30°-40°	418.3	9.7
40°-50°	690.5	16.0
50°-60°	972.3	22.5
60°-70°	1040.2	24.1
70°-80°	660.7	15.3
80°-90°	142.8	3.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4324.5	100.0
0°-180°	4324.5	100.0



REPORT NUMBER: P197805


CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	199.8	4.6			
FM (30°-60°)	1040.6	24.1			
FH (60°-80°)	850.5	19.7			G1/1800
FVH (80°-90°)	71.4	1.7			G1/100
BL (0°-30°)	199.8	4.6	B1/500		
BM (30°-60°)	1040.6	24.1	B2/2500		
BH (60°-80°)	850.5	19.7	B2/1000		G1/1800
BVH (80°-90°)	71.4	1.7			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P197805

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	359.9	359.9	359.9	359.9	359.9	359.9	359.9	359.9	359.9	359.9	359.9
2.5°	367.6	366.6	366.6	366.6	366.6	366.6	366.6	366.6	366.6	366.6	366.6
5°	369.5	369.5	370.4	370.4	371.4	371.4	371.4	372.3	372.3	372.3	373.3
7.5°	373.3	372.3	373.3	373.3	373.3	374.3	374.3	374.3	375.2	376.2	376.2
10°	385.7	384.8	385.7	385.7	385.7	383.8	383.8	384.8	383.8	383.8	383.8
12.5°	400.1	400.1	401.1	402.0	402.0	401.1	400.1	399.1	398.2	398.2	398.2
15°	413.5	414.5	415.4	417.3	418.3	418.3	419.3	420.2	419.3	419.3	418.3
17.5°	434.6	436.5	437.4	438.4	438.4	438.4	440.3	443.2	446.1	448.0	446.1
20°	470.0	470.9	472.9	472.9	471.9	472.9	474.8	475.7	477.6	479.6	480.5
22.5°	493.9	495.8	498.7	498.7	497.7	498.7	500.6	500.6	498.7	499.7	501.6
25°	514.0	515.0	516.9	517.8	518.8	523.6	527.4	526.5	522.6	523.6	522.6
27.5°	537.9	539.9	541.8	541.8	541.8	544.6	548.5	550.4	553.3	552.3	549.4
30°	569.5	572.4	573.4	572.4	574.3	577.2	576.2	578.1	582.9	587.7	582.0
32.5°	594.4	597.3	600.2	604.0	610.7	614.5	612.6	613.6	616.4	620.3	620.3
35°	631.7	636.5	638.4	639.4	646.1	653.8	659.5	664.3	663.3	660.5	665.2
37.5°	688.2	693.0	694.9	698.8	707.4	709.3	717.9	729.4	733.2	729.4	729.4
40°	748.5	753.3	762.9	771.5	784.9	787.8	798.3	803.1	812.7	813.6	807.9
42.5°	798.3	804.0	806.0	820.3	838.5	851.9	863.4	864.3	871.0	876.8	870.1
45°	851.9	856.7	859.6	873.0	882.5	898.8	917.0	924.6	927.5	926.6	930.4
47.5°	901.7	908.4	911.2	921.8	933.3	946.7	957.2	979.2	984.0	974.4	983.0
50°	932.3	940.0	946.7	969.6	989.7	1000.3	1008.9	1027.1	1037.6	1029.0	1031.9
52.5°	980.2	982.1	987.8	997.4	1027.1	1062.5	1072.1	1077.8	1093.1	1097.9	1084.5
55°	1045.3	1052.0	1056.7	1069.2	1081.6	1106.5	1148.6	1156.3	1152.5	1175.4	1151.5
57.5°	1054.8	1067.3	1081.6	1109.4	1134.3	1141.9	1166.8	1196.5	1193.6	1196.5	1198.4
59°	1049.1	1059.6	1072.1	1100.8	1143.8	1154.4	1166.8	1193.6	1206.1	1189.8	1208.9
60°	1051.0	1058.7	1065.4	1088.3	1134.3	1158.2	1165.9	1182.1	1206.1	1184.0	1207.0
62.5°	1043.3	1052.9	1060.6	1074.0	1096.0	1129.5	1159.2	1151.5	1186.0	1168.7	1181.2
65°	1002.2	1012.7	1028.0	1047.2	1073.0	1082.6	1112.3	1128.5	1120.9	1140.0	1119.9
67.5°	933.3	942.8	952.4	975.4	1004.1	1016.5	1024.2	1053.9	1043.3	1065.4	1042.4
70°	841.4	851.9	865.3	877.7	903.6	914.1	922.7	936.1	940.0	940.0	938.0
72.5°	731.3	739.9	748.5	761.0	776.3	785.9	789.7	792.6	807.9	802.1	803.1
75°	606.9	615.5	619.3	624.1	634.6	633.7	637.5	635.6	645.1	641.3	639.4
77.5°	474.8	477.6	488.2	488.2	485.3	490.1	485.3	482.4	480.5	482.4	482.4
80°	329.3	337.9	344.6	349.4	351.3	349.4	350.3	346.5	346.5	343.6	344.6
82.5°	202.9	211.5	214.4	219.2	220.2	220.2	220.2	217.3	218.2	215.4	217.3
85°	99.5	99.5	103.4	108.2	109.1	111.0	111.0	111.0	111.0	111.0	112.0
87.5°	24.9	24.9	26.8	29.7	29.7	30.6	31.6	32.5	32.5	33.5	33.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197805

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-CG-LWR-LW-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	359.9	359.9	359.9	359.9	359.9	359.9	359.9	359.9
2.5°	366.6	366.6	366.6	366.6	366.6	366.6	366.6	366.6
5°	373.3	372.3	372.3	371.4	371.4	370.4	370.4	370.4
7.5°	377.1	377.1	376.2	375.2	374.3	374.3	375.2	375.2
10°	384.8	386.7	387.7	387.7	386.7	386.7	385.7	385.7
12.5°	397.2	399.1	401.1	403.0	403.0	402.0	400.1	399.1
15°	416.4	416.4	417.3	418.3	418.3	416.4	412.5	412.5
17.5°	442.2	440.3	437.4	438.4	439.4	438.4	434.6	436.5
20°	477.6	473.8	471.9	470.0	473.8	473.8	468.1	468.1
22.5°	503.5	500.6	495.8	494.9	497.7	499.7	494.9	492.0
25°	525.5	526.5	520.7	517.8	518.8	519.8	513.1	514.0
27.5°	549.4	550.4	547.5	542.7	540.8	543.7	538.9	537.0
30°	578.1	577.2	579.1	573.4	568.6	571.4	571.4	566.7
32.5°	615.5	612.6	613.6	606.9	601.1	600.2	596.3	590.6
35°	666.2	658.5	652.8	649.0	638.4	636.5	636.5	629.8
37.5°	732.3	720.8	710.2	710.2	694.0	689.2	692.0	683.4
40°	806.0	802.1	785.9	783.0	765.8	754.3	754.3	743.7
42.5°	859.6	864.3	845.2	833.7	822.2	804.0	806.0	792.6
45°	917.9	915.1	898.8	878.7	874.9	855.7	857.6	844.2
47.5°	973.5	956.2	948.6	928.5	919.9	897.8	904.5	894.0
50°	1027.1	1007.9	1000.3	976.3	964.8	940.9	941.9	922.7
52.5°	1082.6	1065.4	1053.9	1023.2	1003.1	985.9	982.1	973.5
55°	1154.4	1136.2	1108.4	1079.7	1064.4	1039.5	1042.4	1029.0
57.5°	1182.1	1170.6	1141.0	1123.7	1095.0	1070.1	1064.4	1040.5
59°	1181.2	1174.5	1144.8	1133.3	1092.2	1071.1	1060.6	1041.4
60°	1174.5	1172.6	1142.9	1128.5	1085.5	1066.3	1056.7	1044.3
62.5°	1154.4	1153.4	1119.9	1102.7	1067.3	1052.0	1046.2	1029.9
65°	1124.7	1108.4	1082.6	1071.1	1034.7	1023.2	1007.0	990.7
67.5°	1053.9	1017.5	1013.7	999.3	967.7	953.4	942.8	927.5
70°	937.1	913.2	913.2	895.0	873.0	866.3	851.9	834.7
72.5°	791.6	785.9	788.7	767.7	757.1	753.3	740.9	725.6
75°	632.7	633.7	630.8	626.0	623.1	624.1	610.7	604.0
77.5°	479.6	488.2	486.3	479.6	486.3	485.3	473.8	470.9
80°	341.7	345.5	347.5	343.6	347.5	344.6	335.0	334.1
82.5°	215.4	216.3	218.2	214.4	215.4	214.4	207.7	207.7
85°	110.1	113.9	109.1	105.3	105.3	101.5	99.5	100.5
87.5°	32.5	34.5	30.6	30.6	28.7	26.8	25.8	25.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)