

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197758

Luminaire Tested: **TT-C3-LED-E1-5WQ-PM-MS/DIM**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197758  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115468)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-5WQ-PM-MS/DIM  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
WIDE DISTRIBUTION WITH DIMMING OCCUPANCY SENSOR  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5652.8 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B3 - U0 - G2


Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P197758  
 CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.3 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197758  
CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral      - - - Horizontal Cone Through 63-Deg Vertical

REPORT NUMBER: P197758

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2826.4	0.0	2826.4
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2826.4	0.0	2826.4
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	5652.8	0.0	5652.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.8	0.7
10°-20°	132.1	2.3
20°-30°	268.5	4.7
30°-40°	462.7	8.2
40°-50°	779.5	13.8
50°-60°	1147.8	20.3
60°-70°	1364.9	24.1
70°-80°	1105.0	19.5
80°-90°	353.5	6.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5652.8	100.0
0°-180°	5652.8	100.0



REPORT NUMBER: P197758


CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	219.7	3.9			
FM (30°-60°)	1195.0	21.1			
FH (60°-80°)	1235.0	21.8			G1/1800
FVH (80°-90°)	176.8	3.1			G2/225
BL (0°-30°)	219.7	3.9	B1/500		
BM (30°-60°)	1195.0	21.1	B2/2500		
BH (60°-80°)	1235.0	21.8	B3/2500		G1/1800
BVH (80°-90°)	176.8	3.1			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P197758

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8
2.5°	396.9	396.9	396.9	396.9	396.9	396.9	395.8	396.9	395.8	395.8	395.8
5°	404.5	404.5	404.5	404.5	403.5	403.5	402.4	402.4	402.4	401.3	402.4
7.5°	407.9	407.9	407.9	407.9	406.8	406.8	406.8	406.8	406.8	406.8	406.8
10°	415.5	415.5	416.6	417.7	419.8	419.8	419.8	421.0	419.8	419.8	419.8
12.5°	431.9	430.8	433.0	435.2	437.4	438.4	438.4	438.4	437.4	437.4	438.4
15°	454.8	452.7	453.7	454.8	456.0	457.1	457.1	456.0	453.7	453.7	453.7
17.5°	484.4	481.1	480.0	478.9	478.9	481.1	483.2	482.2	483.2	482.2	483.2
20°	519.4	517.1	517.1	517.1	518.3	522.6	527.0	529.2	528.1	526.0	529.2
22.5°	542.3	543.4	548.9	547.8	546.7	551.0	556.5	560.9	558.7	555.5	557.6
25°	567.5	567.5	575.2	578.4	575.2	575.2	577.3	580.5	578.4	576.2	578.4
27.5°	595.9	595.9	599.2	602.5	600.2	600.2	603.6	609.1	607.9	606.8	607.9
30°	629.8	625.4	622.1	627.6	633.1	634.2	637.5	646.2	648.4	647.3	649.4
32.5°	661.5	654.9	657.2	660.4	672.5	676.8	675.7	682.3	681.2	678.0	682.3
35°	692.2	699.8	704.1	710.7	715.1	720.6	720.6	732.5	734.8	731.5	734.8
37.5°	751.2	754.5	766.5	767.5	773.0	793.8	795.9	812.4	821.1	816.7	817.9
40°	832.1	830.9	839.8	852.9	863.8	890.0	897.7	908.6	916.3	913.0	917.4
42.5°	897.7	889.0	895.5	923.9	936.0	955.6	965.5	971.0	985.2	980.8	986.3
45°	944.7	947.9	956.8	985.2	992.8	1009.2	1032.1	1042.0	1060.5	1055.2	1058.4
47.5°	990.7	1006.0	1013.6	1026.7	1050.7	1072.6	1101.0	1110.9	1137.2	1134.9	1131.7
50°	1050.7	1062.8	1071.5	1081.3	1114.2	1150.2	1174.3	1178.6	1187.5	1180.9	1191.8
52.5°	1115.2	1114.2	1121.8	1149.1	1195.1	1209.3	1230.1	1249.8	1268.3	1274.9	1268.3
55°	1200.6	1173.2	1204.9	1244.3	1264.0	1297.9	1348.2	1375.5	1411.6	1417.1	1406.1
57.5°	1235.6	1235.6	1268.3	1291.3	1327.4	1387.6	1441.1	1454.2	1472.8	1462.9	1473.9
60°	1231.2	1272.7	1272.7	1313.2	1372.2	1425.8	1445.5	1467.3	1492.5	1491.5	1491.5
62.5°	1236.7	1277.1	1266.1	1336.1	1372.2	1416.0	1459.7	1500.2	1535.2	1534.1	1532.9
63°	1242.1	1277.1	1270.6	1341.6	1371.1	1418.1	1470.7	1511.0	1539.5	1537.3	1538.4
65°	1258.5	1248.7	1288.0	1332.9	1366.8	1436.8	1480.5	1512.1	1531.8	1530.7	1530.7
67.5°	1227.9	1204.9	1260.7	1278.2	1342.7	1405.0	1438.9	1475.0	1489.2	1489.2	1487.0
70°	1133.9	1143.6	1182.0	1210.4	1275.9	1331.8	1360.2	1406.1	1423.6	1423.6	1422.6
72.5°	1038.7	1055.2	1081.3	1121.8	1184.1	1227.9	1261.7	1303.3	1326.3	1325.2	1325.2
75°	917.4	932.7	963.3	1001.6	1056.2	1098.9	1126.2	1165.6	1191.8	1201.7	1190.7
77.5°	780.7	785.1	813.5	852.9	901.0	930.5	972.1	1010.3	1032.1	1031.0	1027.8
80°	614.5	619.9	644.1	688.8	715.1	750.1	788.3	809.1	827.7	827.7	825.5
82.5°	424.2	436.3	460.3	489.8	517.1	547.8	568.6	589.4	604.7	603.6	600.2
85°	239.4	244.9	267.8	286.5	307.2	326.9	341.1	354.3	367.4	367.4	365.1
87.5°	72.1	64.5	77.6	85.3	96.2	106.0	112.6	125.7	134.5	124.7	124.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197758

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8
2.5°	396.9	396.9	396.9	396.9	396.9	396.9	396.9	396.9
5°	402.4	403.5	403.5	404.5	404.5	404.5	404.5	404.5
7.5°	406.8	406.8	406.8	406.8	407.9	407.9	407.9	407.9
10°	419.8	421.0	419.8	419.8	417.7	416.6	416.6	416.6
12.5°	438.4	439.5	439.5	437.4	435.2	433.0	431.9	430.8
15°	456.0	459.2	457.1	456.0	453.7	454.8	454.8	456.0
17.5°	483.2	484.4	481.1	478.9	477.8	480.0	482.2	483.2
20°	530.3	528.1	521.6	519.4	517.1	517.1	519.4	519.4
22.5°	559.9	554.4	550.0	547.8	547.8	547.8	544.5	540.2
25°	580.5	577.3	574.1	576.2	578.4	575.2	567.5	566.3
27.5°	609.1	602.5	601.3	600.2	601.3	599.2	598.1	593.7
30°	646.2	637.5	635.2	633.1	626.5	624.4	626.5	629.8
32.5°	681.2	675.7	678.0	673.5	661.5	657.2	659.3	658.3
35°	731.5	721.7	721.7	712.8	709.6	708.5	699.8	692.2
37.5°	811.3	798.2	794.9	775.3	766.5	768.7	756.7	747.9
40°	908.6	898.8	890.0	868.2	856.1	840.8	833.2	833.2
42.5°	973.1	966.6	954.5	939.2	926.1	899.8	890.0	895.5
45°	1044.2	1035.5	1010.3	995.0	982.9	964.4	953.4	942.6
47.5°	1116.4	1104.4	1074.9	1055.2	1026.7	1021.2	1009.2	993.9
50°	1179.8	1175.4	1154.6	1121.8	1085.7	1077.0	1066.0	1051.8
52.5°	1257.4	1231.2	1213.7	1199.4	1159.0	1130.6	1115.2	1121.8
55°	1384.2	1351.4	1306.6	1261.7	1253.0	1219.1	1180.9	1201.7
57.5°	1457.5	1438.9	1405.0	1334.0	1299.0	1275.9	1250.9	1232.2
60°	1475.0	1441.1	1433.4	1379.8	1324.1	1275.9	1285.8	1242.1
62.5°	1508.9	1462.9	1420.3	1377.7	1343.8	1278.2	1275.9	1253.0
63°	1519.9	1473.9	1429.1	1377.7	1347.1	1285.8	1273.8	1261.7
65°	1517.6	1478.3	1444.4	1377.7	1331.8	1307.7	1248.7	1275.9
67.5°	1476.1	1443.3	1403.9	1358.0	1281.4	1262.9	1221.4	1226.8
70°	1409.4	1366.8	1329.6	1286.9	1225.7	1183.0	1158.0	1137.2
72.5°	1305.5	1267.2	1227.9	1188.5	1133.9	1082.5	1065.0	1042.0
75°	1167.8	1130.6	1094.5	1057.3	1006.0	960.0	941.4	925.0
77.5°	1010.3	978.6	927.2	892.2	862.7	813.5	795.9	778.5
80°	805.8	790.6	753.3	707.5	692.2	644.1	630.9	607.9
82.5°	586.0	570.7	541.2	509.5	491.0	465.8	443.9	428.6
85°	357.5	341.1	325.8	297.4	286.5	267.8	250.4	241.7
87.5°	129.1	115.9	103.9	90.7	84.2	71.0	68.9	62.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)