

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197877

Luminaire Tested: **TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P33418)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
WIDE DISTRIBUTION WITH SOFTENING GLASS LENS AND LumaWatt WIRELESS SENSOR
Light Source: (168) 3000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4335.7 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B2 - U0 - G1

Input Watts (W): 45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197877

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.8 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P197877

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 47.5-Deg Lateral - - - Horizontal Cone Through 54-Deg Vertical

REPORT NUMBER: P197877

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2167.8	0.0	2167.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2167.8	0.0	2167.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	4335.7	0.0	4335.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	1.0
10°-20°	144.1	3.3
20°-30°	296.7	6.8
30°-40°	530.5	12.2
40°-50°	813.9	18.8
50°-60°	1003.5	23.1
60°-70°	907.9	20.9
70°-80°	499.9	11.5
80°-90°	96.7	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4335.7	100.0
0°-180°	4335.7	100.0



REPORT NUMBER: P197877


CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	241.6	5.6			
FM	(30°-60°)	1174.0	27.1			
FH	(60°-80°)	703.9	16.2			G1/1800
FVH	(80°-90°)	48.4	1.1			G1/100
BL	(0°-30°)	241.6	5.6	B1/500		
BM	(30°-60°)	1174.0	27.1	B2/2500		
BH	(60°-80°)	703.9	16.2	B2/1000		G1/1800
BVH	(80°-90°)	48.4	1.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type V Short





REPORT NUMBER: P197877

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5
2.5°	432.4	432.4	432.4	432.4	432.4	432.4	432.4	432.4	432.4	432.4	432.4
5°	438.0	438.0	438.0	438.9	438.0	438.0	438.0	438.0	438.0	438.0	438.0
7.5°	447.4	447.4	447.4	447.4	447.4	447.4	446.4	446.4	447.4	446.4	447.4
10°	460.5	459.5	459.5	460.5	460.5	459.5	460.5	460.5	460.5	460.5	461.4
12.5°	477.3	477.3	478.2	478.2	478.2	479.2	479.2	478.2	479.2	479.2	479.2
15°	499.8	499.8	499.8	499.8	500.7	501.6	500.7	500.7	499.8	499.8	501.6
17.5°	526.0	526.0	526.0	526.0	527.8	527.8	526.9	527.8	528.8	528.8	527.8
20°	557.8	556.8	555.9	556.8	558.7	558.7	559.7	560.6	560.6	560.6	562.5
22.5°	591.5	590.5	592.4	593.3	594.3	595.2	595.2	596.2	598.0	597.1	599.9
25°	628.9	628.0	628.9	630.8	634.5	634.5	635.5	637.3	637.3	636.4	643.0
27.5°	671.0	671.0	672.0	675.7	676.6	677.6	680.4	682.3	685.1	685.1	690.7
30°	716.9	715.9	717.8	721.6	724.4	727.2	730.9	735.6	736.5	737.5	743.1
32.5°	763.7	763.7	765.6	772.1	776.8	781.5	787.1	791.8	793.6	793.6	802.1
35°	813.3	814.2	818.9	823.6	832.9	838.6	844.2	850.7	854.5	856.3	867.6
37.5°	865.7	868.5	872.2	878.8	888.2	897.5	905.9	916.2	921.8	923.7	935.9
40°	915.3	919.0	924.7	934.0	943.4	956.5	966.8	977.1	983.6	987.4	1006.1
42.5°	964.0	965.8	972.4	982.7	994.8	1007.0	1021.0	1032.3	1038.8	1044.4	1065.0
45°	1002.3	1004.2	1012.6	1024.8	1038.8	1053.8	1067.8	1080.9	1087.5	1092.2	1112.8
47.5°	1034.1	1037.9	1047.3	1059.4	1073.5	1091.2	1107.1	1120.3	1128.7	1131.5	1153.0
50°	1057.5	1063.2	1071.6	1085.6	1102.5	1120.3	1137.1	1151.1	1160.5	1164.2	1183.9
52.5°	1070.6	1075.3	1084.7	1098.7	1118.4	1136.2	1153.9	1168.0	1178.3	1182.0	1199.8
54°	1072.5	1075.3	1085.6	1100.6	1120.3	1139.0	1156.7	1170.8	1181.1	1184.8	1203.5
55°	1070.6	1072.5	1083.8	1097.8	1118.4	1137.1	1154.9	1168.9	1180.1	1183.9	1201.7
57.5°	1051.9	1054.7	1064.1	1079.1	1097.8	1119.3	1136.2	1150.2	1161.4	1163.3	1180.1
60°	1013.6	1017.3	1025.7	1041.6	1060.4	1079.1	1095.9	1108.1	1118.4	1124.0	1136.2
62.5°	958.3	960.2	968.6	982.7	999.5	1019.2	1032.3	1044.4	1053.8	1059.4	1069.7
65°	879.7	888.2	894.7	905.9	919.0	934.9	951.8	961.2	965.8	975.2	982.7
67.5°	791.8	797.4	803.9	814.2	822.6	832.9	848.8	857.3	862.9	869.4	876.0
70°	693.5	691.6	699.1	704.7	714.1	720.6	730.9	735.6	742.2	745.9	757.1
72.5°	576.5	579.3	585.9	592.4	595.2	597.1	605.5	608.3	613.9	612.1	626.1
75°	470.7	466.1	467.9	468.9	470.7	468.9	474.5	477.3	480.1	477.3	484.8
77.5°	355.6	350.0	351.9	351.0	351.0	349.1	348.1	348.1	349.1	347.2	351.9
80°	245.2	242.4	243.3	245.2	240.5	241.5	235.8	235.8	235.8	235.8	237.7
82.5°	151.6	147.9	146.9	147.9	147.9	145.1	146.0	142.3	141.3	140.4	148.8
85°	73.9	72.1	73.9	72.1	71.1	71.1	69.3	70.2	68.3	67.4	73.0
87.5°	19.7	18.7	18.7	18.7	17.8	18.7	18.7	18.7	18.7	19.7	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197877

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-SG-LWR-LW-8030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°
0°	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5	430.5
2.5°	432.4	432.4	432.4	432.4	432.4	432.4	432.4	432.4	431.4
5°	438.0	438.0	438.0	438.0	438.0	438.0	438.0	438.0	438.0
7.5°	447.4	447.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4
10°	460.5	461.4	459.5	459.5	460.5	459.5	459.5	458.6	458.6
12.5°	479.2	478.2	479.2	479.2	478.2	477.3	476.4	475.4	476.4
15°	500.7	499.8	499.8	499.8	498.8	498.8	497.9	498.8	497.9
17.5°	526.9	526.9	527.8	525.0	526.0	524.1	524.1	524.1	523.2
20°	560.6	559.7	558.7	555.9	556.8	555.0	554.0	553.1	552.2
22.5°	597.1	595.2	594.3	591.5	592.4	590.5	587.7	585.9	585.9
25°	637.3	635.5	633.6	632.7	631.7	628.0	626.1	623.3	625.2
27.5°	685.1	681.3	678.5	674.8	675.7	671.0	669.2	667.3	667.3
30°	736.5	733.7	729.1	726.2	725.3	720.6	716.9	715.0	714.1
32.5°	792.7	790.8	788.0	783.3	781.5	774.0	771.2	768.4	767.4
35°	859.1	854.5	851.7	845.1	838.6	833.9	827.3	825.4	823.6
37.5°	920.9	920.9	916.2	908.7	899.4	892.8	887.2	883.5	880.7
40°	986.4	984.5	977.1	970.5	961.2	951.8	941.5	937.8	935.9
42.5°	1044.4	1040.7	1033.2	1024.8	1015.4	1004.2	993.0	987.4	986.4
45°	1093.1	1088.4	1080.9	1069.7	1057.5	1046.3	1036.0	1030.4	1027.6
47.5°	1132.4	1126.8	1117.4	1107.1	1093.1	1080.0	1069.7	1064.1	1060.4
50°	1161.4	1156.7	1146.5	1133.4	1119.3	1104.3	1094.0	1087.5	1084.7
52.5°	1180.1	1173.6	1162.4	1148.3	1132.4	1117.4	1105.3	1097.8	1095.0
54°	1183.9	1176.4	1164.2	1149.3	1132.4	1116.5	1105.3	1096.9	1094.0
55°	1182.0	1174.5	1161.4	1147.4	1129.6	1113.7	1101.5	1093.1	1090.3
57.5°	1162.4	1153.9	1141.8	1126.8	1108.1	1092.2	1080.9	1071.6	1068.8
60°	1120.3	1112.8	1098.7	1085.6	1066.9	1051.0	1038.8	1029.5	1026.7
62.5°	1055.7	1049.1	1037.0	1023.9	1004.2	990.2	978.0	972.4	964.9
65°	969.6	964.9	952.7	936.8	922.8	908.7	896.6	892.8	888.2
67.5°	866.6	860.1	855.4	839.5	828.3	815.2	803.0	795.5	793.6
70°	745.0	742.2	737.5	722.5	715.9	704.7	696.3	689.7	687.9
72.5°	613.9	611.1	610.2	602.7	594.3	584.0	580.2	574.6	573.7
75°	477.3	475.4	477.3	471.7	468.9	466.1	464.2	464.2	461.4
77.5°	345.3	348.1	349.1	349.1	351.0	351.0	352.8	350.0	347.2
80°	234.9	237.7	236.8	238.6	237.7	244.3	239.6	243.3	239.6
82.5°	141.3	145.1	145.1	145.1	148.8	147.9	147.9	149.7	148.8
85°	69.3	70.2	69.3	68.3	73.0	72.1	72.1	71.1	72.1
87.5°	20.6	18.7	19.7	17.8	19.7	16.8	18.7	18.7	19.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)