Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1365781

Luminaire Tested: **GSS-SB2C-750-U-T2R**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1365781
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-750-U-T2R
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 5000K FIXTURE w/ TYPE II ROADWAY DISTRIBUTION OPTIC
Light Source:	(52) 5000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	14675.2 lumens
Efficiency:	N/A
Efficacy:	143.9 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B2 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.6 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2770.3	0.0	2770.3
	% Fixture	18.9	0.0	18.9
Street Side	Lumens	11904.9	0.0	11904.9
	% Fixture	81.1	0.0	81.1
Total	Lumens	14675.2	0.0	14675.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.5	1.4
10°-20°	711.3	4.8
20°-30°	1300.2	8.9
30°-40°	2106.8	14.4
40°-50°	2897.7	19.7
50°-60°	3249.0	22.1
60°-70°	2738.3	18.7
70°-80°	1357.2	9.2
80°-90°	112.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14675.2	100.0
0°-180°	14675.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1568.1	10.7			
FM	(30°-60°)	6866.4	46.8			
FH	(60°-80°)	3396.7	23.1			G2/5000
FVH	(80°-90°)	73.7	0.5			G1/100
BL	(0°-30°)	645.9	4.4	B2/1000		
BM	(30°-60°)	1387.2	9.5	B2/2500		
BH	(60°-80°)	698.8	4.8	B2/1000		G2/1000
BVH	(80°-90°)	38.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°	85°
0°	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3
2.5°	2462.8	2449.3	2439.1	2405.2	2384.8	2330.5	2286.4	2211.8	2116.8	2110.0	2035.4
5°	2839.4	2822.4	2808.8	2761.3	2741.0	2646.0	2561.2	2428.9	2293.2	2269.5	2120.2
7.5°	3144.7	3124.3	3110.8	3066.7	3025.9	2951.3	2842.8	2683.3	2486.6	2442.5	2245.7
10°	3358.4	3358.4	3355.0	3327.9	3304.1	3232.9	3107.4	2920.8	2686.7	2635.8	2378.0
12.5°	3524.6	3514.4	3528.0	3545.0	3548.4	3507.7	3392.3	3182.0	2900.4	2849.5	2517.1
15°	3538.2	3541.6	3592.5	3660.3	3745.1	3758.7	3663.7	3443.2	3107.4	3039.5	2679.9
17.5°	3470.3	3487.3	3558.5	3670.5	3833.3	3931.7	3911.3	3714.6	3331.3	3260.0	2829.2
20°	3450.0	3470.3	3541.6	3680.7	3874.0	4036.9	4097.9	3955.4	3555.2	3456.8	2992.0
22.5°	3572.1	3578.9	3629.8	3745.1	3931.7	4118.3	4254.0	4186.1	3792.6	3684.1	3178.6
25°	3904.6	3897.8	3894.4	3921.5	4060.6	4223.4	4389.7	4403.2	4040.3	3931.7	3355.0
27.5°	4457.5	4484.6	4406.6	4257.4	4270.9	4396.4	4525.4	4596.6	4281.1	4162.4	3531.4
30°	5146.1	5142.8	5003.7	4762.8	4579.6	4623.7	4695.0	4779.8	4522.0	4413.4	3728.2
32.5°	5733.0	5719.5	5570.2	5292.0	5003.7	4908.7	4935.8	4952.8	4800.1	4678.0	3928.3
35°	6109.6	6113.0	5970.5	5729.6	5407.4	5251.3	5183.5	5142.8	5078.3	4959.6	4165.8
37.5°	6486.1	6465.8	6286.0	6001.0	5733.0	5604.1	5526.1	5353.1	5336.1	5231.0	4376.1
40°	6767.7	6747.3	6564.1	6238.5	5994.2	5889.1	5858.5	5597.3	5624.5	5532.9	4610.2
42.5°	6896.6	6900.0	6733.8	6438.6	6187.6	6136.7	6197.8	5878.9	5929.8	5845.0	4864.6
45°	6900.0	6883.0	6767.7	6533.6	6343.6	6302.9	6469.2	6197.8	6262.2	6184.2	5159.7
47.5°	6713.4	6713.4	6665.9	6526.8	6425.1	6428.4	6696.4	6520.0	6635.4	6577.7	5502.3
50°	6306.3	6340.2	6360.6	6387.7	6384.3	6516.6	6879.6	6855.9	7035.7	7018.7	5885.7
52.5°	5064.7	5207.2	5719.5	6048.5	6258.8	6506.5	7079.8	7201.9	7541.1	7571.7	6438.6
55°	4040.3	4074.2	4505.0	5353.1	5977.3	6421.7	7151.0	7592.0	8189.1	8236.6	6944.1
57.5°	3280.4	3361.8	3623.0	4433.8	5363.3	6231.7	7198.5	7802.3	8599.5	8677.6	7361.3
60°	2425.5	2473.0	2724.0	3395.7	4491.4	5787.3	7225.6	7995.7	9077.8	9189.8	7904.1
62.5°	1784.4	1787.8	1947.2	2371.2	3545.0	5057.9	7015.3	8151.7	9393.3	9522.2	8077.1
65°	1153.4	1167.0	1326.4	1692.8	2395.0	4145.4	6530.2	7541.1	9084.6	9274.6	7972.0
67.5°	776.8	800.6	895.6	1078.8	1604.6	2958.1	5095.3	6981.4	9369.6	9620.6	8226.4
68°	739.5	742.9	817.5	993.9	1428.2	2618.9	4898.5	6910.2	9383.2	9644.4	8195.8
70°	586.9	593.7	641.1	736.1	970.2	1604.6	3955.4	6313.1	9132.1	9362.8	7751.5
72.5°	447.8	458.0	488.5	525.8	631.0	983.8	2313.6	5142.8	8470.6	8799.7	7018.7
75°	379.9	383.3	407.1	420.6	413.9	597.0	1299.3	4023.3	7205.3	7507.2	5763.6
77.5°	298.5	308.7	342.6	349.4	315.5	413.9	681.9	2296.6	4230.2	4131.8	2774.9
80°	213.7	220.5	247.6	234.1	247.6	285.0	322.3	824.3	1760.6	1536.7	651.3
82.5°	74.6	84.8	169.6	162.8	162.8	128.9	145.9	359.6	458.0	400.3	162.8
85°	13.6	17.0	47.5	67.8	61.1	47.5	61.1	111.9	91.6	78.0	47.5
87.5°	3.4	3.4	6.8	6.8	6.8	10.2	17.0	23.7	27.1	27.1	27.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365781
CATALOG NUMBER: GSS-SB2C-750-U-T2R

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3	1974.3
2.5°	1994.7	1943.8	1845.4	1757.2	1686.0	1618.1	1563.9	1526.5	1499.4	1485.8	1485.8
5°	2038.8	1930.2	1750.4	1591.0	1468.9	1387.5	1336.6	1306.0	1302.7	1299.3	1299.3
7.5°	2106.6	1954.0	1686.0	1485.8	1380.7	1336.6	1323.0	1319.6	1319.6	1326.4	1326.4
10°	2198.2	1994.7	1658.8	1448.5	1390.9	1377.3	1370.5	1380.7	1384.1	1387.5	1390.9
12.5°	2306.8	2045.6	1645.3	1465.5	1431.6	1424.8	1428.2	1424.8	1435.0	1441.7	1438.3
15°	2411.9	2110.0	1658.8	1499.4	1472.3	1468.9	1458.7	1465.5	1462.1	1458.7	1458.7
17.5°	2530.7	2184.7	1672.4	1526.5	1499.4	1485.8	1472.3	1465.5	1451.9	1448.5	1445.1
20°	2659.6	2259.3	1696.2	1550.3	1506.2	1475.7	1451.9	1424.8	1404.4	1394.2	1394.2
22.5°	2791.9	2337.3	1716.5	1553.7	1492.6	1438.3	1397.6	1363.7	1333.2	1312.8	1302.7
25°	2927.6	2415.3	1723.3	1540.1	1451.9	1387.5	1333.2	1292.5	1251.8	1231.4	1224.6
27.5°	3066.7	2483.2	1713.1	1506.2	1397.6	1326.4	1265.3	1221.2	1187.3	1163.6	1163.6
30°	3202.3	2547.6	1686.0	1458.7	1340.0	1268.7	1207.7	1167.0	1136.4	1116.1	1112.7
32.5°	3358.4	2612.1	1652.1	1397.6	1282.3	1217.8	1156.8	1119.5	1092.3	1082.1	1085.5
35°	3514.4	2669.8	1597.8	1340.0	1221.2	1167.0	1109.3	1078.8	1068.6	1061.8	1058.4
37.5°	3667.1	2710.5	1526.5	1268.7	1170.4	1105.9	1078.8	1048.2	1021.1	987.2	983.8
40°	3823.1	2744.4	1435.0	1197.5	1112.7	1061.8	1048.2	1007.5	943.1	885.4	885.4
42.5°	4002.9	2778.3	1336.6	1129.6	1041.4	1017.7	1014.3	949.8	854.9	814.2	810.8
45°	4216.7	2802.1	1248.4	1065.2	966.8	956.6	983.8	899.0	820.9	787.0	790.4
47.5°	4464.3	2856.3	1170.4	993.9	895.6	912.5	915.9	851.5	790.4	749.7	749.7
50°	4783.2	2951.3	1088.9	902.4	844.7	882.0	851.5	804.0	739.5	715.8	712.4
52.5°	5207.2	3029.3	1021.1	827.7	810.8	848.1	807.4	756.5	702.2	668.3	664.9
55°	5529.5	3032.7	956.6	770.1	787.0	780.2	763.3	709.0	668.3	627.6	627.6
57.5°	5875.5	3012.4	899.0	736.1	763.3	732.7	719.2	661.5	620.8	590.3	583.5
60°	6248.7	2975.1	837.9	712.4	742.9	698.8	668.3	620.8	586.9	563.1	563.1
62.5°	6313.1	2795.3	763.3	705.6	719.2	664.9	617.4	580.1	546.2	532.6	532.6
65°	6194.4	2605.3	678.5	671.7	681.9	624.2	569.9	536.0	508.8	495.3	491.9
67.5°	6197.8	2296.6	610.6	631.0	614.0	576.7	522.4	491.9	458.0	447.8	447.8
68°	*6089.2*	*2222.0*	*586.9*	*624.2*	*600.4*	*563.1*	*508.8*	*474.9*	*444.4*	*441.0*	*441.0*
70°	5580.4	1801.3	502.1	576.7	559.7	515.6	447.8	430.8	410.5	407.1	410.5
72.5°	4874.8	1329.8	403.7	485.1	498.7	400.3	393.5	386.7	363.0	363.0	359.6
75°	3813.0	970.2	305.3	383.3	369.8	366.4	335.8	332.4	312.1	308.7	301.9
77.5°	1730.1	495.3	206.9	254.4	295.1	325.7	281.6	271.4	257.8	257.8	254.4
80°	485.1	254.4	139.1	145.9	179.8	264.6	220.5	200.1	210.3	203.5	176.4
82.5°	149.3	105.2	84.8	91.6	84.8	152.7	162.8	125.5	111.9	118.7	125.5
85°	50.9	47.5	40.7	44.1	37.3	61.1	71.2	47.5	50.9	50.9	44.1
87.5°	27.1	27.1	20.4	17.0	13.6	10.2	6.8	6.8	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-6
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-750-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896
CIE u':	0.2101
CIE v':	0.4901
Duv:	0.0035
CIE x:	0.3489
CIE y:	0.3618
CIE z:	0.2893
Peak Wavelength (nm):	443
Dominant Wavelength (nm):	570
Purity:	13.25435
Rf:	70.7
Rg:	96.8

CRI (Ra):	70.2
R1:	68.1
R2:	73.9
R3:	79.4
R4:	72.1
R5:	69.2
R6:	65.7
R7:	78.1
R8:	55.3
R9:	-35.1
R10:	39.3
R11:	71.1
R12:	43.8
R13:	68.1
R14:	88.4
R15:	59.7



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4896K
CIE x = 0.3489
CIE y = 0.3618
Duv = 0.0035

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			


REPORT NUMBER: SP1-2407-184-6

TM-30-18


Summary


R_f = 70.7
R_g = 96.8
CIE R_a = 70.2
R_9 = -35.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-6

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	





REPORT NUMBER: SP1-2407-184-6

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-6

TM-30-18

Measure Comparisons





(END OF REPORT)