

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197949

Luminaire Tested: **TT-C3-LED-E1-RW-PM-LWR-LW-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34693)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-RW-PM-LWR-LW-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION WITH LumaWatt WIRELESS SENSOR
Light Source: (168) 3000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3880.3 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197949

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-LWR-LW-8030

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.6 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197949

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-LWR-LW-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197949

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-LWR-LW-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1940.2	0.0	1940.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1940.2	0.0	1940.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	3880.3	0.0	3880.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	0.5
10°-20°	62.0	1.6
20°-30°	130.1	3.4
30°-40°	247.3	6.4
40°-50°	459.7	11.8
50°-60°	814.6	21.0
60°-70°	1058.0	27.3
70°-80°	842.7	21.7
80°-90°	247.9	6.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3880.3	100.0
0°-180°	3880.3	100.0



REPORT NUMBER: P197949


CATALOG NUMBER: TT-C3-LED-E1-RW-PM-LWR-LW-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	105.1	2.7			
FM	(30°-60°)	760.8	19.6			
FH	(60°-80°)	950.3	24.5			G1/1800
FVH	(80°-90°)	124.0	3.2			G2/225
BL	(0°-30°)	105.1	2.7	B0/110		
BM	(30°-60°)	760.8	19.6	B1/1000		
BH	(60°-80°)	950.3	24.5	B2/1000		G2/1000
BVH	(80°-90°)	124.0	3.2			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P197949

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-LWR-LW-8030

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	182.3	182.3	182.3	182.3	182.3
2.5°	184.0	184.0	184.9	184.9	184.9
5°	187.4	187.4	188.3	188.3	187.4
7.5°	191.7	193.4	192.6	190.9	190.9
10°	198.6	199.4	197.7	196.9	196.0
12.5°	207.1	208.0	204.6	203.7	202.0
15°	219.1	218.3	214.8	211.4	211.4
17.5°	235.4	230.2	224.2	221.7	220.0
20°	254.2	247.4	239.6	233.7	232.8
22.5°	275.6	266.2	255.9	247.4	246.5
25°	296.1	288.4	275.6	264.5	261.0
27.5°	318.4	312.4	296.1	283.3	280.7
30°	344.1	338.9	320.1	308.1	307.3
32.5°	374.0	367.2	346.6	338.1	337.2
35°	410.0	397.1	379.2	373.2	383.4
37.5°	444.2	429.7	415.1	425.4	433.9
40°	474.2	464.7	457.9	479.3	491.3
42.5°	503.3	498.1	503.3	534.9	571.7
45°	534.1	535.8	554.6	641.1	707.0
47.5°	570.0	570.9	615.4	748.0	810.5
50°	609.4	608.5	687.3	828.5	928.6
52.5°	647.9	651.3	759.2	1001.4	1187.1
55°	682.1	701.0	856.7	1175.1	1298.4
57.5°	712.1	748.0	948.3	1226.5	1320.6
60°	744.6	804.5	1012.5	1236.8	1319.8
62.5°	776.3	849.0	1026.2	1282.1	1404.5
65°	805.4	869.6	1046.7	1347.2	1456.7
67.5°	829.4	879.9	1046.7	1290.7	1370.3
70°	849.0	867.0	986.0	1188.8	1264.1
72.5°	844.8	813.9	885.8	1063.9	1107.5
75°	804.5	720.7	780.6	895.3	938.9
77.5°	703.5	603.4	635.9	721.5	749.8
80°	557.2	470.7	489.6	544.3	552.9
82.5°	392.9	338.1	344.9	386.9	392.9
85°	231.1	208.0	201.1	238.8	250.8
87.5°	68.5	59.9	59.1	71.9	79.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)