Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1501643

Luminaire Tested: GSS-SB2C-930-U-T2LG

Issue Date: 07/20/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1501643
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	7/20/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-930-U-T2LG
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 90CRI 3000K FIXTURE w/ TYPE II LOW GLARE DISTRIBUTION FIXTURE
Light Source:	(52) 3000K CCT, 90 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9584.6 lumens
Efficiency:	N/A
Efficacy:	94.0 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type II - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

Iso-Footcandle Lines of Horizontal Illumination




Based on 10 foot mounting height. Maximum calculated value = 23.2 fc
Type II - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2577.4	0.0	2577.4
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	7007.2	0.0	7007.2
	% Fixture	73.1	0.0	73.1
Total	Lumens	9584.6	0.0	9584.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	1.5
10°-20°	416.8	4.3
20°-30°	789.5	8.2
30°-40°	1391.9	14.5
40°-50°	2058.4	21.5
50°-60°	2417.2	25.2
60°-70°	1751.3	18.3
70°-80°	540.1	5.6
80°-90°	74.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9584.6	100.0
0°-180°	9584.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	783.7	8.2			
FM	(30°-60°)	4448.3	46.4			
FH	(60°-80°)	1735.1	18.1			G1/1800
FVH	(80°-90°)	40.1	0.4			G1/100
BL	(0°-30°)	567.6	5.9	B2/1000		
BM	(30°-60°)	1419.2	14.8	B2/2500		
BH	(60°-80°)	556.3	5.8	B2/1000		G2/1000
BVH	(80°-90°)	34.2	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type II Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	67°	75°	85°
0°	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1
2.5°	1572.7	1577.1	1570.5	1574.9	1574.9	1568.3	1566.1	1557.4	1561.8	1559.6	1557.4
5°	1609.8	1612.0	1607.6	1614.2	1614.2	1616.4	1614.2	1603.3	1603.3	1603.3	1598.9
7.5°	1598.9	1598.9	1601.1	1622.9	1644.8	1673.2	1673.2	1668.8	1673.2	1671.0	1651.3
10°	1507.2	1515.9	1535.6	1590.2	1642.6	1703.8	1745.3	1758.4	1758.4	1760.6	1727.8
12.5°	1343.3	1349.9	1395.8	1478.8	1588.0	1699.4	1799.9	1865.4	1872.0	1882.9	1839.2
15°	1197.0	1201.4	1234.1	1319.3	1443.8	1640.4	1830.4	1965.9	1987.7	2033.6	1968.1
17.5°	1210.1	1207.9	1216.7	1249.4	1339.0	1544.3	1823.9	2083.8	2123.1	2204.0	2147.2
20°	1288.7	1288.7	1295.3	1301.8	1334.6	1474.4	1775.8	2179.9	2256.4	2413.7	2348.1
22.5°	1413.2	1413.2	1411.1	1422.0	1422.0	1505.0	1778.0	2252.0	2365.6	2647.4	2584.0
25°	1585.8	1577.1	1577.1	1581.4	1561.8	1620.8	1832.6	2326.3	2474.8	2924.8	2870.2
27.5°	1780.2	1786.8	1782.4	1767.1	1740.9	1786.8	1963.7	2442.1	2597.1	3217.5	3195.6
30°	1992.1	1994.3	1998.6	1989.9	1968.1	2000.8	2169.0	2616.8	2758.8	3523.3	3571.3
32.5°	2199.6	2230.2	2219.3	2197.4	2206.1	2265.1	2422.4	2852.7	2999.1	3807.2	3977.6
35°	2463.9	2474.8	2518.5	2437.7	2439.9	2540.3	2745.7	3162.9	3304.9	4102.1	4383.9
37.5°	2848.3	2868.0	2848.3	2721.6	2702.0	2841.8	3060.2	3468.7	3571.3	4324.9	4761.8
40°	3226.2	3250.2	3283.0	3134.5	3010.0	3125.7	3357.3	3702.4	3809.4	4447.2	5013.0
42.5°	3538.6	3577.9	3542.9	3499.3	3385.7	3407.5	3564.8	3883.7	3990.7	4602.3	5266.4
45°	3802.9	3809.4	3824.7	3794.1	3737.3	3717.7	3741.7	4043.2	4161.1	4672.2	5390.9
47.5°	3912.1	3940.5	3953.6	4006.0	4065.0	4025.7	3892.4	4117.4	4224.4	4667.9	5430.2
50°	3853.1	3881.5	3951.4	4075.9	4217.9	4287.8	4069.4	4220.1	4340.2	4746.5	5511.0
52.5°	3698.0	3728.6	3842.2	3984.2	4222.3	4381.7	4318.4	4434.1	4549.9	4886.3	5646.4
55°	3322.3	3368.2	3527.7	3763.6	4091.2	4331.5	4580.5	4748.7	4875.4	5054.5	5786.2
57.5°	2776.3	2824.3	3003.4	3357.3	3848.7	4124.0	4656.9	5338.4	5395.2	5255.4	5799.3
60°	*2079.5*	*2118.8*	*2372.2*	*2656.1*	*3232.8*	*3743.9*	*4613.3*	*5897.6*	*6041.8*	*5220.5*	*5382.1*
62.5°	1647.0	1695.0	1920.0	2051.1	2463.9	3093.0	4460.4	6052.7	6177.2	4932.2	4801.1
65°	1286.6	1319.3	1529.0	1716.9	1817.3	2112.2	3822.5	5294.8	5406.2	4462.5	3962.3
67.5°	849.7	899.9	1148.9	1406.7	1459.1	1343.3	2629.9	4073.7	4126.2	3547.3	2979.4
70°	609.4	633.4	819.1	1094.3	1173.0	899.9	1432.9	3084.2	3099.5	2380.9	2007.4
72.5°	415.0	419.4	557.0	838.8	934.9	653.1	788.5	2031.4	1979.0	1175.2	1148.9
75°	281.8	286.1	356.0	559.2	661.8	454.3	513.3	1107.4	1063.8	648.7	696.8
77.5°	190.0	194.4	244.6	375.7	441.2	314.5	375.7	585.4	574.5	430.3	373.5
80°	144.2	150.7	181.3	240.3	308.0	183.5	214.1	277.4	281.8	229.4	190.0
82.5°	80.8	89.6	109.2	122.3	198.8	102.7	102.7	166.0	159.5	142.0	102.7
85°	34.9	37.1	43.7	45.9	80.8	43.7	37.1	72.1	74.3	69.9	32.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.7	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1
2.5°	1546.5	1559.6	1546.5	1539.9	1539.9	1529.0	1524.6	1524.6	1509.4	1515.9	1511.5
5°	1581.4	1585.8	1570.5	1550.9	1524.6	1502.8	1472.2	1432.9	1408.9	1406.7	1408.9
7.5°	1636.0	1638.2	1596.7	1553.0	1487.5	1408.9	1315.0	1238.5	1170.8	1159.9	1173.0
10°	1712.5	1708.1	1647.0	1544.3	1406.7	1240.7	1096.5	1026.6	987.3	985.1	982.9
12.5°	1815.2	1786.8	1692.8	1507.2	1266.9	1074.7	1000.4	996.0	1007.0	1015.7	1017.9
15°	1933.1	1896.0	1730.0	1435.1	1124.9	1013.5	1017.9	1055.0	1068.1	1076.9	1076.9
17.5°	2079.5	2031.4	1771.5	1332.4	1052.8	1026.6	1057.2	1092.2	1114.0	1122.7	1120.5
20°	2273.9	2173.4	1804.2	1234.1	1033.2	1048.5	1074.7	1109.6	1131.5	1142.4	1142.4
22.5°	2468.3	2343.8	1810.8	1166.4	1033.2	1050.7	1074.7	1109.6	1133.7	1144.6	1142.4
25°	2732.6	2562.2	1813.0	1118.4	1035.4	1039.7	1061.6	1092.2	1127.1	1138.0	1142.4
27.5°	3014.3	2802.5	1823.9	1107.4	1026.6	1024.4	1039.7	1068.1	1103.1	1131.5	1133.7
30°	3363.8	3073.3	1828.3	1118.4	1028.8	1000.4	1011.3	1039.7	1076.9	1105.3	1114.0
32.5°	3706.8	3324.5	1819.5	1142.4	1033.2	985.1	987.3	1004.8	1044.1	1063.8	1079.0
35°	4069.4	3591.0	1804.2	1175.2	1035.4	978.6	958.9	967.6	993.9	996.0	1002.6
37.5°	4353.3	3789.8	1758.4	1218.8	1039.7	954.5	915.2	908.7	897.8	875.9	880.3
40°	4587.0	3923.0	1681.9	1240.7	1028.8	926.1	860.6	830.0	788.5	755.8	762.3
42.5°	4755.2	4012.6	1590.2	1245.1	1011.3	878.1	797.3	744.8	699.0	664.0	666.2
45°	4829.5	4003.8	1491.9	1212.3	969.8	819.1	738.3	688.1	637.8	600.7	596.3
47.5°	4831.7	3918.6	1356.5	1133.7	899.9	751.4	683.7	629.1	587.6	561.4	559.2
50°	4849.2	3870.6	1229.8	1020.1	808.2	679.3	635.6	581.0	557.0	519.9	508.9
52.5°	4958.4	3949.2	1142.4	895.6	723.0	626.9	594.1	546.1	506.8	482.7	480.5
55°	5135.3	4084.7	1094.3	801.6	642.2	576.7	554.8	513.3	478.4	454.3	447.8
57.5°	5157.1	4154.6	1037.5	714.3	576.7	537.3	528.6	482.7	432.5	415.0	408.5
60°	*4851.3*	*4036.6*	*967.6*	*633.4*	*528.6*	*506.8*	*502.4*	*441.2*	*399.7*	*377.9*	*369.1*
62.5°	4434.1	3741.7	860.6	559.2	491.5	476.2	458.7	410.6	358.2	334.2	327.6
65°	3623.8	3145.4	731.7	508.9	454.3	436.9	432.5	367.0	332.0	318.9	316.7
67.5°	2745.7	2527.2	644.4	471.8	415.0	408.5	393.2	371.3	356.0	340.8	336.4
70°	1941.8	1823.9	548.3	423.8	375.7	364.8	428.1	404.1	349.5	329.8	327.6
72.5°	1177.3	1144.6	474.0	380.1	323.3	340.8	395.4	364.8	314.5	290.5	281.8
75°	742.7	679.3	397.5	323.3	257.7	277.4	345.1	325.5	270.9	246.8	240.3
77.5°	404.1	375.7	299.3	264.3	203.1	225.0	301.4	268.7	216.2	235.9	209.7
80°	176.9	196.6	198.8	152.9	135.4	166.0	216.2	209.7	166.0	168.2	139.8
82.5°	85.2	111.4	128.9	104.8	76.5	98.3	144.2	120.1	111.4	104.8	100.5
85°	26.2	41.5	56.8	50.2	34.9	41.5	67.7	65.5	78.6	67.7	63.3
87.5°	8.7	8.7	6.6	6.6	6.6	8.7	10.9	6.6	2.2	2.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1
2.5°	1509.4	1511.5	1511.5	1513.7	1513.7	1520.3	1529.0	1537.8	1531.2	1539.9	1542.1
5°	1404.5	1415.4	1424.2	1456.9	1483.1	1505.0	1529.0	1550.9	1557.4	1561.8	1572.7
7.5°	1157.7	1188.3	1245.1	1319.3	1402.3	1483.1	1537.8	1594.5	1603.3	1614.2	1629.5
10°	985.1	998.2	1037.5	1114.0	1262.5	1422.0	1555.2	1644.8	1681.9	1703.8	1719.0
12.5°	1013.5	1004.8	998.2	1009.1	1105.3	1310.6	1544.3	1716.9	1786.8	1810.8	1830.4
15°	1081.2	1072.5	1048.5	1017.9	1028.8	1192.6	1507.2	1784.6	1896.0	1935.3	1976.8
17.5°	1120.5	1111.8	1092.2	1059.4	1031.0	1094.3	1437.3	1845.7	2068.5	2116.6	2175.6
20°	1142.4	1133.7	1114.0	1081.2	1048.5	1057.2	1347.7	1922.2	2265.1	2341.6	2428.9
22.5°	1146.8	1135.8	1114.0	1081.2	1061.6	1055.0	1262.5	1968.1	2477.0	2595.0	2695.4
25°	1144.6	1124.9	1096.5	1072.5	1061.6	1059.4	1203.6	1994.3	2706.4	2894.2	3007.8
27.5°	1129.3	1105.3	1076.9	1059.4	1055.0	1068.1	1177.3	2024.9	2975.0	3215.3	3396.6
30°	1111.8	1076.9	1041.9	1035.4	1046.3	1087.8	1199.2	2035.8	3256.8	3564.8	3750.5
32.5°	1065.9	1039.7	1004.8	1002.6	1028.8	1103.1	1249.4	2020.5	3505.8	3914.3	4148.0
35°	1000.4	985.1	965.5	972.0	1013.5	1116.2	1284.4	1972.4	3733.0	4239.7	4512.8
37.5°	884.6	895.6	906.5	921.8	974.2	1114.0	1299.7	1896.0	3920.8	4499.7	4849.2
40°	755.8	792.9	827.9	867.2	937.1	1096.5	1304.0	1802.1	4030.0	4696.3	5148.4
42.5°	675.0	709.9	753.6	810.4	886.8	1057.2	1299.7	1697.2	4065.0	4831.7	5338.4
45°	600.7	642.2	696.8	755.8	843.1	1000.4	1260.3	1583.6	4082.5	4895.0	5419.3
47.5°	561.4	585.4	635.6	694.6	786.4	930.5	1183.9	1500.6	4056.3	4908.1	5517.6
50°	515.5	548.3	581.0	637.8	727.4	843.1	1092.2	1452.6	4099.9	5037.0	5672.6
52.5°	480.5	498.0	533.0	585.4	650.9	762.3	1004.8	1413.2	4220.1	5168.1	5834.3
55°	454.3	474.0	495.8	539.5	589.8	681.5	915.2	1354.3	4359.9	5307.9	5995.9
57.5°	412.8	425.9	456.5	502.4	535.2	602.9	810.4	1284.4	4349.0	5198.6	5716.3
60°	*375.7*	*388.8*	*421.6*	*467.4*	*487.1*	*533.0*	*707.7*	*1194.8*	*4139.3*	*4842.6*	*5200.8*
62.5°	334.2	349.5	388.8	421.6	439.0	474.0	600.7	1031.0	3702.4	4307.5	4598.0
65°	316.7	325.5	351.7	391.0	388.8	421.6	506.8	810.4	2979.4	3291.8	3556.1
67.5°	336.4	349.5	345.1	356.0	349.5	367.0	454.3	650.9	2341.6	2479.2	2632.1
70°	332.0	362.6	377.9	356.0	305.8	325.5	393.2	519.9	1675.4	1662.3	1655.7
72.5°	290.5	321.1	364.8	386.6	299.3	270.9	340.8	450.0	1074.7	1070.3	967.6
75°	246.8	268.7	321.1	349.5	257.7	218.4	292.7	382.3	642.2	650.9	581.0
77.5°	227.2	216.2	268.7	308.0	209.7	168.2	235.9	288.3	353.9	358.2	332.0
80°	163.8	157.3	201.0	225.0	159.5	120.1	133.2	179.1	190.0	170.4	176.9
82.5°	104.8	107.0	120.1	144.2	98.3	65.5	91.7	120.1	102.7	83.0	98.3
85°	67.7	76.5	63.3	74.3	30.6	30.6	39.3	52.4	34.9	24.0	26.2
87.5°	0.0	0.0	4.4	8.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1501643
CATALOG NUMBER: GSS-SB2C-930-U-T2LG

CANDELA DISTRIBUTION (continued):

	285°	293°	295°	305°	315°	325°	335°	345°	355°	360°
0°	1542.1	1542.1	*1542.1*	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1	1542.1
2.5°	1548.7	1546.5	*1546.5*	1550.9	1561.8	1566.1	1572.7	1570.5	1577.1	1572.7
5°	1579.3	1581.4	*1588.0*	1590.2	1596.7	1605.5	1607.6	1605.5	1609.8	1609.8
7.5°	1640.4	1649.2	*1644.8*	1655.7	1647.0	1636.0	1618.6	1605.5	1594.5	1598.9
10°	1743.1	1738.7	*1736.5*	1716.9	1677.5	1620.8	1574.9	1524.6	1515.9	1507.2
12.5°	1856.7	1852.3	*1852.3*	1784.6	1673.2	1555.2	1450.4	1371.7	1345.5	1343.3
15°	2016.1	1987.7	*1961.5*	1819.5	1596.7	1395.8	1273.5	1212.3	1197.0	1197.0
17.5°	2214.9	2140.6	*2096.9*	1793.3	1472.2	1290.9	1218.8	1203.6	1199.2	1210.1
20°	2461.7	2273.9	*2210.5*	1734.3	1426.4	1304.0	1269.1	1271.3	1273.5	1288.7
22.5°	2732.6	2396.2	*2291.3*	1734.3	1472.2	1387.0	1369.6	1393.6	1400.1	1413.2
25°	3034.0	2505.4	*2363.4*	1826.1	1607.6	1544.3	1522.5	1546.5	1564.0	1585.8
27.5°	3372.6	2619.0	*2487.9*	1992.1	1782.4	1743.1	1719.0	1730.0	1754.0	1780.2
30°	3676.2	2809.0	*2678.0*	2245.5	2020.5	1972.4	1930.9	1948.4	1974.6	1992.1
32.5°	3944.9	3040.6	*2929.2*	2512.0	2293.5	2210.5	2164.6	2160.3	2212.7	2199.6
35°	4191.7	3313.6	*3206.6*	2815.6	2570.9	2468.3	2407.1	2485.7	2450.8	2463.9
37.5°	4386.1	3597.6	*3512.4*	3106.1	2859.3	2719.5	2682.3	2778.4	2833.0	2848.3
40°	4545.5	3844.4	*3754.8*	3394.4	3123.6	3020.9	3079.9	3239.3	3232.8	3226.2
42.5°	4667.9	4056.3	*3958.0*	3612.8	3376.9	3396.6	3442.5	3549.5	3575.7	3538.6
45°	4722.5	4189.5	*4110.9*	3785.4	3665.3	3778.9	3798.5	3844.4	3826.9	3802.9
47.5°	4785.8	4307.5	*4224.4*	3942.7	3977.6	4089.0	4049.7	4012.6	3949.2	3912.1
50°	4892.8	4447.2	*4377.4*	4172.0	4298.7	4261.6	4108.7	4025.7	3896.8	3853.1
52.5°	5096.0	4711.5	*4659.1*	4534.6	4449.4	4235.4	4049.7	3901.2	3757.0	3698.0
55°	5277.3	5069.8	*5039.2*	4873.2	4403.6	4097.8	3848.7	3619.4	3372.6	3322.3
57.5°	5382.1	5663.9	*5698.9*	5017.4	4193.9	3785.4	3418.4	3051.5	2817.8	2776.3
60°	*5069.8*	*6306.1*	*6323.6*	*4989.0*	*3816.0*	*3221.9*	*2662.7*	*2402.7*	*2151.5*	*2079.5*
62.5°	4639.5	6172.9	*6157.6*	4818.6	3038.4	2350.3	2022.7	1900.3	1705.9	1647.0
65°	3988.5	5141.9	*5159.3*	4163.3	2020.5	1699.4	1699.4	1544.3	1328.1	1286.6
67.5°	3250.2	3964.5	*3925.2*	2699.8	1240.7	1360.8	1426.4	1203.6	899.9	849.7
70°	2112.2	3027.4	*2972.8*	1557.4	779.8	1133.7	1122.7	904.3	644.4	609.4
72.5°	908.7	1749.6	*1861.0*	795.1	587.6	913.0	895.6	633.4	430.3	415.0
75°	548.3	880.3	*958.9*	506.8	428.1	688.1	620.3	401.9	292.7	281.8
77.5°	347.3	482.7	*478.4*	380.1	321.1	465.3	417.2	277.4	198.8	190.0
80°	201.0	238.1	*246.8*	238.1	216.2	332.0	266.5	201.0	155.1	144.2
82.5°	128.9	148.5	*150.7*	115.8	120.1	214.1	144.2	118.0	89.6	80.8
85°	56.8	63.3	*61.2*	39.3	39.3	87.4	50.2	48.1	34.9	34.9
87.5°	2.2	4.4	*2.2*	2.2	2.2	8.7	4.4	6.6	6.6	6.6
90°	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2106-271-2

Luminaire Tested: GFLD-SA1-A-930-U-WR-X-BK

Test Date: 06/16/2021

Report Generated By FNC07603 / LDUCLS01DT446
Version: v6.09

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Test Information


Test Method:	LM-79-08
Report Number:	SP1-2106-271-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1
Measurement Geometry:	4π
Issue Date:	06/16/2021
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	**GFLD-SA1-A-930-U-WR-X-BK**
Description:	MCGRAW EDISON

N6, BLACK

Spectral Parameters

CCT (K):	3038	CRI (Ra):	92.3		
CIE u':	0.2481	R1:	92.0	R9:	58.9
CIE v':	0.5247	R2:	94.8	R10:	87.0
Duv:	0.0030	R3:	96.7	R11:	93.2
CIE x:	0.4384	R4:	93.0	R12:	81.1
CIE y:	0.4121	R5:	91.4	R13:	92.5
CIE z:	0.1495	R6:	93.7	R14:	97.4
Peak Wavelength (nm):	624	R7:	93.9		
Dominant Wavelength (nm):	581	R8:	82.9		
Purity:	55.6				

Rf:	92.8
Rg:	98



Test Conditions

Stabilization Time:	82M
Operation Time:	12H
Room Temperature (°C) / RH%:	24.3/43%
Sphere Temperature (°C):	24.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	1/31/2021	7/31/2021
Power Meter	XITRON 2801 IN0071	12/1/2020	12/1/2021
AC Power Source	CHROMA 61603 IN0063	12/1/2020	12/1/2021
DC Power Source	AGILENT E3634A IN0208	12/1/2020	12/1/2021
Sphere Thermometer	ONSET IN0085	12/1/2020	12/1/2021
Room Thermometer	ONSET IN0046	12/1/2020	12/1/2021


Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3038K
CIE x = 0.4384
CIE y = 0.4121
Duv = 0.0030

Point lies inside the ANSI 3000K 4-step quadrangle

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

Photopic Flux vs. Wavelength




######

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	718	NR	490	11837	NR	620	36553	NR	750	3581	NR	880	702	NR
365	573	NR	495	13045	NR	625	36706	NR	755	3240	NR	885	837	NR
370	566	NR	500	14286	NR	630	35946	NR	760	2875	NR	890	938	NR
375	689	NR	505	15591	NR	635	35109	NR	765	2561	NR	895	722	NR
380	659	NR	510	16757	NR	640	33848	NR	770	2263	NR	900	712	NR
385	616	NR	515	17969	NR	645	32907	NR	775	1981	NR	905	660	NR
390	575	NR	520	19153	NR	650	31426	NR	780	1758	NR	910	722	NR
395	507	NR	525	20279	NR	655	29538	NR	785	1656	NR	915	683	NR
400	452	NR	530	21424	NR	660	27902	NR	790	1510	NR	920	536	NR
405	442	NR	535	22450	NR	665	25950	NR	795	1317	NR	925	653	NR
410	492	NR	540	23201	NR	670	23596	NR	800	1296	NR	930	693	NR
415	658	NR	545	23916	NR	675	21412	NR	805	1239	NR	935	1009	NR
420	1015	NR	550	24774	NR	680	19353	NR	810	1094	NR	940	1041	NR
425	1715	NR	555	25531	NR	685	17528	NR	815	1156	NR	945	716	NR
430	3048	NR	560	26160	NR	690	15706	NR	820	966	NR	950	700	NR
435	5481	NR	565	26923	NR	695	13845	NR	825	931	NR	955	812	NR
440	9614	NR	570	27732	NR	700	12373	NR	830	938	NR	960	505	NR
445	14315	NR	575	28529	NR	705	10898	NR	835	822	NR	965	551	NR
450	14893	NR	580	29552	NR	710	9649	NR	840	838	NR	970	824	NR
455	11988	NR	585	30530	NR	715	8554	NR	845	759	NR	975	814	NR
460	10638	NR	590	31835	NR	720	7611	NR	850	712	NR	980	926	NR
465	9480	NR	595	32776	NR	725	6679	NR	855	651	NR	985	954	NR
470	8416	NR	600	33912	NR	730	5833	NR	860	789	NR	990	814	NR
475	8624	NR	605	35057	NR	735	5111	NR	865	715	NR	995	765	NR
480	9529	NR	610	35715	NR	740	4579	NR	870	935	NR	1000	954	NR
485	10656	NR	615	36371	NR	745	4054	NR	875	919	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: 2650.8 **S/P: 1.41**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	718	NR	490	11837	NR	620	36553	NR	750	3581	NR	880	702	NR
365	573	NR	495	13045	NR	625	36706	NR	755	3240	NR	885	837	NR
370	566	NR	500	14286	NR	630	35946	NR	760	2875	NR	890	938	NR
375	689	NR	505	15591	NR	635	35109	NR	765	2561	NR	895	722	NR
380	659	NR	510	16757	NR	640	33848	NR	770	2263	NR	900	712	NR
385	616	NR	515	17969	NR	645	32907	NR	775	1981	NR	905	660	NR
390	575	NR	520	19153	NR	650	31426	NR	780	1758	NR	910	722	NR
395	507	NR	525	20279	NR	655	29538	NR	785	1656	NR	915	683	NR
400	452	NR	530	21424	NR	660	27902	NR	790	1510	NR	920	536	NR
405	442	NR	535	22450	NR	665	25950	NR	795	1317	NR	925	653	NR
410	492	NR	540	23201	NR	670	23596	NR	800	1296	NR	930	693	NR
415	658	NR	545	23916	NR	675	21412	NR	805	1239	NR	935	1009	NR
420	1015	NR	550	24774	NR	680	19353	NR	810	1094	NR	940	1041	NR
425	1715	NR	555	25531	NR	685	17528	NR	815	1156	NR	945	716	NR
430	3048	NR	560	26160	NR	690	15706	NR	820	966	NR	950	700	NR
435	5481	NR	565	26923	NR	695	13845	NR	825	931	NR	955	812	NR
440	9614	NR	570	27732	NR	700	12373	NR	830	938	NR	960	505	NR
445	14315	NR	575	28529	NR	705	10898	NR	835	822	NR	965	551	NR
450	14893	NR	580	29552	NR	710	9649	NR	840	838	NR	970	824	NR
455	11988	NR	585	30530	NR	715	8554	NR	845	759	NR	975	814	NR
460	10638	NR	590	31835	NR	720	7611	NR	850	712	NR	980	926	NR
465	9480	NR	595	32776	NR	725	6679	NR	855	651	NR	985	954	NR
470	8416	NR	600	33912	NR	730	5833	NR	860	789	NR	990	814	NR
475	8624	NR	605	35057	NR	735	5111	NR	865	715	NR	995	765	NR
480	9529	NR	610	35715	NR	740	4579	NR	870	935	NR	1000	954	NR
485	10656	NR	615	36371	NR	745	4054	NR	875	919	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1008.8 **S/P: 0.54**

λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)	λ (nm)	Power (µW/nm)	Lumens (ϕ/nm)
360	718	NR	490	11837	NR	620	36553	NR	750	3581	NR	880	702	NR
365	573	NR	495	13045	NR	625	36706	NR	755	3240	NR	885	837	NR
370	566	NR	500	14286	NR	630	35946	NR	760	2875	NR	890	938	NR
375	689	NR	505	15591	NR	635	35109	NR	765	2561	NR	895	722	NR
380	659	NR	510	16757	NR	640	33848	NR	770	2263	NR	900	712	NR
385	616	NR	515	17969	NR	645	32907	NR	775	1981	NR	905	660	NR
390	575	NR	520	19153	NR	650	31426	NR	780	1758	NR	910	722	NR
395	507	NR	525	20279	NR	655	29538	NR	785	1656	NR	915	683	NR
400	452	NR	530	21424	NR	660	27902	NR	790	1510	NR	920	536	NR
405	442	NR	535	22450	NR	665	25950	NR	795	1317	NR	925	653	NR
410	492	NR	540	23201	NR	670	23596	NR	800	1296	NR	930	693	NR
415	658	NR	545	23916	NR	675	21412	NR	805	1239	NR	935	1009	NR
420	1015	NR	550	24774	NR	680	19353	NR	810	1094	NR	940	1041	NR
425	1715	NR	555	25531	NR	685	17528	NR	815	1156	NR	945	716	NR
430	3048	NR	560	26160	NR	690	15706	NR	820	966	NR	950	700	NR
435	5481	NR	565	26923	NR	695	13845	NR	825	931	NR	955	812	NR
440	9614	NR	570	27732	NR	700	12373	NR	830	938	NR	960	505	NR
445	14315	NR	575	28529	NR	705	10898	NR	835	822	NR	965	551	NR
450	14893	NR	580	29552	NR	710	9649	NR	840	838	NR	970	824	NR
455	11988	NR	585	30530	NR	715	8554	NR	845	759	NR	975	814	NR
460	10638	NR	590	31835	NR	720	7611	NR	850	712	NR	980	926	NR
465	9480	NR	595	32776	NR	725	6679	NR	855	651	NR	985	954	NR
470	8416	NR	600	33912	NR	730	5833	NR	860	789	NR	990	814	NR
475	8624	NR	605	35057	NR	735	5111	NR	865	715	NR	995	765	NR
480	9529	NR	610	35715	NR	740	4579	NR	870	935	NR	1000	954	NR
485	10656	NR	615	36371	NR	745	4054	NR	875	919	NR			

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-2

TM-30-18


Summary


R_f = 92.8
R_g = 98
CIE R_a = 92.3
R_9 = 58.9


Spectral Power Distribution Comparison




Color Vector Graphics










Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 94	CES52 = 98	CES77 = 92
CES03 = 32	CES28 = 97	CES53 = 96	CES78 = 88
CES04 = 70	CES29 = 96	CES54 = 95	CES79 = 95
CES05 = 50	CES30 = 97	CES55 = 94	CES80 = 95
CES06 = 51	CES31 = 97	CES56 = 94	CES81 = 85
CES07 = 43	CES32 = 92	CES57 = 93	CES82 = 98
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 96	CES59 = 96	CES84 = 95
CES10 = 76	CES35 = 98	CES60 = 95	CES85 = 86
CES11 = 58	CES36 = 88	CES61 = 94	CES86 = 85
CES12 = 65	CES37 = 95	CES62 = 92	CES87 = 93
CES13 = 44	CES38 = 93	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 90	CES91 = 82
CES17 = 50	CES42 = 97	CES67 = 89	CES92 = 82
CES18 = 57	CES43 = 98	CES68 = 91	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 81
CES20 = 67	CES45 = 99	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 97	CES71 = 87	CES96 = 93
CES22 = 79	CES47 = 96	CES72 = 95	CES97 = 96
CES23 = 92	CES48 = 93	CES73 = 86	CES98 = 94
CES24 = 90	CES49 = 97	CES74 = 93	CES99 = 91
CES25 = 72	CES50 = 98	CES75 = 88	





Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


REPORT NUMBER: SP1-2106-271-2

TM-30-18

Color Rendition by Hue-Angle Bin









Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: SP1-2106-271-2

TM-30-18

Measure Comparisons





(END OF REPORT)