

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198141

Luminaire Tested: **TT-C3-LED-E1-RW-PM-SG-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198141  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34699)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-RW-PM-SG-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4114.3 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2


Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P198141  
 CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.9 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198141  
CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 89-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P198141

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2057.1	0.0	2057.1
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2057.1	0.0	2057.1
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4114.3	0.0	4114.3
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.7	0.6
10°-20°	79.2	1.9
20°-30°	177.5	4.3
30°-40°	367.3	8.9
40°-50°	697.1	16.9
50°-60°	1020.1	24.8
60°-70°	1017.0	24.7
70°-80°	605.3	14.7
80°-90°	128.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4114.3	100.0
0°-180°	4114.3	100.0



REPORT NUMBER: P198141


CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	139.7	3.4			
FM (30°-60°)	1042.3	25.3			
FH (60°-80°)	811.2	19.7			G1/1800
FVH (80°-90°)	64.0	1.6			G1/100
BL (0°-30°)	139.7	3.4	B1/500		
BM (30°-60°)	1042.3	25.3	B2/2500		
BH (60°-80°)	811.2	19.7	B2/1000		G2/1000
BVH (80°-90°)	64.0	1.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198141

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	89°
0°	228.5	228.5	228.5	228.5	228.5	228.5	228.5	228.5	228.5	228.5	228.5
2.5°	230.2	230.2	230.2	230.2	229.4	229.4	229.4	229.4	229.4	229.4	229.4
5°	233.7	233.7	232.8	233.7	232.8	232.8	232.8	232.8	232.8	232.8	232.8
7.5°	238.8	238.8	238.8	238.8	238.8	238.8	237.9	238.8	237.9	237.9	237.9
10°	248.2	247.4	248.2	247.4	247.4	246.5	246.5	246.5	246.5	246.5	246.5
12.5°	260.2	260.2	260.2	259.3	258.5	258.5	257.6	257.6	257.6	256.8	257.6
15°	276.5	277.3	274.7	273.9	273.9	272.2	271.3	272.2	271.3	270.5	271.3
17.5°	296.1	297.0	295.3	293.6	291.9	291.0	290.1	289.3	289.3	289.3	288.4
20°	321.8	321.8	320.1	316.7	314.1	312.4	312.4	311.5	311.5	312.4	309.8
22.5°	350.9	350.1	348.3	346.6	343.2	339.8	338.1	337.2	337.2	338.9	339.8
25°	386.9	387.7	382.6	379.2	375.7	369.7	368.9	369.7	370.6	370.6	372.3
27.5°	423.7	425.4	421.1	416.0	410.8	408.3	406.5	408.3	410.0	412.5	411.7
30°	467.3	466.5	465.6	457.9	451.9	449.3	451.1	456.2	460.5	466.5	467.3
32.5°	514.4	516.1	510.1	504.1	501.5	499.0	501.5	512.7	524.7	528.1	532.4
35°	570.0	566.6	563.2	558.9	554.6	554.6	567.5	580.3	599.1	612.0	612.0
37.5°	626.5	623.9	617.9	612.0	612.0	620.5	633.4	665.0	692.4	711.2	703.5
40°	684.7	681.3	679.6	672.7	673.6	694.1	721.5	760.9	800.3	826.8	821.6
42.5°	743.8	744.6	738.6	736.1	743.8	766.9	814.8	867.9	917.5	950.9	951.7
45°	804.5	804.5	800.3	798.5	813.1	848.2	908.1	980.8	1047.6	1086.1	1090.4
47.5°	860.2	859.3	855.9	855.0	879.9	921.8	997.1	1090.4	1172.6	1215.4	1226.5
50°	908.1	909.0	903.8	908.1	930.3	986.0	1076.7	1189.7	1283.8	1337.7	1342.9
52.5°	945.8	946.6	940.6	944.0	974.0	1038.2	1139.2	1265.9	1368.6	1425.9	1432.8
55°	971.4	968.0	963.7	968.9	1003.1	1074.1	1184.5	1316.4	1423.3	1483.2	1488.4
57.5°	978.3	975.7	971.4	978.3	1015.1	1087.8	1201.7	1334.3	1440.5	1500.4	1507.2
60°	968.0	968.0	962.9	970.6	1007.4	1078.4	1189.7	1318.1	1419.1	1473.8	1483.2
62.5°	941.5	941.5	935.5	941.5	976.6	1042.5	1148.6	1267.6	1359.1	1407.1	1418.2
65°	891.8	891.0	887.6	889.3	918.4	980.8	1077.6	1185.4	1265.0	1307.8	1322.3
67.5°	819.9	817.4	813.9	817.4	838.8	894.4	983.4	1077.6	1143.5	1184.5	1188.0
70°	728.4	725.8	721.5	719.8	742.1	786.6	858.5	941.5	996.3	1026.2	1029.6
72.5°	619.7	623.1	619.7	614.5	629.1	668.4	728.4	791.7	837.1	864.4	868.7
75°	512.7	513.5	505.0	503.3	514.4	539.2	588.0	636.8	676.1	699.3	706.1
77.5°	397.1	397.1	389.4	385.1	391.1	412.5	445.9	485.3	517.8	532.4	544.3
80°	285.9	285.9	279.0	268.7	274.7	285.9	315.8	337.2	362.9	379.2	380.9
82.5°	178.9	176.3	178.0	170.3	172.0	175.5	194.3	208.8	224.2	232.8	233.7
85°	93.3	89.9	88.2	83.9	81.3	87.3	95.9	106.1	109.6	117.3	114.7
87.5°	29.1	27.4	26.5	26.5	24.0	25.7	26.5	28.2	32.5	32.5	34.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P198141

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-8030

**CANDELA DISTRIBUTION (continued):**

	90°
0°	228.5
2.5°	229.4
5°	232.8
7.5°	237.9
10°	246.5
12.5°	256.8
15°	271.3
17.5°	289.3
20°	309.8
22.5°	337.2
25°	370.6
27.5°	410.0
30°	466.5
32.5°	529.8
35°	606.8
37.5°	712.1
40°	820.8
42.5°	957.7
45°	1090.4
47.5°	1226.5
50°	1340.3
52.5°	1430.2
55°	1491.0
57.5°	1507.2
60°	1480.7
62.5°	1415.6
65°	1320.6
67.5°	1188.0
70°	1034.8
72.5°	866.2
75°	698.4
77.5°	540.9
80°	380.9
82.5°	240.5
85°	114.7
87.5°	36.8
90°	0.0

(END OF REPORT)