Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1704728

Luminaire Tested: GSS-SB1A-AMB-U-T1

Issue Date: 10/28/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1704728
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	10/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1A-AMB-U-T1
Description:	GALLEON SITE SLIM HIGH DENSITY LED ARRAYS 1SQUARE 36W 1590K FIXTURE w/ T1 DISTRIBUTION
Light Source:	(26) 1590K CCT, 0 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2116.8 lumens
Efficiency:	N/A
Efficacy:	59.0 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Medium
BUG Rating:	B1 - U0 - G1

Input Watts (W):	35.9
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1704728
CATALOG NUMBER: GSS-SB1A-AMB-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 10 foot mounting height. Maximum calculated value = 3.6 fc
Type I - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1704728
CATALOG NUMBER: GSS-SB1A-AMB-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1704728
CATALOG NUMBER: GSS-SB1A-AMB-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1058.4	0.0	1058.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1058.4	0.0	1058.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	2116.8	0.0	2116.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.5	1.6
10°-20°	106.0	5.0
20°-30°	181.3	8.6
30°-40°	273.0	12.9
40°-50°	346.8	16.4
50°-60°	414.6	19.6
60°-70°	509.2	24.1
70°-80°	240.6	11.4
80°-90°	10.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2116.8	100.0
0°-180°	2116.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1704728
CATALOG NUMBER: GSS-SB1A-AMB-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	160.9	7.6			
FM	(30°-60°)	517.2	24.4			
FH	(60°-80°)	374.9	17.7			G0/660
FVH	(80°-90°)	5.4	0.3			G0/10
BL	(0°-30°)	160.9	7.6	B1/500		
BM	(30°-60°)	517.2	24.4	B1/1000		
BH	(60°-80°)	374.9	17.7	B1/500		G1/500
BVH	(80°-90°)	5.4	0.3			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1
Type I Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1704728
CATALOG NUMBER: GSS-SB1A-AMB-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	354	354	354	354	354	354	354	354	354	*354*	354
2.5°	356	354	354	354	356	355	355	354	354	*354*	354
5°	361	360	360	359	359	358	357	357	357	*356*	357
7.5°	364	364	365	368	367	366	364	361	358	*357*	358
10°	363	363	367	369	372	372	370	363	357	*355*	356
12.5°	364	365	370	373	377	380	375	368	358	*354*	355
15°	363	365	371	379	385	386	384	373	361	*355*	356
17.5°	358	359	367	379	391	399	395	382	368	*360*	360
20°	347	349	358	372	391	409	411	397	377	*363*	361
22.5°	333	334	345	364	389	415	431	414	388	*374*	373
25°	320	321	331	354	384	421	451	435	406	*397*	394
27.5°	311	312	322	346	381	424	467	465	432	*423*	419
30°	305	307	317	343	377	425	487	500	463	*452*	450
32.5°	296	297	308	335	365	423	506	541	508	*493*	495
35°	276	279	292	320	353	420	523	592	572	*549*	548
37.5°	255	258	272	302	341	411	536	636	646	*616*	609
40°	239	242	255	284	328	402	542	669	705	*732*	749
42.5°	227	229	240	265	310	386	537	704	698	*653*	660
45°	211	212	225	251	293	368	525	742	746	*614*	595
47.5°	190	191	205	233	276	345	509	775	833	*659*	632
50°	156	159	175	206	253	324	481	798	937	*732*	699
52.5°	113	118	133	166	219	295	446	812	1066	*837*	795
55°	80	82	93	121	170	253	406	808	1216	*974*	921
57.5°	64	65	70	83	120	196	349	777	1396	*1174*	1094
60°	59	59	60	66	82	135	269	700	1603	*1454*	1333
62.5°	57	57	57	58	64	85	178	576	1814	*1828*	1610
65°	52	52	52	54	56	63	108	373	1854	*2219*	1873
67.5°	46	46	47	49	51	51	68	193	1691	*2548*	2093
70°	*42*	*42*	*42*	*43*	*45*	*44*	*52*	*99*	*1383*	*2822*	*2374*
72.5°	39	40	38	36	38	38	41	55	779	*2494*	2206
75°	37	39	33	30	30	31	32	40	316	*1440*	1294
77.5°	34	37	28	23	23	24	26	28	95	*199*	143
80°	26	29	20	17	16	16	19	21	43	*55*	70
82.5°	15	15	11	10	9	10	14	14	21	*31*	49
85°	4	5	5	4	5	5	7	8	11	*23*	47
87.5°	1	1	1	1	1	2	2	3	5	*6*	7
90°	0	0	0	0	0	0	0	0	0	*0*	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP3-2509-541-1

Test Date: 09/16/2025

Luminaire Tested: GALN-SA1A-AMB-U-T3BC

Data in this report applies to families of products including GALN-SA1A*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2509-541-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	10/02/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GALN-SA1A-AMB-U-T3BC**
Description:	GALLEON AREA AND ROADWAY LUMINAIRE. (1) AMBER, 615MA LIGHTSQUARES TYPE III ROADWAY OPTICS WITH ANGLED BACKLIGHT CONTROL HEATSINK

Spectral Parameters

CCT (K):	1599
CIE u':	0.3452
CIE v':	0.5480
Duv:	0.0099
CIE x:	0.5859
CIE y:	0.4133
CIE z:	0.0008
Peak Wavelength (nm):	596
Dominant Wavelength (nm):	591
Purity:	99.94224
Rf:	1.2
Rg:	0.9

CRI (Ra):	-22.7				
R1:	-36.4	R9:	-395.3		
R2:	50.8	R10:	26.0		
R3:	18.3	R11:	-97.2		
R4:	-69.1	R12:	-14.1		
R5:	-41.9	R13:	-17.6		
R6:	38.5	R14:	46.4		
R7:	-6.7	R15:	-69.4		
R8:	-135.4				



Test Conditions


Stabilization Time:	64M
Operation Time:	2H 4M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2509-541-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	7/1/2025	1/1/2026
Power Meter	XITRON INXT2011006	1/20/2025	1/20/2026
AC Power Source	CHROMA 61604 IN6064A	10/22/2024	10/22/2025
DC Power Source	EYSIGHT N5770A IN0534	10/22/2024	10/22/2025
Sphere Thermometer	TANDD IN4036E	10/22/2024	10/22/2025

REPORT NUMBER: SP3-2509-541-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 1599K
CIE x = 0.5859
CIE y = 0.4133
Duv = 0.0099

Point lies outside the range

REPORT NUMBER: SP3-2509-541-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	26	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	13	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	8	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	1	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	0	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	68	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	123	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	223	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	392	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	669	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	982	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	783	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	315	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	124	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	53	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP3-2509-541-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.23**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	26	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	13	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	8	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	1	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	0	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	68	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	123	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	223	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	392	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	669	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	982	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	783	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	315	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	124	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	53	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP3-2509-541-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 0.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	26	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	13	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	8	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	1	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	0	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	68	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	123	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	223	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	392	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	669	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	982	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	783	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	315	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	124	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	53	NR	745	0	NR	875	0	NR			


REPORT NUMBER: SP3-2509-541-1

TM-30-18


Summary


R_f = 1.2
R_g = 0.9
CIE R_a = -22.7
R_9 = -395.3


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2509-541-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 90	CES26 = 0	CES51 = 17	CES76 = 0
CES02 = 69	CES27 = 30	CES52 = 2	CES77 = 0
CES03 = 30	CES28 = 23	CES53 = 0	CES78 = 0
CES04 = 77	CES29 = 0	CES54 = 12	CES79 = 3
CES05 = 51	CES30 = 29	CES55 = 6	CES80 = 1
CES06 = 56	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 40	CES32 = 0	CES57 = 0	CES82 = 50
CES08 = 38	CES33 = 18	CES58 = 0	CES83 = 20
CES09 = 29	CES34 = 0	CES59 = 10	CES84 = 54
CES10 = 87	CES35 = 22	CES60 = 60	CES85 = 10
CES11 = 70	CES36 = 76	CES61 = 14	CES86 = 0
CES12 = 75	CES37 = 5	CES62 = 55	CES87 = 2
CES13 = 46	CES38 = 38	CES63 = 68	CES88 = 1
CES14 = 76	CES39 = 73	CES64 = 0	CES89 = 0
CES15 = 74	CES40 = 46	CES65 = 0	CES90 = 2
CES16 = 49	CES41 = 73	CES66 = 0	CES91 = 58
CES17 = 56	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 59	CES43 = 0	CES68 = 0	CES93 = 3
CES19 = 80	CES44 = 95	CES69 = 27	CES94 = 0
CES20 = 71	CES45 = 1	CES70 = 0	CES95 = 0
CES21 = 94	CES46 = 5	CES71 = 0	CES96 = 2
CES22 = 86	CES47 = 65	CES72 = 42	CES97 = 1
CES23 = 94	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 95	CES49 = 5	CES74 = 65	CES99 = 0
CES25 = 79	CES50 = 9	CES75 = 0	





REPORT NUMBER: SP3-2509-541-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2509-541-1

TM-30-18

Measure Comparisons





(END OF REPORT)