

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198093

Luminaire Tested: **TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198093  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34701)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS AND LumaWatt WIRELESS SENSOR  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3703.4 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198093

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.5 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198093

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral      - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P198093

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1851.7	0.0	1851.7
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1851.7	0.0	1851.7
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3703.4	0.0	3703.4
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.8	0.6
10°-20°	75.6	2.0
20°-30°	165.1	4.5
30°-40°	332.1	9.0
40°-50°	627.6	16.9
50°-60°	925.8	25.0
60°-70°	911.9	24.6
70°-80°	531.0	14.3
80°-90°	112.4	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3703.4	100.0
0°-180°	3703.4	100.0



REPORT NUMBER: P198093


CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	131.3	3.5			
FM	(30°-60°)	942.8	25.5			
FH	(60°-80°)	721.4	19.5			G1/1800
FVH	(80°-90°)	56.2	1.5			G1/100
BL	(0°-30°)	131.3	3.5	B1/500		
BM	(30°-60°)	942.8	25.5	B1/1000		
BH	(60°-80°)	721.4	19.5	B2/1000		G2/1000
BVH	(80°-90°)	56.2	1.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198093

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0
2.5°	221.7	221.7	221.7	221.7	220.8	221.7	220.8	220.8	220.8	220.8	220.8
5°	224.2	225.1	224.2	224.2	224.2	224.2	224.2	224.2	223.4	223.4	224.2
7.5°	230.2	230.2	230.2	230.2	229.4	230.2	229.4	229.4	229.4	229.4	229.4
10°	238.8	238.8	238.8	238.8	237.9	237.9	237.9	237.1	237.1	237.1	237.1
12.5°	249.1	249.9	249.9	249.1	248.2	248.2	247.4	247.4	247.4	247.4	246.5
15°	264.5	263.6	263.6	261.9	261.9	260.2	261.0	260.2	259.3	258.5	259.3
17.5°	279.9	280.7	280.7	279.0	278.2	277.3	275.6	275.6	274.7	275.6	275.6
20°	303.8	303.8	302.1	300.4	297.8	297.0	295.3	295.3	293.6	295.3	295.3
22.5°	327.8	327.8	326.1	325.2	321.8	319.2	318.4	317.5	316.7	318.4	316.7
25°	357.8	357.8	356.0	352.6	349.2	348.3	345.8	345.8	346.6	347.5	344.1
27.5°	388.6	389.4	387.7	385.1	381.7	378.3	378.3	379.2	380.0	383.4	382.6
30°	426.2	425.4	422.8	419.4	417.7	415.1	416.0	419.4	422.8	426.2	426.2
32.5°	464.7	463.9	463.0	459.6	458.8	457.9	462.2	469.0	475.9	478.4	482.7
35°	505.8	505.8	505.0	502.4	504.1	508.4	515.2	528.1	538.4	550.3	550.3
37.5°	551.2	549.5	550.3	550.3	554.6	562.3	578.6	603.4	624.8	636.8	636.8
40°	598.3	595.7	596.6	600.8	608.5	627.4	655.6	689.8	724.1	739.5	744.6
42.5°	643.6	641.1	644.5	648.8	667.6	696.7	738.6	790.8	839.6	863.6	862.7
45°	685.6	687.3	691.6	701.8	729.2	772.0	831.9	902.1	965.4	993.7	1004.0
47.5°	727.5	728.4	734.3	752.3	790.8	844.8	917.5	1010.8	1081.0	1114.4	1127.2
50°	766.9	768.6	778.9	804.5	849.9	914.9	1004.8	1104.1	1181.1	1220.5	1231.6
52.5°	802.0	803.7	815.7	847.3	901.2	976.6	1070.7	1172.6	1253.9	1299.2	1306.1
55°	831.1	832.8	844.8	878.1	936.3	1014.2	1110.1	1211.1	1287.3	1327.5	1332.6
57.5°	848.2	849.0	861.9	896.1	953.5	1026.2	1118.6	1216.2	1283.0	1318.9	1323.2
60°	849.0	850.7	862.7	893.5	946.6	1013.4	1101.5	1188.8	1249.6	1282.1	1287.3
62.5°	833.6	834.5	844.8	868.7	914.1	972.3	1053.6	1132.3	1187.1	1218.8	1224.8
65°	798.5	798.5	803.7	821.6	856.7	906.4	975.7	1048.5	1099.0	1128.1	1131.5
67.5°	740.3	740.3	741.2	753.2	777.1	816.5	875.6	936.3	981.7	1010.8	1015.1
70°	665.9	665.0	658.2	665.9	681.3	714.7	766.9	813.1	849.9	873.0	888.4
72.5°	571.7	568.3	563.2	561.5	576.9	606.0	648.8	680.4	701.0	725.8	727.5
75°	462.2	460.5	453.6	453.6	469.0	492.1	526.4	547.8	558.0	574.3	577.7
77.5°	344.9	344.1	346.6	347.5	356.0	380.9	400.6	416.0	413.4	423.7	427.1
80°	241.4	243.1	243.1	242.2	250.8	260.2	281.6	285.9	282.4	285.9	285.9
82.5°	153.2	152.3	150.6	153.2	160.1	167.8	176.3	177.2	179.7	177.2	178.9
85°	77.0	76.2	77.9	78.7	82.2	86.4	94.1	95.9	91.6	91.6	89.9
87.5°	26.5	28.2	26.5	27.4	27.4	31.7	30.8	30.8	30.8	30.8	32.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)