

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198226

Luminaire Tested: **TT-C3-LED-E1-T4-PM-CG**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P198226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34707)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-T4-PM-CG
Description: TOPTIER LED AREA/SITE LUMINAIRE
DRIVE LANE DISTRIBUTION WITH CLEAR GLASS LENS
Light Source: (160) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5319.8 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 66.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P198226

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.1 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P198226

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG

Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P198226

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1458.9	0.0	1458.9
	% Fixture	27.4	0.0	27.4
Street Side	Lumens	3860.9	0.0	3860.9
	% Fixture	72.6	0.0	72.6
Total	Lumens	5319.8	0.0	5319.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.1	0.4
10°-20°	77.5	1.5
20°-30°	173.6	3.3
30°-40°	354.2	6.7
40°-50°	681.0	12.8
50°-60°	1183.0	22.2
60°-70°	1515.2	28.5
70°-80°	1085.0	20.4
80°-90°	228.2	4.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5319.8	100.0
0°-180°	5319.8	100.0



REPORT NUMBER: P198226


CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	167.2	3.1			
FM	(30°-60°)	1577.3	29.7			
FH	(60°-80°)	1941.9	36.5			G2/5000
FVH	(80°-90°)	174.5	3.3			G2/225
BL	(0°-30°)	105.9	2.0	B0/110		
BM	(30°-60°)	640.9	12.0	B1/1000		
BH	(60°-80°)	658.3	12.4	B2/1000		G2/1000
BVH	(80°-90°)	53.8	1.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P198226

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	219	219	219	219	219	219	219	219	219	219	219
2.5°	231	231	231	230	229	228	228	227	226	225	223
5°	245	244	244	242	241	239	239	237	234	231	228
7.5°	260	261	260	258	255	253	252	248	244	239	234
10°	278	279	279	277	274	269	269	263	257	251	242
12.5°	304	303	302	302	296	290	292	284	274	265	254
15°	328	330	332	327	323	317	316	306	295	282	268
17.5°	363	365	364	362	357	350	348	336	321	303	284
20°	408	409	405	403	399	390	387	373	353	328	305
22.5°	458	455	454	452	451	441	440	419	390	362	329
25°	501	504	506	509	508	498	498	474	439	401	359
27.5°	551	556	562	569	568	561	565	542	495	449	395
30°	605	613	623	640	645	638	638	609	563	501	435
32.5°	677	681	690	717	732	732	731	699	643	565	483
35°	752	753	777	810	829	844	837	806	743	647	544
37.5°	829	830	864	903	946	958	964	936	855	738	611
40°	906	919	959	1013	1077	1101	1098	1073	976	838	684
42.5°	984	1011	1052	1135	1211	1250	1252	1230	1128	969	779
45°	1077	1094	1157	1253	1362	1413	1418	1408	1312	1129	893
47.5°	1174	1190	1266	1387	1523	1626	1635	1626	1507	1264	995
50°	1280	1286	1377	1539	1736	1849	1855	1859	1698	1438	1094
52.5°	1379	1381	1498	1710	1962	2103	2110	2102	1975	1656	1280
55°	1477	1479	1627	1906	2205	2380	2424	2428	2198	1796	1330
57.5°	1568	1577	1779	2101	2479	2720	2717	2650	2329	1849	1341
60°	1650	1679	1924	2320	2701	2860	2876	2729	2375	1872	1332
62.5°	1720	1752	2061	2494	2840	2934	2928	2761	2440	1952	1391
65°	1776	1822	2159	2580	2870	2962	2961	2841	2509	1969	1367
67.5°	1807	1878	2174	2582	2847	2886	2872	2723	2380	1860	1251
70°	1824	1870	2138	2468	2649	2638	2641	2460	2158	1678	1112
72.5°	1762	1800	1988	2222	2341	2285	2311	2145	1876	1431	937
75°	1608	1626	1717	1866	1930	1892	1892	1772	1514	1174	757
77.5°	1346	1352	1387	1467	1485	1474	1471	1368	1162	897	566
80°	962	984	999	1034	1072	1056	1035	952	813	614	390
82.5°	597	599	614	637	643	664	661	595	491	367	228
85°	279	274	288	304	313	312	319	287	227	168	104
87.5°	44	62	66	65	72	73	76	69	47	33	25
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P198226

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-CG

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	219	219	219	219	219	219	219	219	219	219	219
2.5°	222	222	220	218	216	215	214	213	213	212	212
5°	227	225	222	219	216	214	212	211	209	208	208
7.5°	231	229	224	220	216	213	210	208	207	206	206
10°	239	235	229	222	217	213	210	208	207	206	206
12.5°	250	244	234	227	220	215	212	210	208	208	207
15°	262	255	243	232	224	219	215	214	212	212	212
17.5°	276	268	253	240	231	225	221	219	218	219	220
20°	294	283	264	250	239	233	230	227	227	229	229
22.5°	315	302	279	262	251	243	241	239	238	240	240
25°	337	322	295	276	263	256	254	252	253	254	251
27.5°	371	350	315	293	278	271	268	267	268	269	267
30°	403	378	339	313	294	287	284	284	285	285	285
32.5°	447	416	366	335	316	307	306	306	304	305	304
35°	499	462	403	365	343	333	330	328	328	328	328
37.5°	555	510	441	399	374	362	356	353	354	354	352
40°	618	566	486	434	411	393	386	383	382	380	375
42.5°	702	636	541	479	445	432	419	413	408	407	399
45°	801	730	612	543	498	469	456	446	437	434	428
47.5°	883	797	675	598	548	518	497	482	470	463	465
50°	975	879	747	650	601	569	549	524	506	495	499
52.5°	1126	1019	847	740	656	624	598	569	545	530	538
55°	1168	1056	895	797	732	697	658	622	588	568	568
57.5°	1166	1053	899	813	775	750	721	676	632	603	601
60°	1151	1038	889	802	773	778	766	728	676	636	630
62.5°	1190	1075	915	813	771	776	786	764	713	663	657
65°	1165	1049	894	805	782	783	790	774	733	687	677
67.5°	1063	961	823	746	731	749	771	766	731	700	688
70°	934	844	726	662	651	677	714	721	711	691	687
72.5°	791	712	612	564	560	580	617	641	648	657	657
75°	635	573	487	454	454	476	506	537	556	580	587
77.5°	482	428	367	339	339	359	382	407	439	472	467
80°	330	295	251	237	234	245	265	282	310	332	345
82.5°	189	177	151	139	138	152	166	168	187	200	204
85°	90	79	74	66	67	70	75	79	84	89	89
87.5°	20	19	17	18	18	16	18	17	19	20	18
90°	0	0	0	0	0	0	0	0	0	0	0

(END OF REPORT)