

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197777

Luminaire Tested: **TT-C2-LED-E1-5WQ-PM-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34714)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C2-LED-E1-5WQ-PM-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
WIDE DISTRIBUTION  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3763.6 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B2 - U0 - G2


Input Watts (W): 34  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P197777  
 CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 2.8 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197777  
CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197777

CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1881.8	0.0	1881.8
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1881.8	0.0	1881.8
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3763.6	0.0	3763.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.1	0.7
10°-20°	86.9	2.3
20°-30°	174.9	4.6
30°-40°	304.5	8.1
40°-50°	514.9	13.7
50°-60°	767.5	20.4
60°-70°	918.6	24.4
70°-80°	743.7	19.8
80°-90°	226.6	6.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3763.6	100.0
0°-180°	3763.6	100.0



REPORT NUMBER: P197777


CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	143.9	3.8			
FM (30°-60°)	793.5	21.1			
FH (60°-80°)	831.1	22.1			G1/1800
FVH (80°-90°)	113.3	3.0			G2/225
BL (0°-30°)	143.9	3.8	B1/500		
BM (30°-60°)	793.5	21.1	B1/1000		
BH (60°-80°)	831.1	22.1	B2/1000		G1/1800
BVH (80°-90°)	113.3	3.0			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type V Short





REPORT NUMBER: P197777

CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	46°	55°	65°	75°	85°
0°	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6	263.6
2.5°	268.2	267.5	267.5	267.5	267.5	267.5	267.5	267.5	267.5	267.5	268.2
5°	272.7	272.7	272.1	271.4	271.4	270.8	270.8	270.8	271.4	272.1	272.1
7.5°	274.7	274.0	274.0	273.4	272.7	272.7	272.1	272.7	273.4	274.0	274.0
10°	278.6	279.2	279.9	280.6	281.2	280.6	279.2	280.6	280.6	279.9	278.6
12.5°	287.7	287.7	289.7	291.6	291.6	291.0	289.0	291.6	291.0	289.0	287.7
15°	300.1	300.7	300.7	302.7	301.4	300.1	298.1	301.4	301.4	300.1	299.4
17.5°	317.7	316.4	314.4	315.7	317.0	317.0	313.1	317.0	314.4	313.1	315.1
20°	337.2	336.5	335.9	337.2	342.4	340.4	338.5	341.1	337.8	333.3	334.6
22.5°	352.2	353.5	355.4	357.4	362.6	361.3	357.4	361.9	356.7	355.4	351.5
25°	371.0	370.4	375.6	375.6	378.8	376.9	372.3	378.8	373.6	375.6	369.7
27.5°	389.9	389.3	393.2	393.2	399.0	398.4	392.5	399.0	393.2	391.9	389.9
30°	411.4	410.1	410.7	415.9	424.4	424.4	419.2	422.5	415.9	409.4	408.8
32.5°	434.2	431.6	435.5	443.9	448.5	447.2	442.0	447.2	445.2	434.2	431.6
35°	456.3	459.6	466.7	473.9	482.3	483.6	479.1	481.7	474.5	466.1	459.6
37.5°	493.4	498.6	507.7	524.7	537.7	541.6	537.7	536.4	526.0	507.1	498.0
40°	545.5	546.8	559.1	584.5	598.2	600.8	593.6	595.6	583.2	562.4	542.9
42.5°	587.8	585.8	608.0	630.8	645.1	650.9	643.1	645.7	628.8	608.6	587.1
45°	622.3	624.2	647.0	669.8	692.6	703.7	697.8	693.2	668.5	645.7	626.8
47.5°	654.2	663.3	678.9	712.1	740.8	753.1	748.6	742.1	716.0	678.3	663.9
50°	694.5	700.4	719.3	762.2	788.9	793.5	789.6	789.6	764.8	721.2	701.7
52.5°	738.2	738.8	766.8	811.1	844.9	863.1	859.9	850.8	811.7	773.3	741.4
55°	790.2	783.1	826.7	872.9	923.7	953.6	952.3	932.8	879.4	828.6	786.3
57.5°	819.5	820.8	860.5	930.2	979.0	987.5	992.0	980.3	939.9	861.8	828.6
60°	826.0	841.7	878.1	954.9	993.3	1018.1	1019.4	999.8	957.5	883.3	848.2
62.5°	828.6	847.5	892.4	953.6	1018.7	1042.8	1047.3	1027.2	958.8	894.4	843.0
65°	832.5	835.1	893.7	968.6	1022.0	1042.8	1048.0	1027.2	971.8	889.8	833.2
67.5°	816.3	809.8	861.2	942.5	994.6	1019.4	1025.2	1000.5	944.5	862.5	818.2
70°	757.7	760.3	817.6	895.0	952.3	975.7	979.7	953.0	894.4	823.4	772.0
72.5°	695.8	702.4	750.5	828.6	880.1	902.8	910.0	882.0	832.5	759.6	706.3
75°	609.9	622.3	668.5	738.8	790.2	824.7	831.9	795.4	736.2	673.1	621.6
77.5°	514.9	523.3	567.6	628.1	683.5	701.1	707.6	690.0	631.4	575.4	527.3
80°	404.9	408.1	453.0	501.2	544.2	558.5	568.3	546.1	506.4	455.7	408.8
82.5°	277.9	282.5	314.4	358.7	396.4	402.3	414.6	396.4	359.3	320.3	285.1
85°	144.5	151.0	175.8	199.8	229.1	236.3	240.2	226.5	207.0	175.1	151.7
87.5°	31.2	34.5	38.4	49.5	59.2	67.7	73.6	61.2	48.8	41.0	31.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P197777

CATALOG NUMBER: TT-C2-LED-E1-5WQ-PM-8030

**CANDELA DISTRIBUTION (continued):**

	90°
0°	263.6
2.5°	267.5
5°	272.1
7.5°	274.0
10°	278.6
12.5°	287.1
15°	300.1
17.5°	316.4
20°	333.9
22.5°	349.6
25°	368.4
27.5°	389.9
30°	412.0
32.5°	430.3
35°	455.7
37.5°	497.3
40°	547.4
42.5°	587.8
45°	621.0
47.5°	658.1
50°	695.2
52.5°	742.7
55°	789.6
57.5°	813.7
60°	828.6
62.5°	840.4
65°	841.7
67.5°	807.8
70°	756.4
72.5°	697.8
75°	611.9
77.5°	521.4
80°	404.9
82.5°	284.5
85°	149.1
87.5°	29.3
90°	0.0

(END OF REPORT)