

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197993

Luminaire Tested: **TT-C2-LED-E1-RW-PM-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34691)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C2-LED-E1-RW-PM-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION
Light Source: (168) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3308.1 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 34
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197993

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 2.1 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197993
CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 88-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197993

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1654.1	0.0	1654.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1654.1	0.0	1654.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	3308.1	0.0	3308.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.0	0.4
10°-20°	45.0	1.4
20°-30°	99.5	3.0
30°-40°	198.3	6.0
40°-50°	379.5	11.5
50°-60°	679.3	20.5
60°-70°	900.1	27.2
70°-80°	751.2	22.7
80°-90°	242.4	7.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3308.1	100.0
0°-180°	3308.1	100.0



REPORT NUMBER: P197993


CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	78.8	2.4			
FM (30°-60°)	628.5	19.0			
FH (60°-80°)	825.6	25.0			G1/1800
FVH (80°-90°)	121.2	3.7			G2/225
BL (0°-30°)	78.8	2.4	B0/110		
BM (30°-60°)	628.5	19.0	B1/1000		
BH (60°-80°)	825.6	25.0	B2/1000		G2/1000
BVH (80°-90°)	121.2	3.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P197993

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	88°
0°	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5
2.5°	130.8	130.8	130.8	130.8	131.5	131.5	131.5	131.5	131.5	131.5	131.5
5°	132.8	132.8	133.4	133.4	134.1	134.1	134.1	134.1	133.4	133.4	133.4
7.5°	136.0	136.7	137.3	137.3	137.3	136.7	136.0	136.0	135.4	135.4	135.4
10°	141.9	141.9	142.6	142.6	141.9	141.3	140.6	140.0	140.0	140.0	139.3
12.5°	149.1	149.1	149.7	149.1	147.8	147.1	145.8	145.2	145.2	144.5	144.5
15°	158.8	160.1	160.1	158.2	156.2	154.3	153.6	152.3	152.3	152.3	152.3
17.5°	173.8	173.1	170.5	168.6	167.3	164.0	162.7	162.1	160.8	160.8	160.8
20°	190.7	189.4	186.2	183.6	181.0	177.1	174.4	173.1	172.5	171.8	171.8
22.5°	209.6	207.6	203.1	201.1	195.9	192.0	188.8	186.2	184.2	183.6	184.9
25°	229.1	229.1	225.2	220.0	214.8	208.9	204.4	201.1	198.5	197.9	197.2
27.5°	250.0	251.3	246.1	240.8	235.0	227.2	222.6	218.1	217.4	216.8	216.1
30°	272.1	274.7	269.5	264.3	256.5	248.7	242.8	240.8	238.9	240.2	240.2
32.5°	299.4	300.7	294.9	291.0	280.6	272.7	267.5	266.2	266.9	266.2	268.2
35°	331.3	329.4	324.8	317.0	307.9	300.7	296.8	299.4	306.6	309.2	307.9
37.5°	366.5	359.3	356.7	346.9	338.5	332.6	333.9	340.4	346.3	350.9	349.6
40°	392.5	393.8	386.7	377.5	369.7	368.4	375.6	384.0	395.1	399.0	400.3
42.5°	419.2	427.0	418.5	409.4	405.5	408.1	418.5	435.5	460.2	473.2	471.3
45°	449.8	458.3	449.1	442.0	441.3	451.1	473.9	518.1	554.6	580.6	583.2
47.5°	481.7	488.2	479.7	475.2	481.7	500.6	539.6	598.9	637.9	668.5	673.7
50°	522.0	519.4	512.9	512.3	526.6	561.1	613.8	673.7	744.0	764.2	770.7
52.5°	561.8	552.0	550.7	553.9	579.3	618.4	688.7	806.5	910.0	982.9	990.7
55°	598.9	587.8	590.4	598.9	634.7	693.9	791.5	935.4	1025.9	1077.3	1079.9
57.5°	632.7	626.2	632.1	643.8	697.1	773.3	876.8	995.3	1063.6	1100.1	1106.6
60°	667.2	665.9	673.1	694.5	751.8	819.5	906.1	1010.9	1079.2	1107.2	1113.7
62.5°	699.8	704.3	713.4	734.3	778.5	831.2	915.2	1043.4	1145.6	1189.9	1201.0
65°	734.3	738.2	749.2	752.5	792.2	848.2	977.0	1104.6	1190.6	1247.8	1255.6
67.5°	765.5	770.7	766.8	764.2	798.7	848.2	964.7	1076.6	1148.2	1191.9	1200.3
70°	795.4	789.6	774.0	753.8	763.5	797.4	904.1	1001.1	1073.4	1114.4	1122.9
72.5°	803.2	795.4	753.8	707.6	693.2	718.6	816.9	902.8	962.1	1000.5	1005.7
75°	783.1	766.8	696.5	632.7	605.4	630.8	712.8	786.3	828.0	869.6	872.9
77.5°	702.4	691.9	613.8	536.4	505.8	524.7	593.0	645.1	693.2	733.6	741.4
80°	576.7	567.6	498.6	435.5	394.5	407.5	457.6	499.3	545.5	577.4	587.1
82.5°	424.4	423.1	373.6	314.4	285.8	284.5	322.2	363.2	398.4	429.0	435.5
85°	266.9	266.9	233.0	197.2	167.3	167.9	190.7	220.7	264.9	284.5	286.4
87.5°	90.5	85.9	80.1	65.1	52.1	46.9	50.1	57.3	87.2	108.1	112.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P197993

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-8030

CANDELA DISTRIBUTION (continued):

	90°
0°	129.5
2.5°	131.5
5°	133.4
7.5°	135.4
10°	139.3
12.5°	145.2
15°	151.7
17.5°	160.8
20°	171.8
22.5°	184.2
25°	197.2
27.5°	216.8
30°	239.5
32.5°	267.5
35°	308.5
37.5°	350.9
40°	403.6
42.5°	476.5
45°	576.7
47.5°	673.7
50°	763.5
52.5°	974.4
55°	1082.5
57.5°	1105.9
60°	1111.8
62.5°	1195.1
65°	1254.3
67.5°	1199.7
70°	1120.9
72.5°	1001.8
75°	878.1
77.5°	741.4
80°	579.3
82.5°	435.5
85°	281.9
87.5°	108.7
90°	0.0

(END OF REPORT)