

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197969

Luminaire Tested: **TT-C2-LED-E1-RW-PM-MS/DIM-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34692)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C2-LED-E1-RW-PM-MS/DIM-8030
Description: TOPTIER LED AREA/SITE LUMINAIRE
RECTANGULAR DISTRIBUTION WITH DIMMING OCCUPANCY SENSOR
Light Source: (168) 3000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3092.6 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 34
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P197969

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197969

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 88-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197969

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1546.3	0.0	1546.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1546.3	0.0	1546.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	3092.6	0.0	3092.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.4	0.5
10°-20°	49.3	1.6
20°-30°	104.7	3.4
30°-40°	200.0	6.5
40°-50°	367.7	11.9
50°-60°	636.8	20.6
60°-70°	828.5	26.8
70°-80°	679.0	22.0
80°-90°	212.3	6.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3092.6	100.0
0°-180°	3092.6	100.0



REPORT NUMBER: P197969


CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	84.2	2.7			
FM	(30°-60°)	602.3	19.5			
FH	(60°-80°)	753.7	24.4			G1/1800
FVH	(80°-90°)	106.1	3.4			G2/225
BL	(0°-30°)	84.2	2.7	B0/110		
BM	(30°-60°)	602.3	19.5	B1/1000		
BH	(60°-80°)	753.7	24.4	B2/1000		G2/1000
BVH	(80°-90°)	106.1	3.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P197969

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	88°
0°	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5	144.5
2.5°	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.8	145.8
5°	148.4	148.4	148.4	149.1	149.1	149.1	149.1	149.1	148.4	148.4	148.4
7.5°	151.7	151.7	152.3	152.3	152.3	152.3	151.7	151.7	151.0	151.0	151.0
10°	156.9	156.9	157.5	157.5	156.9	156.2	156.2	156.2	155.6	155.6	155.6
12.5°	164.0	164.0	164.7	164.0	163.4	162.7	162.7	162.1	161.4	161.4	161.4
15°	173.8	173.8	173.1	171.8	170.5	170.5	168.6	168.6	168.6	168.6	167.9
17.5°	186.8	186.2	183.6	182.9	181.0	179.7	178.4	177.7	177.1	177.1	177.7
20°	201.1	199.8	196.6	196.6	193.3	191.4	190.1	188.8	188.8	188.1	187.5
22.5°	218.1	216.8	212.9	211.6	208.3	205.0	203.7	200.5	199.8	199.8	200.5
25°	235.0	235.6	232.4	229.8	225.2	222.0	217.4	215.5	213.5	213.5	212.2
27.5°	254.5	255.2	251.3	248.0	244.1	237.6	235.0	232.4	230.4	231.7	230.4
30°	275.3	276.6	273.4	269.5	263.6	257.1	253.9	253.2	251.3	252.6	251.9
32.5°	299.4	298.8	296.8	292.9	285.1	279.9	277.3	276.6	277.9	278.6	277.9
35°	327.4	324.8	322.9	317.0	309.8	305.9	303.3	305.9	311.8	315.7	314.4
37.5°	356.7	352.8	350.9	344.3	337.8	335.9	339.1	344.3	350.2	355.4	355.4
40°	380.8	382.1	377.5	371.7	366.5	368.4	374.3	383.4	395.1	400.3	399.7
42.5°	404.9	408.8	404.2	398.4	399.0	404.9	413.3	430.3	456.3	464.1	463.5
45°	426.4	434.8	430.9	427.0	432.9	442.6	465.4	503.2	539.0	565.7	567.6
47.5°	454.3	458.9	457.0	457.0	466.1	488.8	523.3	576.1	613.8	639.2	643.1
50°	486.2	481.7	482.3	488.2	511.0	544.8	591.7	641.2	708.9	720.6	723.8
52.5°	512.9	505.1	509.7	520.7	553.9	596.9	655.5	757.0	843.6	921.7	932.8
55°	540.3	531.2	540.3	557.8	606.7	666.6	752.5	870.3	961.4	1010.2	1016.1
57.5°	561.1	559.8	572.8	598.2	658.1	738.2	835.1	936.0	997.2	1031.7	1036.9
60°	587.1	588.4	603.4	637.3	708.9	785.7	857.9	950.4	1010.9	1031.1	1036.9
62.5°	611.9	617.1	634.7	673.1	735.6	794.1	863.8	975.7	1052.6	1096.2	1092.3
65°	635.3	640.5	661.3	687.4	744.7	809.1	925.6	1027.2	1094.9	1143.0	1148.2
67.5°	658.7	665.3	673.7	694.5	749.9	810.4	911.3	996.6	1051.3	1084.5	1086.4
70°	678.9	678.3	676.3	682.2	716.7	763.5	857.3	925.0	976.4	1003.7	1010.2
72.5°	681.5	679.6	656.8	639.9	650.9	688.0	777.9	831.9	870.9	893.7	898.3
75°	660.0	649.0	604.1	567.6	565.7	602.8	678.3	717.3	740.8	770.1	772.0
77.5°	590.4	578.0	527.9	478.4	478.4	502.5	565.7	586.5	615.8	637.9	643.8
80°	475.8	474.5	422.5	383.4	369.1	389.3	440.7	448.5	470.6	489.5	495.4
82.5°	344.3	334.6	305.9	272.7	261.0	274.0	309.2	317.0	325.5	342.4	349.6
85°	208.3	208.9	189.4	170.5	155.6	160.1	187.5	198.5	209.6	220.7	224.6
87.5°	74.9	86.6	67.7	59.9	52.1	49.5	57.9	71.6	84.0	99.6	108.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P197969

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-MS/DIM-8030

CANDELA DISTRIBUTION (continued):

	90°
0°	144.5
2.5°	145.8
5°	147.8
7.5°	151.0
10°	155.6
12.5°	161.4
15°	167.9
17.5°	176.4
20°	187.5
22.5°	199.2
25°	212.9
27.5°	231.7
30°	251.3
32.5°	277.9
35°	317.7
37.5°	355.4
40°	401.6
42.5°	466.1
45°	570.2
47.5°	642.5
50°	729.7
52.5°	923.7
55°	1018.1
57.5°	1038.2
60°	1036.9
62.5°	1102.7
65°	1147.6
67.5°	1087.7
70°	1012.8
72.5°	896.3
75°	776.6
77.5°	647.0
80°	498.0
82.5°	346.9
85°	233.7
87.5°	96.3
90°	0.0

(END OF REPORT)