

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198138

Luminaire Tested: **TT-C2-LED-E1-RW-PM-SG**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198138  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34699)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C2-LED-E1-RW-PM-SG  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3655.9 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 34  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198138

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG

### Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.4 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198138

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG

### Luminous Intensity Polar Plot



— Vertical Plane Through 89-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P198138

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1828.0	0.0	1828.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1828.0	0.0	1828.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3655.9	0.0	3655.9
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.2	0.6
10°-20°	70.4	1.9
20°-30°	157.7	4.3
30°-40°	326.3	8.9
40°-50°	619.5	16.9
50°-60°	906.5	24.8
60°-70°	903.7	24.7
70°-80°	537.9	14.7
80°-90°	113.8	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3655.9	100.0
0°-180°	3655.9	100.0

**Coefficient of Utilization**



REPORT NUMBER: P198138


CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	124.1	3.4			
FM (30°-60°)	926.1	25.3			
FH (60°-80°)	720.8	19.7			G1/1800
FVH (80°-90°)	56.9	1.6			G1/100
BL (0°-30°)	124.1	3.4	B1/500		
BM (30°-60°)	926.1	25.3	B1/1000		
BH (60°-80°)	720.8	19.7	B2/1000		G2/1000
BVH (80°-90°)	56.9	1.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198138

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	89°
0°	203.1	203.1	203.1	203.1	203.1	203.1	203.1	203.1	203.1	203.1	203.1
2.5°	204.6	204.6	204.6	204.6	203.8	203.8	203.8	203.8	203.8	203.8	203.8
5°	207.6	207.6	206.9	207.6	206.9	206.9	206.9	206.9	206.9	206.9	206.9
7.5°	212.2	212.2	212.2	212.2	212.2	212.2	211.4	212.2	211.4	211.4	211.4
10°	220.6	219.8	220.6	219.8	219.8	219.0	219.0	219.0	219.0	219.0	219.0
12.5°	231.2	231.2	231.2	230.4	229.7	229.7	228.9	228.9	228.9	228.2	228.9
15°	245.7	246.4	244.1	243.4	243.4	241.9	241.1	241.9	241.1	240.3	241.1
17.5°	263.1	263.9	262.4	260.9	259.3	258.6	257.8	257.1	257.1	257.1	256.3
20°	286.0	286.0	284.4	281.4	279.1	277.6	277.6	276.8	276.8	277.6	275.3
22.5°	311.8	311.1	309.5	308.0	305.0	301.9	300.4	299.7	299.7	301.2	301.9
25°	343.8	344.5	340.0	336.9	333.9	328.6	327.8	328.6	329.3	329.3	330.8
27.5°	376.5	378.0	374.2	369.6	365.1	362.8	361.3	362.8	364.3	366.6	365.8
30°	415.3	414.5	413.7	406.9	401.6	399.3	400.8	405.4	409.2	414.5	415.3
32.5°	457.1	458.6	453.3	448.0	445.7	443.4	445.7	455.6	466.2	469.3	473.1
35°	506.5	503.5	500.4	496.6	492.8	492.8	504.2	515.6	532.4	543.8	543.8
37.5°	556.7	554.4	549.1	543.8	543.8	551.4	562.8	590.9	615.3	632.0	625.2
40°	608.4	605.4	603.9	597.8	598.5	616.8	641.1	676.1	711.1	734.7	730.1
42.5°	660.9	661.7	656.3	654.1	660.9	681.4	724.0	771.2	815.3	845.0	845.7
45°	714.9	714.9	711.1	709.6	722.5	753.7	806.9	871.6	930.9	965.1	968.9
47.5°	764.3	763.6	760.5	759.8	781.8	819.1	886.0	968.9	1041.9	1080.0	1089.8
50°	806.9	807.7	803.1	806.9	826.7	876.1	956.8	1057.1	1140.8	1188.7	1193.3
52.5°	840.4	841.2	835.8	838.9	865.5	922.5	1012.3	1124.8	1216.1	1267.1	1273.1
55°	863.2	860.2	856.4	860.9	891.3	954.5	1052.6	1169.7	1264.8	1318.0	1322.6
57.5°	869.3	867.0	863.2	869.3	902.0	966.6	1067.8	1185.7	1280.0	1333.2	1339.3
60°	860.2	860.2	855.6	862.4	895.2	958.3	1057.1	1171.2	1261.0	1309.6	1318.0
62.5°	836.6	836.6	831.3	836.6	867.8	926.3	1020.6	1126.4	1207.7	1250.3	1260.2
65°	792.5	791.7	788.7	790.2	816.1	871.6	957.5	1053.3	1124.1	1162.1	1175.0
67.5°	728.6	726.3	723.3	726.3	745.3	794.8	873.9	957.5	1016.1	1052.6	1055.6
70°	647.2	644.9	641.1	639.6	659.4	698.9	762.8	836.6	885.3	911.9	914.9
72.5°	550.6	553.7	550.6	546.1	559.0	594.0	647.2	703.5	743.8	768.1	771.9
75°	455.6	456.3	448.7	447.2	457.1	479.1	522.5	565.8	600.8	621.4	627.4
77.5°	352.9	352.9	346.0	342.2	347.6	366.6	396.2	431.2	460.1	473.1	483.7
80°	254.0	254.0	247.9	238.8	244.1	254.0	280.6	299.7	322.5	336.9	338.4
82.5°	159.0	156.7	158.2	151.3	152.9	155.9	172.6	185.6	199.3	206.9	207.6
85°	82.9	79.9	78.3	74.5	72.3	77.6	85.2	94.3	97.3	104.2	101.9
87.5°	25.9	24.3	23.6	23.6	21.3	22.8	23.6	25.1	28.9	28.9	30.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P198138

CATALOG NUMBER: TT-C2-LED-E1-RW-PM-SG

**CANDELA DISTRIBUTION (continued):**

	90°
0°	203.1
2.5°	203.8
5°	206.9
7.5°	211.4
10°	219.0
12.5°	228.2
15°	241.1
17.5°	257.1
20°	275.3
22.5°	299.7
25°	329.3
27.5°	364.3
30°	414.5
32.5°	470.8
35°	539.2
37.5°	632.8
40°	729.4
42.5°	851.0
45°	968.9
47.5°	1089.8
50°	1191.0
52.5°	1270.9
55°	1324.9
57.5°	1339.3
60°	1315.7
62.5°	1257.9
65°	1173.5
67.5°	1055.6
70°	919.5
72.5°	769.7
75°	620.6
77.5°	480.7
80°	338.4
82.5°	213.7
85°	101.9
87.5°	32.7
90°	0.0

(END OF REPORT)