

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197638

Luminaire Tested: **TT-C3-LED-E1-5MQ-PM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P197638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P33410)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-5MQ-PM
Description: TOPTIER LED AREA/SITE LUMINAIRE
MEDIUM DISTRIBUTION
Light Source: (168) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6258.6 lumens
Efficiency: N/A
Efficacy: 139.1 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G2


Input Watts (W): 45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P197638
 CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.5 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197638
CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197638

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3129.3	0.0	3129.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3129.3	0.0	3129.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	6258.6	0.0	6258.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.8	1.9
10°-20°	348.6	5.6
20°-30°	557.8	8.9
30°-40°	736.7	11.8
40°-50°	921.0	14.7
50°-60°	1105.7	17.7
60°-70°	1208.6	19.3
70°-80°	960.3	15.3
80°-90°	301.1	4.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6258.6	100.0
0°-180°	6258.6	100.0



REPORT NUMBER: P197638


CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	512.6	8.2			
FM (30°-60°)	1381.7	22.1			
FH (60°-80°)	1084.4	17.3			G1/1800
FVH (80°-90°)	150.5	2.4			G2/225
BL (0°-30°)	512.6	8.2	B2/1000		
BM (30°-60°)	1381.7	22.1	B2/2500		
BH (60°-80°)	1084.4	17.3	B3/2500		G1/1800
BVH (80°-90°)	150.5	2.4			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P197638

CATALOG NUMBER: TT-C3-LED-E1-5MQ-PM

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7	1248.7
2.5°	1249.8	1249.8	1249.8	1249.8	1248.7	1249.8	1248.7	1248.7	1249.8	1249.8	1249.8
5°	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6
7.5°	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3	1244.3
10°	1239.9	1241.0	1241.0	1241.0	1239.9	1239.9	1239.9	1241.0	1241.0	1239.9	1239.9
12.5°	1235.5	1235.5	1236.6	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1234.5
15°	1229.0	1229.0	1230.1	1230.1	1230.1	1230.1	1230.1	1229.0	1229.0	1227.9	1227.9
17.5°	1223.5	1223.5	1225.7	1225.7	1226.8	1226.8	1226.8	1224.6	1224.6	1222.4	1222.4
20°	1222.4	1222.4	1223.5	1225.7	1226.8	1227.9	1226.8	1224.6	1222.4	1220.2	1220.2
22.5°	1214.8	1215.9	1218.1	1219.1	1221.3	1221.3	1221.3	1218.1	1217.0	1214.8	1214.8
25°	1204.9	1203.8	1207.1	1209.3	1211.5	1211.5	1210.4	1208.2	1207.1	1203.8	1203.8
27.5°	1189.6	1190.7	1192.9	1196.2	1199.5	1199.5	1198.4	1196.2	1194.0	1191.8	1190.7
30°	1176.5	1177.6	1179.8	1183.1	1185.3	1188.5	1185.3	1183.1	1179.8	1178.7	1177.6
32.5°	1162.3	1163.4	1166.7	1172.1	1175.4	1177.6	1175.4	1173.2	1167.8	1164.5	1163.4
35°	1152.5	1153.5	1156.8	1164.5	1171.0	1171.0	1171.0	1165.6	1159.0	1153.5	1152.5
37.5°	1153.5	1155.7	1163.4	1174.3	1185.3	1186.3	1185.3	1174.3	1164.5	1155.7	1154.6
40°	1162.3	1164.5	1177.6	1194.0	1208.2	1212.6	1209.3	1194.0	1178.7	1166.7	1163.4
42.5°	1161.2	1164.5	1178.7	1199.5	1213.7	1220.2	1213.7	1199.5	1180.9	1167.8	1163.4
45°	1156.8	1159.0	1174.3	1196.2	1213.7	1220.2	1214.8	1198.4	1177.6	1162.3	1159.0
47.5°	1150.3	1152.5	1164.5	1190.7	1210.4	1217.0	1211.5	1194.0	1167.8	1155.7	1153.5
50°	1141.5	1148.1	1167.8	1195.1	1221.3	1225.7	1222.4	1197.3	1169.9	1152.5	1143.7
52.5°	1150.3	1149.2	1172.1	1221.3	1245.4	1259.6	1248.7	1219.1	1177.6	1154.6	1152.5
55°	1169.9	1178.7	1203.8	1249.8	1289.1	1308.8	1293.5	1253.0	1206.0	1177.6	1172.1
57.5°	1168.9	1179.8	1224.6	1270.5	1330.7	1343.8	1326.3	1276.0	1222.4	1185.3	1171.0
60°	1162.3	1166.7	1200.6	1282.6	1316.5	1331.8	1316.5	1277.1	1209.3	1167.8	1167.8
62.5°	1140.4	1148.1	1201.7	1258.5	1306.6	1330.7	1312.1	1262.9	1200.6	1155.7	1141.5
65°	1126.2	1131.7	1184.2	1260.7	1329.6	1355.8	1325.2	1261.8	1187.4	1135.0	1127.3
67.5°	1081.4	1091.2	1140.4	1223.5	1290.2	1311.0	1299.0	1221.3	1140.4	1092.3	1080.3
70°	1004.8	1010.3	1078.1	1156.8	1218.1	1232.3	1214.8	1164.5	1071.5	1018.0	1001.6
72.5°	910.8	918.5	980.8	1068.3	1127.3	1145.9	1125.1	1071.5	975.3	927.2	911.9
75°	815.7	823.3	863.8	958.9	1008.1	1034.4	1010.3	952.4	866.0	819.0	812.4
77.5°	679.0	691.0	753.4	816.8	863.8	891.1	870.4	816.8	749.0	693.2	672.4
80°	533.6	542.3	600.3	656.0	698.7	716.2	706.3	656.0	601.4	544.5	534.7
82.5°	373.9	379.4	429.7	474.5	527.0	527.0	516.1	483.3	428.6	379.4	381.6
85°	200.1	206.7	244.9	279.9	312.7	312.7	302.9	282.1	243.8	205.6	201.2
87.5°	40.5	44.8	59.0	64.5	76.5	82.0	74.4	67.8	59.0	47.0	47.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)