

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P413333

Luminaire Tested: **TT-D5-830-U-RW-PM**

Issue Date: 10/15/2020

Test Information

Test Method: LM-79-08
Report Number: P413333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-981-1)
Test Lab: INNOVATION CENTER
Issue Date: 10/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TT-D5-830-U-RW-PM
Description: TOPTIER LED SITE LUMINAIRE
3000K, 80 CRI LEDS AND RECTANGULAR DISTRIBUTION
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6781 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 74.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P413333
 CATALOG NUMBER: TT-D5-830-U-RW-PM

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P413333
CATALOG NUMBER: TT-D5-830-U-RW-PM

Luminous Intensity Polar Plot



REPORT NUMBER: P413333
 CATALOG NUMBER: TT-D5-830-U-RW-PM


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3390.5	0.0	3390.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3390.5	0.0	3390.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	6781.0	0.0	6781.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.9	0.2
10°-20°	48.4	0.7
20°-30°	111.7	1.6
30°-40°	252.6	3.7
40°-50°	615.4	9.1
50°-60°	1383.9	20.4
60°-70°	2022.6	29.8
70°-80°	1762.4	26.0
80°-90°	570.9	8.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6781.0	100.0
0°-180°	6781.0	100.0




REPORT NUMBER: P413333
 CATALOG NUMBER: TT-D5-830-U-RW-PM

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	86.5	1.3			
FM (30°-60°)	1126.0	16.6			
FH (60°-80°)	1892.5	27.9			G2/5000
FVH (80°-90°)	285.4	4.2			G3/500
BL (0°-30°)	86.5	1.3	B0/110		
BM (30°-60°)	1126.0	16.6	B2/2500		
BH (60°-80°)	1892.5	27.9	B3/2500		G3/2500
BVH (80°-90°)	285.4	4.2			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type IV Short





REPORT NUMBER: P413333
 CATALOG NUMBER: TT-D5-830-U-RW-PM

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9
2.5°	125.5	125.5	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1
5°	130.3	130.3	130.3	130.3	131.9	131.9	130.3	130.3	130.3	130.3	130.3
7.5°	138.4	136.8	138.4	138.4	138.4	136.8	136.8	136.8	135.2	135.2	135.2
10°	146.4	146.4	148.0	146.4	146.4	144.8	144.8	144.8	143.2	143.2	143.2
12.5°	157.7	157.7	157.7	157.7	156.1	156.1	154.5	152.9	151.2	151.2	151.2
15°	172.2	170.5	170.5	168.9	167.3	165.7	164.1	164.1	162.5	162.5	162.5
17.5°	186.6	186.6	185.0	183.4	180.2	178.6	178.6	177.0	175.4	175.4	175.4
20°	204.3	204.3	202.7	199.5	196.3	194.7	193.1	193.1	191.5	191.5	191.5
22.5°	225.3	223.6	220.4	217.2	214.0	212.4	210.8	209.2	209.2	209.2	209.2
25°	247.8	246.2	244.6	239.7	234.9	233.3	230.1	230.1	228.5	230.1	230.1
27.5°	275.1	273.5	270.3	265.5	259.0	255.8	254.2	254.2	255.8	255.8	257.4
30°	308.9	305.7	302.5	296.0	289.6	284.8	284.8	286.4	291.2	294.4	294.4
32.5°	349.1	347.5	342.7	336.3	325.0	321.8	325.0	334.7	341.1	345.9	349.1
35°	395.8	394.2	387.8	376.5	368.5	366.8	376.5	392.6	413.5	419.9	423.2
37.5°	447.3	448.9	440.9	428.0	419.9	423.2	442.5	473.0	494.0	508.4	511.6
40°	511.6	514.9	505.2	490.7	482.7	495.6	526.1	561.5	598.5	616.2	621.1
42.5°	587.3	592.1	579.2	564.7	559.9	580.8	624.3	682.2	748.2	769.1	777.1
45°	680.6	683.8	667.7	654.8	651.6	688.6	762.6	859.2	963.8	1012.0	1020.1
47.5°	791.6	790.0	775.5	759.4	762.6	815.7	926.8	1057.1	1168.1	1242.1	1258.2
50°	918.7	910.7	899.4	880.1	901.0	978.2	1118.2	1275.9	1462.5	1528.5	1557.5
52.5°	1045.8	1031.3	1021.7	1008.8	1045.8	1145.6	1341.9	1617.0	1898.6	2049.8	2080.4
55°	1160.1	1148.8	1144.0	1145.6	1203.5	1346.7	1604.1	1956.5	2228.4	2353.9	2376.4
57.5°	1272.7	1266.3	1261.4	1271.1	1362.8	1549.4	1839.0	2168.9	2392.5	2485.8	2501.9
60°	1378.9	1385.3	1382.1	1411.1	1522.1	1710.3	1961.3	2286.3	2501.9	2587.2	2604.9
62.5°	1496.3	1501.2	1501.2	1533.3	1623.4	1789.2	2045.0	2424.7	2698.2	2823.7	2843.0
65°	1597.7	1600.9	1607.4	1609.0	1692.6	1858.3	2193.0	2551.8	2796.4	2941.2	2954.0
67.5°	1673.3	1676.5	1668.5	1660.4	1724.8	1874.4	2181.7	2535.7	2752.9	2862.3	2872.0
70°	1734.5	1720.0	1697.5	1657.2	1678.1	1790.8	2088.4	2407.0	2625.8	2724.0	2738.4
72.5°	1742.5	1729.6	1658.8	1568.7	1543.0	1641.1	1924.3	2210.7	2399.0	2492.3	2493.9
75°	1694.2	1660.4	1543.0	1407.8	1359.6	1452.9	1695.8	1956.5	2107.7	2186.6	2194.6
77.5°	1531.7	1499.5	1351.5	1197.1	1142.4	1222.8	1428.8	1639.5	1784.3	1861.6	1866.4
80°	1243.7	1232.5	1097.3	955.7	889.8	936.4	1116.6	1282.3	1399.8	1491.5	1499.5
82.5°	917.1	907.5	804.5	680.6	627.5	666.1	794.8	917.1	1026.5	1100.5	1105.4
85°	572.8	553.5	489.1	402.2	366.8	392.6	477.9	559.9	658.1	716.0	719.2
87.5°	191.5	183.4	157.7	130.3	109.4	114.2	140.0	170.5	249.4	275.1	291.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)