

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197757

Luminaire Tested: **TT-C3-LED-E1-5WQ-PM-MS/DIM-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197757  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P115468)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
WIDE DISTRIBUTION WITH DIMMING OCCUPANCY SENSOR  
Light Source: (168) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4838.2 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short - Semi-Cutoff  
BUG Rating: B3 - U0 - G2

Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197757

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.7 fc  
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P197757

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 63-Deg Vertical

REPORT NUMBER: P197757

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2419.1	0.0	2419.1
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2419.1	0.0	2419.1
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4838.2	0.0	4838.2
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.2	0.7
10°-20°	113.0	2.3
20°-30°	229.8	4.7
30°-40°	396.0	8.2
40°-50°	667.2	13.8
50°-60°	982.4	20.3
60°-70°	1168.2	24.1
70°-80°	945.7	19.5
80°-90°	302.6	6.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4838.2	100.0
0°-180°	4838.2	100.0



REPORT NUMBER: P197757


CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	188.0	3.9			
FM (30°-60°)	1022.8	21.1			
FH (60°-80°)	1057.0	21.8			G1/1800
FVH (80°-90°)	151.3	3.1			G2/225
BL (0°-30°)	188.0	3.9	B1/500		
BM (30°-60°)	1022.8	21.1	B2/2500		
BH (60°-80°)	1057.0	21.8	B3/2500		G1/1800
BVH (80°-90°)	151.3	3.1			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P197757

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	329.4	329.4	329.4	329.4	329.4	329.4	329.4	329.4	329.4	329.4	329.4
2.5°	339.7	339.7	339.7	339.7	339.7	339.7	338.8	339.7	338.8	338.8	338.8
5°	346.2	346.2	346.2	346.2	345.4	345.4	344.4	344.4	344.4	343.4	344.4
7.5°	349.1	349.1	349.1	349.1	348.1	348.1	348.1	348.1	348.1	348.1	348.1
10°	355.6	355.6	356.6	357.5	359.3	359.3	359.3	360.3	359.3	359.3	359.3
12.5°	369.7	368.7	370.6	372.4	374.4	375.2	375.2	375.2	374.4	374.4	375.2
15°	389.3	387.5	388.3	389.3	390.2	391.2	391.2	390.2	388.3	388.3	388.3
17.5°	414.6	411.8	410.8	409.9	409.9	411.8	413.6	412.7	413.6	412.7	413.6
20°	444.5	442.6	442.6	442.6	443.6	447.3	451.0	452.9	452.0	450.2	452.9
22.5°	464.1	465.1	469.8	468.8	467.9	471.6	476.3	480.0	478.2	475.4	477.3
25°	485.7	485.7	492.3	495.1	492.3	492.3	494.1	496.9	495.1	493.1	495.1
27.5°	510.0	510.0	512.9	515.6	513.7	513.7	516.6	521.3	520.3	519.4	520.3
30°	539.0	535.3	532.5	537.2	541.9	542.8	545.6	553.1	555.0	554.0	555.8
32.5°	566.2	560.5	562.4	565.2	575.6	579.3	578.3	584.0	583.0	580.3	584.0
35°	592.4	598.9	602.6	608.3	612.0	616.7	616.7	627.0	628.9	626.1	628.9
37.5°	642.9	645.7	656.1	656.9	661.6	679.4	681.2	695.3	702.8	699.0	700.0
40°	712.2	711.2	718.8	730.0	739.3	761.7	768.3	777.6	784.2	781.5	785.2
42.5°	768.3	760.9	766.4	790.7	801.1	817.9	826.3	831.0	843.2	839.5	844.1
45°	808.5	811.3	818.9	843.2	849.7	863.8	883.4	891.8	907.7	903.1	905.9
47.5°	847.9	861.0	867.5	878.7	899.3	918.0	942.4	950.8	973.3	971.4	968.6
50°	899.3	909.6	917.1	925.5	953.7	984.5	1005.1	1008.8	1016.3	1010.7	1020.1
52.5°	954.5	953.7	960.2	983.5	1022.9	1035.0	1052.8	1069.7	1085.6	1091.2	1085.6
55°	1027.5	1004.1	1031.3	1065.0	1081.8	1110.8	1153.9	1177.3	1208.2	1212.9	1203.5
57.5°	1057.5	1057.5	1085.6	1105.2	1136.1	1187.6	1233.4	1244.6	1260.5	1252.1	1261.5
60°	1053.8	1089.3	1089.3	1123.9	1174.5	1220.3	1237.2	1255.8	1277.4	1276.5	1276.5
62.5°	1058.5	1093.0	1083.6	1143.6	1174.5	1211.9	1249.3	1284.0	1313.9	1313.0	1312.0
63°	1063.1	1093.0	1087.5	1148.3	1173.5	1213.7	1258.7	1293.3	1317.7	1315.8	1316.7
65°	1077.1	1068.7	1102.4	1140.8	1169.8	1229.7	1267.1	1294.2	1311.1	1310.1	1310.1
67.5°	1050.9	1031.3	1079.0	1094.0	1149.2	1202.5	1231.5	1262.4	1274.6	1274.6	1272.7
70°	970.5	978.8	1011.7	1036.0	1092.1	1139.8	1164.1	1203.5	1218.4	1218.4	1217.6
72.5°	889.0	903.1	925.5	960.2	1013.5	1050.9	1079.9	1115.5	1135.1	1134.2	1134.2
75°	785.2	798.3	824.4	857.3	904.0	940.5	963.9	997.6	1020.1	1028.5	1019.1
77.5°	668.2	672.0	696.3	730.0	771.1	796.4	832.0	864.7	883.4	882.4	879.7
80°	526.0	530.6	551.2	589.5	612.0	642.0	674.7	692.5	708.4	708.4	706.5
82.5°	363.1	373.4	394.0	419.3	442.6	468.8	486.6	504.4	517.6	516.6	513.7
85°	204.9	209.6	229.2	245.2	262.9	279.8	291.9	303.2	314.4	314.4	312.5
87.5°	61.7	55.2	66.4	73.0	82.3	90.7	96.4	107.6	115.2	106.7	106.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P197757

CATALOG NUMBER: TT-C3-LED-E1-5WQ-PM-MS/DIM-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	329.4	329.4	329.4	329.4	329.4	329.4	329.4	329.4
2.5°	339.7	339.7	339.7	339.7	339.7	339.7	339.7	339.7
5°	344.4	345.4	345.4	346.2	346.2	346.2	346.2	346.2
7.5°	348.1	348.1	348.1	348.1	349.1	349.1	349.1	349.1
10°	359.3	360.3	359.3	359.3	357.5	356.6	356.6	356.6
12.5°	375.2	376.2	376.2	374.4	372.4	370.6	369.7	368.7
15°	390.2	393.0	391.2	390.2	388.3	389.3	389.3	390.2
17.5°	413.6	414.6	411.8	409.9	408.9	410.8	412.7	413.6
20°	453.9	452.0	446.4	444.5	442.6	442.6	444.5	444.5
22.5°	479.2	474.5	470.7	468.8	468.8	468.8	466.1	462.3
25°	496.9	494.1	491.3	493.1	495.1	492.3	485.7	484.7
27.5°	521.3	515.6	514.7	513.7	514.7	512.9	511.9	508.2
30°	553.1	545.6	543.7	541.9	536.2	534.4	536.2	539.0
32.5°	583.0	578.3	580.3	576.4	566.2	562.4	564.3	563.4
35°	626.1	617.7	617.7	610.1	607.3	606.4	598.9	592.4
37.5°	694.3	683.1	680.4	663.5	656.1	657.9	647.6	640.1
40°	777.6	769.3	761.7	743.1	732.7	719.6	713.1	713.1
42.5°	832.9	827.3	817.0	803.9	792.7	770.2	761.7	766.4
45°	893.7	886.3	864.7	851.6	841.3	825.4	816.0	806.7
47.5°	955.5	945.2	920.0	903.1	878.7	874.0	863.8	850.7
50°	1009.7	1006.0	988.2	960.2	929.2	921.8	912.4	900.2
52.5°	1076.2	1053.8	1038.7	1026.6	991.9	967.6	954.5	960.2
55°	1184.7	1156.7	1118.3	1079.9	1072.4	1043.4	1010.7	1028.5
57.5°	1247.4	1231.5	1202.5	1141.7	1111.8	1092.1	1070.6	1054.6
60°	1262.4	1233.4	1226.8	1181.0	1133.3	1092.1	1100.5	1063.1
62.5°	1291.4	1252.1	1215.6	1179.2	1150.2	1094.0	1092.1	1072.4
63°	1300.8	1261.5	1223.1	1179.2	1152.9	1100.5	1090.2	1079.9
65°	1298.9	1265.2	1236.2	1179.2	1139.8	1119.2	1068.7	1092.1
67.5°	1263.4	1235.3	1201.6	1162.3	1096.8	1080.9	1045.4	1050.0
70°	1206.3	1169.8	1138.0	1101.4	1049.1	1012.5	991.1	973.3
72.5°	1117.3	1084.6	1050.9	1017.2	970.5	926.5	911.5	891.8
75°	999.5	967.6	936.8	904.9	861.0	821.7	805.8	791.7
77.5°	864.7	837.5	793.6	763.6	738.4	696.3	681.2	666.3
80°	689.7	676.6	644.8	605.5	592.4	551.2	540.0	520.3
82.5°	501.6	488.5	463.2	436.1	420.2	398.7	379.9	366.8
85°	306.0	291.9	278.8	254.5	245.2	229.2	214.3	206.8
87.5°	110.5	99.2	88.9	77.6	72.1	60.8	59.0	53.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)