

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P400600

Luminaire Tested: **TT-D2-735-U-5CQ-PM**

Issue Date: 5/19/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P400600  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/19/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D2-735-U-5CQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
3500K, 70 CRI LEDS AND CONCENTRATED DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4925 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1


Input Watts (W): 39.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P400600  
 CATALOG NUMBER: TT-D2-735-U-5CQ-PM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2 fc  
 Type V - Short - N/A

REPORT NUMBER: P400600  
CATALOG NUMBER: TT-D2-735-U-5CQ-PM

### Luminous Intensity Polar Plot



— Vertical Plane Through 5-Deg Lateral      - - - Horizontal Cone Through 2.5-Deg Vertical

REPORT NUMBER: P400600  
 CATALOG NUMBER: TT-D2-735-U-5CQ-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2462.5	0.0	2462.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2462.5	0.0	2462.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4925.0	0.0	4925.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.2	2.4
10°-20°	343.2	7.0
20°-30°	545.8	11.1
30°-40°	717.9	14.6
40°-50°	878.7	17.8
50°-60°	951.8	19.3
60°-70°	818.8	16.6
70°-80°	460.3	9.3
80°-90°	91.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4925.0	100.0
0°-180°	4925.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P400600


CATALOG NUMBER: TT-D2-735-U-5CQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	503.1	10.2			
FM (30°-60°)	1274.2	25.9			
FH (60°-80°)	639.6	13.0			G0/660
FVH (80°-90°)	45.6	0.9			G1/100
BL (0°-30°)	503.1	10.2	B2/1000		
BM (30°-60°)	1274.2	25.9	B2/2500		
BH (60°-80°)	639.6	13.0	B2/1000		G0/660
BVH (80°-90°)	45.6	0.9			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G1**

Type V Short





REPORT NUMBER: P400600  
 CATALOG NUMBER: TT-D2-735-U-5CQ-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1	1232.1
2.5°	1229.0	1232.9	1231.3	1231.3	1231.3	1231.3	1229.7	1231.3	1231.3	1232.1	1231.3
5°	1229.7	1229.0	1229.0	1229.7	1229.7	1230.5	1229.0	1229.7	1230.5	1230.5	1231.3
7.5°	1227.4	1228.2	1226.6	1228.2	1226.6	1227.4	1227.4	1228.2	1227.4	1228.2	1229.7
10°	1222.7	1223.5	1222.7	1222.7	1222.7	1224.3	1221.1	1223.5	1222.7	1223.5	1222.7
12.5°	1214.1	1218.0	1216.4	1218.0	1218.0	1218.0	1215.6	1217.2	1218.0	1218.0	1218.0
15°	1210.1	1210.9	1208.6	1211.7	1212.5	1213.3	1210.1	1211.7	1211.7	1212.5	1213.3
17.5°	1201.5	1205.4	1204.7	1207.0	1206.2	1208.6	1207.8	1207.0	1206.2	1207.8	1206.2
20°	1195.3	1199.2	1198.4	1200.7	1201.5	1203.9	1201.5	1201.5	1199.2	1200.0	1202.3
22.5°	1189.0	1190.6	1190.6	1192.9	1192.9	1195.3	1192.9	1192.1	1192.1	1191.3	1193.7
25°	1178.8	1179.6	1178.8	1181.1	1182.7	1184.3	1183.5	1181.9	1181.1	1181.1	1180.4
27.5°	1162.3	1165.5	1167.0	1170.2	1171.0	1173.3	1170.2	1170.2	1168.6	1167.0	1167.8
30°	1149.8	1151.4	1151.4	1158.4	1158.4	1162.3	1158.4	1157.6	1156.8	1156.1	1154.5
32.5°	1138.0	1140.4	1142.7	1148.2	1152.1	1153.7	1151.4	1149.8	1145.9	1143.5	1142.7
35°	1128.6	1129.4	1134.1	1142.0	1146.7	1150.6	1147.4	1143.5	1138.0	1134.1	1137.3
37.5°	1121.6	1122.4	1129.4	1139.6	1148.2	1151.4	1146.7	1140.4	1131.8	1127.1	1125.5
40°	1115.3	1120.0	1127.8	1142.0	1151.4	1156.1	1152.1	1143.5	1131.0	1121.6	1120.8
42.5°	1112.2	1114.5	1126.3	1142.7	1156.1	1162.3	1156.8	1145.1	1129.4	1118.4	1117.7
45°	1104.3	1111.4	1122.4	1143.5	1158.4	1166.3	1158.4	1143.5	1124.7	1112.2	1109.8
47.5°	1098.1	1100.4	1117.7	1142.0	1160.0	1166.3	1158.4	1139.6	1116.1	1099.6	1098.1
50°	1083.2	1088.7	1105.9	1131.8	1152.9	1159.2	1149.8	1124.7	1098.1	1080.0	1076.9
52.5°	1060.4	1065.1	1085.5	1117.7	1138.0	1145.1	1131.0	1104.3	1073.0	1051.0	1051.0
55°	1025.2	1032.2	1053.4	1086.3	1112.2	1118.4	1102.0	1073.8	1038.5	1016.6	1015.8
57.5°	982.9	987.6	1010.3	1046.3	1071.4	1080.8	1064.4	1033.0	997.7	971.9	969.5
60°	928.0	934.3	958.6	993.0	1018.9	1026.7	1012.6	981.3	945.2	917.8	917.8
62.5°	862.2	869.2	893.5	928.8	955.4	967.2	947.6	917.8	880.2	853.5	851.2
65°	785.3	791.6	813.6	850.4	877.8	886.4	871.6	840.2	804.2	779.1	776.7
67.5°	699.1	707.7	729.7	761.0	784.6	795.5	786.1	757.9	720.3	694.4	692.1
70°	605.9	612.1	629.4	658.4	685.0	692.9	678.7	659.9	624.7	601.2	598.0
72.5°	506.3	511.8	525.9	553.3	572.2	582.3	574.5	550.2	522.0	502.4	505.5
75°	406.0	405.2	420.9	440.5	457.7	464.8	459.3	443.6	417.8	401.3	400.5
77.5°	305.7	313.5	319.0	335.5	349.6	355.0	347.2	334.7	315.1	301.8	304.1
80°	214.8	210.1	220.2	230.4	239.8	245.3	240.6	233.6	220.2	210.1	208.5
82.5°	131.7	127.8	132.5	141.9	148.1	149.7	150.5	141.9	136.4	128.5	130.1
85°	58.0	58.8	62.7	69.0	69.8	70.5	70.5	69.0	62.7	61.9	60.4
87.5°	14.1	14.1	14.9	17.2	17.2	18.0	18.0	15.7	14.9	13.3	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)