

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387197

Luminaire Tested: **TT-D2-740-U-5CQ-PM**

Issue Date: 2/18/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P387197  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-17)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 2/18/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D2-740-U-5CQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
4000K, 70 CRI LEDS AND CONCENTRATED DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5211 lumens  
Efficiency: N/A  
Efficacy: 132.9 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1

Input Watts (W): 39.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P387197

CATALOG NUMBER: TT-D2-740-U-5CQ-PM

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd


--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.1 fc  
 Type V - Short - N/A

REPORT NUMBER: P387197  
CATALOG NUMBER: TT-D2-740-U-5CQ-PM

## Luminous Intensity Polar Plot



REPORT NUMBER: P387197

CATALOG NUMBER: TT-D2-740-U-5CQ-PM


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2605.5   | 0.0    | 2605.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2605.5   | 0.0    | 2605.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 5211.0   | 0.0    | 5211.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 124.0  | 2.4       |
| 10°-20°   | 363.1  | 7.0       |
| 20°-30°   | 577.5  | 11.1      |
| 30°-40°   | 759.6  | 14.6      |
| 40°-50°   | 929.8  | 17.8      |
| 50°-60°   | 1007.0 | 19.3      |
| 60°-70°   | 866.4  | 16.6      |
| 70°-80°   | 487.1  | 9.3       |
| 80°-90°   | 96.6   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5211.0 | 100.0     |
| 0°-180°   | 5211.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P387197


CATALOG NUMBER: TT-D2-740-U-5CQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 532.3  | 10.2      |                         |      |         |
| FM   | (30°-60°)   | 1348.2 | 25.9      |                         |      |         |
| FH   | (60°-80°)   | 676.7  | 13.0      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 48.3   | 0.9       |                         |      | G1/100  |
| BL   | (0°-30°)    | 532.3  | 10.2      | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1348.2 | 25.9      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 676.7  | 13.0      | B2/1000                 |      | G1/1800 |
| BVH  | (80°-90°)   | 48.3   | 0.9       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type V Short



REPORT NUMBER: P387197

CATALOG NUMBER: TT-D2-740-U-5CQ-PM

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 | 1303.6 |
| 2.5°  | 1300.3 | 1304.5 | 1302.8 | 1302.8 | 1302.8 | 1302.8 | 1301.2 | 1302.8 | 1302.8 | 1303.6 | 1302.8 |
| 5°    | 1301.2 | 1300.3 | 1300.3 | 1301.2 | 1301.2 | 1302.0 | 1300.3 | 1301.2 | 1302.0 | 1302.0 | 1302.8 |
| 7.5°  | 1298.7 | 1299.5 | 1297.8 | 1299.5 | 1297.8 | 1298.7 | 1298.7 | 1299.5 | 1298.7 | 1299.5 | 1301.2 |
| 10°   | 1293.7 | 1294.5 | 1293.7 | 1293.7 | 1293.7 | 1295.3 | 1292.0 | 1294.5 | 1293.7 | 1294.5 | 1293.7 |
| 12.5° | 1284.6 | 1288.7 | 1287.1 | 1288.7 | 1288.7 | 1288.7 | 1286.2 | 1287.9 | 1288.7 | 1288.7 | 1288.7 |
| 15°   | 1280.4 | 1281.2 | 1278.8 | 1282.1 | 1282.9 | 1283.7 | 1280.4 | 1282.1 | 1282.1 | 1282.9 | 1283.7 |
| 17.5° | 1271.3 | 1275.4 | 1274.6 | 1277.1 | 1276.3 | 1278.8 | 1277.9 | 1277.1 | 1276.3 | 1277.9 | 1276.3 |
| 20°   | 1264.7 | 1268.8 | 1268.0 | 1270.5 | 1271.3 | 1273.8 | 1271.3 | 1271.3 | 1268.8 | 1269.6 | 1272.1 |
| 22.5° | 1258.0 | 1259.7 | 1259.7 | 1262.2 | 1262.2 | 1264.7 | 1262.2 | 1261.3 | 1261.3 | 1260.5 | 1263.0 |
| 25°   | 1247.2 | 1248.1 | 1247.2 | 1249.7 | 1251.4 | 1253.1 | 1252.2 | 1250.6 | 1249.7 | 1249.7 | 1248.9 |
| 27.5° | 1229.8 | 1233.2 | 1234.8 | 1238.1 | 1239.0 | 1241.4 | 1238.1 | 1238.1 | 1236.5 | 1234.8 | 1235.6 |
| 30°   | 1216.6 | 1218.2 | 1218.2 | 1225.7 | 1225.7 | 1229.8 | 1225.7 | 1224.9 | 1224.0 | 1223.2 | 1221.5 |
| 32.5° | 1204.1 | 1206.6 | 1209.1 | 1214.9 | 1219.1 | 1220.7 | 1218.2 | 1216.6 | 1212.4 | 1209.9 | 1209.1 |
| 35°   | 1194.2 | 1195.0 | 1200.0 | 1208.3 | 1213.2 | 1217.4 | 1214.1 | 1209.9 | 1204.1 | 1200.0 | 1203.3 |
| 37.5° | 1186.7 | 1187.5 | 1195.0 | 1205.8 | 1214.9 | 1218.2 | 1213.2 | 1206.6 | 1197.5 | 1192.5 | 1190.9 |
| 40°   | 1180.1 | 1185.1 | 1193.3 | 1208.3 | 1218.2 | 1223.2 | 1219.1 | 1209.9 | 1196.7 | 1186.7 | 1185.9 |
| 42.5° | 1176.8 | 1179.2 | 1191.7 | 1209.1 | 1223.2 | 1229.8 | 1224.0 | 1211.6 | 1195.0 | 1183.4 | 1182.6 |
| 45°   | 1168.5 | 1175.9 | 1187.5 | 1209.9 | 1225.7 | 1234.0 | 1225.7 | 1209.9 | 1190.0 | 1176.8 | 1174.3 |
| 47.5° | 1161.8 | 1164.3 | 1182.6 | 1208.3 | 1227.3 | 1234.0 | 1225.7 | 1205.8 | 1180.9 | 1163.5 | 1161.8 |
| 50°   | 1146.1 | 1151.9 | 1170.1 | 1197.5 | 1219.9 | 1226.5 | 1216.6 | 1190.0 | 1161.8 | 1142.8 | 1139.4 |
| 52.5° | 1122.0 | 1127.0 | 1148.6 | 1182.6 | 1204.1 | 1211.6 | 1196.7 | 1168.5 | 1135.3 | 1112.1 | 1112.1 |
| 55°   | 1084.7 | 1092.2 | 1114.6 | 1149.4 | 1176.8 | 1183.4 | 1166.0 | 1136.1 | 1098.8 | 1075.6 | 1074.8 |
| 57.5° | 1039.9 | 1044.9 | 1069.0 | 1107.1 | 1133.6 | 1143.6 | 1126.2 | 1093.0 | 1055.7 | 1028.3 | 1025.8 |
| 60°   | 981.9  | 988.5  | 1014.2 | 1050.7 | 1078.1 | 1086.4 | 1071.4 | 1038.3 | 1000.1 | 971.1  | 971.1  |
| 62.5° | 912.2  | 919.7  | 945.4  | 982.7  | 1010.9 | 1023.3 | 1002.6 | 971.1  | 931.3  | 903.1  | 900.6  |
| 65°   | 830.9  | 837.6  | 860.8  | 899.8  | 928.8  | 937.9  | 922.2  | 889.0  | 850.8  | 824.3  | 821.8  |
| 67.5° | 739.7  | 748.8  | 772.1  | 805.2  | 830.1  | 841.7  | 831.8  | 801.9  | 762.1  | 734.7  | 732.3  |
| 70°   | 641.0  | 647.7  | 665.9  | 696.6  | 724.8  | 733.1  | 718.2  | 698.3  | 660.9  | 636.1  | 632.7  |
| 72.5° | 535.7  | 541.5  | 556.5  | 585.5  | 605.4  | 616.2  | 607.9  | 582.2  | 552.3  | 531.6  | 534.9  |
| 75°   | 429.6  | 428.7  | 445.3  | 466.1  | 484.3  | 491.8  | 486.0  | 469.4  | 442.0  | 424.6  | 423.8  |
| 77.5° | 323.4  | 331.7  | 337.5  | 354.9  | 369.9  | 375.7  | 367.4  | 354.1  | 333.4  | 319.3  | 321.8  |
| 80°   | 227.2  | 222.2  | 233.0  | 243.8  | 253.8  | 259.6  | 254.6  | 247.1  | 233.0  | 222.2  | 220.6  |
| 82.5° | 139.3  | 135.2  | 140.1  | 150.1  | 156.7  | 158.4  | 159.2  | 150.1  | 144.3  | 136.0  | 137.7  |
| 85°   | 61.4   | 62.2   | 66.3   | 73.0   | 73.8   | 74.6   | 74.6   | 73.0   | 66.3   | 65.5   | 63.9   |
| 87.5° | 14.9   | 14.9   | 15.8   | 18.2   | 18.2   | 19.1   | 19.1   | 16.6   | 15.8   | 14.1   | 14.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2006-844-6

Luminaire Tested: TT-D2-740-U-RW

Test Date: 06/30/2020

Data applicable to product families TT-x-740 and TTN-x-740



### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2006-844-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 06/30/2020  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: MCGRAW-EDISON  
 Catalog Number: **TT-D2-740-U-RW**  
 Description: MCGRAW EDISON

### RECTANGULAR DISTRIBUTION

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3623   | CRI (Ra): | 72.6 |      |       |
| CIE u':                   | 0.2297 | R1:       | 69.4 | R9:  | -22.4 |
| CIE v':                   | 0.5166 | R2:       | 78.4 | R10: | 49.0  |
| Duv:                      | 0.0060 | R3:       | 86.1 | R11: | 67.4  |
| CIE x:                    | 0.4044 | R4:       | 72.3 | R12: | 39.3  |
| CIE y:                    | 0.4042 | R5:       | 68.2 | R13: | 70.5  |
| CIE z:                    | 0.1914 | R6:       | 69.2 | R14: | 91.9  |
| Peak Wavelength (nm):     | 588    | R7:       | 83.0 |      |       |
| Dominant Wavelength (nm): | 578    | R8:       | 54.2 |      |       |
| Purity:                   | 42.8   |           |      |      |       |
| Rf:                       | 76.2   |           |      |      |       |
| Rg:                       | 94.3   |           |      |      |       |



### Test Conditions

Stabilization Time: 207M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.9/42%  
 Sphere Temperature (°C): 25.8

REPORT NUMBER: SP1-2006-844-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/3/2019        | 12/3/2020            |
| AC Power Source                | IN0063                | 12/3/2019        | 12/3/2020            |
| DC Power Source                | IN0208                | 12/3/2019        | 12/3/2020            |
| Sphere Thermometer             | IN0085                | 12/3/2019        | 12/3/2020            |
| Room Thermometer               | IN0046                | 12/3/2019        | 12/3/2020            |

REPORT NUMBER: SP1-2006-844-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2006-844-6

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1254             | 0.0              | 490       | 9219             | 1.3              | 620       | 54761            | 14.3             | 750       | 2901             | 0.0              | 880       | 1835             | 0.0              |
| 365       | 1158             | 0.0              | 495       | 12322            | 2.2              | 625       | 51064            | 11.3             | 755       | 2733             | 0.0              | 885       | 1690             | 0.0              |
| 370       | 1131             | 0.0              | 500       | 17160            | 3.8              | 630       | 47879            | 8.7              | 760       | 2503             | 0.0              | 890       | 1819             | 0.0              |
| 375       | 1414             | 0.0              | 505       | 23071            | 6.5              | 635       | 44248            | 6.6              | 765       | 2289             | 0.0              | 895       | 1314             | 0.0              |
| 380       | 1275             | 0.0              | 510       | 29162            | 10.0             | 640       | 41034            | 4.9              | 770       | 2078             | 0.0              | 900       | 1547             | 0.0              |
| 385       | 1122             | 0.0              | 515       | 34992            | 14.5             | 645       | 37515            | 3.6              | 775       | 1927             | 0.0              | 905       | 1281             | 0.0              |
| 390       | 1074             | 0.0              | 520       | 40102            | 19.4             | 650       | 33900            | 2.5              | 780       | 1724             | 0.0              | 910       | 1345             | 0.0              |
| 395       | 1058             | 0.0              | 525       | 44194            | 23.7             | 655       | 30384            | 1.7              | 785       | 1617             | 0.0              | 915       | 1561             | 0.0              |
| 400       | 885              | 0.0              | 530       | 48014            | 28.3             | 660       | 26883            | 1.1              | 790       | 1709             | 0.0              | 920       | 1368             | 0.0              |
| 405       | 912              | 0.0              | 535       | 51019            | 31.6             | 665       | 23703            | 0.8              | 795       | 1561             | 0.0              | 925       | 1730             | 0.0              |
| 410       | 1108             | 0.0              | 540       | 53190            | 34.7             | 670       | 20603            | 0.5              | 800       | 1525             | 0.0              | 930       | 1629             | 0.0              |
| 415       | 1763             | 0.0              | 545       | 55452            | 36.9             | 675       | 18039            | 0.3              | 805       | 1332             | 0.0              | 935       | 1796             | 0.0              |
| 420       | 3421             | 0.0              | 550       | 57280            | 38.9             | 680       | 15849            | 0.2              | 810       | 1269             | 0.0              | 940       | 1595             | 0.0              |
| 425       | 6610             | 0.0              | 555       | 59041            | 40.3             | 685       | 13806            | 0.1              | 815       | 1261             | 0.0              | 945       | 1410             | 0.0              |
| 430       | 12444            | 0.1              | 560       | 60976            | 41.4             | 690       | 12093            | 0.1              | 820       | 1551             | 0.0              | 950       | 1937             | 0.0              |
| 435       | 21116            | 0.2              | 565       | 62904            | 41.8             | 695       | 10566            | 0.0              | 825       | 1708             | 0.0              | 955       | 2186             | 0.0              |
| 440       | 33463            | 0.5              | 570       | 64555            | 42.0             | 700       | 9300             | 0.0              | 830       | 1592             | 0.0              | 960       | 1583             | 0.0              |
| 445       | 49089            | 1.0              | 575       | 65785            | 40.9             | 705       | 8110             | 0.0              | 835       | 1642             | 0.0              | 965       | 1953             | 0.0              |
| 450       | 57374            | 1.5              | 580       | 66948            | 39.8             | 710       | 7052             | 0.0              | 840       | 1514             | 0.0              | 970       | 1519             | 0.0              |
| 455       | 42663            | 1.4              | 585       | 67963            | 37.8             | 715       | 6233             | 0.0              | 845       | 1376             | 0.0              | 975       | 1168             | 0.0              |
| 460       | 25334            | 1.0              | 590       | 68001            | 35.2             | 720       | 5362             | 0.0              | 850       | 1592             | 0.0              | 980       | 1593             | 0.0              |
| 465       | 17751            | 0.9              | 595       | 67308            | 31.9             | 725       | 4563             | 0.0              | 855       | 1667             | 0.0              | 985       | 1722             | 0.0              |
| 470       | 12447            | 0.8              | 600       | 66343            | 28.6             | 730       | 3976             | 0.0              | 860       | 1662             | 0.0              | 990       | 1648             | 0.0              |
| 475       | 8641             | 0.7              | 605       | 64393            | 24.9             | 735       | 3424             | 0.0              | 865       | 1916             | 0.0              | 995       | 2495             | 0.0              |
| 480       | 7423             | 0.7              | 610       | 61634            | 21.2             | 740       | 3222             | 0.0              | 870       | 1655             | 0.0              | 1000      | 2643             | 0.0              |
| 485       | 7759             | 0.9              | 615       | 58349            | 17.6             | 745       | 3060             | 0.0              | 875       | 2036             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2006-844-6

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 1941.7

S/P: 0.51

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1254             | 0.0              | 490       | 9219             | 14.2             | 620       | 54761            | 0.7              | 750       | 2901             | 0.0              | 880       | 1835             | 0.0              |
| 365       | 1158             | 0.0              | 495       | 12322            | 19.9             | 625       | 51064            | 0.4              | 755       | 2733             | 0.0              | 885       | 1690             | 0.0              |
| 370       | 1131             | 0.0              | 500       | 17160            | 28.7             | 630       | 47879            | 0.3              | 760       | 2503             | 0.0              | 890       | 1819             | 0.0              |
| 375       | 1414             | 0.0              | 505       | 23071            | 39.2             | 635       | 44248            | 0.2              | 765       | 2289             | 0.0              | 895       | 1314             | 0.0              |
| 380       | 1275             | 0.0              | 510       | 29162            | 49.4             | 640       | 41034            | 0.1              | 770       | 2078             | 0.0              | 900       | 1547             | 0.0              |
| 385       | 1122             | 0.0              | 515       | 34992            | 58.0             | 645       | 37515            | 0.1              | 775       | 1927             | 0.0              | 905       | 1281             | 0.0              |
| 390       | 1074             | 0.0              | 520       | 40102            | 63.7             | 650       | 33900            | 0.0              | 780       | 1724             | 0.0              | 910       | 1345             | 0.0              |
| 395       | 1058             | 0.0              | 525       | 44194            | 66.1             | 655       | 30384            | 0.0              | 785       | 1617             | 0.0              | 915       | 1561             | 0.0              |
| 400       | 885              | 0.0              | 530       | 48014            | 66.2             | 660       | 26883            | 0.0              | 790       | 1709             | 0.0              | 920       | 1368             | 0.0              |
| 405       | 912              | 0.0              | 535       | 51019            | 63.6             | 665       | 23703            | 0.0              | 795       | 1561             | 0.0              | 925       | 1730             | 0.0              |
| 410       | 1108             | 0.1              | 540       | 53190            | 58.8             | 670       | 20603            | 0.0              | 800       | 1525             | 0.0              | 930       | 1629             | 0.0              |
| 415       | 1763             | 0.2              | 545       | 55452            | 53.2             | 675       | 18039            | 0.0              | 805       | 1332             | 0.0              | 935       | 1796             | 0.0              |
| 420       | 3421             | 0.6              | 550       | 57280            | 46.8             | 680       | 15849            | 0.0              | 810       | 1269             | 0.0              | 940       | 1595             | 0.0              |
| 425       | 6610             | 1.6              | 555       | 59041            | 40.3             | 685       | 13806            | 0.0              | 815       | 1261             | 0.0              | 945       | 1410             | 0.0              |
| 430       | 12444            | 4.2              | 560       | 60976            | 34.1             | 690       | 12093            | 0.0              | 820       | 1551             | 0.0              | 950       | 1937             | 0.0              |
| 435       | 21116            | 9.4              | 565       | 62904            | 28.2             | 695       | 10566            | 0.0              | 825       | 1708             | 0.0              | 955       | 2186             | 0.0              |
| 440       | 33463            | 18.7             | 570       | 64555            | 22.8             | 700       | 9300             | 0.0              | 830       | 1592             | 0.0              | 960       | 1583             | 0.0              |
| 445       | 49089            | 32.9             | 575       | 65785            | 17.9             | 705       | 8110             | 0.0              | 835       | 1642             | 0.0              | 965       | 1953             | 0.0              |
| 450       | 57374            | 44.5             | 580       | 66948            | 13.8             | 710       | 7052             | 0.0              | 840       | 1514             | 0.0              | 970       | 1519             | 0.0              |
| 455       | 42663            | 37.3             | 585       | 67963            | 10.4             | 715       | 6233             | 0.0              | 845       | 1376             | 0.0              | 975       | 1168             | 0.0              |
| 460       | 25334            | 24.5             | 590       | 68001            | 7.6              | 720       | 5362             | 0.0              | 850       | 1592             | 0.0              | 980       | 1593             | 0.0              |
| 465       | 17751            | 18.7             | 595       | 67308            | 5.4              | 725       | 4563             | 0.0              | 855       | 1667             | 0.0              | 985       | 1722             | 0.0              |
| 470       | 12447            | 14.3             | 600       | 66343            | 3.7              | 730       | 3976             | 0.0              | 860       | 1662             | 0.0              | 990       | 1648             | 0.0              |
| 475       | 8641             | 10.8             | 605       | 64393            | 2.5              | 735       | 3424             | 0.0              | 865       | 1916             | 0.0              | 995       | 2495             | 0.0              |
| 480       | 7423             | 10.0             | 610       | 61634            | 1.7              | 740       | 3222             | 0.0              | 870       | 1655             | 0.0              | 1000      | 2643             | 0.0              |
| 485       | 7759             | 11.2             | 615       | 58349            | 1.1              | 745       | 3060             | 0.0              | 875       | 2036             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2006-844-6

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 5289.9**
**S/P: 1.39**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1254             | 0.0              | 490       | 9219             | 7.7              | 620       | 54761            | 0.0              | 750       | 2901             | 0.0              | 880       | 1835             | 0.0              |
| 365       | 1158             | 0.0              | 495       | 12322            | 10.2             | 625       | 51064            | 0.0              | 755       | 2733             | 0.0              | 885       | 1690             | 0.0              |
| 370       | 1131             | 0.0              | 500       | 17160            | 13.8             | 630       | 47879            | 0.0              | 760       | 2503             | 0.0              | 890       | 1819             | 0.0              |
| 375       | 1414             | 0.0              | 505       | 23071            | 17.7             | 635       | 44248            | 0.0              | 765       | 2289             | 0.0              | 895       | 1314             | 0.0              |
| 380       | 1275             | 0.0              | 510       | 29162            | 20.9             | 640       | 41034            | 0.0              | 770       | 2078             | 0.0              | 900       | 1547             | 0.0              |
| 385       | 1122             | 0.0              | 515       | 34992            | 22.9             | 645       | 37515            | 0.0              | 775       | 1927             | 0.0              | 905       | 1281             | 0.0              |
| 390       | 1074             | 0.0              | 520       | 40102            | 23.3             | 650       | 33900            | 0.0              | 780       | 1724             | 0.0              | 910       | 1345             | 0.0              |
| 395       | 1058             | 0.0              | 525       | 44194            | 22.4             | 655       | 30384            | 0.0              | 785       | 1617             | 0.0              | 915       | 1561             | 0.0              |
| 400       | 885              | 0.0              | 530       | 48014            | 20.7             | 660       | 26883            | 0.0              | 790       | 1709             | 0.0              | 920       | 1368             | 0.0              |
| 405       | 912              | 0.0              | 535       | 51019            | 18.4             | 665       | 23703            | 0.0              | 795       | 1561             | 0.0              | 925       | 1730             | 0.0              |
| 410       | 1108             | 0.0              | 540       | 53190            | 15.6             | 670       | 20603            | 0.0              | 800       | 1525             | 0.0              | 930       | 1629             | 0.0              |
| 415       | 1763             | 0.1              | 545       | 55452            | 12.9             | 675       | 18039            | 0.0              | 805       | 1332             | 0.0              | 935       | 1796             | 0.0              |
| 420       | 3421             | 0.4              | 550       | 57280            | 10.3             | 680       | 15849            | 0.0              | 810       | 1269             | 0.0              | 940       | 1595             | 0.0              |
| 425       | 6610             | 1.0              | 555       | 59041            | 8.0              | 685       | 13806            | 0.0              | 815       | 1261             | 0.0              | 945       | 1410             | 0.0              |
| 430       | 12444            | 2.6              | 560       | 60976            | 6.0              | 690       | 12093            | 0.0              | 820       | 1551             | 0.0              | 950       | 1937             | 0.0              |
| 435       | 21116            | 5.6              | 565       | 62904            | 4.4              | 695       | 10566            | 0.0              | 825       | 1708             | 0.0              | 955       | 2186             | 0.0              |
| 440       | 33463            | 11.2             | 570       | 64555            | 3.2              | 700       | 9300             | 0.0              | 830       | 1592             | 0.0              | 960       | 1583             | 0.0              |
| 445       | 49089            | 19.4             | 575       | 65785            | 2.2              | 705       | 8110             | 0.0              | 835       | 1642             | 0.0              | 965       | 1953             | 0.0              |
| 450       | 57374            | 26.4             | 580       | 66948            | 1.5              | 710       | 7052             | 0.0              | 840       | 1514             | 0.0              | 970       | 1519             | 0.0              |
| 455       | 42663            | 22.4             | 585       | 67963            | 1.0              | 715       | 6233             | 0.0              | 845       | 1376             | 0.0              | 975       | 1168             | 0.0              |
| 460       | 25334            | 14.9             | 590       | 68001            | 0.7              | 720       | 5362             | 0.0              | 850       | 1592             | 0.0              | 980       | 1593             | 0.0              |
| 465       | 17751            | 11.6             | 595       | 67308            | 0.4              | 725       | 4563             | 0.0              | 855       | 1667             | 0.0              | 985       | 1722             | 0.0              |
| 470       | 12447            | 8.9              | 600       | 66343            | 0.3              | 730       | 3976             | 0.0              | 860       | 1662             | 0.0              | 990       | 1648             | 0.0              |
| 475       | 8641             | 6.6              | 605       | 64393            | 0.2              | 735       | 3424             | 0.0              | 865       | 1916             | 0.0              | 995       | 2495             | 0.0              |
| 480       | 7423             | 6.0              | 610       | 61634            | 0.1              | 740       | 3222             | 0.0              | 870       | 1655             | 0.0              | 1000      | 2643             | 0.0              |
| 485       | 7759             | 6.4              | 615       | 58349            | 0.1              | 745       | 3060             | 0.0              | 875       | 2036             | 0.0              |           |                  |                  |





### Summary

$R_f = 76.2$   
 $R_g = 94.3$   
 CIE  $R_a = 72.6$   
 $R_g = -22.4$

### Spectral Power Distribution Comparison



### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 66 | CES51 = 88 | CES76 = 55 |
| CES02 = 61 | CES27 = 89 | CES52 = 88 | CES77 = 73 |
| CES03 = 31 | CES28 = 83 | CES53 = 78 | CES78 = 59 |
| CES04 = 70 | CES29 = 69 | CES54 = 85 | CES79 = 84 |
| CES05 = 48 | CES30 = 83 | CES55 = 84 | CES80 = 81 |
| CES06 = 51 | CES31 = 73 | CES56 = 74 | CES81 = 79 |
| CES07 = 40 | CES32 = 65 | CES57 = 73 | CES82 = 92 |
| CES08 = 39 | CES33 = 79 | CES58 = 74 | CES83 = 90 |
| CES09 = 29 | CES34 = 74 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 85 | CES60 = 90 | CES85 = 79 |
| CES11 = 57 | CES36 = 92 | CES61 = 84 | CES86 = 73 |
| CES12 = 63 | CES37 = 80 | CES62 = 87 | CES87 = 78 |
| CES13 = 42 | CES38 = 92 | CES63 = 73 | CES88 = 81 |
| CES14 = 74 | CES39 = 97 | CES64 = 68 | CES89 = 72 |
| CES15 = 71 | CES40 = 92 | CES65 = 65 | CES90 = 80 |
| CES16 = 47 | CES41 = 93 | CES66 = 61 | CES91 = 78 |
| CES17 = 49 | CES42 = 82 | CES67 = 58 | CES92 = 63 |
| CES18 = 56 | CES43 = 80 | CES68 = 68 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 76 | CES94 = 57 |
| CES20 = 65 | CES45 = 86 | CES70 = 60 | CES95 = 69 |
| CES21 = 86 | CES46 = 83 | CES71 = 54 | CES96 = 78 |
| CES22 = 78 | CES47 = 86 | CES72 = 85 | CES97 = 85 |
| CES23 = 92 | CES48 = 77 | CES73 = 52 | CES98 = 77 |
| CES24 = 91 | CES49 = 81 | CES74 = 95 | CES99 = 67 |
| CES25 = 72 | CES50 = 88 | CES75 = 56 |            |





Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)