

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436902

Luminaire Tested: **TT-D6-740-U-RW-PM-HSS**

Issue Date: 12/2/2020

Test Information

Test Method: LM-79-08
Report Number: P436902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-5)
Test Lab: INNOVATION CENTER
Issue Date: 12/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: TT-D6-740-U-RW-PM-HSS
Description: TOPTIER LED SITE LUMINAIRE
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7911.1 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U2 - G3


Input Watts (W): 105.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1 fc
 Type IV - Short - N/A

REPORT NUMBER: P436902
CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2498.2	3.2	2501.4
	% Fixture	31.6	0.0	31.6
Street Side	Lumens	5374.8	34.9	5409.7
	% Fixture	67.9	0.4	68.4
Total	Lumens	7872.9	38.1	7911.1
	% Fixture	99.5	0.5	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.5	0.3
10°-20°	85.2	1.1
20°-30°	196.5	2.5
30°-40°	421.1	5.3
40°-50°	902.0	11.4
50°-60°	1703.4	21.5
60°-70°	2116.9	26.8
70°-80°	1812.3	22.9
80°-90°	613.0	7.7
90°-100°	26.5	0.3
100°-110°	7.6	0.1
110°-120°	1.7	0.0
120°-130°	0.9	0.0
130°-140°	0.6	0.0
140°-150°	0.4	0.0
150°-160°	0.2	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	7872.9	99.5
0°-180°	7911.1	100.0




REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	161.8	2.0			
FM (30°-60°)	1810.4	22.9			
FH (60°-80°)	2928.3	37.0			G2/5000
FVH (80°-90°)	474.3	6.0			G3/500
BL (0°-30°)	142.5	1.8	B1/500		
BM (30°-60°)	1216.0	15.4	B2/2500		
BH (60°-80°)	1000.9	12.7	B3/2500		G3/2500
BVH (80°-90°)	138.8	1.8			G2/225
UL (90°-100°)	26.5	0.3		U2/50	
UH (100°-180°)	11.6	0.1		U2/50	

BUG Rating: B3-U2-G3

Type IV Short





REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9
2.5°	226.7	226.7	226.7	224.7	224.7	224.7	222.8	220.8	218.8	218.8	218.8
5°	238.5	238.5	238.5	238.5	236.6	234.6	232.6	230.6	228.7	228.7	226.7
7.5°	254.3	252.3	254.3	252.3	252.3	250.4	248.4	246.4	242.5	242.5	240.5
10°	270.1	270.1	270.1	270.1	270.1	268.1	266.1	264.2	262.2	260.2	258.2
12.5°	289.8	289.8	289.8	287.8	289.8	287.8	285.8	285.8	283.9	279.9	279.9
15°	309.5	309.5	309.5	309.5	311.5	311.5	311.5	309.5	309.5	307.5	305.5
17.5°	333.1	331.2	333.1	333.1	335.1	337.1	339.1	341.0	341.0	339.1	339.1
20°	358.8	356.8	358.8	358.8	362.7	366.7	372.6	376.5	378.5	374.5	374.5
22.5°	386.4	384.4	388.3	388.3	394.3	400.2	410.0	414.0	419.9	417.9	417.9
25°	419.9	417.9	419.9	421.9	429.7	439.6	451.4	461.3	467.2	467.2	469.2
27.5°	457.3	457.3	459.3	461.3	469.2	484.9	502.7	520.4	534.2	532.2	534.2
30°	508.6	508.6	512.5	514.5	524.4	542.1	565.8	589.4	609.1	609.1	613.1
32.5°	565.8	563.8	569.7	571.7	581.5	605.2	638.7	676.1	701.8	701.8	705.7
35°	634.8	632.8	638.7	638.7	650.5	684.0	727.4	778.7	822.0	824.0	829.9
37.5°	721.5	717.5	717.5	723.5	737.3	780.6	839.8	910.7	956.1	960.0	969.9
40°	824.0	822.0	826.0	824.0	841.7	895.0	969.9	1052.7	1105.9	1115.7	1127.6
42.5°	950.2	954.1	948.2	948.2	969.9	1031.0	1119.7	1216.3	1312.9	1324.7	1330.6
45°	1103.9	1111.8	1103.9	1101.9	1121.7	1192.6	1314.8	1484.4	1596.7	1636.2	1648.0
47.5°	1289.2	1293.2	1283.3	1279.4	1301.0	1391.7	1549.4	1738.7	1870.7	1900.3	1931.8
50°	1496.2	1490.3	1482.4	1476.5	1517.9	1630.2	1813.6	2008.7	2235.4	2239.4	2251.2
52.5°	1709.1	1691.4	1693.3	1691.4	1748.5	1870.7	2115.2	2446.4	2791.3	2862.3	2870.2
55°	1922.0	1900.3	1898.3	1918.0	1998.9	2174.3	2481.8	2911.6	3191.5	3234.9	3228.9
57.5°	2134.9	2125.0	2121.1	2138.8	2257.1	2466.1	2813.0	3175.7	3414.2	3410.3	3368.9
60°	2355.7	2363.6	2349.8	2383.3	2505.5	2714.4	2966.8	3319.6	3540.4	3522.7	3481.3
62.5°	2582.4	2602.1	2588.3	2592.2	2671.1	2824.8	3073.2	3483.2	3788.8	3814.4	3767.1
65°	2807.1	2820.9	2799.2	2738.1	2781.5	2925.4	3280.2	3674.5	3907.1	3930.7	3895.2
67.5°	2996.3	3010.1	2935.2	2838.6	2844.5	2949.0	3260.5	3637.0	3844.0	3828.2	3771.0
70°	3158.0	3132.4	3010.1	2844.5	2775.6	2824.8	3118.6	3451.7	3662.6	3654.7	3587.7
72.5°	3211.2	3177.7	2970.7	2714.4	2578.4	2596.2	2882.0	3179.7	3351.2	3365.0	3284.1
75°	3126.4	3069.3	2785.4	2464.1	2288.6	2300.5	2544.9	2818.9	2956.9	2941.1	2878.1
77.5°	2820.9	2763.7	2456.2	2113.2	1941.7	1959.4	2152.6	2367.5	2481.8	2475.9	2432.6
80°	2341.9	2290.6	2020.6	1701.2	1545.5	1555.3	1703.2	1872.7	1961.4	1981.1	1957.5
82.5°	1730.8	1695.3	1504.1	1245.8	1119.7	1117.7	1230.1	1360.2	1446.9	1488.3	1472.5
85°	1070.4	1052.7	946.2	778.7	689.9	688.0	755.0	851.6	930.4	985.6	950.2
87.5°	425.8	419.9	388.3	313.4	274.0	260.2	244.4	305.5	311.5	368.6	366.7
90°	104.5	102.5	100.5	94.6	84.8	72.9	59.1	43.4	27.6	21.7	11.8
92.5°	92.6	92.6	90.7	84.8	76.9	65.1	53.2	39.4	25.6	19.7	9.9
95°	74.9	74.9	72.9	69.0	61.1	53.2	41.4	31.5	19.7	15.8	7.9
97.5°	57.2	55.2	55.2	51.3	47.3	39.4	31.5	23.7	15.8	11.8	5.9
100°	41.4	41.4	39.4	37.5	33.5	29.6	23.7	17.7	9.9	7.9	3.9
102.5°	29.6	27.6	27.6	27.6	23.7	19.7	15.8	11.8	7.9	5.9	2.0
105°	19.7	17.7	17.7	17.7	15.8	13.8	9.9	7.9	3.9	3.9	2.0
107.5°	11.8	11.8	11.8	11.8	9.9	7.9	5.9	3.9	2.0	2.0	2.0
110°	5.9	5.9	5.9	7.9	5.9	5.9	3.9	2.0	2.0	2.0	2.0



REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
112.5°	3.9	3.9	3.9	3.9	3.9	3.9	2.0	2.0	2.0	2.0	2.0
115°	2.0	2.0	2.0	3.9	3.9	2.0	2.0	0.0	0.0	2.0	2.0
117.5°	0.0	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
120°	0.0	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
122.5°	0.0	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
125°	0.0	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
127.5°	0.0	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
130°	0.0	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
132.5°	0.0	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	2.0
135°	0.0	0.0	0.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	2.0	0.0	2.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9	214.9
2.5°	216.8	216.8	216.8	214.9	214.9	214.9	212.9	212.9	210.9	210.9	210.9
5°	224.7	224.7	222.8	222.8	220.8	218.8	218.8	216.8	216.8	214.9	214.9
7.5°	238.5	238.5	236.6	234.6	230.6	228.7	226.7	224.7	224.7	222.8	222.8
10°	256.3	256.3	252.3	248.4	244.4	240.5	238.5	234.6	232.6	232.6	232.6
12.5°	277.9	276.0	272.0	266.1	262.2	256.3	252.3	248.4	244.4	244.4	244.4
15°	303.6	303.6	295.7	289.8	281.9	274.0	268.1	262.2	258.2	256.3	256.3
17.5°	335.1	335.1	325.3	315.4	305.5	295.7	287.8	279.9	276.0	274.0	274.0
20°	370.6	370.6	360.7	348.9	335.1	321.3	309.5	299.6	293.7	291.7	291.7
22.5°	414.0	414.0	400.2	384.4	366.7	346.9	331.2	319.3	313.4	309.5	309.5
25°	463.2	459.3	445.5	425.8	400.2	376.5	354.8	343.0	335.1	329.2	331.2
27.5°	530.3	524.4	506.6	473.1	441.6	410.0	384.4	368.6	358.8	354.8	356.8
30°	607.2	601.2	575.6	538.2	490.8	449.5	417.9	400.2	390.3	384.4	386.4
32.5°	699.8	691.9	660.4	609.1	553.9	494.8	455.4	433.7	423.8	417.9	415.9
35°	822.0	812.2	772.7	701.8	624.9	553.9	498.7	471.1	461.3	455.4	457.3
37.5°	960.0	946.2	893.0	806.3	709.7	619.0	555.9	520.4	508.6	498.7	498.7
40°	1117.7	1101.9	1032.9	918.6	802.3	689.9	609.1	569.7	555.9	555.9	555.9
42.5°	1314.8	1299.1	1220.2	1052.7	898.9	766.8	670.2	624.9	611.1	615.0	615.0
45°	1620.4	1598.7	1472.5	1251.8	1025.1	845.7	733.3	682.1	672.2	682.1	682.1
47.5°	1900.3	1872.7	1687.4	1437.1	1149.3	924.5	796.4	737.3	733.3	755.0	755.0
50°	2213.7	2178.3	1983.1	1586.9	1249.8	1011.3	853.6	782.6	784.6	816.1	826.0
52.5°	2820.9	2783.4	2446.4	1858.9	1358.2	1042.8	877.2	792.5	792.5	827.9	841.7
55°	3181.6	3104.8	2665.2	2036.3	1403.5	1080.3	867.4	753.0	749.1	788.5	800.3
57.5°	3299.9	3221.1	2710.5	1985.1	1374.0	1032.9	810.2	646.6	638.7	689.9	686.0
60°	3396.5	3292.0	2637.6	1813.6	1206.4	932.4	699.8	481.0	447.5	492.8	490.8
62.5°	3668.5	3556.2	2641.5	1612.5	1009.3	778.7	526.3	270.1	201.1	236.6	220.8
65°	3804.6	3694.2	2682.9	1517.9	908.8	644.6	376.5	110.4	7.9	7.9	3.9
67.5°	3688.3	3589.7	2629.7	1494.2	895.0	640.7	382.4	108.4	0.0	0.0	0.0
70°	3518.7	3424.1	2507.5	1411.4	849.6	617.0	374.5	108.4	0.0	0.0	0.0
72.5°	3221.1	3124.5	2296.5	1293.2	780.6	565.8	346.9	102.5	0.0	0.0	0.0
75°	2828.8	2755.8	2028.4	1139.4	688.0	498.7	307.5	90.7	0.0	0.0	0.0
77.5°	2395.1	2308.4	1701.2	948.2	575.6	414.0	260.2	74.9	0.0	0.0	0.0
80°	1922.0	1858.9	1340.5	743.2	445.5	323.3	203.0	57.2	0.0	0.0	0.0
82.5°	1429.2	1375.9	991.6	532.2	317.4	224.7	140.0	37.5	0.0	0.0	0.0
85°	938.3	924.5	636.7	323.3	189.2	124.2	74.9	17.7	0.0	0.0	0.0
87.5°	339.1	350.9	232.6	92.6	51.3	21.7	9.9	2.0	0.0	0.0	0.0
90°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
92.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
95°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
97.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
100°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
102.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
105°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
107.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
110°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436902
 CATALOG NUMBER: TT-D6-740-U-RW-PM-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
115°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
117.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
120°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
122.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
125°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
127.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
130°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
132.5°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
135°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	2.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	2.0	2.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)