

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P543099

Luminaire Tested: **TT-D10-750-U-5CQ-PM**

Issue Date: 6/22/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P543099  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2012-100-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D10-750-U-5CQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
5000K, 70 CRI LEDS AND CONCENTRATED DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 21857.9 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G2

Input Watts (W): 193.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P543099

CATALOG NUMBER: TT-D10-750-U-5CQ-PM

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.8 fc  
 Type V - Short - N/A

REPORT NUMBER: P543099  
CATALOG NUMBER: TT-D10-750-U-5CQ-PM

## Luminous Intensity Polar Plot



REPORT NUMBER: P543099

CATALOG NUMBER: TT-D10-750-U-5CQ-PM


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 10929.0  | 0.0    | 10929.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 10929.0  | 0.0    | 10929.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 21857.9  | 0.0    | 21857.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 520.5   | 2.4       |
| 10°-20°   | 1507.6  | 6.9       |
| 20°-30°   | 2422.8  | 11.1      |
| 30°-40°   | 3262.0  | 14.9      |
| 40°-50°   | 4036.1  | 18.5      |
| 50°-60°   | 4329.7  | 19.8      |
| 60°-70°   | 3528.4  | 16.1      |
| 70°-80°   | 1882.2  | 8.6       |
| 80°-90°   | 368.6   | 1.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 21857.9 | 100.0     |
| 0°-180°   | 21857.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P543099


CATALOG NUMBER: TT-D10-750-U-5CQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 2225.5 | 10.2      |                         |      |         |
| FM   | (30°-60°)   | 5813.9 | 26.6      |                         |      |         |
| FH   | (60°-80°)   | 2705.3 | 12.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 184.3  | 0.8       |                         |      | G2/225  |
| BL   | (0°-30°)    | 2225.5 | 10.2      | B3/2500                 |      |         |
| BM   | (30°-60°)   | 5813.9 | 26.6      | B4/8500                 |      |         |
| BH   | (60°-80°)   | 2705.3 | 12.4      | B4/5000                 |      | G2/5000 |
| BVH  | (80°-90°)   | 184.3  | 0.8       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G2**

Type V Short



REPORT NUMBER: P543099

CATALOG NUMBER: TT-D10-750-U-5CQ-PM

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 | 5524.9 |
| 2.5°  | 5514.9 | 5514.9 | 5513.9 | 5511.9 | 5508.9 | 5506.9 | 5507.9 | 5510.9 | 5513.9 | 5514.9 | 5515.9 |
| 5°    | 5486.9 | 5488.9 | 5485.9 | 5481.9 | 5478.9 | 5477.9 | 5476.9 | 5480.9 | 5483.9 | 5484.9 | 5485.9 |
| 7.5°  | 5445.9 | 5448.9 | 5446.9 | 5442.9 | 5438.9 | 5436.9 | 5436.9 | 5438.9 | 5441.9 | 5444.9 | 5444.9 |
| 10°   | 5401.9 | 5401.9 | 5400.9 | 5396.9 | 5392.9 | 5389.9 | 5390.9 | 5392.9 | 5396.9 | 5399.9 | 5400.9 |
| 12.5° | 5362.9 | 5363.9 | 5360.9 | 5354.9 | 5348.9 | 5345.9 | 5345.9 | 5350.9 | 5356.9 | 5359.9 | 5361.9 |
| 15°   | 5332.9 | 5333.9 | 5330.9 | 5321.9 | 5314.9 | 5312.9 | 5314.9 | 5318.9 | 5324.9 | 5328.9 | 5329.9 |
| 17.5° | 5304.9 | 5305.9 | 5301.9 | 5291.9 | 5285.9 | 5282.9 | 5282.9 | 5288.9 | 5296.9 | 5299.9 | 5300.9 |
| 20°   | 5278.9 | 5277.9 | 5272.9 | 5261.9 | 5253.9 | 5249.9 | 5251.9 | 5259.9 | 5269.9 | 5274.9 | 5274.9 |
| 22.5° | 5259.9 | 5258.9 | 5251.9 | 5239.9 | 5230.9 | 5223.9 | 5227.9 | 5237.9 | 5249.9 | 5258.9 | 5258.9 |
| 25°   | 5255.9 | 5253.9 | 5242.9 | 5228.9 | 5213.9 | 5207.9 | 5213.9 | 5227.9 | 5242.9 | 5253.9 | 5255.9 |
| 27.5° | 5254.9 | 5251.9 | 5239.9 | 5220.9 | 5205.9 | 5200.9 | 5205.9 | 5222.9 | 5241.9 | 5254.9 | 5255.9 |
| 30°   | 5249.9 | 5247.9 | 5231.9 | 5210.9 | 5192.9 | 5186.9 | 5193.9 | 5212.9 | 5233.9 | 5245.9 | 5248.9 |
| 32.5° | 5237.9 | 5234.9 | 5218.9 | 5194.9 | 5174.9 | 5166.9 | 5173.9 | 5195.9 | 5216.9 | 5233.9 | 5235.9 |
| 35°   | 5231.9 | 5229.9 | 5209.9 | 5179.9 | 5156.9 | 5144.9 | 5154.9 | 5177.9 | 5202.9 | 5222.9 | 5225.9 |
| 37.5° | 5236.9 | 5233.9 | 5211.9 | 5176.9 | 5145.9 | 5132.9 | 5141.9 | 5168.9 | 5199.9 | 5222.9 | 5226.9 |
| 40°   | 5255.9 | 5251.9 | 5224.9 | 5182.9 | 5142.9 | 5127.9 | 5138.9 | 5172.9 | 5212.9 | 5238.9 | 5245.9 |
| 42.5° | 5288.9 | 5284.9 | 5248.9 | 5195.9 | 5145.9 | 5127.9 | 5145.9 | 5190.9 | 5242.9 | 5276.9 | 5281.9 |
| 45°   | 5316.9 | 5312.9 | 5271.9 | 5206.9 | 5149.9 | 5128.9 | 5153.9 | 5214.9 | 5283.9 | 5328.9 | 5334.9 |
| 47.5° | 5318.9 | 5312.9 | 5263.9 | 5190.9 | 5126.9 | 5107.9 | 5144.9 | 5220.9 | 5307.9 | 5365.9 | 5372.9 |
| 50°   | 5266.9 | 5260.9 | 5202.9 | 5121.9 | 5053.9 | 5035.9 | 5091.9 | 5185.9 | 5287.9 | 5353.9 | 5362.9 |
| 52.5° | 5150.9 | 5144.9 | 5083.9 | 4992.9 | 4920.9 | 4906.9 | 4975.9 | 5082.9 | 5193.9 | 5267.9 | 5277.9 |
| 55°   | 4972.9 | 4963.9 | 4903.9 | 4804.9 | 4723.9 | 4716.9 | 4788.9 | 4902.9 | 5022.9 | 5094.9 | 5111.9 |
| 57.5° | 4734.9 | 4724.9 | 4660.9 | 4554.9 | 4474.9 | 4465.9 | 4538.9 | 4655.9 | 4782.9 | 4851.9 | 4869.9 |
| 60°   | 4435.9 | 4434.9 | 4362.9 | 4255.9 | 4179.9 | 4166.9 | 4231.9 | 4351.9 | 4474.9 | 4547.9 | 4564.9 |
| 62.5° | 4090.0 | 4090.0 | 4018.0 | 3922.0 | 3836.0 | 3823.0 | 3884.0 | 4002.0 | 4116.0 | 4187.9 | 4209.9 |
| 65°   | 3696.0 | 3688.0 | 3633.0 | 3533.0 | 3447.0 | 3437.0 | 3497.0 | 3591.0 | 3708.0 | 3776.0 | 3797.0 |
| 67.5° | 3257.0 | 3248.0 | 3209.0 | 3114.0 | 3040.0 | 3019.0 | 3070.0 | 3166.0 | 3268.0 | 3334.0 | 3348.0 |
| 70°   | 2789.0 | 2785.0 | 2745.0 | 2660.0 | 2591.0 | 2575.0 | 2622.0 | 2704.0 | 2790.0 | 2844.0 | 2867.0 |
| 72.5° | 2308.0 | 2310.0 | 2268.0 | 2198.0 | 2150.0 | 2134.0 | 2165.0 | 2222.0 | 2318.0 | 2353.0 | 2372.0 |
| 75°   | 1833.0 | 1831.0 | 1805.0 | 1745.0 | 1700.0 | 1680.0 | 1712.0 | 1768.0 | 1813.0 | 1858.0 | 1880.0 |
| 77.5° | 1377.0 | 1374.0 | 1360.0 | 1310.0 | 1280.0 | 1265.0 | 1282.0 | 1321.0 | 1359.0 | 1398.0 | 1404.0 |
| 80°   | 956.0  | 957.0  | 941.0  | 910.0  | 878.0  | 876.0  | 890.0  | 910.0  | 941.0  | 967.0  | 971.0  |
| 82.5° | 584.0  | 586.0  | 573.0  | 561.0  | 534.0  | 534.0  | 544.0  | 562.0  | 578.0  | 599.0  | 593.0  |
| 85°   | 278.0  | 278.0  | 275.0  | 265.0  | 256.0  | 253.0  | 258.0  | 265.0  | 272.0  | 282.0  | 283.0  |
| 87.5° | 68.0   | 69.0   | 70.0   | 66.0   | 61.0   | 59.0   | 62.0   | 65.0   | 69.0   | 75.0   | 72.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2006-844-1

Luminaire Tested: TT-D4-750-U-WQ

Data valid for TT-D\* and TTN families of products

Test Date: 11/06/2020

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2006-844-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 11/06/2020  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: MCGRAW-EDISON  
 Catalog Number: **TT-D4-750-U-WQ**  
 Description: MCGRAW EDISON

### DISTRIBUTION

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 4778   | CRI (Ra): | 71.0 |      |       |
| CIE u':                   | 0.2092 | R1:       | 67.7 | R9:  | -28.7 |
| CIE v':                   | 0.4955 | R2:       | 75.2 | R10: | 41.2  |
| Duv:                      | 0.0068 | R3:       | 80.8 | R11: | 67.2  |
| CIE x:                    | 0.3535 | R4:       | 71.5 | R12: | 35.9  |
| CIE y:                    | 0.3721 | R5:       | 67.8 | R13: | 68.5  |
| CIE z:                    | 0.2744 | R6:       | 65.6 | R14: | 89.2  |
| Peak Wavelength (nm):     | 449    | R7:       | 82.2 |      |       |
| Dominant Wavelength (nm): | 570    | R8:       | 57.2 |      |       |
| Purity:                   | 17.8   |           |      |      |       |
| Rf:                       | 73.3   |           |      |      |       |
| Rg:                       | 94.5   |           |      |      |       |



### Test Conditions

Stabilization Time: 62M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.6/45%  
 Sphere Temperature (°C): 24.7

REPORT NUMBER: SP1-2006-844-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/3/2019        | 12/3/2020            |
| AC Power Source                | IN0063                | 12/3/2019        | 12/3/2020            |
| DC Power Source                | IN0208                | 12/3/2019        | 12/3/2020            |
| Sphere Thermometer             | IN0085                | 12/3/2019        | 12/3/2020            |
| Room Thermometer               | IN0046                | 12/3/2019        | 12/3/2020            |

REPORT NUMBER: SP1-2006-844-1

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2006-844-1

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2529             | 0.0              | 490       | 21819            | 3.1              | 620       | 83437            | 21.7             | 750       | 4608             | 0.0              | 880       | 3335             | 0.0              |
| 365       | 2361             | 0.0              | 495       | 29270            | 5.3              | 625       | 77569            | 17.1             | 755       | 4412             | 0.0              | 885       | 2653             | 0.0              |
| 370       | 2648             | 0.0              | 500       | 40589            | 9.0              | 630       | 71183            | 12.9             | 760       | 4227             | 0.0              | 890       | 2411             | 0.0              |
| 375       | 2655             | 0.0              | 505       | 54498            | 15.2             | 635       | 65734            | 9.9              | 765       | 3922             | 0.0              | 895       | 2118             | 0.0              |
| 380       | 2428             | 0.0              | 510       | 68399            | 23.5             | 640       | 60418            | 7.2              | 770       | 3461             | 0.0              | 900       | 2873             | 0.0              |
| 385       | 2334             | 0.0              | 515       | 81428            | 33.7             | 645       | 54736            | 5.3              | 775       | 3226             | 0.0              | 905       | 3367             | 0.0              |
| 390       | 2269             | 0.0              | 520       | 92826            | 45.0             | 650       | 49620            | 3.6              | 780       | 2883             | 0.0              | 910       | 2749             | 0.0              |
| 395       | 2020             | 0.0              | 525       | 101684           | 54.6             | 655       | 44517            | 2.6              | 785       | 2864             | 0.0              | 915       | 2283             | 0.0              |
| 400       | 1873             | 0.0              | 530       | 108580           | 63.9             | 660       | 39493            | 1.6              | 790       | 2715             | 0.0              | 920       | 2425             | 0.0              |
| 405       | 2015             | 0.0              | 535       | 113290           | 70.3             | 665       | 35066            | 1.1              | 795       | 2547             | 0.0              | 925       | 2705             | 0.0              |
| 410       | 2831             | 0.0              | 540       | 116042           | 75.6             | 670       | 30825            | 0.7              | 800       | 2585             | 0.0              | 930       | 3144             | 0.0              |
| 415       | 5121             | 0.0              | 545       | 118948           | 79.2             | 675       | 27031            | 0.5              | 805       | 2308             | 0.0              | 935       | 2539             | 0.0              |
| 420       | 10348            | 0.0              | 550       | 119916           | 81.5             | 680       | 23555            | 0.3              | 810       | 2796             | 0.0              | 940       | 2288             | 0.0              |
| 425       | 21288            | 0.1              | 555       | 120734           | 82.5             | 685       | 20841            | 0.2              | 815       | 2196             | 0.0              | 945       | 1604             | 0.0              |
| 430       | 41173            | 0.3              | 560       | 121523           | 82.6             | 690       | 18232            | 0.1              | 820       | 2415             | 0.0              | 950       | 3031             | 0.0              |
| 435       | 73003            | 0.9              | 565       | 121859           | 81.0             | 695       | 16035            | 0.1              | 825       | 2281             | 0.0              | 955       | 3356             | 0.0              |
| 440       | 111013           | 1.7              | 570       | 122246           | 79.5             | 700       | 14010            | 0.0              | 830       | 2524             | 0.0              | 960       | 3704             | 0.0              |
| 445       | 154787           | 3.2              | 575       | 121449           | 75.6             | 705       | 12408            | 0.0              | 835       | 2461             | 0.0              | 965       | 2847             | 0.0              |
| 450       | 176733           | 4.6              | 580       | 120111           | 71.4             | 710       | 11063            | 0.0              | 840       | 2195             | 0.0              | 970       | 2985             | 0.0              |
| 455       | 124334           | 4.2              | 585       | 117354           | 65.2             | 715       | 10136            | 0.0              | 845       | 2487             | 0.0              | 975       | 3963             | 0.0              |
| 460       | 72664            | 3.0              | 590       | 114565           | 59.2             | 720       | 8693             | 0.0              | 850       | 3144             | 0.0              | 980       | 3221             | 0.0              |
| 465       | 49806            | 2.6              | 595       | 111127           | 52.7             | 725       | 7522             | 0.0              | 855       | 2809             | 0.0              | 985       | 3794             | 0.0              |
| 470       | 32995            | 2.1              | 600       | 107253           | 46.2             | 730       | 6612             | 0.0              | 860       | 2621             | 0.0              | 990       | 3296             | 0.0              |
| 475       | 22184            | 1.7              | 605       | 101156           | 39.2             | 735       | 5947             | 0.0              | 865       | 2410             | 0.0              | 995       | 1779             | 0.0              |
| 480       | 18691            | 1.8              | 610       | 95370            | 32.8             | 740       | 5253             | 0.0              | 870       | 3143             | 0.0              | 1000      | 2977             | 0.0              |
| 485       | 18593            | 2.2              | 615       | 89556            | 27.0             | 745       | 5032             | 0.0              | 875       | 3421             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2006-844-1

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 4867.6

S/P: 0.66

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2529             | 0.0              | 490       | 21819            | 33.6             | 620       | 83437            | 1.0              | 750       | 4608             | 0.0              | 880       | 3335             | 0.0              |
| 365       | 2361             | 0.0              | 495       | 29270            | 47.3             | 625       | 77569            | 0.7              | 755       | 4412             | 0.0              | 885       | 2653             | 0.0              |
| 370       | 2648             | 0.0              | 500       | 40589            | 67.9             | 630       | 71183            | 0.4              | 760       | 4227             | 0.0              | 890       | 2411             | 0.0              |
| 375       | 2655             | 0.0              | 505       | 54498            | 92.6             | 635       | 65734            | 0.2              | 765       | 3922             | 0.0              | 895       | 2118             | 0.0              |
| 380       | 2428             | 0.0              | 510       | 68399            | 115.9            | 640       | 60418            | 0.2              | 770       | 3461             | 0.0              | 900       | 2873             | 0.0              |
| 385       | 2334             | 0.0              | 515       | 81428            | 135.0            | 645       | 54736            | 0.1              | 775       | 3226             | 0.0              | 905       | 3367             | 0.0              |
| 390       | 2269             | 0.0              | 520       | 92826            | 147.5            | 650       | 49620            | 0.1              | 780       | 2883             | 0.0              | 910       | 2749             | 0.0              |
| 395       | 2020             | 0.0              | 525       | 101684           | 152.1            | 655       | 44517            | 0.0              | 785       | 2864             | 0.0              | 915       | 2283             | 0.0              |
| 400       | 1873             | 0.0              | 530       | 108580           | 149.7            | 660       | 39493            | 0.0              | 790       | 2715             | 0.0              | 920       | 2425             | 0.0              |
| 405       | 2015             | 0.1              | 535       | 113290           | 141.2            | 665       | 35066            | 0.0              | 795       | 2547             | 0.0              | 925       | 2705             | 0.0              |
| 410       | 2831             | 0.2              | 540       | 116042           | 128.2            | 670       | 30825            | 0.0              | 800       | 2585             | 0.0              | 930       | 3144             | 0.0              |
| 415       | 5121             | 0.5              | 545       | 118948           | 114.0            | 675       | 27031            | 0.0              | 805       | 2308             | 0.0              | 935       | 2539             | 0.0              |
| 420       | 10348            | 1.7              | 550       | 119916           | 98.1             | 680       | 23555            | 0.0              | 810       | 2796             | 0.0              | 940       | 2288             | 0.0              |
| 425       | 21288            | 5.2              | 555       | 120734           | 82.5             | 685       | 20841            | 0.0              | 815       | 2196             | 0.0              | 945       | 1604             | 0.0              |
| 430       | 41173            | 14.0             | 560       | 121523           | 67.9             | 690       | 18232            | 0.0              | 820       | 2415             | 0.0              | 950       | 3031             | 0.0              |
| 435       | 73003            | 32.6             | 565       | 121859           | 54.7             | 695       | 16035            | 0.0              | 825       | 2281             | 0.0              | 955       | 3356             | 0.0              |
| 440       | 111013           | 62.0             | 570       | 122246           | 43.1             | 700       | 14010            | 0.0              | 830       | 2524             | 0.0              | 960       | 3704             | 0.0              |
| 445       | 154787           | 103.6            | 575       | 121449           | 33.1             | 705       | 12408            | 0.0              | 835       | 2461             | 0.0              | 965       | 2847             | 0.0              |
| 450       | 176733           | 137.0            | 580       | 120111           | 24.7             | 710       | 11063            | 0.0              | 840       | 2195             | 0.0              | 970       | 2985             | 0.0              |
| 455       | 124334           | 108.6            | 585       | 117354           | 17.9             | 715       | 10136            | 0.0              | 845       | 2487             | 0.0              | 975       | 3963             | 0.0              |
| 460       | 72664            | 70.2             | 590       | 114565           | 12.8             | 720       | 8693             | 0.0              | 850       | 3144             | 0.0              | 980       | 3221             | 0.0              |
| 465       | 49806            | 52.6             | 595       | 111127           | 8.9              | 725       | 7522             | 0.0              | 855       | 2809             | 0.0              | 985       | 3794             | 0.0              |
| 470       | 32995            | 38.0             | 600       | 107253           | 6.0              | 730       | 6612             | 0.0              | 860       | 2621             | 0.0              | 990       | 3296             | 0.0              |
| 475       | 22184            | 27.7             | 605       | 101156           | 4.0              | 735       | 5947             | 0.0              | 865       | 2410             | 0.0              | 995       | 1779             | 0.0              |
| 480       | 18691            | 25.2             | 610       | 95370            | 2.6              | 740       | 5253             | 0.0              | 870       | 3143             | 0.0              | 1000      | 2977             | 0.0              |
| 485       | 18593            | 27.0             | 615       | 89556            | 1.7              | 745       | 5032             | 0.0              | 875       | 3421             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2006-844-1

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 12457.9**    **S/P: 1.7**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2529             | 0.0              | 490       | 21819            | 18.2             | 620       | 83437            | 0.1              | 750       | 4608             | 0.0              | 880       | 3335             | 0.0              |
| 365       | 2361             | 0.0              | 495       | 29270            | 24.2             | 625       | 77569            | 0.0              | 755       | 4412             | 0.0              | 885       | 2653             | 0.0              |
| 370       | 2648             | 0.0              | 500       | 40589            | 32.6             | 630       | 71183            | 0.0              | 760       | 4227             | 0.0              | 890       | 2411             | 0.0              |
| 375       | 2655             | 0.0              | 505       | 54498            | 41.8             | 635       | 65734            | 0.0              | 765       | 3922             | 0.0              | 895       | 2118             | 0.0              |
| 380       | 2428             | 0.0              | 510       | 68399            | 49.1             | 640       | 60418            | 0.0              | 770       | 3461             | 0.0              | 900       | 2873             | 0.0              |
| 385       | 2334             | 0.0              | 515       | 81428            | 53.2             | 645       | 54736            | 0.0              | 775       | 3226             | 0.0              | 905       | 3367             | 0.0              |
| 390       | 2269             | 0.0              | 520       | 92826            | 54.0             | 650       | 49620            | 0.0              | 780       | 2883             | 0.0              | 910       | 2749             | 0.0              |
| 395       | 2020             | 0.0              | 525       | 101684           | 51.6             | 655       | 44517            | 0.0              | 785       | 2864             | 0.0              | 915       | 2283             | 0.0              |
| 400       | 1873             | 0.0              | 530       | 108580           | 46.9             | 660       | 39493            | 0.0              | 790       | 2715             | 0.0              | 920       | 2425             | 0.0              |
| 405       | 2015             | 0.0              | 535       | 113290           | 40.8             | 665       | 35066            | 0.0              | 795       | 2547             | 0.0              | 925       | 2705             | 0.0              |
| 410       | 2831             | 0.1              | 540       | 116042           | 34.0             | 670       | 30825            | 0.0              | 800       | 2585             | 0.0              | 930       | 3144             | 0.0              |
| 415       | 5121             | 0.3              | 545       | 118948           | 27.6             | 675       | 27031            | 0.0              | 805       | 2308             | 0.0              | 935       | 2539             | 0.0              |
| 420       | 10348            | 1.2              | 550       | 119916           | 21.5             | 680       | 23555            | 0.0              | 810       | 2796             | 0.0              | 940       | 2288             | 0.0              |
| 425       | 21288            | 3.3              | 555       | 120734           | 16.3             | 685       | 20841            | 0.0              | 815       | 2196             | 0.0              | 945       | 1604             | 0.0              |
| 430       | 41173            | 8.7              | 560       | 121523           | 12.0             | 690       | 18232            | 0.0              | 820       | 2415             | 0.0              | 950       | 3031             | 0.0              |
| 435       | 73003            | 19.5             | 565       | 121859           | 8.6              | 695       | 16035            | 0.0              | 825       | 2281             | 0.0              | 955       | 3356             | 0.0              |
| 440       | 111013           | 37.1             | 570       | 122246           | 6.0              | 700       | 14010            | 0.0              | 830       | 2524             | 0.0              | 960       | 3704             | 0.0              |
| 445       | 154787           | 61.1             | 575       | 121449           | 4.0              | 705       | 12408            | 0.0              | 835       | 2461             | 0.0              | 965       | 2847             | 0.0              |
| 450       | 176733           | 81.4             | 580       | 120111           | 2.7              | 710       | 11063            | 0.0              | 840       | 2195             | 0.0              | 970       | 2985             | 0.0              |
| 455       | 124334           | 65.1             | 585       | 117354           | 1.7              | 715       | 10136            | 0.0              | 845       | 2487             | 0.0              | 975       | 3963             | 0.0              |
| 460       | 72664            | 42.8             | 590       | 114565           | 1.1              | 720       | 8693             | 0.0              | 850       | 3144             | 0.0              | 980       | 3221             | 0.0              |
| 465       | 49806            | 32.5             | 595       | 111127           | 0.7              | 725       | 7522             | 0.0              | 855       | 2809             | 0.0              | 985       | 3794             | 0.0              |
| 470       | 32995            | 23.6             | 600       | 107253           | 0.5              | 730       | 6612             | 0.0              | 860       | 2621             | 0.0              | 990       | 3296             | 0.0              |
| 475       | 22184            | 16.9             | 605       | 101156           | 0.3              | 735       | 5947             | 0.0              | 865       | 2410             | 0.0              | 995       | 1779             | 0.0              |
| 480       | 18691            | 15.0             | 610       | 95370            | 0.2              | 740       | 5253             | 0.0              | 870       | 3143             | 0.0              | 1000      | 2977             | 0.0              |
| 485       | 18593            | 15.3             | 615       | 89556            | 0.1              | 745       | 5032             | 0.0              | 875       | 3421             | 0.0              |           |                  |                  |

### Summary

$R_f = 73.3$   
 $R_g = 94.5$   
 CIE  $R_a = 71.0$   
 $R_g = -28.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 60 | CES51 = 89 | CES76 = 47 |
| CES02 = 59 | CES27 = 86 | CES52 = 88 | CES77 = 65 |
| CES03 = 30 | CES28 = 79 | CES53 = 76 | CES78 = 50 |
| CES04 = 69 | CES29 = 62 | CES54 = 83 | CES79 = 78 |
| CES05 = 46 | CES30 = 79 | CES55 = 82 | CES80 = 74 |
| CES06 = 50 | CES31 = 66 | CES56 = 71 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 70 | CES82 = 89 |
| CES08 = 38 | CES33 = 75 | CES58 = 71 | CES83 = 87 |
| CES09 = 29 | CES34 = 67 | CES59 = 86 | CES84 = 86 |
| CES10 = 72 | CES35 = 81 | CES60 = 90 | CES85 = 79 |
| CES11 = 56 | CES36 = 94 | CES61 = 84 | CES86 = 77 |
| CES12 = 61 | CES37 = 75 | CES62 = 84 | CES87 = 76 |
| CES13 = 41 | CES38 = 88 | CES63 = 72 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 66 | CES89 = 73 |
| CES15 = 70 | CES40 = 89 | CES65 = 61 | CES90 = 78 |
| CES16 = 46 | CES41 = 92 | CES66 = 58 | CES91 = 77 |
| CES17 = 49 | CES42 = 75 | CES67 = 55 | CES92 = 63 |
| CES18 = 55 | CES43 = 75 | CES68 = 65 | CES93 = 78 |
| CES19 = 71 | CES44 = 99 | CES69 = 74 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 55 | CES95 = 67 |
| CES21 = 85 | CES46 = 82 | CES71 = 48 | CES96 = 77 |
| CES22 = 77 | CES47 = 84 | CES72 = 83 | CES97 = 84 |
| CES23 = 91 | CES48 = 76 | CES73 = 45 | CES98 = 73 |
| CES24 = 90 | CES49 = 80 | CES74 = 92 | CES99 = 63 |
| CES25 = 71 | CES50 = 88 | CES75 = 48 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)