

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198094

Luminaire Tested: **TT-C3-LED-E1-RW-PM-SG-LWR-LW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198094  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34701)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-RW-PM-SG-LWR-LW  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION WITH SOFTENING GLASS LENS AND LumaWatt WIRELESS SENSOR  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4327 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type III - Short - Full Cutoff  
BUG Rating: B2 - U0 - G2

Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P198094

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.1 fc  
 Type III - Short - Full Cutoff

REPORT NUMBER: P198094

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW

### Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P198094

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2163.5	0.0	2163.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2163.5	0.0	2163.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4327.0	0.0	4327.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.5	0.6
10°-20°	88.3	2.0
20°-30°	193.0	4.5
30°-40°	388.0	9.0
40°-50°	733.3	16.9
50°-60°	1081.7	25.0
60°-70°	1065.4	24.6
70°-80°	620.4	14.3
80°-90°	131.3	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4327.0	100.0
0°-180°	4327.0	100.0



REPORT NUMBER: P198094


CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	153.4	3.5			
FM	(30°-60°)	1101.5	25.5			
FH	(60°-80°)	842.9	19.5			G1/1800
FVH	(80°-90°)	65.7	1.5			G1/100
BL	(0°-30°)	153.4	3.5	B1/500		
BM	(30°-60°)	1101.5	25.5	B2/2500		
BH	(60°-80°)	842.9	19.5	B2/1000		G2/1000
BVH	(80°-90°)	65.7	1.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P198094

CATALOG NUMBER: TT-C3-LED-E1-RW-PM-SG-LWR-LW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	257	257	257	257	257	257	257	257	257	257	257
2.5°	259	259	259	259	258	259	258	258	258	258	258
5°	262	263	262	262	262	262	262	262	261	261	262
7.5°	269	269	269	269	268	269	268	268	268	268	268
10°	279	279	279	279	278	278	278	277	277	277	277
12.5°	291	292	292	291	290	290	289	289	289	289	288
15°	309	308	308	306	306	304	305	304	303	302	303
17.5°	327	328	328	326	325	324	322	322	321	322	322
20°	355	355	353	351	348	347	345	345	343	345	345
22.5°	383	383	381	380	376	373	372	371	370	372	370
25°	418	418	416	412	408	407	404	404	405	406	402
27.5°	454	455	453	450	446	442	442	443	444	448	447
30°	498	497	494	490	488	485	486	490	494	498	498
32.5°	543	542	541	537	536	535	540	548	556	559	564
35°	591	591	590	587	589	594	602	617	629	643	643
37.5°	644	642	643	643	648	657	676	705	730	744	744
40°	699	696	697	702	711	733	766	806	846	864	870
42.5°	752	749	753	758	780	814	863	924	981	1009	1008
45°	801	803	808	820	852	902	972	1054	1128	1161	1173
47.5°	850	851	858	879	924	987	1072	1181	1263	1302	1317
50°	896	898	910	940	993	1069	1174	1290	1380	1426	1439
52.5°	937	939	953	990	1053	1141	1251	1370	1465	1518	1526
55°	971	973	987	1026	1094	1185	1297	1415	1504	1551	1557
57.5°	991	992	1007	1047	1114	1199	1307	1421	1499	1541	1546
60°	992	994	1008	1044	1106	1184	1287	1389	1460	1498	1504
62.5°	974	975	987	1015	1068	1136	1231	1323	1387	1424	1431
65°	933	933	939	960	1001	1059	1140	1225	1284	1318	1322
67.5°	865	865	866	880	908	954	1023	1094	1147	1181	1186
70°	778	777	769	778	796	835	896	950	993	1020	1038
72.5°	668	664	658	656	674	708	758	795	819	848	850
75°	540	538	530	530	548	575	615	640	652	671	675
77.5°	403	402	405	406	416	445	468	486	483	495	499
80°	282	284	284	283	293	304	329	334	330	334	334
82.5°	179	178	176	179	187	196	206	207	210	207	209
85°	90	89	91	92	96	101	110	112	107	107	105
87.5°	31	33	31	32	32	37	36	36	36	36	38
90°	0	0	0	0	0	0	0	0	0	0	0

(END OF REPORT)