

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436812

Luminaire Tested: **TT-D3-750-U-5WQ-PM-HSS**

Issue Date: 12/2/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P436812  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D3-750-U-5WQ-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
5000K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5122 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U2 - G2


Input Watts (W): 47.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P436812  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P436812  
CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436812  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1804.1	1.2	1805.3
	% Fixture	35.2	0.0	35.2
<b>Street Side</b>	Lumens	3296.0	20.7	3316.7
	% Fixture	64.3	0.4	64.8
<b>Total</b>	Lumens	5100.1	21.9	5122.0
	% Fixture	99.6	0.4	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.3	0.7
10°-20°	121.7	2.4
20°-30°	260.7	5.1
30°-40°	472.2	9.2
40°-50°	787.8	15.4
50°-60°	1091.2	21.3
60°-70°	1130.9	22.1
70°-80°	910.1	17.8
80°-90°	291.1	5.7
90°-100°	14.7	0.3
100°-110°	4.7	0.1
110°-120°	0.9	0.0
120°-130°	0.6	0.0
130°-140°	0.4	0.0
140°-150°	0.3	0.0
150°-160°	0.2	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	5100.1	99.6
0°-180°	5122.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P436812


CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	213.0	4.2			
FM (30°-60°)	1361.7	26.6			
FH (60°-80°)	1499.8	29.3			G1/1800
FVH (80°-90°)	221.5	4.3			G2/225
BL (0°-30°)	203.7	4.0	B1/500		
BM (30°-60°)	989.6	19.3	B1/1000		
BH (60°-80°)	541.2	10.6	B2/1000		G2/1000
BVH (80°-90°)	69.6	1.4			G1/100
UL (90°-100°)	14.7	0.3		U2/50	
UH (100°-180°)	7.2	0.1		U1/10	

**BUG Rating: B2-U2-G2**

Type IV Short





REPORT NUMBER: P436812  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0
2.5°	348.0	347.0	347.0	346.0	346.0	346.0	346.0	346.0	345.0	344.0	343.0
5°	357.0	357.0	356.0	356.0	355.0	354.0	355.0	354.0	353.0	352.0	351.0
7.5°	369.0	368.0	368.0	366.0	366.0	365.0	365.0	365.0	364.0	362.0	361.0
10°	386.0	384.0	384.0	382.0	381.0	380.0	380.0	378.0	378.0	377.0	376.0
12.5°	405.0	403.0	405.0	404.0	402.0	400.0	400.0	398.0	397.0	396.0	392.0
15°	430.0	427.0	429.0	429.0	428.0	427.0	427.0	423.0	421.0	419.0	415.0
17.5°	460.0	458.0	459.0	460.0	463.0	463.0	464.0	459.0	455.0	448.0	445.0
20°	498.0	497.0	500.0	500.0	503.0	503.0	504.0	499.0	492.0	487.0	481.0
22.5°	535.0	535.0	539.0	539.0	542.0	540.0	540.0	538.0	530.0	524.0	518.0
25°	573.0	572.0	576.0	579.0	583.0	578.0	580.0	577.0	569.0	561.0	553.0
27.5°	615.0	613.0	615.0	619.0	626.0	622.0	624.0	619.0	611.0	600.0	593.0
30°	661.0	658.0	661.0	667.0	672.0	674.0	673.0	666.0	659.0	643.0	638.0
32.5°	706.0	706.0	713.0	724.0	730.0	729.0	730.0	724.0	714.0	694.0	682.0
35°	761.0	765.0	774.0	790.0	803.0	798.0	798.0	796.0	779.0	755.0	739.0
37.5°	834.0	838.0	856.0	875.0	899.0	897.0	898.0	892.0	859.0	834.0	811.0
40°	919.0	923.0	950.0	977.0	999.9	1006.9	1007.9	994.9	959.0	923.0	887.0
42.5°	996.9	1001.9	1029.9	1067.9	1092.9	1103.9	1105.9	1084.9	1046.9	1005.9	961.0
45°	1074.9	1080.9	1112.9	1152.9	1188.9	1193.9	1194.9	1176.9	1134.9	1087.9	1029.9
47.5°	1154.9	1159.9	1192.9	1240.9	1279.9	1289.9	1290.9	1273.9	1222.9	1165.9	1097.9
50°	1227.9	1237.9	1282.9	1333.9	1385.9	1393.9	1394.9	1375.9	1315.9	1251.9	1161.9
52.5°	1313.9	1318.9	1366.9	1451.9	1495.9	1526.9	1527.9	1490.9	1426.9	1340.9	1224.9
55°	1413.9	1422.9	1471.9	1556.9	1635.9	1656.9	1662.9	1618.9	1533.9	1440.9	1304.9
57.5°	1471.9	1488.9	1560.9	1641.9	1740.9	1754.9	1757.9	1711.9	1617.9	1515.9	1364.9
60°	1502.9	1512.9	1588.9	1714.9	1791.9	1804.9	1803.9	1768.9	1674.9	1550.9	1392.9
62.5°	1537.9	1554.9	1618.9	1746.9	1813.9	1845.9	1840.9	1804.9	1708.9	1572.9	1419.9
65°	1527.9	1541.9	1635.9	1739.9	1850.9	1885.9	1878.9	1830.9	1713.9	1576.9	1412.9
67.5°	1487.9	1498.9	1591.9	1720.9	1826.9	1851.9	1863.9	1816.9	1685.9	1533.9	1368.9
70°	1405.9	1422.9	1512.9	1644.9	1741.9	1759.9	1761.9	1732.9	1614.9	1454.9	1295.9
72.5°	1292.9	1306.9	1404.9	1538.9	1622.9	1643.9	1645.9	1601.9	1512.9	1346.9	1190.9
75°	1157.9	1170.9	1246.9	1386.9	1469.9	1490.9	1488.9	1447.9	1353.9	1196.9	1051.9
77.5°	990.9	1014.9	1081.9	1196.9	1277.9	1288.9	1290.9	1245.9	1169.9	1033.9	893.0
80°	782.0	805.0	881.0	967.0	1034.9	1043.9	1046.9	1008.9	940.0	820.0	700.0
82.5°	556.0	576.0	636.0	706.0	763.0	763.0	765.0	734.0	681.0	578.0	484.0
85°	317.0	332.0	372.0	422.0	463.0	458.0	459.0	431.0	396.0	316.0	256.0
87.5°	104.0	111.0	120.0	139.0	158.0	146.0	152.0	126.0	114.0	85.0	66.0
90°	55.0	55.0	53.0	51.0	47.0	41.0	41.0	33.0	25.0	16.0	6.0
92.5°	50.0	50.0	48.0	46.0	42.0	37.0	37.0	30.0	22.0	14.0	5.0
95°	41.0	41.0	40.0	38.0	35.0	31.0	30.0	25.0	19.0	11.0	4.0
97.5°	32.0	32.0	31.0	30.0	27.0	24.0	24.0	19.0	14.0	9.0	3.0
100°	24.0	24.0	24.0	22.0	21.0	18.0	18.0	15.0	11.0	7.0	2.0
102.5°	17.0	18.0	17.0	16.0	15.0	13.0	13.0	11.0	8.0	5.0	2.0
105°	12.0	12.0	11.0	11.0	10.0	9.0	9.0	7.0	5.0	3.0	1.0
107.5°	7.0	7.0	7.0	7.0	6.0	6.0	6.0	5.0	3.0	2.0	1.0
110°	4.0	4.0	4.0	4.0	3.0	3.0	3.0	2.0	2.0	1.0	1.0



REPORT NUMBER: P436812  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
112.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
115°	1.0	1.0	1.0	2.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
117.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
120°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
122.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
125°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
127.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
130°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
132.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
135°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
140°	1.0	1.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
142.5°	1.0	1.0	1.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0
145°	1.0	1.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
147.5°	1.0	1.0	1.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.0
150°	1.0	1.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
160°	1.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
162.5°	1.0	1.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
165°	1.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
167.5°	1.0	1.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
170°	1.0	0.0	0.0	0.0	0.0	1.0	0.0	1.0	1.0	1.0	1.0
172.5°	1.0	1.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
175°	1.0	1.0	1.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0
177.5°	0.0	1.0	0.0	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P436812

CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0
2.5°	343.0	343.0	342.0	341.0	341.0	341.0	340.0	340.0	340.0	339.0	339.0
5°	351.0	350.0	350.0	349.0	349.0	348.0	348.0	347.0	346.0	346.0	345.0
7.5°	362.0	361.0	359.0	360.0	358.0	357.0	356.0	356.0	356.0	355.0	355.0
10°	375.0	375.0	373.0	373.0	371.0	370.0	369.0	369.0	370.0	370.0	369.0
12.5°	392.0	391.0	391.0	390.0	389.0	388.0	389.0	389.0	388.0	387.0	386.0
15°	413.0	413.0	413.0	414.0	413.0	413.0	413.0	412.0	410.0	408.0	408.0
17.5°	445.0	444.0	442.0	443.0	445.0	448.0	445.0	442.0	439.0	439.0	438.0
20°	478.0	479.0	479.0	480.0	483.0	486.0	482.0	480.0	478.0	476.0	474.0
22.5°	514.0	515.0	515.0	514.0	516.0	515.0	513.0	511.0	509.0	506.0	504.0
25°	549.0	550.0	549.0	548.0	549.0	546.0	543.0	540.0	535.0	530.0	530.0
27.5°	588.0	587.0	583.0	584.0	582.0	580.0	574.0	567.0	560.0	555.0	555.0
30°	629.0	629.0	621.0	625.0	621.0	620.0	607.0	598.0	588.0	581.0	580.0
32.5°	674.0	672.0	666.0	670.0	666.0	662.0	646.0	634.0	617.0	607.0	606.0
35°	728.0	723.0	718.0	722.0	722.0	711.0	695.0	673.0	649.0	637.0	636.0
37.5°	794.0	791.0	785.0	790.0	794.0	783.0	759.0	727.0	693.0	675.0	674.0
40°	867.0	863.0	860.0	867.0	870.0	859.0	827.0	782.0	736.0	710.0	706.0
42.5°	936.0	927.0	922.0	932.0	929.0	917.0	873.0	821.0	758.0	728.0	723.0
45°	997.9	987.9	980.9	989.9	985.9	962.0	913.0	843.0	767.0	730.0	724.0
47.5°	1058.9	1043.9	1032.9	1044.9	1036.9	999.9	940.0	854.0	757.0	713.0	703.0
50°	1110.9	1092.9	1085.9	1099.9	1087.9	1035.9	959.0	849.0	732.0	668.0	652.0
52.5°	1172.9	1145.9	1138.9	1165.9	1138.9	1069.9	963.0	837.0	675.0	598.0	583.0
55°	1235.9	1205.9	1194.9	1219.9	1178.9	1076.9	943.0	768.0	589.0	507.0	485.0
57.5°	1268.9	1240.9	1230.9	1248.9	1172.9	1008.9	854.0	640.0	460.0	368.0	344.0
60°	1298.9	1249.9	1236.9	1260.9	1110.9	851.0	661.0	459.0	278.0	209.0	191.0
62.5°	1319.9	1272.9	1245.9	1256.9	996.9	619.0	380.0	221.0	105.0	73.0	72.0
65°	1308.9	1268.9	1250.9	1242.9	866.0	356.0	140.0	56.0	3.0	3.0	2.0
67.5°	1274.9	1230.9	1225.9	1232.9	857.0	342.0	130.0	51.0	0.0	0.0	0.0
70°	1199.9	1168.9	1168.9	1192.9	818.0	324.0	121.0	47.0	0.0	0.0	0.0
72.5°	1098.9	1074.9	1088.9	1124.9	760.0	299.0	109.0	42.0	0.0	0.0	0.0
75°	978.0	953.0	971.0	1010.9	688.0	267.0	95.0	36.0	0.0	0.0	0.0
77.5°	824.0	807.0	835.0	872.0	592.0	225.0	78.0	29.0	0.0	0.0	0.0
80°	642.0	633.0	670.0	703.0	478.0	177.0	59.0	21.0	0.0	0.0	0.0
82.5°	443.0	439.0	475.0	509.0	342.0	124.0	40.0	14.0	0.0	0.0	0.0
85°	232.0	232.0	260.0	291.0	191.0	67.0	20.0	6.0	0.0	0.0	0.0
87.5°	51.0	49.0	53.0	68.0	38.0	13.0	3.0	1.0	0.0	0.0	0.0
90°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
105°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436812  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
117.5°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
122.5°	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0
125°	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	1.0	1.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)