

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P197998

Luminaire Tested: **TT-C3-LED-E1-RW-PM**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P197998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34691)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-RW-PM  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
RECTANGULAR DISTRIBUTION  
Light Source: (168) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5082.2 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B3 - U0 - G3

Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P197998

CATALOG NUMBER: TT-C3-LED-E1-RW-PM

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.3 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P197998

CATALOG NUMBER: TT-C3-LED-E1-RW-PM

### Luminous Intensity Polar Plot



— Vertical Plane Through 88-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P197998

CATALOG NUMBER: TT-C3-LED-E1-RW-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2541.1	0.0	2541.1
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2541.1	0.0	2541.1
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	5082.2	0.0	5082.2
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.9	0.4
10°-20°	69.2	1.4
20°-30°	152.8	3.0
30°-40°	304.6	6.0
40°-50°	583.0	11.5
50°-60°	1043.5	20.5
60°-70°	1382.8	27.2
70°-80°	1154.0	22.7
80°-90°	372.3	7.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5082.2	100.0
0°-180°	5082.2	100.0



REPORT NUMBER: P197998


CATALOG NUMBER: TT-C3-LED-E1-RW-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	121.0	2.4			
FM	(30°-60°)	965.6	19.0			
FH	(60°-80°)	1268.4	25.0			G1/1800
FVH	(80°-90°)	186.2	3.7			G2/225
BL	(0°-30°)	121.0	2.4	B1/500		
BM	(30°-60°)	965.6	19.0	B1/1000		
BH	(60°-80°)	1268.4	25.0	B3/2500		G3/2500
BVH	(80°-90°)	186.2	3.7			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G3**

Type IV Short





REPORT NUMBER: P197998

CATALOG NUMBER: TT-C3-LED-E1-RW-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	88°
0°	199	199	199	199	199	199	199	199	199	199	199
2.5°	201	201	201	201	202	202	202	202	202	202	202
5°	204	204	205	205	206	206	206	206	205	205	205
7.5°	209	210	211	211	211	210	209	209	208	208	208
10°	218	218	219	219	218	217	216	215	215	215	214
12.5°	229	229	230	229	227	226	224	223	223	222	222
15°	244	246	246	243	240	237	236	234	234	234	234
17.5°	267	266	262	259	257	252	250	249	247	247	247
20°	293	291	286	282	278	272	268	266	265	264	264
22.5°	322	319	312	309	301	295	290	286	283	282	284
25°	352	352	346	338	330	321	314	309	305	304	303
27.5°	384	386	378	370	361	349	342	335	334	333	332
30°	418	422	414	406	394	382	373	370	367	369	369
32.5°	460	462	453	447	431	419	411	409	410	409	412
35°	509	506	499	487	473	462	456	460	471	475	473
37.5°	563	552	548	533	520	511	513	523	532	539	537
40°	603	605	594	580	568	566	577	590	607	613	615
42.5°	644	656	643	629	623	627	643	669	707	727	724
45°	691	704	690	679	678	693	728	796	852	892	896
47.5°	740	750	737	730	740	769	829	920	980	1027	1035
50°	802	798	788	787	809	862	943	1035	1143	1174	1184
52.5°	863	848	846	851	890	950	1058	1239	1398	1510	1522
55°	920	903	907	920	975	1066	1216	1437	1576	1655	1659
57.5°	972	962	971	989	1071	1188	1347	1529	1634	1690	1700
60°	1025	1023	1034	1067	1155	1259	1392	1553	1658	1701	1711
62.5°	1075	1082	1096	1128	1196	1277	1406	1603	1760	1828	1845
65°	1128	1134	1151	1156	1217	1303	1501	1697	1829	1917	1929
67.5°	1176	1184	1178	1174	1227	1303	1482	1654	1764	1831	1844
70°	1222	1213	1189	1158	1173	1225	1389	1538	1649	1712	1725
72.5°	1234	1222	1158	1087	1065	1104	1255	1387	1478	1537	1545
75°	1203	1178	1070	972	930	969	1095	1208	1272	1336	1341
77.5°	1079	1063	943	824	777	806	911	991	1065	1127	1139
80°	886	872	766	669	606	626	703	767	838	887	902
82.5°	652	650	574	483	439	437	495	558	612	659	669
85°	410	410	358	303	257	258	293	339	407	437	440
87.5°	139	132	123	100	80	72	77	88	134	166	172
90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P197998

CATALOG NUMBER: TT-C3-LED-E1-RW-PM

**CANDELA DISTRIBUTION (continued):**

	90°
0°	199
2.5°	202
5°	205
7.5°	208
10°	214
12.5°	223
15°	233
17.5°	247
20°	264
22.5°	283
25°	303
27.5°	333
30°	368
32.5°	411
35°	474
37.5°	539
40°	620
42.5°	732
45°	886
47.5°	1035
50°	1173
52.5°	1497
55°	1663
57.5°	1699
60°	1708
62.5°	1836
65°	1927
67.5°	1843
70°	1722
72.5°	1539
75°	1349
77.5°	1139
80°	890
82.5°	669
85°	433
87.5°	167
90°	0

(END OF REPORT)