

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198189

Luminaire Tested: **TT-C3-LED-E1-T4-PM-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P198189  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34703)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-C3-LED-E1-T4-PM-8030  
Description: TOPTIER LED AREA/SITE LUMINAIRE  
DRIVE LANE DISTRIBUTION  
Light Source: (160) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4152.3 lumens  
Efficiency: N/A  
Efficacy: 62.4 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short - Non-Cutoff  
BUG Rating: B2 - U0 - G3


Input Watts (W): 66.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P198189  
 CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.4 fc  
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P198189  
CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P198189

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1133.2	0.0	1133.2
	% Fixture	27.3	0.0	27.3
<b>Street Side</b>	Lumens	3019.0	0.0	3019.0
	% Fixture	72.7	0.0	72.7
<b>Total</b>	Lumens	4152.3	0.0	4152.3
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.3	0.4
10°-20°	56.7	1.4
20°-30°	123.8	3.0
30°-40°	245.2	5.9
40°-50°	464.4	11.2
50°-60°	824.5	19.9
60°-70°	1141.8	27.5
70°-80°	979.4	23.6
80°-90°	300.1	7.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4152.3	100.0
0°-180°	4152.3	100.0



REPORT NUMBER: P198189


CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	118.3	2.8			
FM (30°-60°)	1083.4	26.1			
FH (60°-80°)	1589.7	38.3			G1/1800
FVH (80°-90°)	227.6	5.5			G3/500
BL (0°-30°)	78.6	1.9	B0/110		
BM (30°-60°)	450.7	10.9	B1/1000		
BH (60°-80°)	531.5	12.8	B2/1000		G2/1000
BVH (80°-90°)	72.5	1.7			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P198189

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1
2.5°	171.2	170.4	170.4	170.4	169.7	168.9	168.9	168.2	167.4	166.7	165.2
5°	180.2	178.7	178.7	178.7	178.0	177.2	176.5	175.0	172.7	170.4	168.9
7.5°	190.8	191.6	191.6	189.3	187.8	186.3	185.5	182.5	179.5	175.7	172.7
10°	203.6	204.4	204.4	202.9	199.9	198.3	196.8	193.8	188.5	183.3	178.7
12.5°	218.0	219.5	220.2	218.0	214.2	211.2	211.9	206.6	199.9	193.1	186.3
15°	239.1	238.3	240.6	236.1	232.3	228.5	227.8	220.2	213.4	204.4	196.1
17.5°	264.7	261.7	261.7	259.4	257.2	251.1	248.1	240.6	229.3	218.7	205.9
20°	291.1	290.4	288.9	287.3	282.8	276.0	276.8	264.7	251.1	236.1	220.2
22.5°	322.0	325.1	320.5	320.5	316.8	311.5	309.2	293.4	275.3	254.2	236.1
25°	355.2	356.0	356.0	357.5	356.7	347.7	343.2	328.8	307.7	279.8	253.4
27.5°	389.2	392.2	391.4	395.2	397.5	391.4	387.6	371.1	340.9	310.0	276.8
30°	426.9	429.1	432.9	441.9	444.2	438.2	435.2	415.6	385.4	341.6	300.2
32.5°	469.9	472.9	476.6	494.0	502.3	495.5	491.0	473.6	435.9	387.6	334.9
35°	517.4	517.4	530.2	551.3	564.1	559.6	561.1	543.0	502.3	441.9	377.1
37.5°	570.2	570.2	586.8	613.1	638.0	639.5	647.8	626.7	576.9	499.3	418.6
40°	616.9	626.7	651.6	685.5	724.8	737.6	741.4	720.2	659.2	567.1	464.6
42.5°	671.2	682.5	713.5	764.0	813.8	841.7	843.2	822.8	759.5	653.1	530.9
45°	726.3	740.6	778.3	842.4	918.6	951.8	952.5	953.3	895.2	755.7	608.6
47.5°	788.9	800.2	850.0	926.1	1023.4	1077.7	1095.8	1098.1	1018.9	862.0	676.5
50°	856.7	860.5	929.1	1037.0	1168.2	1243.6	1254.2	1261.7	1150.1	982.7	748.1
52.5°	926.9	932.2	1012.1	1161.4	1326.6	1420.1	1438.2	1441.2	1351.5	1157.7	886.9
55°	999.3	1003.8	1107.1	1310.0	1515.1	1638.1	1670.5	1690.9	1549.8	1270.0	942.7
57.5°	1073.2	1084.5	1222.5	1464.6	1723.3	1886.2	1908.8	1877.9	1662.2	1327.4	958.6
60°	1147.1	1167.5	1347.7	1637.3	1928.4	2054.4	2060.4	1974.4	1716.5	1359.0	964.6
62.5°	1216.5	1250.4	1478.9	1797.2	2064.9	2141.1	2141.1	2027.2	1794.2	1461.6	1034.0
65°	1286.6	1327.4	1577.7	1911.1	2139.6	2223.3	2233.1	2169.0	1928.4	1524.2	1054.3
67.5°	1347.7	1410.3	1638.1	1977.5	2206.0	2265.6	2254.2	2148.7	1896.0	1480.5	997.8
70°	1415.6	1458.6	1681.1	1975.9	2146.4	2156.2	2150.2	2036.3	1793.4	1399.0	925.4
72.5°	1442.7	1477.4	1651.6	1873.4	1976.7	1975.2	1964.6	1864.3	1634.3	1272.3	825.8
75°	1414.8	1412.6	1515.9	1664.5	1744.4	1745.2	1736.9	1651.6	1429.2	1092.8	699.1
77.5°	1263.2	1258.7	1304.0	1394.5	1480.5	1488.0	1473.7	1378.6	1190.1	905.0	584.5
80°	1019.6	1000.8	1034.7	1108.6	1175.0	1168.2	1180.3	1076.2	924.6	698.4	441.9
82.5°	690.1	696.1	738.3	782.8	854.5	860.5	847.7	790.4	669.0	506.8	310.7
85°	356.7	365.0	418.6	488.0	512.8	541.5	538.5	498.5	404.2	294.1	184.8
87.5°	62.6	54.3	76.2	115.4	140.3	167.4	166.7	119.2	93.5	63.4	39.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P198189

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-8030

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1	162.1
2.5°	165.2	164.4	163.7	162.1	160.6	159.9	159.1	158.4	158.4	157.6	157.6
5°	168.2	166.7	165.2	162.9	161.4	159.9	158.4	157.6	156.9	156.1	156.1
7.5°	171.2	169.7	166.7	163.7	160.6	159.1	158.4	156.9	156.1	155.4	155.4
10°	176.5	174.2	169.7	165.2	162.1	159.9	157.6	156.9	156.1	156.1	155.4
12.5°	182.5	178.7	173.5	168.2	163.7	160.6	159.1	158.4	157.6	157.6	156.9
15°	191.6	187.8	179.5	172.0	168.2	164.4	162.1	161.4	160.6	161.4	160.6
17.5°	200.6	196.1	185.5	178.0	172.0	168.9	166.7	165.9	165.2	166.7	166.7
20°	212.7	205.9	194.6	184.8	178.0	174.2	173.5	172.0	172.7	173.5	173.5
22.5°	225.5	217.2	203.6	192.3	186.3	181.8	181.0	181.0	181.0	181.8	182.5
25°	241.3	230.8	213.4	202.1	194.6	190.8	190.1	190.1	190.8	191.6	191.6
27.5°	260.9	247.4	226.3	211.9	203.6	199.9	199.1	199.9	201.4	202.1	202.1
30°	283.6	267.7	240.6	225.5	215.7	211.2	211.2	211.9	213.4	214.9	212.7
32.5°	310.7	290.4	260.2	239.8	229.3	224.7	224.7	226.3	225.5	226.3	228.5
35°	345.4	321.3	283.6	259.4	245.9	240.6	240.6	241.3	241.3	242.8	243.6
37.5°	382.4	353.0	308.5	282.1	267.0	259.4	257.2	257.9	259.4	258.7	260.2
40°	423.1	387.6	337.9	304.7	288.9	280.6	276.0	276.0	275.3	274.5	273.8
42.5°	477.4	435.9	374.1	333.3	313.7	304.7	297.1	294.9	293.4	294.1	288.9
45°	546.0	497.8	420.1	375.6	343.2	328.8	321.3	316.8	313.0	310.0	307.0
47.5°	604.1	543.0	462.3	411.8	377.8	360.5	348.4	340.9	333.3	330.3	330.3
50°	666.7	604.9	511.3	445.7	415.6	394.4	381.6	368.0	357.5	350.7	354.5
52.5°	788.1	709.7	585.2	510.6	454.8	431.4	416.3	398.2	383.9	374.8	375.6
55°	823.6	741.4	625.2	553.6	505.3	482.7	459.3	435.2	413.3	400.5	401.2
57.5°	828.8	745.1	632.8	570.2	542.3	527.2	506.8	475.1	447.2	426.9	424.6
60°	825.1	742.9	632.0	568.7	548.3	551.3	545.3	518.1	480.4	455.5	452.5
62.5°	880.1	784.3	664.4	581.5	555.1	559.6	567.1	551.3	514.3	480.4	475.1
65°	884.7	791.9	669.0	598.1	577.7	577.7	582.2	570.2	540.0	505.3	497.0
67.5°	831.1	748.1	633.5	571.7	561.1	573.2	589.0	581.5	552.1	527.2	518.9
70°	771.5	690.1	587.5	528.7	523.4	540.0	565.6	572.4	558.8	538.5	535.5
72.5°	678.0	616.2	520.4	474.4	472.9	489.5	515.9	534.7	538.5	539.2	537.7
75°	584.5	521.1	443.5	408.8	411.8	429.9	453.3	473.6	494.0	510.6	517.4
77.5°	478.9	432.1	370.3	337.1	343.2	363.5	382.4	402.7	423.8	452.5	456.3
80°	367.3	335.6	279.8	265.5	264.7	281.3	303.9	316.0	346.2	369.5	367.3
82.5°	259.4	234.5	202.9	190.1	193.1	204.4	218.7	227.0	248.9	261.7	265.5
85°	153.1	142.5	124.4	112.4	115.4	126.7	129.0	139.5	144.8	153.1	150.8
87.5°	32.4	27.9	24.9	25.6	22.6	23.4	26.4	25.6	25.6	30.2	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)