

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P198166

Luminaire Tested: **TT-C3-LED-E1-T4-PM-LWR-LW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P198166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P34705)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-C3-LED-E1-T4-PM-LWR-LW
Description: TOPTIER LED AREA/SITE LUMINAIRE
DRIVE LANE DISTRIBUTION WITH LumaWatt WIRELESS SENSOR
Light Source: (160) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4943.2 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B2 - U0 - G2


Input Watts (W): 66.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P198166
 CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P198166
CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P198166

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1501.1	0.0	1501.1
	% Fixture	30.4	0.0	30.4
Street Side	Lumens	3442.1	0.0	3442.1
	% Fixture	69.6	0.0	69.6
Total	Lumens	4943.2	0.0	4943.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.7	0.5
10°-20°	77.5	1.6
20°-30°	163.6	3.3
30°-40°	310.9	6.3
40°-50°	574.3	11.6
50°-60°	1006.6	20.4
60°-70°	1365.9	27.6
70°-80°	1110.5	22.5
80°-90°	311.1	6.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4943.2	100.0
0°-180°	4943.2	100.0



REPORT NUMBER: P198166


CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	153.0	3.1			
FM (30°-60°)	1291.5	26.1			
FH (60°-80°)	1781.7	36.0			G1/1800
FVH (80°-90°)	215.9	4.4			G2/225
BL (0°-30°)	110.9	2.2	B1/500		
BM (30°-60°)	600.3	12.1	B1/1000		
BH (60°-80°)	694.7	14.1	B2/1000		G2/1000
BVH (80°-90°)	95.2	1.9			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P198166

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	46°	55°	65°	75°	85°
0°	225	225	225	225	225	225	225	225	225	225	225
2.5°	234	235	235	235	234	233	233	232	231	231	230
5°	245	245	245	244	243	242	241	240	237	235	234
7.5°	258	258	258	257	255	252	253	250	247	243	239
10°	273	274	275	272	270	267	266	262	258	253	248
12.5°	291	290	292	289	287	282	281	276	269	263	257
15°	313	314	313	311	307	302	302	295	287	278	268
17.5°	344	344	340	339	332	326	324	318	305	294	282
20°	378	376	371	372	366	357	355	345	331	314	298
22.5°	417	415	409	408	400	393	393	379	360	338	316
25°	448	449	450	451	445	434	433	418	393	365	336
27.5°	486	491	490	495	492	482	480	464	433	400	364
30°	529	536	532	542	542	535	531	515	484	437	394
32.5°	577	578	584	597	603	599	596	581	541	489	433
35°	632	627	637	662	671	672	671	653	617	553	482
37.5°	687	685	704	729	756	767	762	756	704	624	533
40°	739	748	773	804	847	873	874	862	808	711	594
42.5°	790	808	840	894	949	991	986	976	929	813	672
45°	860	878	910	975	1063	1115	1116	1134	1094	950	778
47.5°	924	940	987	1074	1182	1277	1273	1299	1248	1076	861
50°	1012	1007	1076	1197	1344	1464	1490	1503	1407	1234	950
52.5°	1090	1085	1171	1333	1516	1671	1657	1689	1649	1448	1140
55°	1168	1168	1276	1489	1730	1933	1945	1999	1891	1608	1207
57.5°	1254	1263	1416	1682	1977	2199	2201	2206	2032	1672	1225
60°	1337	1361	1560	1872	2172	2354	2370	2301	2086	1713	1232
62.5°	1429	1453	1697	2030	2316	2417	2412	2344	2175	1828	1321
65°	1498	1543	1798	2139	2371	2491	2493	2481	2325	1926	1358
67.5°	1568	1636	1850	2181	2410	2473	2470	2424	2264	1871	1284
70°	1643	1693	1886	2143	2293	2301	2304	2238	2108	1758	1191
72.5°	1669	1705	1831	1985	2055	2053	2025	2000	1890	1585	1058
75°	1623	1626	1645	1712	1744	1717	1732	1695	1632	1362	902
77.5°	1443	1438	1384	1360	1361	1355	1356	1311	1284	1122	732
80°	1126	1125	1082	1015	994	988	994	972	947	847	557
82.5°	781	769	750	697	694	682	685	681	669	602	395
85°	379	395	412	408	395	397	410	409	395	345	230
87.5°	52	75	78	75	95	119	95	97	78	80	51
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P198166

CATALOG NUMBER: TT-C3-LED-E1-T4-PM-LWR-LW

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	225	225	225	225	225	225	225	225	225	225	225
2.5°	229	228	227	226	225	224	223	223	222	222	222
5°	233	232	230	228	227	225	224	223	221	221	220
7.5°	237	236	233	230	228	226	225	224	223	221	221
10°	245	242	238	234	230	228	226	225	225	224	224
12.5°	253	250	243	238	233	230	228	228	227	227	226
15°	263	259	251	244	238	235	232	232	232	232	232
17.5°	275	269	260	252	246	242	239	239	238	239	240
20°	291	283	271	261	254	251	249	248	248	249	250
22.5°	306	297	281	271	265	260	259	259	258	260	260
25°	324	313	296	283	275	271	271	271	272	273	271
27.5°	348	335	312	296	289	285	283	285	286	287	285
30°	372	358	329	311	301	297	297	299	300	301	299
32.5°	405	384	353	330	319	315	315	316	316	318	317
35°	451	422	383	356	340	334	333	334	336	335	339
37.5°	495	462	413	384	368	359	355	354	356	357	358
40°	547	507	450	414	394	384	378	378	377	378	374
42.5°	614	569	497	451	423	414	403	400	397	398	392
45°	705	648	562	501	464	445	434	425	421	419	413
47.5°	768	707	614	548	509	484	467	455	445	440	441
50°	852	773	677	597	557	529	509	488	473	467	470
52.5°	1011	916	767	673	606	575	554	528	506	495	498
55°	1064	967	830	734	674	636	603	572	543	525	526
57.5°	1069	973	841	761	720	694	663	622	582	557	555
60°	1064	966	839	758	729	728	709	673	626	589	586
62.5°	1134	1029	875	775	734	737	741	716	668	623	613
65°	1147	1036	890	796	765	759	756	739	700	651	643
67.5°	1083	978	845	764	743	756	767	752	715	678	667
70°	998	903	779	704	692	712	736	741	720	690	686
72.5°	884	804	695	635	630	645	673	696	693	686	684
75°	753	691	596	550	550	569	590	615	634	646	649
77.5°	620	558	488	449	454	479	494	519	540	556	557
80°	466	432	371	350	352	369	390	405	422	436	432
82.5°	337	306	264	252	260	268	285	298	303	307	315
85°	194	185	162	155	157	165	175	178	183	181	185
87.5°	47	50	47	46	47	45	43	52	53	54	52
90°	0	0	0	0	0	0	0	0	0	0	0

(END OF REPORT)