

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436787

Luminaire Tested: **TT-D2-830-U-5WQ-PM-HSS**

Issue Date: 12/2/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P436787  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D2-830-U-5WQ-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
3000K, 80 CRI LEDS AND WIDE DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3781.9 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U2 - G2


Input Watts (W): 39.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P436787  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P436787  
CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436787  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1332.1	0.8	1332.9
	% Fixture	35.2	0.0	35.2
<b>Street Side</b>	Lumens	2433.7	15.2	2449.0
	% Fixture	64.4	0.4	64.8
<b>Total</b>	Lumens	3765.8	16.1	3781.9
	% Fixture	99.6	0.4	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.3	0.7
10°-20°	89.8	2.4
20°-30°	192.5	5.1
30°-40°	348.6	9.2
40°-50°	581.7	15.4
50°-60°	805.8	21.3
60°-70°	835.0	22.1
70°-80°	672.0	17.8
80°-90°	215.0	5.7
90°-100°	10.9	0.3
100°-110°	3.5	0.1
110°-120°	0.7	0.0
120°-130°	0.4	0.0
130°-140°	0.3	0.0
140°-150°	0.2	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	3765.8	99.6
0°-180°	3781.9	100.0

**Coefficient of Utilization**



REPORT NUMBER: P436787


CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	157.3	4.2			
FM (30°-60°)	1005.5	26.6			
FH (60°-80°)	1107.4	29.3			G1/1800
FVH (80°-90°)	163.6	4.3			G2/225
BL (0°-30°)	150.4	4.0	B1/500		
BM (30°-60°)	730.7	19.3	B1/1000		
BH (60°-80°)	399.6	10.6	B1/500		G1/500
BVH (80°-90°)	51.4	1.4			G1/100
UL (90°-100°)	10.9	0.3		U2/50	
UH (100°-180°)	5.2	0.1		U1/10	

**BUG Rating: B1-U2-G2**

Type IV Short





REPORT NUMBER: P436787

CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6
2.5°	256.9	256.2	256.2	255.5	255.5	255.5	255.5	255.5	254.7	254.0	253.3
5°	263.6	263.6	262.9	262.9	262.1	261.4	262.1	261.4	260.6	259.9	259.2
7.5°	272.4	271.7	271.7	270.2	270.2	269.5	269.5	269.5	268.8	267.3	266.5
10°	285.0	283.5	283.5	282.0	281.3	280.6	280.6	279.1	279.1	278.4	277.6
12.5°	299.0	297.6	299.0	298.3	296.8	295.3	295.3	293.9	293.1	292.4	289.4
15°	317.5	315.3	316.8	316.8	316.0	315.3	315.3	312.3	310.8	309.4	306.4
17.5°	339.6	338.2	338.9	339.6	341.9	341.9	342.6	338.9	335.9	330.8	328.6
20°	367.7	367.0	369.2	369.2	371.4	371.4	372.1	368.4	363.3	359.6	355.1
22.5°	395.0	395.0	398.0	398.0	400.2	398.7	398.7	397.2	391.3	386.9	382.5
25°	423.1	422.3	425.3	427.5	430.5	426.8	428.2	426.0	420.1	414.2	408.3
27.5°	454.1	452.6	454.1	457.0	462.2	459.3	460.7	457.0	451.1	443.0	437.8
30°	488.0	485.8	488.0	492.5	496.2	497.6	496.9	491.7	486.6	474.8	471.1
32.5°	521.3	521.3	526.4	534.6	539.0	538.3	539.0	534.6	527.2	512.4	503.6
35°	561.9	564.8	571.5	583.3	592.9	589.2	589.2	587.7	575.2	557.5	545.6
37.5°	615.8	618.7	632.0	646.1	663.8	662.3	663.0	658.6	634.2	615.8	598.8
40°	678.5	681.5	701.4	721.4	738.3	743.5	744.3	734.7	708.1	681.5	654.9
42.5°	736.1	739.8	760.5	788.6	807.0	815.1	816.6	801.1	773.0	742.8	709.6
45°	793.7	798.2	821.8	851.3	877.9	881.6	882.3	869.0	838.0	803.3	760.5
47.5°	852.8	856.5	880.8	916.3	945.1	952.5	953.2	940.7	903.0	860.9	810.7
50°	906.7	914.1	947.3	985.0	1023.3	1029.3	1030.0	1016.0	971.7	924.4	858.0
52.5°	970.2	973.9	1009.3	1072.1	1104.6	1127.5	1128.2	1100.9	1053.6	990.1	904.5
55°	1044.0	1050.7	1086.8	1149.6	1207.9	1223.4	1227.9	1195.4	1132.6	1064.0	963.5
57.5°	1086.8	1099.4	1152.6	1212.4	1285.5	1295.8	1298.0	1264.0	1194.6	1119.3	1007.8
60°	1109.7	1117.1	1173.2	1266.3	1323.1	1332.7	1332.0	1306.1	1236.7	1145.2	1028.5
62.5°	1135.6	1148.1	1195.4	1289.9	1339.4	1363.0	1359.3	1332.7	1261.8	1161.4	1048.5
65°	1128.2	1138.5	1207.9	1284.7	1366.7	1392.5	1387.4	1351.9	1265.5	1164.4	1043.3
67.5°	1098.7	1106.8	1175.4	1270.7	1349.0	1367.4	1376.3	1341.6	1244.9	1132.6	1010.8
70°	1038.1	1050.7	1117.1	1214.6	1286.2	1299.5	1301.0	1279.6	1192.4	1074.3	956.9
72.5°	954.7	965.0	1037.4	1136.3	1198.3	1213.8	1215.3	1182.8	1117.1	994.6	879.4
75°	855.0	864.6	920.7	1024.1	1085.4	1100.9	1099.4	1069.1	999.7	883.8	776.7
77.5°	731.7	749.4	798.9	883.8	943.6	951.7	953.2	920.0	863.9	763.4	659.3
80°	577.4	594.4	650.5	714.0	764.2	770.8	773.0	745.0	694.0	605.4	516.8
82.5°	410.5	425.3	469.6	521.3	563.4	563.4	564.8	541.9	502.8	426.8	357.4
85°	234.1	245.1	274.7	311.6	341.9	338.2	338.9	318.2	292.4	233.3	189.0
87.5°	76.8	82.0	88.6	102.6	116.7	107.8	112.2	93.0	84.2	62.8	48.7
90°	40.6	40.6	39.1	37.7	34.7	30.3	30.3	24.4	18.5	11.8	4.4
92.5°	36.9	36.9	35.4	34.0	31.0	27.3	27.3	22.2	16.2	10.3	3.7
95°	30.3	30.3	29.5	28.1	25.8	22.9	22.2	18.5	14.0	8.1	3.0
97.5°	23.6	23.6	22.9	22.2	19.9	17.7	17.7	14.0	10.3	6.6	2.2
100°	17.7	17.7	17.7	16.2	15.5	13.3	13.3	11.1	8.1	5.2	1.5
102.5°	12.6	13.3	12.6	11.8	11.1	9.6	9.6	8.1	5.9	3.7	1.5
105°	8.9	8.9	8.1	8.1	7.4	6.6	6.6	5.2	3.7	2.2	0.7
107.5°	5.2	5.2	5.2	5.2	4.4	4.4	4.4	3.7	2.2	1.5	0.7
110°	3.0	3.0	3.0	3.0	2.2	2.2	2.2	1.5	1.5	0.7	0.7



REPORT NUMBER: P436787  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
112.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	0.7	0.7	0.7	0.7
115°	0.7	0.7	0.7	1.5	0.7	0.7	0.7	0.7	0.7	0.7	0.7
117.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
120°	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
122.5°	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
125°	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
127.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
130°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
132.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
135°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7	0.7
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
140°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
142.5°	0.7	0.7	0.7	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
145°	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
147.5°	0.7	0.7	0.7	0.0	0.0	0.7	0.7	0.7	0.7	0.7	0.7
150°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
160°	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
162.5°	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
165°	0.7	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
167.5°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
170°	0.7	0.0	0.0	0.0	0.0	0.7	0.0	0.7	0.7	0.7	0.7
172.5°	0.7	0.7	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
175°	0.7	0.7	0.7	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7
177.5°	0.0	0.7	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P436787

CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6	249.6
2.5°	253.3	253.3	252.5	251.8	251.8	251.8	251.0	251.0	251.0	250.3	250.3
5°	259.2	258.4	258.4	257.7	257.7	256.9	256.9	256.2	255.5	255.5	254.7
7.5°	267.3	266.5	265.1	265.8	264.3	263.6	262.9	262.9	262.9	262.1	262.1
10°	276.9	276.9	275.4	275.4	273.9	273.2	272.4	272.4	273.2	273.2	272.4
12.5°	289.4	288.7	288.7	288.0	287.2	286.5	287.2	287.2	286.5	285.7	285.0
15°	304.9	304.9	304.9	305.7	304.9	304.9	304.9	304.2	302.7	301.2	301.2
17.5°	328.6	327.8	326.3	327.1	328.6	330.8	328.6	326.3	324.1	324.1	323.4
20°	352.9	353.7	353.7	354.4	356.6	358.8	355.9	354.4	352.9	351.5	350.0
22.5°	379.5	380.2	380.2	379.5	381.0	380.2	378.8	377.3	375.8	373.6	372.1
25°	405.4	406.1	405.4	404.6	405.4	403.1	400.9	398.7	395.0	391.3	391.3
27.5°	434.1	433.4	430.5	431.2	429.7	428.2	423.8	418.6	413.5	409.8	409.8
30°	464.4	464.4	458.5	461.5	458.5	457.8	448.2	441.5	434.1	429.0	428.2
32.5°	497.6	496.2	491.7	494.7	491.7	488.8	477.0	468.1	455.6	448.2	447.4
35°	537.5	533.8	530.1	533.1	533.1	525.0	513.2	496.9	479.2	470.3	469.6
37.5°	586.2	584.0	579.6	583.3	586.2	578.1	560.4	536.8	511.7	498.4	497.6
40°	640.1	637.2	635.0	640.1	642.4	634.2	610.6	577.4	543.4	524.2	521.3
42.5°	691.1	684.4	680.8	688.1	685.9	677.1	644.6	606.2	559.7	537.5	533.8
45°	736.9	729.5	724.3	731.0	728.0	710.3	674.1	622.4	566.3	539.0	534.6
47.5°	781.9	770.8	762.7	771.6	765.7	738.3	694.0	630.5	558.9	526.4	519.1
50°	820.3	807.0	801.8	812.2	803.3	764.9	708.1	626.9	540.5	493.2	481.4
52.5°	866.1	846.1	841.0	860.9	841.0	790.0	711.0	618.0	498.4	441.5	430.5
55°	912.6	890.4	882.3	900.8	870.5	795.2	696.3	567.0	434.9	374.3	358.1
57.5°	937.0	916.3	908.9	922.2	866.1	745.0	630.5	472.5	339.6	271.7	254.0
60°	959.1	922.9	913.3	931.1	820.3	628.3	488.0	338.9	205.3	154.3	141.0
62.5°	974.6	939.9	920.0	928.1	736.1	457.0	280.6	163.2	77.5	53.9	53.2
65°	966.5	937.0	923.7	917.8	639.4	262.9	103.4	41.3	2.2	2.2	1.5
67.5°	941.4	908.9	905.2	910.4	632.8	252.5	96.0	37.7	0.0	0.0	0.0
70°	886.0	863.1	863.1	880.8	604.0	239.2	89.3	34.7	0.0	0.0	0.0
72.5°	811.4	793.7	804.1	830.6	561.1	220.8	80.5	31.0	0.0	0.0	0.0
75°	722.1	703.6	716.9	746.5	508.0	197.1	70.1	26.6	0.0	0.0	0.0
77.5°	608.4	595.8	616.5	643.8	437.1	166.1	57.6	21.4	0.0	0.0	0.0
80°	474.0	467.4	494.7	519.1	352.9	130.7	43.6	15.5	0.0	0.0	0.0
82.5°	327.1	324.1	350.7	375.8	252.5	91.6	29.5	10.3	0.0	0.0	0.0
85°	171.3	171.3	192.0	214.9	141.0	49.5	14.8	4.4	0.0	0.0	0.0
87.5°	37.7	36.2	39.1	50.2	28.1	9.6	2.2	0.7	0.0	0.0	0.0
90°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
105°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436787  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
117.5°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
122.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
125°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)