

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387203

Luminaire Tested: **TT-D2-830-U-5WQ-PM**

Issue Date: 2/18/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P387203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-14)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 2/18/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: TT-D2-830-U-5WQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
3000K, 80 CRI LEDS AND WIDE DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4695 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 39.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P387203  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.6 fc  
 Type V - Short - N/A

REPORT NUMBER: P387203  
CATALOG NUMBER: TT-D2-830-U-5WQ-PM

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P387203

CATALOG NUMBER: TT-D2-830-U-5WQ-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2347.5	0.0	2347.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2347.5	0.0	2347.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4695.0	0.0	4695.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.5	0.7
10°-20°	108.4	2.3
20°-30°	222.5	4.7
30°-40°	395.4	8.4
40°-50°	666.5	14.2
50°-60°	983.1	20.9
60°-70°	1153.8	24.6
70°-80°	898.9	19.1
80°-90°	235.0	5.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4695.0	100.0
0°-180°	4695.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P387203  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	181.2	3.9			
FM (30°-60°)	1022.5	21.8			
FH (60°-80°)	1026.3	21.9			G1/1800
FVH (80°-90°)	117.5	2.5			G2/225
BL (0°-30°)	181.2	3.9	B1/500		
BM (30°-60°)	1022.5	21.8	B2/2500		
BH (60°-80°)	1026.3	21.9	B3/2500		G1/1800
BVH (80°-90°)	117.5	2.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**  
 Type V Short





REPORT NUMBER: P387203  
 CATALOG NUMBER: TT-D2-830-U-5WQ-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	316.0	316.0	316.0	316.0	316.0	316.0	316.0	316.0	316.0	316.0	316.0
2.5°	321.2	321.2	321.2	320.4	320.4	320.4	320.4	321.2	321.2	321.2	321.2
5°	328.5	328.5	327.1	325.6	324.1	324.1	324.8	325.6	326.3	327.8	327.8
7.5°	333.0	333.0	332.2	330.8	328.5	328.5	329.3	330.8	331.5	331.5	330.8
10°	338.9	339.6	341.8	342.6	341.1	341.1	341.8	342.6	341.1	338.9	338.9
12.5°	352.9	353.6	356.6	358.8	358.8	357.3	358.1	359.5	355.9	352.2	352.9
15°	372.8	372.8	373.6	375.8	374.3	372.8	374.3	375.1	372.8	372.1	373.6
17.5°	399.4	399.4	395.0	398.7	399.4	398.7	400.2	396.5	394.2	397.2	398.7
20°	428.2	425.3	423.0	426.0	431.9	429.7	432.6	424.5	422.3	423.8	424.5
22.5°	446.7	448.9	450.4	451.8	460.0	457.0	460.0	451.1	449.6	446.7	444.5
25°	468.8	471.0	479.9	475.5	480.6	476.2	479.9	474.7	477.7	468.8	468.8
27.5°	493.9	498.3	503.5	501.3	507.9	505.7	507.9	500.6	501.3	497.6	496.1
30°	527.9	527.9	526.4	530.8	542.6	541.2	541.9	532.3	525.7	526.4	529.4
32.5°	561.8	557.4	559.6	572.9	580.3	577.3	578.8	574.4	559.6	556.7	558.9
35°	593.6	600.2	605.4	616.5	626.8	625.3	624.6	617.2	607.6	595.8	592.1
37.5°	643.1	650.4	664.5	684.4	702.9	706.5	696.9	687.3	665.2	648.2	639.4
40°	708.0	708.8	725.0	763.4	780.4	783.3	778.2	761.9	728.0	708.8	708.0
42.5°	764.9	759.7	786.3	818.8	834.3	835.7	832.1	818.8	786.3	759.0	764.1
45°	809.2	809.2	840.9	866.8	891.9	897.8	891.1	863.1	841.7	809.9	807.7
47.5°	849.8	860.8	887.4	919.2	954.6	962.7	954.6	921.4	885.2	861.6	849.0
50°	898.5	911.8	931.0	980.4	1020.3	1031.4	1019.6	983.4	931.0	911.0	903.7
52.5°	955.3	966.4	996.7	1058.7	1088.2	1104.5	1094.9	1060.2	998.2	967.9	962.0
55°	1023.3	1012.9	1060.2	1120.0	1174.6	1196.0	1176.8	1121.5	1067.6	1012.9	1023.3
57.5°	1058.0	1046.2	1112.6	1169.5	1245.5	1273.6	1249.9	1173.9	1112.6	1049.8	1057.2
60°	1060.9	1066.1	1116.3	1209.3	1261.7	1273.6	1266.2	1216.0	1118.5	1070.5	1056.5
62.5°	1052.1	1083.8	1126.6	1222.6	1269.9	1298.7	1273.6	1224.1	1131.1	1089.0	1052.8
65°	1040.3	1072.0	1135.5	1203.4	1283.9	1312.7	1289.1	1207.1	1138.4	1072.0	1044.7
67.5°	1019.6	1008.5	1086.8	1177.6	1247.7	1264.7	1249.9	1179.0	1086.0	1007.0	1021.8
70°	953.9	944.3	1011.5	1111.1	1178.3	1201.9	1184.2	1112.6	1012.9	946.5	955.3
72.5°	856.4	859.4	924.3	1019.6	1091.9	1106.7	1097.1	1018.8	928.0	863.1	851.2
75°	742.7	750.1	812.1	898.5	964.2	973.1	963.5	902.2	811.4	754.5	739.0
77.5°	610.6	621.6	671.8	758.2	801.8	821.7	806.2	760.4	675.5	624.6	609.1
80°	473.2	476.9	512.4	581.8	639.4	652.6	637.9	584.0	516.8	478.4	467.3
82.5°	310.1	316.0	347.7	400.9	438.5	434.9	438.5	396.5	351.4	314.5	296.1
85°	138.1	149.9	171.3	196.4	220.7	227.4	220.7	199.3	171.3	146.9	144.0
87.5°	9.6	11.1	13.3	14.0	15.5	11.8	11.8	11.8	10.3	11.8	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)