

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436820

Luminaire Tested: **TT-D3-830-U-5MQ-PM-HSS**

Issue Date: 12/2/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P436820  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D3-830-U-5MQ-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
3000K, 80 CRI LEDS AND MEDIUM DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5039 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U2 - G2  
  
Input Watts (W): 47.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P436820  
 CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P436820  
CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436820  
 CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1908.0	1.3	1909.3
	% Fixture	37.9	0.0	37.9
<b>Street Side</b>	Lumens	3112.6	17.1	3129.7
	% Fixture	61.8	0.3	62.1
<b>Total</b>	Lumens	5020.6	18.5	5039.0
	% Fixture	99.6	0.4	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.4	2.2
10°-20°	329.8	6.5
20°-30°	524.8	10.4
30°-40°	672.3	13.3
40°-50°	796.5	15.8
50°-60°	872.3	17.3
60°-70°	829.2	16.5
70°-80°	660.2	13.1
80°-90°	224.3	4.5
90°-100°	11.8	0.2
100°-110°	3.9	0.1
110°-120°	0.9	0.0
120°-130°	0.5	0.0
130°-140°	0.4	0.0
140°-150°	0.4	0.0
150°-160°	0.3	0.0
160°-170°	0.2	0.0
170°-180°	0.1	0.0
0°-90°	5020.6	99.6
0°-180°	5039.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P436820  
 CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	489.8	9.7			
FM (30°-60°)	1357.0	26.9			
FH (60°-80°)	1095.0	21.7			G1/1800
FVH (80°-90°)	170.8	3.4			G2/225
BL (0°-30°)	476.1	9.4	B1/500		
BM (30°-60°)	984.2	19.5	B1/1000		
BH (60°-80°)	394.3	7.8	B1/500		G1/500
BVH (80°-90°)	53.4	1.1			G1/100
UL (90°-100°)	11.8	0.2		U2/50	
UH (100°-180°)	6.6	0.1		U1/10	

**BUG Rating: B1-U2-G2**  
 Type IV Short





REPORT NUMBER: P436820

CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	1170.9	1170.1	1170.1	1170.1	1170.1	1169.2	1170.1	1168.3	1169.2	1166.5	1166.5
5°	1173.6	1171.8	1172.7	1172.7	1172.7	1171.8	1172.7	1170.1	1170.9	1167.4	1166.5
7.5°	1174.5	1173.6	1173.6	1173.6	1173.6	1171.8	1172.7	1170.9	1170.1	1167.4	1165.6
10°	1174.5	1173.6	1173.6	1173.6	1172.7	1170.9	1171.8	1169.2	1169.2	1165.6	1163.8
12.5°	1174.5	1173.6	1174.5	1172.7	1172.7	1170.9	1170.9	1168.3	1168.3	1163.8	1162.0
15°	1173.6	1172.7	1172.7	1173.6	1172.7	1170.9	1170.9	1168.3	1167.4	1162.0	1160.3
17.5°	1172.7	1171.8	1172.7	1173.6	1174.5	1172.7	1173.6	1169.2	1167.4	1162.0	1159.4
20°	1173.6	1172.7	1173.6	1175.4	1175.4	1175.4	1175.4	1170.9	1167.4	1162.0	1157.6
22.5°	1170.9	1170.9	1170.9	1170.9	1172.7	1170.1	1170.1	1167.4	1162.9	1158.5	1154.0
25°	1164.7	1164.7	1165.6	1166.5	1166.5	1164.7	1163.8	1161.2	1157.6	1152.2	1146.9
27.5°	1157.6	1157.6	1158.5	1158.5	1160.3	1158.5	1157.6	1154.0	1150.5	1144.2	1138.0
30°	1149.6	1149.6	1149.6	1151.4	1152.2	1152.2	1151.4	1146.9	1142.5	1135.3	1127.3
32.5°	1140.7	1140.7	1143.3	1145.1	1146.0	1146.0	1146.0	1140.7	1135.3	1126.4	1114.8
35°	1133.5	1133.5	1137.1	1143.3	1146.9	1145.1	1144.2	1140.7	1132.7	1122.9	1104.2
37.5°	1138.0	1138.0	1146.0	1154.9	1162.9	1161.2	1161.2	1154.9	1144.2	1128.2	1105.1
40°	1148.7	1149.6	1162.0	1173.6	1183.4	1185.2	1185.2	1178.1	1162.0	1141.6	1109.5
42.5°	1151.4	1153.1	1165.6	1182.5	1191.4	1195.9	1195.9	1186.1	1169.2	1145.1	1107.7
45°	1151.4	1152.2	1166.5	1184.3	1198.6	1202.1	1202.1	1191.4	1170.1	1146.9	1101.5
47.5°	1151.4	1150.5	1162.9	1187.9	1202.1	1204.8	1204.8	1193.2	1172.7	1143.3	1092.6
50°	1148.7	1153.1	1171.8	1191.4	1216.4	1219.9	1219.0	1206.6	1178.1	1147.8	1085.5
52.5°	1154.9	1154.0	1179.0	1218.1	1240.4	1248.4	1249.3	1233.3	1203.9	1160.3	1081.0
55°	1180.7	1181.6	1205.7	1251.1	1284.9	1300.1	1298.3	1277.8	1235.9	1185.2	1093.5
57.5°	1189.6	1198.6	1233.3	1272.5	1324.1	1337.5	1337.5	1312.5	1261.8	1204.8	1102.4
60°	1171.8	1175.4	1218.1	1284.9	1332.1	1334.8	1335.7	1317.9	1264.4	1194.1	1084.6
62.5°	1167.4	1174.5	1207.5	1282.3	1312.5	1332.1	1331.2	1307.2	1261.8	1186.1	1078.3
65°	1147.8	1153.1	1211.0	1266.2	1333.0	1352.6	1348.1	1320.5	1250.2	1177.2	1058.7
67.5°	1107.7	1113.1	1166.5	1244.0	1304.5	1323.2	1327.7	1295.6	1222.6	1135.3	1016.9
70°	1040.9	1049.0	1103.3	1179.0	1243.1	1253.8	1252.0	1232.4	1159.4	1065.9	955.5
72.5°	947.4	959.9	1028.5	1100.6	1155.8	1171.8	1164.7	1142.5	1082.8	982.2	871.8
75°	848.6	860.2	914.5	995.5	1053.4	1064.1	1058.7	1032.0	971.5	872.6	772.9
77.5°	740.9	750.7	797.0	879.8	922.5	931.4	934.1	898.5	841.5	752.4	663.4
80°	595.7	600.2	662.5	716.8	754.2	772.0	770.2	743.5	686.5	612.6	523.6
82.5°	439.9	443.4	491.5	537.8	571.7	587.7	578.8	552.1	506.7	443.4	375.8
85°	269.8	263.6	302.8	337.5	358.0	368.6	359.7	344.6	304.5	254.7	207.5
87.5°	97.1	91.7	109.5	114.9	138.0	134.5	142.5	114.9	92.6	65.9	46.3
90°	42.7	42.7	41.9	40.1	36.5	32.9	32.1	26.7	19.6	12.5	4.5
92.5°	39.2	39.2	38.3	36.5	32.9	29.4	29.4	24.0	17.8	11.6	4.5
95°	32.9	32.9	32.1	30.3	27.6	24.9	24.9	19.6	15.1	9.8	3.6
97.5°	25.8	25.8	24.9	24.0	21.4	19.6	19.6	16.0	11.6	7.1	2.7
100°	19.6	19.6	18.7	17.8	16.9	15.1	14.2	11.6	8.9	5.3	1.8
102.5°	14.2	14.2	14.2	13.4	11.6	10.7	10.7	8.9	6.2	4.5	1.8
105°	9.8	9.8	9.8	8.9	8.0	7.1	7.1	6.2	4.5	2.7	0.9
107.5°	6.2	6.2	6.2	6.2	5.3	4.5	4.5	3.6	2.7	1.8	0.9
110°	3.6	2.7	3.6	3.6	3.6	2.7	2.7	1.8	1.8	0.9	0.9



REPORT NUMBER: P436820  
 CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
112.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.9	0.9	0.9	0.9
115°	0.9	0.9	0.9	1.8	1.8	0.9	0.9	0.9	0.9	0.9	0.9
117.5°	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
120°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
122.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
125°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
127.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
130°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
132.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
135°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
137.5°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
140°	0.0	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
142.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
145°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
147.5°	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	0.9	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
155°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
157.5°	0.9	0.9	0.9	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
160°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
162.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
165°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
167.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
170°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
172.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
175°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
177.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
180°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9





REPORT NUMBER: P436820

CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5	1166.5
2.5°	1166.5	1165.6	1164.7	1165.6	1164.7	1164.7	1163.8	1163.8	1162.9	1162.9	1162.0
5°	1166.5	1165.6	1164.7	1165.6	1163.8	1164.7	1164.7	1163.8	1162.9	1162.0	1161.2
7.5°	1165.6	1165.6	1163.8	1164.7	1162.9	1162.9	1162.0	1162.0	1161.2	1161.2	1160.3
10°	1163.8	1162.9	1162.9	1162.9	1161.2	1161.2	1160.3	1159.4	1159.4	1158.5	1157.6
12.5°	1162.0	1161.2	1160.3	1160.3	1159.4	1158.5	1157.6	1157.6	1156.7	1155.8	1154.9
15°	1159.4	1158.5	1158.5	1158.5	1157.6	1157.6	1156.7	1155.8	1154.0	1153.1	1152.2
17.5°	1158.5	1157.6	1158.5	1158.5	1157.6	1158.5	1156.7	1154.9	1153.1	1152.2	1151.4
20°	1157.6	1157.6	1157.6	1156.7	1155.8	1154.9	1154.0	1153.1	1152.2	1151.4	1150.5
22.5°	1153.1	1152.2	1150.5	1145.1	1138.9	1134.4	1133.5	1135.3	1135.3	1135.3	1132.7
25°	1145.1	1142.5	1135.3	1125.5	1114.8	1107.7	1103.3	1103.3	1102.4	1100.6	1099.7
27.5°	1135.3	1130.0	1117.5	1105.1	1089.9	1081.0	1070.3	1064.1	1061.4	1060.5	1058.7
30°	1122.0	1114.0	1097.9	1081.9	1063.2	1050.7	1033.8	1023.1	1016.9	1014.2	1012.4
32.5°	1105.9	1097.9	1079.2	1059.6	1037.4	1019.6	998.2	981.3	969.7	964.4	961.7
35°	1095.3	1083.7	1062.3	1039.2	1016.9	991.1	965.3	942.1	924.3	918.1	914.5
37.5°	1090.8	1080.1	1057.0	1033.8	1008.9	977.7	947.4	914.5	890.5	879.8	876.2
40°	1093.5	1080.1	1054.3	1029.4	1000.0	965.3	925.2	884.2	853.1	837.9	834.4
42.5°	1087.2	1072.1	1041.8	1015.1	978.6	939.4	890.5	843.3	801.4	788.9	783.6
45°	1076.6	1057.9	1024.9	991.1	952.8	904.7	853.9	793.4	743.5	728.4	723.9
47.5°	1065.9	1040.0	1000.9	969.7	923.4	867.3	807.6	740.0	677.6	662.5	659.8
50°	1049.8	1025.8	984.0	947.4	900.2	835.2	767.6	683.0	612.6	586.8	579.7
52.5°	1042.7	1011.6	971.5	943.0	886.0	812.1	726.6	635.8	534.3	502.2	495.1
55°	1049.8	1010.7	967.9	940.3	874.4	782.7	677.6	561.9	444.3	410.5	400.7
57.5°	1037.4	1003.5	960.8	929.6	844.1	722.2	606.4	457.7	335.7	292.1	288.5
60°	1021.3	973.3	933.2	904.7	780.9	608.2	471.9	325.9	202.1	164.7	157.6
62.5°	1015.1	965.3	918.9	884.2	696.3	447.0	287.6	164.7	83.7	58.8	53.4
65°	995.5	951.0	918.1	869.1	608.2	276.0	123.8	49.0	3.6	2.7	2.7
67.5°	958.1	912.7	890.5	862.0	599.3	263.6	112.2	44.5	1.8	0.0	0.0
70°	894.0	858.4	843.3	828.1	573.5	244.0	102.4	40.1	0.9	0.0	0.0
72.5°	809.4	785.4	782.7	780.9	536.1	225.3	91.7	35.6	0.9	0.0	0.0
75°	724.8	695.4	699.9	710.6	489.7	199.5	79.3	31.2	0.9	0.0	0.0
77.5°	618.0	596.6	607.3	625.1	429.2	169.2	65.0	24.9	0.9	0.0	0.0
80°	486.2	471.9	496.0	512.0	350.8	134.5	49.0	17.8	0.0	0.0	0.0
82.5°	345.5	337.5	359.7	380.2	260.9	95.3	33.8	11.6	0.0	0.0	0.0
85°	186.1	181.7	203.0	225.3	156.7	54.3	16.9	5.3	0.0	0.0	0.0
87.5°	46.3	42.7	43.6	52.5	38.3	11.6	2.7	0.9	0.0	0.0	0.0
90°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
102.5°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
110°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436820  
 CATALOG NUMBER: TT-D3-830-U-5MQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
115°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
117.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
122.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
125°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
127.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
130°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
135°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
147.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
162.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
165°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
167.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
170°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
172.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
175°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
177.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
180°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9

(END OF REPORT)