

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436766

Luminaire Tested: **TT-D2-735-U-RW-PM-HSS**

Issue Date: 12/2/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P436766  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D2-735-U-RW-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
3500K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3145 lumens  
Efficiency: N/A  
Efficacy: 80.2 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U2 - G2


Input Watts (W): 39.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P436766  
CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	993.1	1.3	994.4
	% Fixture	31.6	0.0	31.6
<b>Street Side</b>	Lumens	2136.7	13.9	2150.6
	% Fixture	67.9	0.4	68.4
<b>Total</b>	Lumens	3129.9	15.2	3145.0
	% Fixture	99.5	0.5	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	9.0	0.3
10°-20°	33.9	1.1
20°-30°	78.1	2.5
30°-40°	167.4	5.3
40°-50°	358.6	11.4
50°-60°	677.2	21.5
60°-70°	841.6	26.8
70°-80°	720.5	22.9
80°-90°	243.7	7.7
90°-100°	10.5	0.3
100°-110°	3.0	0.1
110°-120°	0.7	0.0
120°-130°	0.4	0.0
130°-140°	0.2	0.0
140°-150°	0.2	0.0
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3129.9	99.5
0°-180°	3145.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	64.3	2.0			
FM (30°-60°)	719.7	22.9			
FH (60°-80°)	1164.2	37.0			G1/1800
FVH (80°-90°)	188.5	6.0			G2/225
BL (0°-30°)	56.7	1.8	B0/110		
BM (30°-60°)	483.4	15.4	B1/1000		
BH (60°-80°)	397.9	12.7	B1/500		G1/500
BVH (80°-90°)	55.2	1.8			G1/100
UL (90°-100°)	10.5	0.3		U2/50	
UH (100°-180°)	4.6	0.1		U1/10	

**BUG Rating: B1-U2-G2**

Type IV Short





REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4
2.5°	90.1	90.1	90.1	89.3	89.3	89.3	88.6	87.8	87.0	87.0	87.0
5°	94.8	94.8	94.8	94.8	94.0	93.3	92.5	91.7	90.9	90.9	90.1
7.5°	101.1	100.3	101.1	100.3	100.3	99.5	98.7	98.0	96.4	96.4	95.6
10°	107.4	107.4	107.4	107.4	107.4	106.6	105.8	105.0	104.2	103.4	102.7
12.5°	115.2	115.2	115.2	114.4	115.2	114.4	113.6	113.6	112.8	111.3	111.3
15°	123.0	123.0	123.0	123.0	123.8	123.8	123.8	123.0	123.0	122.3	121.5
17.5°	132.4	131.7	132.4	132.4	133.2	134.0	134.8	135.6	135.6	134.8	134.8
20°	142.6	141.8	142.6	142.6	144.2	145.8	148.1	149.7	150.5	148.9	148.9
22.5°	153.6	152.8	154.4	154.4	156.7	159.1	163.0	164.6	166.9	166.1	166.1
25°	166.9	166.1	166.9	167.7	170.8	174.8	179.5	183.4	185.7	185.7	186.5
27.5°	181.8	181.8	182.6	183.4	186.5	192.8	199.8	206.9	212.4	211.6	212.4
30°	202.2	202.2	203.8	204.5	208.5	215.5	224.9	234.3	242.2	242.2	243.7
32.5°	224.9	224.1	226.5	227.3	231.2	240.6	253.9	268.8	279.0	279.0	280.6
35°	252.3	251.6	253.9	253.9	258.6	271.9	289.2	309.6	326.8	327.6	329.9
37.5°	286.8	285.3	285.3	287.6	293.1	310.3	333.8	362.1	380.1	381.7	385.6
40°	327.6	326.8	328.4	327.6	334.6	355.8	385.6	418.5	439.6	443.6	448.3
42.5°	377.7	379.3	376.9	376.9	385.6	409.9	445.1	483.5	521.9	526.6	529.0
45°	438.9	442.0	438.9	438.1	445.9	474.1	522.7	590.1	634.8	650.5	655.2
47.5°	512.5	514.1	510.2	508.6	517.2	553.3	616.0	691.2	743.7	755.5	768.0
50°	594.8	592.5	589.3	587.0	603.4	648.1	721.0	798.6	888.7	890.3	895.0
52.5°	679.4	672.4	673.2	672.4	695.1	743.7	840.9	972.5	1109.7	1137.9	1141.0
55°	764.1	755.5	754.7	762.5	794.6	864.4	986.6	1157.5	1268.8	1286.0	1283.7
57.5°	848.7	844.8	843.2	850.3	897.3	980.4	1118.3	1262.5	1357.3	1355.8	1339.3
60°	936.5	939.6	934.1	947.5	996.1	1079.1	1179.4	1319.7	1407.5	1400.4	1384.0
62.5°	1026.6	1034.5	1029.0	1030.5	1061.9	1123.0	1221.8	1384.8	1506.2	1516.4	1497.6
65°	1116.0	1121.4	1112.8	1088.5	1105.8	1163.0	1304.0	1460.8	1553.2	1562.6	1548.5
67.5°	1191.2	1196.7	1166.9	1128.5	1130.8	1172.4	1296.2	1445.9	1528.2	1521.9	1499.2
70°	1255.4	1245.3	1196.7	1130.8	1103.4	1123.0	1239.8	1372.2	1456.1	1452.9	1426.3
72.5°	1276.6	1263.3	1181.0	1079.1	1025.0	1032.1	1145.7	1264.1	1332.2	1337.7	1305.6
75°	1242.9	1220.2	1107.3	979.6	909.8	914.5	1011.7	1120.7	1175.5	1169.2	1144.2
77.5°	1121.4	1098.7	976.5	840.1	771.9	779.0	855.8	941.2	986.6	984.3	967.1
80°	931.0	910.6	803.3	676.3	614.4	618.3	677.1	744.5	779.8	787.6	778.2
82.5°	688.1	674.0	597.9	495.3	445.1	444.3	489.0	540.7	575.2	591.7	585.4
85°	425.5	418.5	376.2	309.6	274.3	273.5	300.1	338.5	369.9	391.8	377.7
87.5°	169.3	166.9	154.4	124.6	108.9	103.4	97.2	121.5	123.8	146.5	145.8
90°	41.5	40.8	40.0	37.6	33.7	29.0	23.5	17.2	11.0	8.6	4.7
92.5°	36.8	36.8	36.0	33.7	30.6	25.9	21.2	15.7	10.2	7.8	3.9
95°	29.8	29.8	29.0	27.4	24.3	21.2	16.5	12.5	7.8	6.3	3.1
97.5°	22.7	21.9	21.9	20.4	18.8	15.7	12.5	9.4	6.3	4.7	2.4
100°	16.5	16.5	15.7	14.9	13.3	11.8	9.4	7.1	3.9	3.1	1.6
102.5°	11.8	11.0	11.0	11.0	9.4	7.8	6.3	4.7	3.1	2.4	0.8
105°	7.8	7.1	7.1	7.1	6.3	5.5	3.9	3.1	1.6	1.6	0.8
107.5°	4.7	4.7	4.7	4.7	3.9	3.1	2.4	1.6	0.8	0.8	0.8
110°	2.4	2.4	2.4	3.1	2.4	2.4	1.6	0.8	0.8	0.8	0.8



REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
112.5°	1.6	1.6	1.6	1.6	1.6	1.6	0.8	0.8	0.8	0.8	0.8
115°	0.8	0.8	0.8	1.6	1.6	0.8	0.8	0.0	0.0	0.8	0.8
117.5°	0.0	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
120°	0.0	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
122.5°	0.0	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
125°	0.0	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
127.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
130°	0.0	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
132.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.8
135°	0.0	0.0	0.0	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.8	0.0	0.8	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4
2.5°	86.2	86.2	86.2	85.4	85.4	85.4	84.6	84.6	83.9	83.9	83.9
5°	89.3	89.3	88.6	88.6	87.8	87.0	87.0	86.2	86.2	85.4	85.4
7.5°	94.8	94.8	94.0	93.3	91.7	90.9	90.1	89.3	89.3	88.6	88.6
10°	101.9	101.9	100.3	98.7	97.2	95.6	94.8	93.3	92.5	92.5	92.5
12.5°	110.5	109.7	108.1	105.8	104.2	101.9	100.3	98.7	97.2	97.2	97.2
15°	120.7	120.7	117.6	115.2	112.1	108.9	106.6	104.2	102.7	101.9	101.9
17.5°	133.2	133.2	129.3	125.4	121.5	117.6	114.4	111.3	109.7	108.9	108.9
20°	147.3	147.3	143.4	138.7	133.2	127.7	123.0	119.1	116.8	116.0	116.0
22.5°	164.6	164.6	159.1	152.8	145.8	137.9	131.7	127.0	124.6	123.0	123.0
25°	184.2	182.6	177.1	169.3	159.1	149.7	141.1	136.4	133.2	130.9	131.7
27.5°	210.8	208.5	201.4	188.1	175.5	163.0	152.8	146.5	142.6	141.1	141.8
30°	241.4	239.0	228.8	213.9	195.1	178.7	166.1	159.1	155.2	152.8	153.6
32.5°	278.2	275.1	262.5	242.2	220.2	196.7	181.0	172.4	168.5	166.1	165.4
35°	326.8	322.9	307.2	279.0	248.4	220.2	198.3	187.3	183.4	181.0	181.8
37.5°	381.7	376.2	355.0	320.5	282.1	246.1	221.0	206.9	202.2	198.3	198.3
40°	444.3	438.1	410.6	365.2	319.0	274.3	242.2	226.5	221.0	221.0	221.0
42.5°	522.7	516.4	485.1	418.5	357.4	304.8	266.4	248.4	242.9	244.5	244.5
45°	644.2	635.6	585.4	497.6	407.5	336.2	291.5	271.2	267.2	271.2	271.2
47.5°	755.5	744.5	670.8	571.3	456.9	367.5	316.6	293.1	291.5	300.1	300.1
50°	880.1	866.0	788.4	630.9	496.9	402.0	339.3	311.1	311.9	324.4	328.4
52.5°	1121.4	1106.5	972.5	739.0	540.0	414.6	348.7	315.0	315.0	329.1	334.6
55°	1264.9	1234.3	1059.5	809.5	558.0	429.5	344.8	299.4	297.8	313.5	318.2
57.5°	1311.9	1280.5	1077.6	789.2	546.2	410.6	322.1	257.0	253.9	274.3	272.7
60°	1350.3	1308.7	1048.6	721.0	479.6	370.7	278.2	191.2	177.9	195.9	195.1
62.5°	1458.4	1413.8	1050.1	641.0	401.2	309.6	209.2	107.4	79.9	94.0	87.8
65°	1512.5	1468.6	1066.6	603.4	361.3	256.3	149.7	43.9	3.1	3.1	1.6
67.5°	1466.3	1427.1	1045.4	594.0	355.8	254.7	152.0	43.1	0.0	0.0	0.0
70°	1398.9	1361.2	996.8	561.1	337.8	245.3	148.9	43.1	0.0	0.0	0.0
72.5°	1280.5	1242.1	913.0	514.1	310.3	224.9	137.9	40.8	0.0	0.0	0.0
75°	1124.6	1095.6	806.4	453.0	273.5	198.3	122.3	36.0	0.0	0.0	0.0
77.5°	952.2	917.7	676.3	376.9	228.8	164.6	103.4	29.8	0.0	0.0	0.0
80°	764.1	739.0	532.9	295.4	177.1	128.5	80.7	22.7	0.0	0.0	0.0
82.5°	568.2	547.0	394.2	211.6	126.2	89.3	55.6	14.9	0.0	0.0	0.0
85°	373.0	367.5	253.1	128.5	75.2	49.4	29.8	7.1	0.0	0.0	0.0
87.5°	134.8	139.5	92.5	36.8	20.4	8.6	3.9	0.8	0.0	0.0	0.0
90°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
92.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
95°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
97.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
100°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
102.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
105°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
107.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
110°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436766  
 CATALOG NUMBER: TT-D2-735-U-RW-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
115°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
117.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
120°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
122.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
125°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
127.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
130°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
132.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
135°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.8	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.8	0.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)