

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436800

Luminaire Tested: **TT-D3-735-U-5MQ-PM-HSS**

Issue Date: 12/2/2020

Test Information

Test Method: LM-79-08
Report Number: P436800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-1)
Test Lab: INNOVATION CENTER
Issue Date: 12/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-D3-735-U-5MQ-PM-HSS
Description: TOPTIER LED SITE LUMINAIRE
3500K, 70 CRI LEDS AND MEDIUM DISTRIBUTION WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5348.9 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U2 - G2


Input Watts (W): 47.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P436800
 CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2 fc
 Type IV - Short - N/A

REPORT NUMBER: P436800
CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P436800

CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2025.4	1.3	2026.7
	% Fixture	37.9	0.0	37.9
Street Side	Lumens	3304.1	18.1	3322.1
	% Fixture	61.8	0.3	62.1
Total	Lumens	5329.4	19.4	5348.9
	% Fixture	99.6	0.4	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	2.2
10°-20°	350.0	6.5
20°-30°	557.0	10.4
30°-40°	713.7	13.3
40°-50°	845.5	15.8
50°-60°	926.0	17.3
60°-70°	880.2	16.5
70°-80°	700.8	13.1
80°-90°	238.1	4.5
90°-100°	12.5	0.2
100°-110°	4.1	0.1
110°-120°	0.9	0.0
120°-130°	0.5	0.0
130°-140°	0.4	0.0
140°-150°	0.4	0.0
150°-160°	0.3	0.0
160°-170°	0.2	0.0
170°-180°	0.1	0.0
0°-90°	5329.4	99.6
0°-180°	5348.9	100.0

Coefficient of Utilization



REPORT NUMBER: P436800


CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	519.9	9.7			
FM	(30°-60°)	1440.4	26.9			
FH	(60°-80°)	1162.4	21.7			G1/1800
FVH	(80°-90°)	181.3	3.4			G2/225
BL	(0°-30°)	505.4	9.4	B2/1000		
BM	(30°-60°)	1044.7	19.5	B2/2500		
BH	(60°-80°)	418.5	7.8	B1/500		G1/500
BVH	(80°-90°)	56.7	1.1			G1/100
UL	(90°-100°)	12.5	0.2		U2/50	
UH	(100°-180°)	6.9	0.1		U1/10	

BUG Rating: B2-U2-G2

Type IV Short



REPORT NUMBER: P436800

CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1243.0	1242.0	1242.0	1242.0	1242.0	1241.1	1242.0	1240.1	1241.1	1238.3	1238.3
5°	1245.8	1243.9	1244.9	1244.9	1244.9	1243.9	1244.9	1242.0	1243.0	1239.2	1238.3
7.5°	1246.8	1245.8	1245.8	1245.8	1245.8	1243.9	1244.9	1243.0	1242.0	1239.2	1237.3
10°	1246.8	1245.8	1245.8	1245.8	1244.9	1243.0	1243.9	1241.1	1241.1	1237.3	1235.4
12.5°	1246.8	1245.8	1246.8	1244.9	1244.9	1243.0	1243.0	1240.1	1240.1	1235.4	1233.5
15°	1245.8	1244.9	1244.9	1245.8	1244.9	1243.0	1243.0	1240.1	1239.2	1233.5	1231.6
17.5°	1244.9	1243.9	1244.9	1245.8	1246.8	1244.9	1245.8	1241.1	1239.2	1233.5	1230.7
20°	1245.8	1244.9	1245.8	1247.7	1247.7	1247.7	1247.7	1243.0	1239.2	1233.5	1228.8
22.5°	1243.0	1243.0	1243.0	1243.0	1244.9	1242.0	1242.0	1239.2	1234.5	1229.7	1225.0
25°	1236.4	1236.4	1237.3	1238.3	1238.3	1236.4	1235.4	1232.6	1228.8	1223.1	1217.5
27.5°	1228.8	1228.8	1229.7	1229.7	1231.6	1229.7	1228.8	1225.0	1221.2	1214.6	1208.0
30°	1220.3	1220.3	1220.3	1222.2	1223.1	1223.1	1222.2	1217.5	1212.7	1205.2	1196.7
32.5°	1210.8	1210.8	1213.7	1215.6	1216.5	1216.5	1216.5	1210.8	1205.2	1195.7	1183.4
35°	1203.3	1203.3	1207.1	1213.7	1217.5	1215.6	1214.6	1210.8	1202.3	1191.9	1172.1
37.5°	1208.0	1208.0	1216.5	1226.0	1234.5	1232.6	1232.6	1226.0	1214.6	1197.6	1173.0
40°	1219.4	1220.3	1233.5	1245.8	1256.2	1258.1	1258.1	1250.5	1233.5	1211.8	1177.8
42.5°	1222.2	1224.1	1237.3	1255.3	1264.7	1269.4	1269.4	1259.1	1241.1	1215.6	1175.9
45°	1222.2	1223.1	1238.3	1257.2	1272.3	1276.1	1276.1	1264.7	1242.0	1217.5	1169.3
47.5°	1222.2	1221.2	1234.5	1260.9	1276.1	1278.9	1278.9	1266.6	1244.9	1213.7	1159.8
50°	1219.4	1224.1	1243.9	1264.7	1291.2	1295.0	1294.0	1280.8	1250.5	1218.4	1152.2
52.5°	1226.0	1225.0	1251.5	1293.1	1316.7	1325.2	1326.2	1309.1	1278.0	1231.6	1147.5
55°	1253.4	1254.3	1279.8	1328.1	1364.0	1380.0	1378.2	1356.4	1312.0	1258.1	1160.7
57.5°	1262.8	1272.3	1309.1	1350.7	1405.6	1419.7	1419.7	1393.3	1339.4	1278.9	1170.2
60°	1243.9	1247.7	1293.1	1364.0	1414.1	1416.9	1417.9	1398.9	1342.2	1267.6	1151.3
62.5°	1239.2	1246.8	1281.7	1361.1	1393.3	1414.1	1413.1	1387.6	1339.4	1259.1	1144.7
65°	1218.4	1224.1	1285.5	1344.1	1415.0	1435.8	1431.1	1401.8	1327.1	1249.6	1123.9
67.5°	1175.9	1181.5	1238.3	1320.5	1384.8	1404.6	1409.3	1375.3	1297.8	1205.2	1079.5
70°	1105.0	1113.5	1171.1	1251.5	1319.5	1330.9	1329.0	1308.2	1230.7	1131.4	1014.2
72.5°	1005.7	1019.0	1091.7	1168.3	1226.9	1243.9	1236.4	1212.7	1149.4	1042.6	925.4
75°	900.8	913.1	970.8	1056.8	1118.2	1129.6	1123.9	1095.5	1031.3	926.3	820.5
77.5°	786.4	796.8	846.0	933.9	979.3	988.7	991.6	953.7	893.2	798.7	704.2
80°	632.4	637.1	703.3	760.9	800.6	819.5	817.6	789.3	728.8	650.3	555.8
82.5°	466.9	470.7	521.8	570.9	606.8	623.9	614.4	586.0	537.8	470.7	398.9
85°	286.4	279.8	321.4	358.2	380.0	391.3	381.9	365.8	323.3	270.3	220.2
87.5°	103.0	97.4	116.3	121.9	146.5	142.7	151.2	121.9	98.3	69.9	49.2
90°	45.4	45.4	44.4	42.5	38.8	35.0	34.0	28.4	20.8	13.2	4.7
92.5°	41.6	41.6	40.6	38.8	35.0	31.2	31.2	25.5	18.9	12.3	4.7
95°	35.0	35.0	34.0	32.1	29.3	26.5	26.5	20.8	16.1	10.4	3.8
97.5°	27.4	27.4	26.5	25.5	22.7	20.8	20.8	17.0	12.3	7.6	2.8
100°	20.8	20.8	19.8	18.9	18.0	16.1	15.1	12.3	9.5	5.7	1.9
102.5°	15.1	15.1	15.1	14.2	12.3	11.3	11.3	9.5	6.6	4.7	1.9
105°	10.4	10.4	10.4	9.5	8.5	7.6	7.6	6.6	4.7	2.8	0.9
107.5°	6.6	6.6	6.6	6.6	5.7	4.7	4.7	3.8	2.8	1.9	0.9
110°	3.8	2.8	3.8	3.8	3.8	2.8	2.8	1.9	1.9	0.9	0.9

REPORT NUMBER: P436800

CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
112.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	0.9	0.9	0.9	0.9
115°	0.9	0.9	0.9	1.9	1.9	0.9	0.9	0.9	0.9	0.9	0.9
117.5°	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
120°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
122.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
125°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
127.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
130°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
132.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
135°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
137.5°	0.0	0.0	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
140°	0.0	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
142.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
145°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
147.5°	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	0.9	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
155°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
157.5°	0.9	0.9	0.9	0.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
160°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
162.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
165°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
167.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
170°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
172.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
175°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
177.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
180°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9

REPORT NUMBER: P436800

CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3	1238.3
2.5°	1238.3	1237.3	1236.4	1237.3	1236.4	1236.4	1235.4	1235.4	1234.5	1234.5	1233.5
5°	1238.3	1237.3	1236.4	1237.3	1235.4	1236.4	1236.4	1235.4	1234.5	1233.5	1232.6
7.5°	1237.3	1237.3	1235.4	1236.4	1234.5	1234.5	1233.5	1233.5	1232.6	1232.6	1231.6
10°	1235.4	1234.5	1234.5	1234.5	1232.6	1232.6	1231.6	1230.7	1230.7	1229.7	1228.8
12.5°	1233.5	1232.6	1231.6	1231.6	1230.7	1229.7	1228.8	1228.8	1227.9	1226.9	1226.0
15°	1230.7	1229.7	1229.7	1229.7	1228.8	1228.8	1227.9	1226.9	1225.0	1224.1	1223.1
17.5°	1229.7	1228.8	1229.7	1229.7	1228.8	1229.7	1227.9	1226.0	1224.1	1223.1	1222.2
20°	1228.8	1228.8	1228.8	1227.9	1226.9	1226.0	1225.0	1224.1	1223.1	1222.2	1221.2
22.5°	1224.1	1223.1	1221.2	1215.6	1209.0	1204.2	1203.3	1205.2	1205.2	1205.2	1202.3
25°	1215.6	1212.7	1205.2	1194.8	1183.4	1175.9	1171.1	1171.1	1170.2	1168.3	1167.4
27.5°	1205.2	1199.5	1186.3	1173.0	1157.0	1147.5	1136.2	1129.6	1126.7	1125.8	1123.9
30°	1191.0	1182.5	1165.5	1148.5	1128.6	1115.4	1097.4	1086.1	1079.5	1076.6	1074.7
32.5°	1174.0	1165.5	1145.6	1124.8	1101.2	1082.3	1059.6	1041.6	1029.4	1023.7	1020.9
35°	1162.6	1150.3	1127.7	1103.1	1079.5	1052.0	1024.6	1000.1	981.2	974.5	970.8
37.5°	1157.9	1146.6	1122.0	1097.4	1071.0	1037.9	1005.7	970.8	945.2	933.9	930.1
40°	1160.7	1146.6	1119.2	1092.7	1061.5	1024.6	982.1	938.6	905.5	889.5	885.7
42.5°	1154.1	1138.1	1105.9	1077.6	1038.8	997.2	945.2	895.1	850.7	837.5	831.8
45°	1142.8	1122.9	1088.0	1052.0	1011.4	960.4	906.5	842.2	789.3	773.2	768.5
47.5°	1131.4	1104.0	1062.4	1029.4	980.2	920.7	857.3	785.5	719.3	703.3	700.4
50°	1114.4	1088.9	1044.5	1005.7	955.6	886.6	814.8	725.0	650.3	622.9	615.3
52.5°	1106.9	1073.8	1031.3	1001.0	940.5	862.1	771.3	674.9	567.1	533.1	525.6
55°	1114.4	1072.8	1027.5	998.2	928.2	830.9	719.3	596.4	471.7	435.8	425.4
57.5°	1101.2	1065.3	1019.9	986.8	896.1	766.6	643.7	485.9	356.4	310.0	306.3
60°	1084.2	1033.1	990.6	960.4	829.0	645.6	501.0	346.0	214.6	174.9	167.3
62.5°	1077.6	1024.6	975.5	938.6	739.2	474.5	305.3	174.9	88.9	62.4	56.7
65°	1056.8	1009.5	974.5	922.5	645.6	293.0	131.4	52.0	3.8	2.8	2.8
67.5°	1017.1	968.9	945.2	915.0	636.1	279.8	119.1	47.3	1.9	0.0	0.0
70°	949.0	911.2	895.1	879.1	608.7	259.0	108.7	42.5	0.9	0.0	0.0
72.5°	859.2	833.7	830.9	829.0	569.0	239.1	97.4	37.8	0.9	0.0	0.0
75°	769.4	738.2	743.0	754.3	519.9	211.7	84.1	33.1	0.9	0.0	0.0
77.5°	656.0	633.3	644.6	663.6	455.6	179.6	69.0	26.5	0.9	0.0	0.0
80°	516.1	501.0	526.5	543.5	372.4	142.7	52.0	18.9	0.0	0.0	0.0
82.5°	366.8	358.2	381.9	403.6	277.0	101.1	35.9	12.3	0.0	0.0	0.0
85°	197.6	192.8	215.5	239.1	166.4	57.7	18.0	5.7	0.0	0.0	0.0
87.5°	49.2	45.4	46.3	55.8	40.6	12.3	2.8	0.9	0.0	0.0	0.0
90°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
102.5°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
110°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P436800

CATALOG NUMBER: TT-D3-735-U-5MQ-PM-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
115°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
117.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
122.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
125°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
127.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
130°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
135°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
147.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
162.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
165°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
167.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
170°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
172.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
175°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
177.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
180°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2411-284-1

Test Date: 11/15/2024

Luminaire Tested: TTN-D0-735-U-WQ


Data in this report applies to families of products including TT-D* and TTN-D*

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2411-284-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **TTN-D0-735-U-WQ**
 Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE. 3500K, 70 CRI LEDS AND WIDE DISTRIBUTION

Spectral Parameters

CCT (K):	3405	CRI (Ra):	73.9		
CIE u':	0.2365	R1:	71.3	R9:	-18.0
CIE v':	0.5180	R2:	80.3	R10:	53.1
Duv:	0.0036	R3:	87.8	R11:	68.6
CIE x:	0.4148	R4:	73.2	R12:	42.6
CIE y:	0.4038	R5:	69.8	R13:	72.5
CIE z:	0.1814	R6:	71.8	R14:	92.7
Peak Wavelength (nm):	596	R7:	82.8	R15:	64.3
Dominant Wavelength (nm):	579	R8:	54.1		
Purity:	45.70672				
Rf:	76.6				
Rg:	95.4				



Test Conditions


Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.9

REPORT NUMBER: SP1-2411-284-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2411-284-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2411-284-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	846	NR	750	28	NR	880	1	NR
365	0	NR	495	160	NR	625	793	NR	755	25	NR	885	0	NR
370	0	NR	500	225	NR	630	739	NR	760	22	NR	890	0	NR
375	0	NR	505	308	NR	635	681	NR	765	19	NR	895	0	NR
380	0	NR	510	392	NR	640	623	NR	770	16	NR	900	0	NR
385	0	NR	515	474	NR	645	563	NR	775	14	NR	905	0	NR
390	0	NR	520	545	NR	650	506	NR	780	12	NR	910	0	NR
395	1	NR	525	603	NR	655	451	NR	785	10	NR	915	0	NR
400	3	NR	530	649	NR	660	399	NR	790	9	NR	920	0	NR
405	5	NR	535	687	NR	665	352	NR	795	8	NR	925	0	NR
410	11	NR	540	721	NR	670	307	NR	800	6	NR	930	0	NR
415	21	NR	545	751	NR	675	268	NR	805	6	NR	935	0	NR
420	43	NR	550	779	NR	680	234	NR	810	5	NR	940	0	NR
425	88	NR	555	811	NR	685	203	NR	815	4	NR	945	0	NR
430	163	NR	560	843	NR	690	176	NR	820	4	NR	950	0	NR
435	288	NR	565	873	NR	695	152	NR	825	3	NR	955	0	NR
440	416	NR	570	907	NR	700	131	NR	830	3	NR	960	0	NR
445	566	NR	575	938	NR	705	112	NR	835	3	NR	965	0	NR
450	810	NR	580	965	NR	710	96	NR	840	2	NR	970	0	NR
455	669	NR	585	986	NR	715	81	NR	845	2	NR	975	0	NR
460	338	NR	590	997	NR	720	69	NR	850	2	NR	980	0	NR
465	246	NR	595	997	NR	725	58	NR	855	1	NR	985	0	NR
470	182	NR	600	991	NR	730	49	NR	860	1	NR	990	0	NR
475	115	NR	605	968	NR	735	42	NR	865	1	NR	995	0	NR
480	97	NR	610	939	NR	740	37	NR	870	1	NR	1000	0	NR
485	103	NR	615	896	NR	745	32	NR	875	1	NR			

REPORT NUMBER: SP1-2411-284-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.33

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	846	NR	750	28	NR	880	1	NR
365	0	NR	495	160	NR	625	793	NR	755	25	NR	885	0	NR
370	0	NR	500	225	NR	630	739	NR	760	22	NR	890	0	NR
375	0	NR	505	308	NR	635	681	NR	765	19	NR	895	0	NR
380	0	NR	510	392	NR	640	623	NR	770	16	NR	900	0	NR
385	0	NR	515	474	NR	645	563	NR	775	14	NR	905	0	NR
390	0	NR	520	545	NR	650	506	NR	780	12	NR	910	0	NR
395	1	NR	525	603	NR	655	451	NR	785	10	NR	915	0	NR
400	3	NR	530	649	NR	660	399	NR	790	9	NR	920	0	NR
405	5	NR	535	687	NR	665	352	NR	795	8	NR	925	0	NR
410	11	NR	540	721	NR	670	307	NR	800	6	NR	930	0	NR
415	21	NR	545	751	NR	675	268	NR	805	6	NR	935	0	NR
420	43	NR	550	779	NR	680	234	NR	810	5	NR	940	0	NR
425	88	NR	555	811	NR	685	203	NR	815	4	NR	945	0	NR
430	163	NR	560	843	NR	690	176	NR	820	4	NR	950	0	NR
435	288	NR	565	873	NR	695	152	NR	825	3	NR	955	0	NR
440	416	NR	570	907	NR	700	131	NR	830	3	NR	960	0	NR
445	566	NR	575	938	NR	705	112	NR	835	3	NR	965	0	NR
450	810	NR	580	965	NR	710	96	NR	840	2	NR	970	0	NR
455	669	NR	585	986	NR	715	81	NR	845	2	NR	975	0	NR
460	338	NR	590	997	NR	720	69	NR	850	2	NR	980	0	NR
465	246	NR	595	997	NR	725	58	NR	855	1	NR	985	0	NR
470	182	NR	600	991	NR	730	49	NR	860	1	NR	990	0	NR
475	115	NR	605	968	NR	735	42	NR	865	1	NR	995	0	NR
480	97	NR	610	939	NR	740	37	NR	870	1	NR	1000	0	NR
485	103	NR	615	896	NR	745	32	NR	875	1	NR			

REPORT NUMBER: SP1-2411-284-1

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 2.47


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	846	NR	750	28	NR	880	1	NR
365	0	NR	495	160	NR	625	793	NR	755	25	NR	885	0	NR
370	0	NR	500	225	NR	630	739	NR	760	22	NR	890	0	NR
375	0	NR	505	308	NR	635	681	NR	765	19	NR	895	0	NR
380	0	NR	510	392	NR	640	623	NR	770	16	NR	900	0	NR
385	0	NR	515	474	NR	645	563	NR	775	14	NR	905	0	NR
390	0	NR	520	545	NR	650	506	NR	780	12	NR	910	0	NR
395	1	NR	525	603	NR	655	451	NR	785	10	NR	915	0	NR
400	3	NR	530	649	NR	660	399	NR	790	9	NR	920	0	NR
405	5	NR	535	687	NR	665	352	NR	795	8	NR	925	0	NR
410	11	NR	540	721	NR	670	307	NR	800	6	NR	930	0	NR
415	21	NR	545	751	NR	675	268	NR	805	6	NR	935	0	NR
420	43	NR	550	779	NR	680	234	NR	810	5	NR	940	0	NR
425	88	NR	555	811	NR	685	203	NR	815	4	NR	945	0	NR
430	163	NR	560	843	NR	690	176	NR	820	4	NR	950	0	NR
435	288	NR	565	873	NR	695	152	NR	825	3	NR	955	0	NR
440	416	NR	570	907	NR	700	131	NR	830	3	NR	960	0	NR
445	566	NR	575	938	NR	705	112	NR	835	3	NR	965	0	NR
450	810	NR	580	965	NR	710	96	NR	840	2	NR	970	0	NR
455	669	NR	585	986	NR	715	81	NR	845	2	NR	975	0	NR
460	338	NR	590	997	NR	720	69	NR	850	2	NR	980	0	NR
465	246	NR	595	997	NR	725	58	NR	855	1	NR	985	0	NR
470	182	NR	600	991	NR	730	49	NR	860	1	NR	990	0	NR
475	115	NR	605	968	NR	735	42	NR	865	1	NR	995	0	NR
480	97	NR	610	939	NR	740	37	NR	870	1	NR	1000	0	NR
485	103	NR	615	896	NR	745	32	NR	875	1	NR			

REPORT NUMBER: SP1-2411-284-1





TM-30-18

Summary

$R_f = 76.6$
 $R_g = 95.4$
 $CIE R_a = 73.9$
 $R_g = -18.0$







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 67	CES51 = 88	CES76 = 56
CES02 = 62	CES27 = 89	CES52 = 88	CES77 = 75
CES03 = 31	CES28 = 83	CES53 = 78	CES78 = 60
CES04 = 70	CES29 = 69	CES54 = 86	CES79 = 85
CES05 = 48	CES30 = 83	CES55 = 85	CES80 = 82
CES06 = 51	CES31 = 72	CES56 = 75	CES81 = 78
CES07 = 41	CES32 = 65	CES57 = 75	CES82 = 92
CES08 = 40	CES33 = 78	CES58 = 76	CES83 = 90
CES09 = 29	CES34 = 74	CES59 = 87	CES84 = 88
CES10 = 75	CES35 = 86	CES60 = 91	CES85 = 79
CES11 = 58	CES36 = 93	CES61 = 84	CES86 = 72
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 79
CES13 = 43	CES38 = 92	CES63 = 74	CES88 = 82
CES14 = 74	CES39 = 96	CES64 = 69	CES89 = 72
CES15 = 71	CES40 = 92	CES65 = 66	CES90 = 82
CES16 = 47	CES41 = 93	CES66 = 62	CES91 = 79
CES17 = 50	CES42 = 83	CES67 = 60	CES92 = 63
CES18 = 56	CES43 = 79	CES68 = 68	CES93 = 77
CES19 = 72	CES44 = 99	CES69 = 76	CES94 = 56
CES20 = 65	CES45 = 86	CES70 = 61	CES95 = 70
CES21 = 86	CES46 = 83	CES71 = 55	CES96 = 79
CES22 = 79	CES47 = 85	CES72 = 85	CES97 = 85
CES23 = 92	CES48 = 78	CES73 = 53	CES98 = 78
CES24 = 91	CES49 = 81	CES74 = 95	CES99 = 68
CES25 = 72	CES50 = 88	CES75 = 57	



Color Rendition by Hue-Angle Bin


Measure Comparisons


(END OF REPORT)