

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P543202

Luminaire Tested: **TT-D9-735-U-5WQ-PM**

Issue Date: 6/22/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P543202  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2012-100-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/22/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D9-735-U-5WQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
3500K, 70 CRI LEDS AND WIDE DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20022 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G3


Input Watts (W): 173.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P543202  
 CATALOG NUMBER: TT-D9-735-U-5WQ-PM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.8 fc  
 Type V - Short - N/A

REPORT NUMBER: P543202  
CATALOG NUMBER: TT-D9-735-U-5WQ-PM

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 59-Deg Vertical

REPORT NUMBER: P543202

CATALOG NUMBER: TT-D9-735-U-5WQ-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	10011.0	0.0	10011.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	10011.0	0.0	10011.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	20022.0	0.0	20022.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.3	0.8
10°-20°	497.1	2.5
20°-30°	1038.9	5.2
30°-40°	1911.1	9.5
40°-50°	3144.8	15.7
50°-60°	4387.1	21.9
60°-70°	4569.0	22.8
70°-80°	3329.6	16.6
80°-90°	987.1	4.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20022.0	100.0
0°-180°	20022.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P543202


CATALOG NUMBER: TT-D9-735-U-5WQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	846.7	4.2			
FM (30°-60°)	4721.5	23.6			
FH (60°-80°)	3949.3	19.7			G2/5000
FVH (80°-90°)	493.5	2.5			G3/500
BL (0°-30°)	846.7	4.2	B2/1000		
BM (30°-60°)	4721.5	23.6	B3/5000		
BH (60°-80°)	3949.3	19.7	B4/5000		G2/5000
BVH (80°-90°)	493.5	2.5			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G3**

Type V Short





REPORT NUMBER: P543202

CATALOG NUMBER: TT-D9-735-U-5WQ-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6	1699.6
2.5°	1690.4	1691.4	1691.4	1692.3	1691.4	1692.3	1690.4	1689.5	1688.6	1689.5	1688.6
5°	1651.2	1653.9	1653.9	1656.7	1657.6	1660.3	1658.5	1657.6	1654.8	1653.9	1653.0
7.5°	1623.8	1624.7	1627.5	1632.9	1637.5	1641.2	1640.2	1636.6	1632.0	1628.4	1627.5
10°	1622.9	1622.0	1624.7	1629.3	1638.4	1641.2	1640.2	1633.8	1630.2	1627.5	1627.5
12.5°	1652.1	1651.2	1654.8	1661.2	1673.1	1673.1	1674.9	1664.9	1657.6	1655.8	1655.8
15°	1709.6	1706.9	1716.0	1721.5	1735.2	1735.2	1736.1	1724.2	1716.0	1713.3	1713.3
17.5°	1787.2	1784.5	1794.5	1803.6	1817.3	1818.2	1819.1	1806.4	1795.4	1790.8	1792.7
20°	1887.6	1883.9	1893.1	1905.9	1925.0	1924.1	1923.2	1910.4	1896.7	1891.2	1893.1
22.5°	2011.7	2016.3	2030.0	2047.3	2071.1	2074.7	2069.2	2051.9	2031.8	2023.6	2024.5
25°	2162.3	2166.9	2183.3	2210.7	2242.7	2241.8	2238.1	2212.5	2183.3	2171.5	2174.2
27.5°	2345.8	2348.5	2373.2	2401.5	2445.3	2449.9	2441.6	2401.5	2371.4	2347.6	2344.9
30°	2529.3	2532.9	2556.7	2597.7	2645.2	2657.1	2634.2	2595.9	2556.7	2531.1	2526.5
32.5°	2729.2	2737.4	2759.3	2799.4	2862.4	2868.8	2855.1	2800.4	2755.6	2732.8	2731.9
35°	2926.3	2938.2	2969.2	3024.9	3089.7	3112.5	3081.5	3024.9	2972.0	2929.1	2924.5
37.5°	3144.5	3160.0	3192.9	3265.0	3329.8	3351.7	3323.4	3260.4	3186.5	3149.0	3145.4
40°	3354.4	3379.1	3440.2	3516.0	3592.6	3611.8	3591.7	3507.8	3429.3	3378.1	3345.3
42.5°	3583.5	3599.0	3670.2	3786.1	3862.8	3905.7	3858.3	3780.7	3668.4	3595.4	3588.1
45°	3843.7	3892.0	3952.3	4091.0	4217.9	4265.3	4215.1	4082.8	3941.3	3882.9	3849.1
47.5°	4086.4	4123.0	4226.1	4384.0	4536.4	4581.2	4531.9	4379.4	4210.6	4112.9	4080.1
50°	4287.3	4338.4	4443.3	4650.5	4783.8	4841.3	4774.7	4639.6	4433.3	4326.5	4287.3
52.5°	4478.9	4536.4	4667.0	4872.3	5087.8	5166.2	5083.2	4856.8	4654.2	4519.1	4464.3
55°	4582.1	4635.0	4776.5	5046.7	5268.5	5320.5	5261.2	5032.1	4763.7	4617.7	4566.6
57.5°	4598.5	4642.3	4817.6	5103.3	5270.3	5321.4	5266.7	5090.5	4802.1	4626.8	4583.9
59°	4563.8	4605.8	4793.8	5078.6	5245.7	5356.1	5242.0	5067.7	4777.4	4592.1	4547.4
60°	4542.8	4583.0	4759.2	5043.0	5221.9	5336.0	5218.3	5033.9	4740.0	4571.1	4525.5
62.5°	4437.9	4475.3	4705.3	4955.4	5152.6	5242.0	5147.1	4946.3	4690.7	4463.4	4413.2
65°	4235.2	4253.5	4473.5	4720.8	4980.0	5033.9	4971.8	4718.1	4455.2	4240.7	4214.2
67.5°	4011.6	4035.3	4224.3	4496.3	4741.8	4813.9	4729.0	4495.4	4210.6	4018.0	3987.9
70°	3649.2	3673.9	3926.7	4159.5	4358.5	4469.8	4337.5	4152.2	3912.1	3666.6	3623.7
72.5°	3298.7	3310.6	3490.4	3764.2	4004.3	3982.4	3979.7	3760.6	3476.7	3315.2	3296.0
75°	2841.4	2847.8	3057.8	3285.0	3505.0	3528.7	3471.2	3280.5	3042.2	2845.1	2842.3
77.5°	2348.5	2367.7	2511.0	2722.8	2890.7	2971.0	2872.5	2733.7	2496.4	2369.5	2353.1
80°	1807.3	1831.0	1977.0	2145.9	2291.0	2297.4	2277.3	2160.5	1964.3	1833.7	1814.6
82.5°	1248.7	1273.3	1402.0	1528.0	1668.5	1675.8	1653.0	1541.7	1390.1	1277.9	1259.6
85°	690.1	712.0	799.6	896.3	1010.4	1010.4	978.5	913.7	790.5	719.3	701.9
87.5°	116.8	118.7	172.5	226.4	328.6	339.5	309.4	247.4	181.6	142.4	130.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)