

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436737

Luminaire Tested: **TT-D1-740-U-5WQ-PM-HSS**

Issue Date: 12/2/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P436737  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-017-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D1-740-U-5WQ-PM-HSS  
Description: TOPTIER LED SITE LUMINAIRE  
4000K, 70 CRI LEDS AND WIDE DISTRIBUTION WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3120 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U1 - G2


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P436737  
 CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P436737  
CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436737  
 CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1098.9	0.7	1099.6
	% Fixture	35.2	0.0	35.2
<b>Street Side</b>	Lumens	2007.7	12.6	2020.3
	% Fixture	64.4	0.4	64.8
<b>Total</b>	Lumens	3106.6	13.3	3120.0
	% Fixture	99.6	0.4	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.9	0.7
10°-20°	74.1	2.4
20°-30°	158.8	5.1
30°-40°	287.6	9.2
40°-50°	479.9	15.4
50°-60°	664.7	21.3
60°-70°	688.9	22.1
70°-80°	554.4	17.8
80°-90°	177.3	5.7
90°-100°	9.0	0.3
100°-110°	2.9	0.1
110°-120°	0.6	0.0
120°-130°	0.3	0.0
130°-140°	0.2	0.0
140°-150°	0.2	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	3106.6	99.6
0°-180°	3120.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P436737  
 CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	129.7	4.2			
FM (30°-60°)	829.5	26.6			
FH (60°-80°)	913.6	29.3			G1/1800
FVH (80°-90°)	134.9	4.3			G2/225
BL (0°-30°)	124.1	4.0	B1/500		
BM (30°-60°)	602.8	19.3	B1/1000		
BH (60°-80°)	329.7	10.6	B1/500		G1/500
BVH (80°-90°)	42.4	1.4			G1/100
UL (90°-100°)	9.0	0.3		U1/10	
UH (100°-180°)	4.4	0.1		U1/10	

**BUG Rating: B1-U1-G2**

Type IV Short





REPORT NUMBER: P436737

CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9
2.5°	212.0	211.4	211.4	210.8	210.8	210.8	210.8	210.8	210.1	209.5	208.9
5°	217.5	217.5	216.8	216.8	216.2	215.6	216.2	215.6	215.0	214.4	213.8
7.5°	224.8	224.2	224.2	222.9	222.9	222.3	222.3	222.3	221.7	220.5	219.9
10°	235.1	233.9	233.9	232.7	232.1	231.5	231.5	230.2	230.2	229.6	229.0
12.5°	246.7	245.5	246.7	246.1	244.9	243.6	243.6	242.4	241.8	241.2	238.8
15°	261.9	260.1	261.3	261.3	260.7	260.1	260.1	257.7	256.4	255.2	252.8
17.5°	280.2	279.0	279.6	280.2	282.0	282.0	282.6	279.6	277.1	272.9	271.1
20°	303.3	302.7	304.6	304.6	306.4	306.4	307.0	303.9	299.7	296.6	293.0
22.5°	325.9	325.9	328.3	328.3	330.1	328.9	328.9	327.7	322.8	319.2	315.5
25°	349.0	348.4	350.8	352.7	355.1	352.1	353.3	351.5	346.6	341.7	336.8
27.5°	374.6	373.4	374.6	377.0	381.3	378.9	380.1	377.0	372.2	365.5	361.2
30°	402.6	400.8	402.6	406.3	409.3	410.5	409.9	405.7	401.4	391.7	388.6
32.5°	430.0	430.0	434.3	441.0	444.6	444.0	444.6	441.0	434.9	422.7	415.4
35°	463.5	466.0	471.4	481.2	489.1	486.1	486.1	484.8	474.5	459.9	450.1
37.5°	508.0	510.4	521.4	533.0	547.6	546.4	547.0	543.3	523.2	508.0	494.0
40°	559.8	562.2	578.7	595.1	609.1	613.4	614.0	606.1	584.1	562.2	540.3
42.5°	607.3	610.3	627.4	650.5	665.8	672.5	673.7	660.9	637.7	612.8	585.4
45°	654.8	658.4	677.9	702.3	724.2	727.3	727.9	716.9	691.3	662.7	627.4
47.5°	703.5	706.6	726.7	755.9	779.7	785.7	786.4	776.0	744.9	710.2	668.8
50°	748.0	754.1	781.5	812.5	844.2	849.1	849.7	838.1	801.6	762.6	707.8
52.5°	800.4	803.4	832.6	884.4	911.2	930.1	930.7	908.2	869.2	816.8	746.2
55°	861.3	866.8	896.6	948.4	996.5	1009.3	1012.9	986.1	934.4	877.7	794.9
57.5°	896.6	907.0	950.8	1000.2	1060.5	1069.0	1070.8	1042.8	985.5	923.4	831.4
60°	915.5	921.6	967.9	1044.6	1091.5	1099.4	1098.8	1077.5	1020.3	944.7	848.5
62.5°	936.8	947.2	986.1	1064.1	1104.9	1124.4	1121.4	1099.4	1041.0	958.1	864.9
65°	930.7	939.2	996.5	1059.8	1127.5	1148.8	1144.5	1115.3	1044.0	960.6	860.7
67.5°	906.3	913.0	969.7	1048.3	1112.8	1128.1	1135.4	1106.7	1027.0	934.4	833.9
70°	856.4	866.8	921.6	1002.0	1061.1	1072.0	1073.2	1055.6	983.7	886.2	789.4
72.5°	787.6	796.1	855.8	937.4	988.6	1001.4	1002.6	975.8	921.6	820.5	725.4
75°	705.3	713.3	759.6	844.8	895.4	908.2	907.0	882.0	824.7	729.1	640.8
77.5°	603.6	618.2	659.1	729.1	778.4	785.1	786.4	758.9	712.7	629.8	543.9
80°	476.3	490.3	536.6	589.0	630.4	635.9	637.7	614.6	572.6	499.5	426.4
82.5°	338.7	350.8	387.4	430.0	464.7	464.7	466.0	447.1	414.8	352.1	294.8
85°	193.1	202.2	226.6	257.0	282.0	279.0	279.6	262.5	241.2	192.5	155.9
87.5°	63.3	67.6	73.1	84.7	96.2	88.9	92.6	76.7	69.4	51.8	40.2
90°	33.5	33.5	32.3	31.1	28.6	25.0	25.0	20.1	15.2	9.7	3.7
92.5°	30.5	30.5	29.2	28.0	25.6	22.5	22.5	18.3	13.4	8.5	3.0
95°	25.0	25.0	24.4	23.1	21.3	18.9	18.3	15.2	11.6	6.7	2.4
97.5°	19.5	19.5	18.9	18.3	16.4	14.6	14.6	11.6	8.5	5.5	1.8
100°	14.6	14.6	14.6	13.4	12.8	11.0	11.0	9.1	6.7	4.3	1.2
102.5°	10.4	11.0	10.4	9.7	9.1	7.9	7.9	6.7	4.9	3.0	1.2
105°	7.3	7.3	6.7	6.7	6.1	5.5	5.5	4.3	3.0	1.8	0.6
107.5°	4.3	4.3	4.3	4.3	3.7	3.7	3.7	3.0	1.8	1.2	0.6
110°	2.4	2.4	2.4	2.4	1.8	1.8	1.8	1.2	1.2	0.6	0.6



REPORT NUMBER: P436737  
 CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
112.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	0.6	0.6	0.6	0.6
115°	0.6	0.6	0.6	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6
117.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
120°	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
122.5°	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
125°	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
127.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
130°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
132.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
135°	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
140°	0.6	0.6	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
142.5°	0.6	0.6	0.6	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6
145°	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
147.5°	0.6	0.6	0.6	0.0	0.0	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.6	0.6	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
160°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
162.5°	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
165°	0.6	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
167.5°	0.6	0.6	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
170°	0.6	0.0	0.0	0.0	0.0	0.6	0.0	0.6	0.6	0.6	0.6
172.5°	0.6	0.6	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
175°	0.6	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6
177.5°	0.0	0.6	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P436737

CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9
2.5°	208.9	208.9	208.3	207.7	207.7	207.7	207.1	207.1	207.1	206.5	206.5
5°	213.8	213.2	213.2	212.6	212.6	212.0	212.0	211.4	210.8	210.8	210.1
7.5°	220.5	219.9	218.7	219.3	218.1	217.5	216.8	216.8	216.8	216.2	216.2
10°	228.4	228.4	227.2	227.2	226.0	225.4	224.8	224.8	225.4	225.4	224.8
12.5°	238.8	238.2	238.2	237.6	236.9	236.3	236.9	236.9	236.3	235.7	235.1
15°	251.6	251.6	251.6	252.2	251.6	251.6	251.6	251.0	249.7	248.5	248.5
17.5°	271.1	270.4	269.2	269.8	271.1	272.9	271.1	269.2	267.4	267.4	266.8
20°	291.2	291.8	291.8	292.4	294.2	296.0	293.6	292.4	291.2	289.9	288.7
22.5°	313.1	313.7	313.7	313.1	314.3	313.7	312.5	311.3	310.0	308.2	307.0
25°	334.4	335.0	334.4	333.8	334.4	332.6	330.7	328.9	325.9	322.8	322.8
27.5°	358.2	357.5	355.1	355.7	354.5	353.3	349.6	345.4	341.1	338.1	338.1
30°	383.1	383.1	378.3	380.7	378.3	377.6	369.7	364.2	358.2	353.9	353.3
32.5°	410.5	409.3	405.7	408.1	405.7	403.2	393.5	386.2	375.8	369.7	369.1
35°	443.4	440.4	437.3	439.8	439.8	433.1	423.3	409.9	395.3	388.0	387.4
37.5°	483.6	481.8	478.1	481.2	483.6	476.9	462.3	442.8	422.1	411.1	410.5
40°	528.1	525.7	523.8	528.1	529.9	523.2	503.7	476.3	448.3	432.5	430.0
42.5°	570.1	564.6	561.6	567.7	565.9	558.6	531.7	500.1	461.7	443.4	440.4
45°	607.9	601.8	597.5	603.0	600.6	586.0	556.1	513.5	467.2	444.6	441.0
47.5°	645.0	635.9	629.2	636.5	631.6	609.1	572.6	520.2	461.1	434.3	428.2
50°	676.7	665.8	661.5	670.0	662.7	631.0	584.1	517.1	445.9	406.9	397.1
52.5°	714.5	698.0	693.8	710.2	693.8	651.7	586.6	509.8	411.1	364.2	355.1
55°	752.9	734.6	727.9	743.1	718.1	656.0	574.4	467.8	358.8	308.8	295.4
57.5°	773.0	755.9	749.8	760.8	714.5	614.6	520.2	389.8	280.2	224.2	209.5
60°	791.2	761.4	753.5	768.1	676.7	518.3	402.6	279.6	169.3	127.3	116.3
62.5°	804.0	775.4	758.9	765.6	607.3	377.0	231.5	134.6	64.0	44.5	43.9
65°	797.3	773.0	762.0	757.1	527.5	216.8	85.3	34.1	1.8	1.8	1.2
67.5°	776.6	749.8	746.8	751.0	522.0	208.3	79.2	31.1	0.0	0.0	0.0
70°	730.9	712.0	712.0	726.7	498.2	197.4	73.7	28.6	0.0	0.0	0.0
72.5°	669.4	654.8	663.3	685.2	462.9	182.1	66.4	25.6	0.0	0.0	0.0
75°	595.7	580.5	591.4	615.8	419.1	162.6	57.9	21.9	0.0	0.0	0.0
77.5°	501.9	491.5	508.6	531.1	360.6	137.0	47.5	17.7	0.0	0.0	0.0
80°	391.0	385.6	408.1	428.2	291.2	107.8	35.9	12.8	0.0	0.0	0.0
82.5°	269.8	267.4	289.3	310.0	208.3	75.5	24.4	8.5	0.0	0.0	0.0
85°	141.3	141.3	158.4	177.2	116.3	40.8	12.2	3.7	0.0	0.0	0.0
87.5°	31.1	29.8	32.3	41.4	23.1	7.9	1.8	0.6	0.0	0.0	0.0
90°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
105°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P436737  
 CATALOG NUMBER: TT-D1-740-U-5WQ-PM-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.6	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
117.5°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.6	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
122.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
125°	0.6	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.6	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)