

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P413323

Luminaire Tested: **TT-D4-740-U-RW-PM**

Issue Date: 10/15/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P413323  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-981-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/15/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D4-740-U-RW-PM  
Description: TOPTIER LED SITE LUMINAIRE  
4000K, 70 CRI LEDS AND RECTANGULAR DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6050 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G3  
  
Input Watts (W): 57.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P413323  
 CATALOG NUMBER: TT-D4-740-U-RW-PM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P413323  
CATALOG NUMBER: TT-D4-740-U-RW-PM

### Luminous Intensity Polar Plot



REPORT NUMBER: P413323  
 CATALOG NUMBER: TT-D4-740-U-RW-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3025.0	0.0	3025.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	3025.0	0.0	3025.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	6050.0	0.0	6050.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	11.5	0.2
10°-20°	43.1	0.7
20°-30°	99.7	1.6
30°-40°	225.4	3.7
40°-50°	549.1	9.1
50°-60°	1234.8	20.4
60°-70°	1804.6	29.8
70°-80°	1572.4	26.0
80°-90°	509.3	8.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6050.0	100.0
0°-180°	6050.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P413323  
 CATALOG NUMBER: TT-D4-740-U-RW-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	77.2	1.3			
FM (30°-60°)	1004.6	16.6			
FH (60°-80°)	1688.5	27.9			G1/1800
FVH (80°-90°)	254.7	4.2			G3/500
BL (0°-30°)	77.2	1.3	B0/110		
BM (30°-60°)	1004.6	16.6	B2/2500		
BH (60°-80°)	1688.5	27.9	B3/2500		G3/2500
BVH (80°-90°)	254.7	4.2			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G3**

Type IV Short





REPORT NUMBER: P413323  
 CATALOG NUMBER: TT-D4-740-U-RW-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5	110.5
2.5°	112.0	112.0	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4
5°	116.3	116.3	116.3	116.3	117.7	117.7	116.3	116.3	116.3	116.3	116.3
7.5°	123.5	122.0	123.5	123.5	123.5	122.0	122.0	122.0	120.6	120.6	120.6
10°	130.6	130.6	132.1	130.6	130.6	129.2	129.2	129.2	127.8	127.8	127.8
12.5°	140.7	140.7	140.7	140.7	139.2	139.2	137.8	136.4	134.9	134.9	134.9
15°	153.6	152.2	152.2	150.7	149.3	147.9	146.4	146.4	145.0	145.0	145.0
17.5°	166.5	166.5	165.1	163.6	160.8	159.3	159.3	157.9	156.5	156.5	156.5
20°	182.3	182.3	180.9	178.0	175.1	173.7	172.3	172.3	170.8	170.8	170.8
22.5°	201.0	199.5	196.7	193.8	190.9	189.5	188.1	186.6	186.6	186.6	186.6
25°	221.1	219.6	218.2	213.9	209.6	208.1	205.3	205.3	203.8	205.3	205.3
27.5°	245.5	244.0	241.2	236.9	231.1	228.2	226.8	226.8	228.2	228.2	229.7
30°	275.6	272.7	269.9	264.1	258.4	254.1	254.1	255.5	259.8	262.7	262.7
32.5°	311.5	310.1	305.8	300.0	290.0	287.1	290.0	298.6	304.3	308.6	311.5
35°	353.1	351.7	346.0	335.9	328.7	327.3	335.9	350.3	368.9	374.7	377.5
37.5°	399.1	400.5	393.3	381.8	374.7	377.5	394.8	422.0	440.7	453.6	456.5
40°	456.5	459.4	450.8	437.8	430.7	442.1	469.4	501.0	534.0	549.8	554.1
42.5°	524.0	528.3	516.8	503.9	499.6	518.2	557.0	608.7	667.5	686.2	693.4
45°	607.2	610.1	595.7	584.3	581.4	614.4	680.4	766.6	859.9	902.9	910.1
47.5°	706.3	704.8	691.9	677.6	680.4	727.8	826.9	943.1	1042.2	1108.2	1122.6
50°	819.7	812.5	802.5	785.2	803.9	872.8	997.7	1138.4	1304.9	1363.7	1389.6
52.5°	933.1	920.2	911.5	900.1	933.1	1022.1	1197.2	1442.7	1693.9	1828.8	1856.1
55°	1035.0	1025.0	1020.6	1022.1	1073.8	1201.5	1431.2	1745.6	1988.2	2100.2	2120.3
57.5°	1135.5	1129.7	1125.4	1134.1	1215.9	1382.4	1640.8	1935.1	2134.6	2217.9	2232.2
60°	1230.2	1236.0	1233.1	1258.9	1358.0	1525.9	1749.9	2039.9	2232.2	2308.3	2324.1
62.5°	1335.0	1339.3	1339.3	1368.0	1448.4	1596.3	1824.5	2163.3	2407.4	2519.3	2536.5
65°	1425.5	1428.3	1434.1	1435.5	1510.2	1658.0	1956.6	2276.7	2494.9	2624.1	2635.6
67.5°	1492.9	1495.8	1488.6	1481.4	1538.9	1672.4	1946.6	2262.4	2456.2	2553.8	2562.4
70°	1547.5	1534.6	1514.5	1478.6	1497.2	1597.7	1863.3	2147.5	2342.8	2430.3	2443.2
72.5°	1554.7	1543.2	1480.0	1399.6	1376.7	1464.2	1716.9	1972.4	2140.3	2223.6	2225.0
75°	1511.6	1481.4	1376.7	1256.1	1213.0	1296.3	1513.0	1745.6	1880.5	1950.9	1958.0
77.5°	1366.6	1337.9	1205.8	1068.0	1019.2	1091.0	1274.7	1462.8	1592.0	1660.9	1665.2
80°	1109.7	1099.6	979.0	852.7	793.8	835.5	996.2	1144.1	1248.9	1330.7	1337.9
82.5°	818.2	809.6	717.8	607.2	559.8	594.3	709.1	818.2	915.9	981.9	986.2
85°	511.0	493.8	436.4	358.9	327.3	350.3	426.3	499.6	587.1	638.8	641.7
87.5°	170.8	163.6	140.7	116.3	97.6	101.9	124.9	152.2	222.5	245.5	259.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)